

SSW900 - SOFT STARTER

PRICE LIST



Protected Chassis Enclosure

Motor Voltage	Motor HP ¹	Starter Amps ²	Catalog Number	Frame Size ³	Dimensions (in.) HxWxD	Approx. Weight (lbs.)	List Price	Multiplier New (Old)
230 Vac	Input Power Supply: Three-Phase 230 Vac							
	3	10	SSW900A0010T5E2B	A	7.9" x 5.0" x 8.0"	4.3	\$1,386	E19 (E1)
	5	17	SSW900A0017T5E2B	A	7.9" x 5.0" x 8.0"	4.3	\$1,429	E19 (E1)
	7.5	24	SSW900A0024T5E2B	A	7.9" x 5.0" x 8.0"	4.3	\$1,572	E19 (E1)
	10	30	SSW900A0030T5E2B	A	7.9" x 5.0" x 8.0"	4.3	\$1,703	E19 (E1)
	15	45	SSW900B0045T5E2B	B	8.2" x 5.7" x 10.2"	8.9	\$1,976	E19 (E1)
	20	61	SSW900B0061T5E2B	B	8.2" x 5.7" x 10.2"	8.9	\$2,181	E19 (E1)
	25 / 30	85	SSW900B0085T5E2B	B	8.2" x 5.7" x 10.2"	8.9	\$2,771	E19 (E1)
	40	105	SSW900B0105T5E2B	B	8.2" x 5.7" x 10.2"	8.9	\$3,160	E19 (E1)
	50	130	SSW900C0130T5E2B	C	10.9" x 8.8" x 10.3"	14.4	\$3,547	E19 (E1)
	60	171	SSW900C0171T5E2B	C	10.9" x 8.8" x 10.3"	14.4	\$4,270	E19 (E1)
	75	200	SSW900C0200T5E2B	C	10.9" x 8.8" x 10.3"	14.4	\$5,354	E19 (E1)
	100	255	SSW900D0255T5E3B	D	13.0" x 8.9" x 11.1"	28.3	\$7,188	E19 (E1)
	125	312	SSW900D0312T5E3B	D	13.0" x 8.9" x 11.1"	28.3	\$7,896	E19 (E1)
	150	365	SSW900D0365T5E3B	D	13.0" x 8.9" x 11.1"	28.3	\$8,721	E19 (E1)
	150	412	SSW900D0412T5E3B	D	13.0" x 8.9" x 11.1"	28.3	\$9,465	E19 (E1)
	200	480	SSW900E0480T5E3B	E	22.6" x 15.4" x 10.2"	83.7	\$11,730	E19 (E1)
	250	604	SSW900E0604T5E3B	E	22.6" x 15.4" x 10.2"	83.7	\$13,082	E19 (E1)
	250	670	SSW900E0670T5E3B	E	22.6" x 15.4" x 10.2"	83.7	\$14,878	E19 (E1)
	350	820	SSW900F0820T5E3B	F	29.9" x 29.9" x 12.4"	166.2	Available in November 2021.	
400	950	SSW900F0950T5E3B	F	29.9" x 29.9" x 12.4"	166.2			
450	1100	SSW900G1100T5E3B	G	36.0" x 36.0" x 12.4"	236.3			
550	1400	SSW900G1400T5E3B	G	36.0" x 36.0" x 12.4"	236.3			
Input Power Supply: Three-Phase 460 Vac								
460 Vac	5	10	SSW900A0010T5E2B	A	7.9" x 5.0" x 8.0"	4.3	\$1,386	E19 (E1)
	10	17	SSW900A0017T5E2B	A	7.9" x 5.0" x 8.0"	4.3	\$1,429	E19 (E1)
	15	24	SSW900A0024T5E2B	A	7.9" x 5.0" x 8.0"	4.3	\$1,572	E19 (E1)
	20	30	SSW900A0030T5E2B	A	7.9" x 5.0" x 8.0"	4.3	\$1,703	E19 (E1)
	30	45	SSW900B0045T5E2B	B	8.2" x 5.7" x 10.2"	8.9	\$1,976	E19 (E1)
	40	61	SSW900B0061T5E2B	B	8.2" x 5.7" x 10.2"	8.9	\$2,181	E19 (E1)
	50 / 60 / 75	85	SSW900B0085T5E2B	B	8.2" x 5.7" x 10.2"	8.9	\$2,771	E19 (E1)
	75	105	SSW900B0105T5E2B	B	8.2" x 5.7" x 10.2"	8.9	\$3,160	E19 (E1)
	100	130	SSW900C0130T5E2B	C	10.9" x 8.8" x 10.3"	14.4	\$3,547	E19 (E1)
	125	171	SSW900C0171T5E2B	C	10.9" x 8.8" x 10.3"	14.4	\$4,270	E19 (E1)
	150	200	SSW900C0200T5E2B	C	10.9" x 8.8" x 10.3"	14.4	\$5,354	E19 (E1)
	200	255	SSW900D0255T5E3B	D	13.0" x 8.9" x 11.1"	28.3	\$7,188	E19 (E1)
	250	312	SSW900D0312T5E3B	D	13.0" x 8.9" x 11.1"	28.3	\$7,896	E19 (E1)
	300	365	SSW900D0365T5E3B	D	13.0" x 8.9" x 11.1"	28.3	\$8,721	E19 (E1)
	350	412	SSW900D0412T5E3B	D	13.0" x 8.9" x 11.1"	28.3	\$9,465	E19 (E1)
	400	480	SSW900E0480T5E3B	E	22.6" x 15.4" x 10.2"	83.7	\$11,730	E19 (E1)
	500	604	SSW900E0604T5E3B	E	22.6" x 15.4" x 10.2"	83.7	\$13,082	E19 (E1)
	600	670	SSW900E0670T5E3B	E	22.6" x 15.4" x 10.2"	83.7	\$14,878	E19 (E1)
	700	820	SSW900F0820T5E3B	F	29.9" x 29.9" x 12.4"	166.2	Available in November 2021.	
	800	950	SSW900F0950T5E3B	F	29.9" x 29.9" x 12.4"	166.2		
900	1100	SSW900G1100T5E3B	G	36.0" x 36.0" x 12.4"	236.3			
1200	1400	SSW900G1400T5E3B	G	36.0" x 36.0" x 12.4"	236.3			

Notes:

- "HP" rating based on FLA values from WEG W22, 2 and 4 pole, NEMA Premium motors.
- Motor FLA may vary with speed and manufacturer. ALWAYS compare motor FLA to Nominal AMPS of the starter.
- Frame-A & D are rated for 55°C as a standard and duty cycle will be 3 x In for 30s, 10 Starts/hr.
Frame- B & C are rated for 55°C as a standard and duty cycle will be 3 x In for 30s, 10 Starts/hr with ventilation kit (3 x In for 30s, 3 starts/hr w/o ventilation kit).
Frame- E, F & G are rated for 40°C as a standard and duty cycle will be 3 x In for 30s, 5 starts/hr.

Protected Chassis Enclosure

Motor Voltage	Motor HP ¹	Starter Amps ²	Catalog Number	Frame Size ³	Dimensions (in.) HxWxD	Approx. Weight (lbs.)	List Price	Multiplier New (Old)
575 Vac	Input Power Supply: Three-Phase 575 Vac							
	7.5	10	SSW900A0010T5E2B	A	7.9" x 5.0" x 8.0"	4.3	\$1,386	E19 (E1)
	15	17	SSW900A0017T5E2B	A	7.9" x 5.0" x 8.0"	4.3	\$1,429	E19 (E1)
	20	24	SSW900A0024T5E2B	A	7.9" x 5.0" x 8.0"	4.3	\$1,572	E19 (E1)
	30	30	SSW900A0030T5E2B	A	7.9" x 5.0" x 8.0"	4.3	\$1,703	E19 (E1)
	40	45	SSW900B0045T5E2B	B	8.2" x 5.7" x 10.2"	8.9	\$1,976	E19 (E1)
	60	61	SSW900B0061T5E2B	B	8.2" x 5.7" x 10.2"	8.9	\$2,181	E19 (E1)
	75	85	SSW900B0085T5E2B	B	8.2" x 5.7" x 10.2"	8.9	\$2,771	E19 (E1)
	100	105	SSW900B0105T5E2B	B	8.2" x 5.7" x 10.2"	8.9	\$3,160	E19 (E1)
	125	130	SSW900C0130T5E2B	C	10.9" x 8.8" x 10.3"	14.4	\$3,547	E19 (E1)
	150	171	SSW900C0171T5E2B	C	10.9" x 8.8" x 10.3"	14.4	\$4,270	E19 (E1)
	200	200	SSW900C0200T5E2B	C	10.9" x 8.8" x 10.3"	14.4	\$5,354	E19 (E1)
	250	255	SSW900D0255T5E3B	D	13.0" x 8.9" x 11.1"	28.3	\$7,188	E19 (E1)
	300	312	SSW900D0312T5E3B	D	13.0" x 8.9" x 11.1"	28.3	\$7,896	E19 (E1)
	350	365	SSW900D0365T5E3B	D	13.0" x 8.9" x 11.1"	28.3	\$8,721	E19 (E1)
	450	412	SSW900D0412T5E3B	D	13.0" x 8.9" x 11.1"	28.3	\$9,465	E19 (E1)
	500	480	SSW900E0480T5E3B	E	22.6" x 15.4" x 10.2"	83.7	\$11,730	E19 (E1)
	650	604	SSW900E0604T5E3B	E	22.6" x 15.4" x 10.2"	83.7	\$13,082	E19 (E1)
	750	670	SSW900E0670T5E3B	E	22.6" x 15.4" x 10.2"	83.7	\$14,878	E19 (E1)
	850	820	SSW900F0820T5E3B	F	29.9" x 29.9" x 12.4"	166.2	Available in November 2021.	
1050	950	SSW900F0950T5E3B	F	29.9" x 29.9" x 12.4"	166.2			
1200	1100	SSW900G1100T5E3B	G	36.0" x 36.0" x 12.4"	236.3			
1500	1400	SSW900G1400T5E3B	G	36.0" x 36.0" x 12.4"	236.3			
690 Vac 4	Input Power Supply: Three-Phase 690 Vac							
	150	130	SSW900C0130T6E2B	C	10.9" x 8.8" x 10.3"	14.4	\$4,529	E19 (E1)
	200	171	SSW900C0171T6E2B	C	10.9" x 8.8" x 10.3"	14.4	\$5,705	E19 (E1)
	250	200	SSW900C0200T6E2B	C	10.9" x 8.8" x 10.3"	14.4	\$7,172	E19 (E1)
	300	255	SSW900D0255T6E3B	D	13.0" x 8.9" x 11.1"	28.3	\$8,242	E19 (E1)
	400	312	SSW900D0312T6E3B	D	13.0" x 8.9" x 11.1"	28.3	\$8,948	E19 (E1)
	450	365	SSW900D0365T6E3B	D	13.0" x 8.9" x 11.1"	28.3	\$9,299	E19 (E1)
	550	412	SSW900D0412T6E3B	D	13.0" x 8.9" x 11.1"	28.3	\$11,181	E19 (E1)
	600	480	SSW900E0480T6E3B	E	22.6" x 15.4" x 10.2"	83.7	\$13,841	E19 (E1)
	750	604	SSW900E0604T6E3B	E	22.6" x 15.4" x 10.2"	83.7	\$15,439	E19 (E1)
	850	670	SSW900E0670T6E3B	E	22.6" x 15.4" x 10.2"	83.7	\$14,932	E19 (E1)
	1000	820	SSW900F0820T6E3B	F	29.9" x 29.9" x 12.4"	166.2	Available in November 2021.	
	1200	950	SSW900F0950T6E3B	F	29.9" x 29.9" x 12.4"	166.2		
	1400	1100	SSW900G1100T6E3B	G	36.0" x 36.0" x 12.4"	236.3		
	1700	1400	SSW900G1400T6E3B	G	36.0" x 36.0" x 12.4"	236.3		

Notes:

- "HP" rating based on FLA values from WEG W22, 2 and 4 pole, NEMA Premium motors.
- Motor FLA may vary with speed and manufacturer. ALWAYS compare motor FLA to Nominal AMPS of the starter.
- Frame-A & D are rated for 55°C as a standard and duty cycle will be 3 x In for 30s, 10 Starts/hr.
Frame- B & C are rated for 55°C as a standard and duty cycle will be 3 x In for 30s, 10 Starts/hr with ventilation kit (3 x In for 30s, 3 starts/hr w/o ventilation kit).
Frame- E, F & G are rated for 40°C as a standard and duty cycle will be 3 x In for 30s, 5 starts/hr.
- The 690VAC Soft starters are not "UL Listed" and are non-stocked items. Please consult WEG for availability.

Options and Accessories

Type	CATALOG NUMBER	Description	List Price	Multiplier New (Old)
Keypad	SSW900-HMI-BLT	Standard Bluetooth Keypad	\$345	E19 (E1)
	SSW900-KMD-CB01	Remote Keypad Frame + 1m (3.3ft) Cable	\$65	E19 (E1)
	SSW900-KMD-CB02	Remote Keypad Frame + 2m (6.6ft) Cable	\$75	E19 (E1)
	SSW900-KMD-CB03	Remote Keypad Frame + 3m (10ft) Cable	\$85	E19 (E1)
	SSW900-KMD-CB05	Remote Keypad Frame + 5m (16ft) Cable	\$115	E19 (E1)
	SSW900-KMD-CB07	Remote Keypad Frame + 7.5m (26ft) Cable	\$155	E19 (E1)
	SSW900-KMD-CB10	Remote Keypad Frame + 10m (33ft) Cable	\$195	E19 (E1)
	SSW900-KMD-CB20	Remote Keypad Frame + 20m (66ft) Cable	\$355	E19 (E1)
Communication	SSW900-CDN-N	Devicenet Anybus plug-in module	\$1,280	E19 (E1)
	SSW900-CETH-IP-N	Ethernet/IP Anybus plug-in module	\$2,215	E19 (E1)
	SSW900-CMB-TCP-N	Modbus-TCP Anybus plug-in module	\$1,800	E19 (E1)
	SSW900-CPDP-N	Profibus DP Anybus plug-in module	\$1,175	E19 (E1)
	SSW900-CPN-IO-N	Profinet IO Anybus plug-in module	\$2,075	E19 (E1)
	SSW900-CRS485-W	RS485 plug-in module	\$170	E19 (E1)
	SSW900-CAN-W	CANopen and DeviceNet plug-in module	\$330	E19 (E1)
	SSW900-CETH-W	Ethernet/IP plug-in module (Available in December 2021)	\$1,220	E19 (E1)
I/O Expansion	SSW900-PT100-W	PT100 temperature transducer module (6 inputs)	\$430	E19 (E1)
Ventilation Kits	SSW0708900-KVT-2B	Ventilation Kit for SSW07, Frame-2 and SSW900, Frame-B (45 to 105 A)	\$65	GA (E1)
	SSW0708900-KVT-3C	Ventilation Kit for SSW07, Frame-3 and SSW900, Frame-C (130 to 200 A)	\$94	GA (E1)
IP20 Kits	SSW0708900-IP20-3C	IP20 Kit for SSW07, Frame-3 and SSW900, Frame-C (130 to 200 A)	\$62	GA (E1)
	SSW0708900-IP20-4D	IP20 Kit for SSW07, Frame-4 and SSW900, Frame-D (255 to 412 A)	\$130	GA (E1)
Front cover kit	SSW0708900-PROT-3C	Front cover kit for power terminals for SSW07, Frame-3 and SSW900, Frame-C (130 to 200 A)	\$55	GA (E1)
	SSW0708900-PROT-4D	Front cover kit for power terminals for SSW07, Frame-4 and SSW900, Frame D (255 to 412 A)	\$65	GA (E1)
	SSW900-PROT-E	Front cover kit for power terminals for SSW900 frame E (480 to 670 A)	\$130	E19 (E1)
External Current Transformers	SSW900-KECA-10	External Current Transformer for SSW900 10A	\$415	E19 (E1)
	SSW900-KECA-17	External Current Transformer for SSW900 17A	\$435	E19 (E1)
	SSW900-KECA-24	External Current Transformer for SSW900 24A	\$455	E19 (E1)
	SSW900-KECA-30	External Current Transformer for SSW900 30A	\$470	E19 (E1)
	SSW900-KECA-45	External Current Transformer for SSW900 45A	\$510	E19 (E1)
	SSW900-KECA-61	External Current Transformer for SSW900 61A	\$540	E19 (E1)
	SSW900-KECA-85	External Current Transformer for SSW900 85A	\$565	E19 (E1)
	SSW900-KECA-105	External Current Transformer for SSW900 105A	\$580	E19 (E1)
	SSW900-KECA-130	External Current Transformer for SSW900 130A	\$620	E19 (E1)
	SSW900-KECA-171	External Current Transformer for SSW900 171A	\$650	E19 (E1)
	SSW900-KECA-200	External Current Transformer for SSW900 200A	\$680	E19 (E1)
	SSW900-KECA-255	External Current Transformer for SSW900 255A	\$845	E19 (E1)
	SSW900-KECA-312	External Current Transformer for SSW900 312A	\$885	E19 (E1)
	SSW900-KECA-365	External Current Transformer for SSW900 365A	\$915	E19 (E1)
SSW900-KECA-412	External Current Transformer for SSW900 412A	\$930	E19 (E1)	



WEG Electric Corp.
6655 Sugarloaf Parkway
Duluth, GA 30097

Phone: 1-800-ASK-4WEG
Fax: 1-770-338-1632
info-us@weg.net
www.weg.net