



RESIN IMP LACKTHERM[®] 1364 H COMP B

PRODUCT DESCRIPTION:	Epoxy hardener bi-component, solventless.	
INDICATION OF USE:	Insulation bonding for mica and fiberglass tapes.	
APPLICATION SYSTEM:	Brush.	
CHARACTERISTICS:	<p>Code: 10001690 (2,7 Kg)</p> <p>Aspect / Color: Liquid clearly viscous</p> <p>Solids Content: 100% (ASTM D2697/03)</p> <p>Density: 0,96 ± 0,02 g/cm³ (ASTM D1475/98)</p> <p>Viscosity Brookfield: 12500 ± 2500 cPs 25°C (ASTM D2196)</p> <p>Dielectric Strength: 60 kV/mm (min) (IEC 60464-2)</p> <p>Thermal Class: H (180°C) (DIN 46452/77)</p> <p>Mixture Characteristics</p> <p>Component A: RESIN IMP LACKTHERM[®] 1364 H COMP A</p> <p>Mix rate: 65A:35B parts per weight</p> <p>Cure: 3h – 6h / 25°C – 30°C</p> <p>Forced dry oven: 3h – 6h / 25°C – 30°C. Estufa: 5min. – 15min. / 80°C – 130°C or to apply in the preheated part</p> <p>Pot life: 2h (25°C)</p> <p>Shelf life: 12 months</p> <p>Emergency record: ONU Not classified</p>	
RECOMMENDATIONS:	<p>To conserve in cool, distant place of ignition points;</p> <p>To keep the closed packing after the partial use;</p> <p>To use in place with good ventilation.</p>	
SAFETY PRECAUTIONS:	<p>Handling, dilution and the use of paints during the painting and drying process shall be carried out far away from flames, sparks or excessive heat and in ventilated rooms since they are flammable products.</p> <p>Contact with the skin may cause irritations.</p> <p>If swallowed, do not provoke vomit. In case of eye contact, rinse the eyes under running water. In any case, seek immediate medical attention.</p> <p>Do not smoke in the working area.</p> <p>Make sure that electric installations are perfect and that they will not release sparks.</p> <p>Do not wash the skin, hands or other parts of the body with solvents or thinners. Wash your hands first with alcohol and then wash them with running water and cleaning pastes. Use a skin restoring protective cream.</p> <p>In case of fire, use CO₂ or chemical fire extinguishers. Water is not recommended to extinguish the flames caused by the burning of paints.</p> <p>Paints and thinners shall be stored in ventilated rooms and protected against inclemency. The storage temperature may vary from 10 to 40°C.</p> <p>If intoxication symptoms are caused due to inhalation of solvent vapors, remove the person immediately from the working area and bring him to a ventilated room. In case of unconsciousness, call for a doctor right away.</p>	
NOTE:	<p>All information stated in this Technical Bulletin is based on our experience and knowledge. Nevertheless, as we do not have control over the use of our products, no warranty either expressed or implied can be granted or suggested with regards to this information whatsoever. Therefore, we do not assume any liability for coverage rate, performance or any damages or injuries resulting from improper use of the given information.</p>	