



IMP LACKTH 13231 F COMP B

PRODUCT DESCRIPTION:	Epoxy hardener.
INDICATION OF USE:	Encapsulation of electrical components in general.
APPLICATION SYSTEM:	Filling.
CHARACTERISTICS:	<p>Code: 10001695 (0,9 Kg)</p> <p>Aspect/Color: Clear liquid.</p> <p>Viscosity Brookfield: 40 – 60 cPs 25°C (ASTM D2196)</p> <p>Dielectric Streight: 60 kV/mm (mín.) (IEC 604647)</p> <p>Solids Content: 100% (ASTM D2697/03)</p> <p>Thermal Class: F (155°C) (DIN 46452/77)</p> <p>Mixture Characteristic</p> <p>Component A: Resin Imp Lackth 13231 F Comp A</p> <p>Catalisys: 77A:23B parts by weigh</p> <p>Cure: 1h - 3h / 25 ° C - 30 ° C. Stove: 45min. - 60 min. / 40 ° C - 50 ° C or encapsulate the preheated part.</p> <p>Shelf Life of the mixture 30min. (25°C)</p> <p>Emergency Record: ONU not classified.</p> <p>Shelf Life: 12 months</p>
RECOMMENDATIONS:	<p>Store in a cool place away from sources of ignition.</p> <p>Keep container closed after use.</p> <p>Use in a well ventilated place.</p>
SAFETY PRECAUTIONS:	<p>When using this product, always use PPE's: safety goggles, PVC gloves, apron and mask with organic vapors.</p> <p>Storage must be in ventilated areas, protected from weathering.</p> <p>Do not smoke in the work area. - In case of fire, use CO2 extinguishers or chemical powder.</p> <p>Use water in the form of mist, except in energized equipment.</p> <p>Contact with skin causes irritation.</p> <p>Do not use thinner to clean the skin, hands and body parts. To clean hands use alcohol, and then wash with water and cleaning paste. Use skin restorative skin cream.</p> <p>If swallowed, induce vomiting only if victim is conscious. In case of contact with eyes, rinse thoroughly with water.</p> <p>If symptoms of poisoning occur due to inhalation of solvent vapors, immediately remove the person to a ventilated area.</p> <p>In the event of an accident, provide first aid and call for medical attention immediately.</p>
NOTE:	<p>All information mentioned in this technical bulletin is based on our experience and knowledge, however, as we have no control over the use of our products, no guarantee - expressed or implied is given or suggested in relation to this information. We do not assume any responsibility for the performance, performance or any material or personal damages resulting from the incorrect use of the information provided.</p>