



WEG Standard Product Catalog

Electrical and Mechanical



Register to keep your
catalog up-to-date





Electrical Data

SECTION B

Single-Phase Wiring Diagrams B-2


Three-Phase Wiring Diagrams B-3

Single-Phase Wiring Diagrams


ALWAYS USE WIRING DIAGRAM SUPPLIED ON MOTOR NAMEPLATE

FOR MOTORS WITH THERMAL PROTECTION


Single Voltage / Single Rotation



Single Voltage / Reversible Rotation




Dual Voltage / Single Rotation




Dual Voltage / Reversible Rotation

Split-Phase Motor



Capacitor Motor




Three-Phase Wiring Diagrams

ALWAYS USE WIRING DIAGRAM SUPPLIED ON MOTOR NAMEPLATE


colored leads are only applicable on the NEW ROLLED STEEL motor lines

DOL




9 leads | Valid for voltage Code: E | Frames 56 and 143/5

DOL




9 leads | Valid for voltage Code: E | Frames 182/4 and 213/5 for E Code (except for fire pump motors)


WYE-DELTA - LOW VOLTAGE



WYE-DELTA - HIGH VOLTAGE





PWS - LOW VOLTAGE




12 leads | Valid for voltage Code: E and V | Frames 254/6 and above
Motors are capable of WYE/Delta start (both voltages)
Motors capable of part-winding start at the low voltage

WYE-DELTA




12 leads | Valid for voltage Code: G | Frames 254/6 and above
Motors are capable of WYE/Delta start | Motors are capable of part-winding start

WYE-DELTA




WYE-DELTA (IEC - Metric)



6 leads | Valid for voltage Code: J, H, P, Q, W & Y | All frames
Q and H codes may have only 3 leads (1HP and all IEEE models)

DOL



3 leads | Valid for voltage Code: Q and H | All frames
Q and H codes, non-IEEE-841 motors, can also have 6 leads


Single Phase - General Purpose - TEFC - Cast Iron	B-5
Single Phase - General Purpose - TEFC - Cast Iron - C-Face	B-7
Single Phase - General Purpose - TEFC - Rolled Steel - Standard Efficiency	B-9
Single Phase - General Purpose - TEFC - Rolled Steel - Standard Efficiency - C-Face	B-11
Single Phase - General Purpose - ODP - Rolled Steel - Standard Efficiency	B-13
Single Phase - General Purpose - ODP - Rolled Steel - Standard Efficiency - C-Face	B-15
Single Phase - General Purpose - ODP - Rolled Steel - Premium Efficiency	B-17
Single Phase - General Purpose - ODP - Rolled Steel - Premium Efficiency - C-Face	B-19
TEFC – W22 NEMA Premium® Efficiency	B-21
C & D Flanges Dimensions – Valid for Cast Iron TEFC and ODP - C-Flange additional detail	B-23
D-Flange additional detail	B-23
Rolled Steel - General Purpose - Three Phase - TEFC	B-24
Rolled Steel - General Purpose - Three Phase - ODP	B-26
ODP – Cast Iron - Three Phase - General Purpose	B-27
Explosion Proof - Three Phase	B-30
Fractional - Three Phase - TEFC - NEMA Premium®	B-32
Fractional - Three Phase - TEFC - NEMA Premium® - C-Face	B-33
Fractional - Three Phase - TEFC - Standard Efficiency	B-34
Fractional - Three Phase - TEFC - Standard Efficiency - C-Face	B-35
Fractional - Three Phase - ODP - Premium Efficiency	B-36
Fractional - Three Phase - ODP - Premium Efficiency - C-Face	B-37
Fractional - Three Phase - ODP - Standard Efficiency	B-38
Fractional - Three Phase - ODP - Standard Efficiency - C-Face	B-39
Cooling Tower Motors - Three Phase - TEFC	B-40
Cooling Tower Motors - Three Phase - TEAO	B-44
CCP - JM - Three Phase - TEFC - Rolled Steel	B-47
CCP - JM - Three Phase - TEFC - Cast Iron	B-49
CCP - JP - Three Phase - TEFC - Rolled Steel	B-52
CCP - JP - Three Phase - TEFC - Cast Iron	B-54
CCP - JM - Three Phase - ODP - Rolled Steel	B-57
CCP - JP - Three Phase - ODP - Rolled Steel	B-57
CCP - JP and JM - Three Phase - ODP - Cast Iron	B-60
IEC Metric Motors - Cast Iron Frames	B-62
IEC Metric Motors - Cast Iron Frames - Additional C-Flange Detail	B-64

Single Phase - General Purpose - TEFC - Cast Iron

Frame	2E	J	A	P	AB	2F	B	EV	BA	U	N-W	Key Length
143/5T	5.5	1.457	6.457	7.244	7.126	4	6.142	0.571	2.25	0.875	2.25	1.575
182/4T	7.5	1.614	8.661	8.937	8.11	4.5	6.969	0.734	2.75	1.125	2.75	1.969
213/5T	8.5	1.791	9.764	10.787	9.212	5.5	8.858	0.929	3.5	1.375	3.375	2.48


Frame	Width	R	Depth	D	G	HB	O	HH	HK	Hole H	C	LM	S	AA	DE	NDE
143/5T	0.187	0.766	0.187	3.5	0.354	1.043	7.122	4.75	3.583	0.34	14.49	8.11	0.187	NPT 3/4"	6205 ZZ	6203 ZZ
182/4T	0.25	0.984	0.25	4.5	0.394	1.574	8.897	5.5	3.7	0.41	17.012	9.134	0.25	NPT 1"	6207 ZZ	6206 ZZ
213/5T	0.313	1.203	0.313	5.25	0.669	2.362	10.84	7	3.7	0.41	20.095	9.134	0.313	NPT 1"	6308 ZZ	6206 ZZ

Frames 143/5




Single Phase - General Purpose - TEFC - Cast Iron

Frames 182/4




Frame 213/5



Single Phase - General Purpose - TEFC - Cast Iron - C-Face


Frame	Type	Flange	Size	BC	AJ	AK	BD	S	T	AH	Angle	BF Number
143/5T	C	C	FC-149	0.125	5.875	4.5	6.5	UNC 3/8"x16	0.157	2.125	45°	4
182/4T	C	C	FC-184	0.125	7.25	8.5	8.875	UNC 1/2"x13	0.25	2.625	45°	4
213/5T	C	C	FC-184	0.25	7.25	8.5	8.875	UNC 1/2"x13	0.25	3.125	45°	4

Frames 143/5




Single Phase - General Purpose - TEFC - Cast Iron - C-Face

Frames 182/4



Frame 213/5




Single Phase - General Purpose - TEFC - Rolled Steel - Standard Efficiency

Frame	2E	J	A	P	AH	2F	B	BA	CH	U	N-W	Key Length
48	4.236	1.835	6.142	6.693	1.689	2.748	3.543	2.5	1.417	0.5	1.5	1.26
W56	4.874	1.62	6.535	6.693	2.063	3	4.016	2.75	1.417	0.625	1.874	1.417
56	4.874	1.732	6.535	7.638	2.062	3	4.016	2.75	1.377	0.625	1.874	1.417
56H	4.874	1.732	6.535	7.638	2.062	3.000/5.000	6.496	2.75	1.377	0.625	1.874	1.417
143/5T	5.5	1.732	6.535	7.638	2.132	4.000/5.000	6.496	2.25	1.377	0.875	2.25	1.417
182/4T	7.5	1.299	8.661	9.435	2.62	4.500/5.500	6.299	2.75	1.377	1.125	2.75	1.969
213/5T	8.5	1.575	9.449	10.965	3.129	5.500/7.000	7.953	3.5	1.929	1.375	3.38	2.48


Frame	R	Depth	D	G	O	HD	Hole H	C	AA	T	DE	NDE
48	0.451		3	0.075	5.83	6.354	0.343	*	0.881"	0.524	6203 ZZ	6202 ZZ
W56	0.517	0.187	3.5	0.12	6.33	6.854	0.343	*	0.881"	0.524	6203 ZZ	6202 ZZ
56	0.517	0.187	3.5	0.12	6.724	7.327	0.343	*	0.881"	0.603	6203 ZZ	6202 ZZ
56H	0.517	0.187	3.5	0.12	6.724	7.327	0.343	*	0.881"	0.603	6204 ZZ	6202 ZZ
143/5T	0.771	0.187	3.5	0.12	6.724	7.327	0.343	*	1.118"	0.603	6205 ZZ	6203 ZZ
182/4T	0.984	0.25	4.5	0.167	8.557	9.218	0.406	*	1.118"	0.661	6206 ZZ	6205 ZZ
213/5T	1.203	0.313	5.25	0.167	10.144	10.905	0.406	*	1.377"	0.761	6208 ZZ	6206 ZZ

* Dimension changes with output speed

Frame 48




Frame W56




Single Phase - General Purpose - TEFC - Rolled Steel - Standard Efficiency


Frame 56




Frames 56H - 143T/5T



Frame 182/4T




Frame 213/5T




Single Phase - General Purpose - TEFC - Rolled Steel - Standard Efficiency - C-Face

Frame	Type	Flange	Size	AJ	AK	BD	S	T	AH	Angle	BB	BF Number
W56	C	C	FC-149	5.874	4.5	6.47	UNC 3/8"x16-2B	0.157	2.063	45°	0.157	4
48	C	C	FC-95	3.748	3	4.74	UNC 1/4"x20-2B	0.157	1.689	45°	0.157	4
56	C	C	FC-149	5.874	4.5	6.45	UNC 3/8"x16-2B	0.157	2.062	45°	0.157	4
143/5T	C	C	FC-149	5.874	4.5	6.45	UNC 3/8"x16	0.157	2.132	45°	0.157	4
56H	C	C	FC-149	5.874	4.5	6.45	UNC 3/8"x16-2B	0.157	2.062	45°	0.157	4
182/4T	C	C	FC-184	7.25	8.5	8.846	UNC 1/2"x13	0.25	2.62	45°	0.25	4
213/5T	C	C	FC-184	7.25	8.5	9.401	UNC 1/2"x13	0.25	3.129	45°	0.25	4


Frame W56




Frame 48




Frame 56






Frame 182/4T



Frame 213/5T




Single Phase - General Purpose - ODP - Rolled Steel - Standard Efficiency

Frame	2E	J	A	P	AB	AH	2F	B	BA	CH	U	N-W	Key Length	R
48	4.236	1.835	6.142	5.709	5.52	1.689	2.748	3.543	2.5	1.22	0.5	1.5	1.26	0.451
W56	4.874	1.62	6.535	5.709	5.52	2.063	3	4.016	2.75	1.22	0.625	1.874	1.417	0.517
56	4.874	1.732	6.535	6.456	3.323	2.062	3	4.016	2.75	1.377	0.625	1.874	1.417	0.517
56H	4.874	1.732	6.535	6.456	5.882	2.062	3.000/5.000	6.496	2.75	1.377	0.625	1.874	1.417	0.517
143/5T	5.5	1.732	6.535	6.467	5.882	2.132	4.000/5.000	6.496	2.25	1.377	0.875	2.25	1.417	0.771
182/4T	7.5	1.299	8.661	8.114	6.696	2.62	4.500/5.500	6.299	2.75	1.377	1.125	2.75	1.969	0.984
213/5T	8.5	1.575	9.449	9.846	7.973	3.129	5.500/7.000	7.953	3.5	1.929	1.375	3.38	2.48	1.203


Frame	D	G	HB	O	HD	HK	Hole H	C	LL	LM	S	AA	T	DE	NDE
48	3	0.075	1.559	5.83	6.354	2.65	0.343	*	3.835	3.697		NPT 1/2"	0.524	6203 ZZ	6202 ZZ
W56	3.5	0.12	2.055	6.33	6.854	2.65	0.343	*	3.835	3.697	0.187	NPT 1/2"	0.524	6203 ZZ	6202 ZZ
56	3.5	0.12	1.784	6.724	6.728	2.629	0.343	*	4.563	4.09	0.187	NPT 1/2"	0.004	6203 ZZ	6202 ZZ
56H	3.5	0.12	1.783	6.724	6.728	2.638	0.343	*	4.543	4.106	0.187	NPT 1/2"	0.004	6204 ZZ	6202 ZZ
143/5T	3.5	0.12	1.783	6.724	6.728	2.638	0.343	*	4.543	4.106	0.187	1.118"	0.004	6205 ZZ	6202 ZZ
182/4T	4.5	0.167	2.784	8.557	8.557	2.629	0.406	*	4.563	4.09	0.25	1.118"	0	6206 ZZ	6205 ZZ
213/5T	5.25	0.167	2.982	10.144	10.173	3.022	0.406	*	5.551	5.25	0.313	1.377"	0.029	6208 ZZ	6206 ZZ

Dimensions change with output speed


Frame 48



Frame W56






Frame 56







Single Phase - General Purpose - ODP - Rolled Steel - Standard Efficiency





Frame 56H



Frame 143/5T




Frame 182/4T - 213/5T




Single Phase - General Purpose - ODP - Rolled Steel - Standard Efficiency - C-Face

Frame	Type	Flange	Size	AJ	AK	BD	S	T	AH	Angle	BF Number
W56	C	C	FC-149	5.874	4.5	6.47	UNC 3/8"x16-2B	0.157	2.063	45°	4
48	C	C	FC-95	3.748	3	4.74	UNC 1/4"x20-2B	0.157	1.689	45°	4
56	C	C	FC-149	5.874	4.5	6.45	UNC 3/8"x16-2B	0.157	2.062	45°	4
143/5T	C	C	FC-149	5.874	4.5	6.45	UNC 3/8"x16	0.157	2.132	45°	4
56H	C	C	FC-149	5.874	4.5	6.45	UNC 3/8"x16-2B	0.157	2.062	45°	4
182/4T	C	C	FC-184	7.25	8.5	8.846	UNC 1/2"x13	0.25	2.62	45°	4
213/5T	C	C	FC-184	7.25	8.5	9.401	UNC 1/2"x13	0.25	3.129	45°	4


Frame 48



Frame W56




Frame 56




Single Phase - General Purpose - ODP - Rolled Steel - Standard Efficiency - C-Face


Frame 56H



Frame 143/5T



Frame 182/4T - 213/5T





Single Phase - General Purpose - ODP - Rolled Steel - Premium Efficiency

Frame	2E	J	A	P	AB	AH	2F	B	BA	CH	U	N-W	Key Length	R	Depth
48	4.236	1.835	6.142	5.709	5.52	1.689	2.748	3.543	2.5	1.22	0.5	1.5	1.26	0.451	
W56	4.874	1.62	6.535	5.709	5.52	2.063	3	4.016	2.75	1.22	0.625	1.874	1.417	0.517	0.187
56	4.874	1.732	6.535	6.456	3.323	2.062	3	4.016	2.75	1.377	0.625	1.874	1.417	0.517	0.187
56H	4.874	1.732	6.535	6.456	5.882	2.062	3.000/5.000	6.496	2.75	1.377	0.625	1.874	1.417	0.517	0.187
143/5T	5.5	1.732	6.535	6.467	5.882	2.132	4.000/5.000	6.496	2.25	1.377	0.875	2.25	1.417	0.771	0.187



Frame	D	G	HB	O	HD	HK	Hole H	C	LL	LM	S	T	DE	NDE
48	3	0.075	1.559	5.83	6.354	2.65	0.343	*	3.835	3.697		0.524	6203 ZZ	6202 ZZ
W56	3.5	0.12	2.055	6.33	6.854	2.65	0.343	*	3.835	3.697	0.187	0.524	6203 ZZ	6202 ZZ
56	3.5	0.12	1.784	6.724	6.728	2.629	0.343	*	4.563	4.09	0.187	0.004	6203 ZZ	6202 ZZ
56H	3.5	0.12	1.783	6.724	6.728	2.638	0.343	*	4.543	4.106	0.187	0.004	6204 ZZ	6202 ZZ
143/5T	3.5	0.12	1.783	6.724	6.728	2.638	0.343	*	4.543	4.106	0.187	0.004	6205 ZZ	6202 ZZ

Dimensions change with output speed

Frame 48






Frame W56






Single Phase - General Purpose - ODP - Rolled Steel - Premium Efficiency





Frame 56



Frame 56H






Frame 143/5T





Single Phase - General Purpose - ODP - Rolled Steel - Premium Efficiency - C-Face

Frame	Type	Flange	Size	BB	AJ	AK	BD	S	T	AH	Angle	BF Number
W56	C	C	FC-149	0.157	5.874	4.5	6.47	UNC 3/8"x16-2B	0.157	2.063	45°	4
48	C	C	FC-95	0.157	3.748	3	4.74	UNC 1/4"x20-2B	0.157	1.689	45°	4
56	C	C	FC-149	0.157	5.874	4.5	6.45	UNC 3/8"x16-2B	0.157	2.062	45°	4
143/5T	C	C	FC-149	0.157	5.874	4.5	6.45	UNC 3/8"x16	0.157	2.132	45°	4
56H	C	C	FC-149	0.157	5.874	4.5	6.45	UNC 3/8"x16-2B	0.157	2.062	45°	4

Frame W56




Frame 48




Single Phase - General Purpose - ODP - Rolled Steel - Premium Efficiency - C-Face


Frame 56



Frame 143/5T



Frame 56H






TEFC – W22 NEMA Premium® Efficiency

Frame	Mounting				A	B	C	D	G	J	O	K	P	T	Keyway			Shaft Extension									
	2E	2F	H	BA											S	R	ES	N-W	U								
143T	5.500	4.000	0.344	2.250	6.457	5.157	12.346	3.500	0.354	1.437	7.122		7.047	-	0.187	0.765	1.575	2.250	0.875								
L143T						13.566	13.346																				
145T		5.000				6.142	14.566																				
L145T						14.860	16.041																				
182T	7.500	4.500	0.406	2.750	8.661	5.945	16.041	4.500	0.394	1.594	9.343	-	8.740	1.772	0.250	0.984	1.969	2.750	1.125								
L182T						15.860	17.041																				
184T		5.500				6.969	18.021													19.527							
L184T						7.362	19.527													19.517							
213T	8.500	5.500	0.531	3.500	9.764	7.362	19.527	5.250	0.827	1.988	10.841		10.669		0.313	1.203	2.480	3.375	1.375								
L213T						8.858	20.905																				
215T		7.000					23.213													24.945							
L215T						11.732	25.061																				
254T	10.000	8.252	0.657	4.250	12.126	10.000	23.213	6.250		2.539	12.598	2.559	12.953	2.087	0.375	1.406	2.756	4.000	1.625								
256T		10.000				11.732	24.945										25.061										
284TS						11.575	26.433										26.557										
L284T						13.071	27.929										28.120										
286TS	11.000	9.500	0.657	5.250	15.157		29.616	8.000	1.300	3.189	15.953	3.189	15.827	2.441	0.500		3.149	4.622									
286T						14.567	31.116									3.750	2.125										
324TS		10.500					32.276									34.251	3.937	2.375									
L324T						14.567	31.116									3.937	2.375										
326TS	12.500	12.000	0.660	5.875	17.165	16.220	32.276	9.000	1.480	3.150	17.957	4.921	17.914		0.625	2.019	4.330	5.874	2.375								
326T						34.251	36.732													39.730	1.811	19.566	5.669	19.134			
364/5TS		11.260/12.244					6.625													19.921	18.386	36.732	39.730	1.811	19.566	5.669	19.134
L364/5T							6.625													19.921	18.386	36.732	39.730	1.811	19.566	5.669	19.134
404/5TS	15.984	12.244/13.740	0.810	7.500	21.929	20.315	41.200	11.000	1.630	3.937	22.795	5.866	23.583	-	0.625	2.021	3.000	4.750	2.375								
404/5T						20.315	44.950													1.630	3.937	5.866					
444/5TS		14.500/16.500					23.897													44.951	1.654	22.795	5.866				
L444/5T						23.897	48.701													1.654	22.795	5.866					
445/7TS	18.000	16.500/20.000	0.810	7.500	21.929		48.701	11.000	1.630	4.331	23.874	8.780	25.866	-	0.625	2.021	3.000	4.750	2.375								
445/7T						31.535	52.588													1.630	4.331	8.780					
447/9TS		20.000/25.000					56.338													1.630	4.331	8.780					
L447/9T						31.535	53.431													1.630	4.331	8.780					
L447/9TS	20.000	20.000/25.000	1.250	8.500	24.724	24.449	48.215	12.500	2.146	4.724	25.425	7.228		25.866	0.625	2.021	3.000	4.750	2.375								
504/5TS						54.095	55.027													2.146	4.724	25.425	7.228				
504/5T						29.921	61.902													2.146	4.724	25.425	7.228				
586/7TS		22.000/25.000					62.506													2.146	4.724	25.425	7.228				
586/7T	23.000	28.000/32.000	1.181	10.000	29.528	37.980	69.381	14.500	2.492	5.512	28.985	13.030	28.977		0.625	2.021	3.000	4.750	2.375								
588/9TS						69.381	69.381													2.492	5.512	28.985	13.030				
588/9T						69.381	69.381													2.492	5.512	28.985	13.030				
L588/9T						69.381	69.381													2.492	5.512	28.985	13.030				


Frame	Terminal Box										d1	Bearings	
	AB	HB	HD	HF	HG	HH	HK	LL	LM	AA		D.E.	N.D.E
143T	6.181	1.728		3.500		4.250	2.638	4.252	3.858	NPT3/4"	A 4	6205 ZZ	6204 ZZ
L143T						4.750							
145T						5.000							
L145T						5.500							
182T	7.559	2.236	4.500	6.250	3.110	5.512	5.236	NPT1"	6207 ZZ	6206 ZZ			
L182T				7.000									
184T				8.376									
L184T				9.250									
213T	8.583	3.006	5.250	9.500	3.937	7.815	7.480	NPT1 1/2"	6309 C3	6209 C3			
L213T				10.250									
215T				10.500									
L215T				11.250									
254T	10.394	3.061	6.565	12.362	4.645	9.055	8.661	NPT 2"	6312 C3	6212 C3			
256T				12.362									
284TS				14.213									
L284TS				15.748									
284T	10.984	3.535	7.000	15.748	5.787	12.362	12.283	UNC 3/4"-10	6314 C3	6314 C3			
286TS				6316 C3									
286T				6314 C3									
324TS				6319 C3									
324T	12.480	4.811	8.708	6314 C3	6.968	14.921	15.039		6316 C3	6316 C3			
326TS				6314 C3									
326T				6314 C3									
364/5TS				6314 C3									
364/5T	16.378	4.055		13.977(top mounted)	15.906	17.165	2xNPT 3"		6322 C3	6319 C3			
404/5TS		5.040		6314 C3									
404/5T		18.386		5.394					6314 C3				
444/5TS		20.670		15.078					27.401		25.889	27.007	11.803
444/5T	20.670	15.078	27.401	25.889	27.007	11.500			8.464	15.906	17.165	6314 C3	6314 C3
445/7TS												6314 C3	
445/7T												6314 C3	
447/9TS												6314 C3	
447/9T	23.071	15.078	27.401	25.889	27.007	11.500		8.464	15.906	17.165	6314 C3	6314 C3	
L447/9TS											6314 C3		
L447/9T											6314 C3		
504/5TS											6314 C3		
504/5T	20.670	15.275	30.305	24.291	29.409	10.394		6.968	14.921	15.039	6314 C3	6314 C3	
586/7TS											6314 C3		
586/7T											6314 C3		
588/9TS											6314 C3		
588/9T	27.600	6.063	35.346	26.182	33.346	13.386	12.519 (side mounted)/ 13.977(top mounted)	15.906	17.165	UNC 7/8"-9	6322 C3	6319 C3	
										UNC 3/4"-10	6314 C3	6314 C3	
										UNC 7/8"-9	6322 C3	6319 C3	

TEFC – W22 NEMA Premium® Efficiency *continued*


Frames 143T to 215T




Frames 254T to 326T




Frames 364 to 444/5T





Frames 445/7T to 586/7T




Frame 588/9T




C & D Flanges Dimensions – Valid for Cast Iron TEFC and ODP - C-Flange additional detail

Frame	Type	Size	AJ	AK	AH	BA	BB	BC	BD	BF (holes)				
										Quantity	Thread			
143/5	C	FC-140	5.875	4.500	2.125	2.250	0.157	0.125	6.500	4	UNC 3/8"x16			
182/4	C	FC-184	7.250	8.500	2.625	2.750	0.125		8.875		UNC 1/2"x13			
213/5	C				3.125	3.500								
254/6	C				3.750	4.250								
284/6T	C	FC-228	9.000	10.500	4.375	4.750	0.250	11.030	8					
284/6TS	C				3.000			13.580						
324/6T	C	FC-279	11.000	12.500	5.000	5.250		15.550						
324/6TS	C				3.500									
364/5T	C				5.625	5.875								
364/5TS	C				3.500									
404/5T	C	FC-355	14.000	16.000	7.000	6.625	0.250	17.910	8					
404/5TS	C				4.000									
444/5T	C				FC-368	14.500					16.500	8.250	8.500	
444/5TS	C											4.500		
445/7T	C	8.250	10.000											
445/7TS	C	4.500												
447/9T	C	FC-368	14.500	16.500	8.250	10.000	0.250	17.910	8	UNC 5/8"x11				
447/9TS	C				4.500									
504/5T	C				FC-368						14.500	16.500	10.375	8.500
504/5TS	C												4.500	
586/7T	C	11.375	10.000											
586/7TS	C	4.500												
588/9T	C	FC-368	14.500	16.500	11.375	10.000	0.250	17.910	8	UNC 5/8"x11				
588/9TS	C				4.500									



D-Flange additional detail


Frame	Type	Size	AJ	AK	BA	BB	BD	BF (holes)	
								Quantity	Thread
143/5	D	FD-254	10.000	9.000	2.250	0.197	11.000	4	0.562
182/4	D				2.750				
213/5	D				3.500				
254/6	D	FD-317	12.500	11.000	4.250	0.203	14.000		0.828
284/6T	D				4.750				
284/6TS	D								
324/6T	D	FD-406	16.000	14.000	5.250	0.197	18.000		
324/6TS	D								
364/5T	D				5.875		17.710		
364/5TS	D								
404/5T	D	FD-508	20.000	18.000	6.625	0.203	22.000	8	
404/5TS	D								
444/5T	D								
444/5TS	D								
445/7T	D								
445/7TS	D								
447/9T	D	FD-558	22.000	20.000		0.250	21.650		
447/9TS	D								
504/5T	D								
504/5TS	D								
586/7T	D	FD-762	30.000	30.000		0.250	24.800		
586/7TS	D								
588/9T	D								
588/9TS	D								




Frame	P	AB	HK	HB	J	2E	A	H1	D	G	LL	LM
143/5T	7.638	5.882	2.638	1.783	1.732	5.500	6.535	-	3.500	0.120	4.543	4.106
182/4T	9.435	6.696	2.629	2.784	1.299	7.500	8.661	-	4.500	0.167	4.563	4.090
213/5T	10.965	7.973	3.022	2.982	1.575	8.500	9.449	-	5.250	0.167	5.551	5.250
254/6T	13.180	9.448	3.645	3.631	1.693	10.000	11.417	-	6.250	0.187	6.299	6.017

Frame	AA	O	T	Hole H	2F	B	BA	N-W	ES	U	d1	S	R
143/5T	1.118"	6.724	0.603	0.343	4.000/5.000	6.496	2.250	2.250	1.417	0.875	A 3.15	0.187	0.771
182/4T	1.118"	8.557	0.661	0.406	4.500/5.500	6.299	2.750	2.750	1.969	1.125	A 3.15	0.250	0.984
213/5T	1.377"	10.144	0.761	0.406	5.500/7.000	7.953	3.500	3.380	2.480	1.375	A 4	0.313	1.203
254/6T	1.732"	12.010	0.83	0.530	8.252/10.000	11.417	4.250	4.000	2.756	1.625	A 4	0.375	1.416


Frames 143



Frames 182



Frame 213 to 256




Rolled Steel - General Purpose - Three Phase - TEFC - *continued*


Dimensions for C-Face motors

Frame	Size	AJ	AK	BD	BF	BB	AH	Angle	BF Number
143/5T	FC-149	5.874	4.500	6.449	UNC 3/8"x16	0.157	2.132	45°	4
182/4T	FC-184	7.250	8.500	8.846	UNC 1/2"x13	0.250	2.620	45°	4
213/5T	FC-184	7.250	8.500	9.401	UNC 1/2"x13	0.250	3.129	45°	4
254/6T	FC-184	7.250	8.500	11.084	UNC 1/2"x13	0.250	3.750	45°	4


Frames 143



Frames 182



Frame 213 to 254




Rolled Steel - General Purpose - Three Phase - ODP


Frame	A	AA	AB	P	2E	J	HB	HK	H1	G	D	HD1
143/5T	6.535	1.118"	5.882	6.467	5.500	1.732	1.783	2.638	-	0.120	3.500	8.622
182/4T	8.661	1.118"	6.696	8.114	7.500	1.299	2.784	2.629	-	0.167	4.500	11.441
213/5T	9.449	1.377"	7.973	9.846	8.500	1.575	2.982	3.022	-	0.167	5.250	13.764

Frame	HD2	LL	LM	O	2F	H	B	BA	N-W	ES	U	d1	R	S
143/5T	8.150	4.543	4.106	6.724	4.000/5.000	0.343	6.496	2.250	2.250	1.417	0.875	A 3.15	0.771	0.187
182/4T	-	4.563	4.090	8.557	4.500/5.500	0.406	6.299	2.750	2.750	1.969	1.125	A 3.15	0.984	0.250
213/5T	-	5.551	5.250	10.144	5.500/7.000	0.406	7.953	3.500	3.380	2.480	1.375	A 4	1.203	0.313


Frames 143



Frames 182



Frame 213 to 256







ODP – Cast Iron - Three Phase - General Purpose

NEMA FRAMES	MOUNTING				A	B	C	C WITH DRIP COVER	CH	D	G	J
	2E	2F	H	BA								
254T	10.000	8.250	0.530	4.250	11.496	9.507	20.537	22.368	1.831	6.250	0.630	1.526
254/6T		8.250				11.200	22.285	24.116				1.485
		10.000										
284T	11.000	9.500	0.530	4.750	13.780	11.032	23.158	25.028	1.870	7.000	0.787	2.496
284TS							21.783	23.653				
284/6T		9.500				12.529	24.658	26.529				
		11.000										
284/6TS		11.000					23.283	25.154				
324T	12.500	10.500	0.660	5.250	15.157	12.176	25.807	27.677	1.870	8.000	0.974	2.802
324TS							24.307	27.177				
324/6T		10.500				13.554	27.307	29.177				
		12.000										
324/6TS		10.500					25.807	27.677				
364/5T	14.000	11.250	0.660	5.875	17.165	15.323	29.725	32.186	2.461	9.000	1.181	3.524
		12.250										
364/5TS		11.250					27.600	30.061				
		12.250										
404/5T	16.000	12.250	0.810	6.625	19.921	17.866	34.100	36.482	2.382	10.000	1.181	3.937
		13.750										
404/5TS		12.250					31.100	33.482				
		13.750										
444/5T	18.000	14.500	0.810	7.500	21.260	19.737	38.108	41.199	3.091	11.000	1.181	2.944
		16.500										
444/5TS		14.500					34.358	37.449				
		16.500										

	K	O	P	P WITH PROTECTION SCREEN	P WITH DRIP COVER	T	KEYWAY			SHAFT EXTENSION		AB	HB	HH	AA	d1	BEARINGS	
							S	R	ES	N-W	U						D.E.	O.D.E.
254T	3.012	12.337	12.598	12.824	14.913	2.023	0.375	1.416	2.756	4.000	1.625	10.462	2.360	8.376	NPT1.1/2"	A4	6309-Z-C3	6209-Z-C3
254/6T	3.563													9.250				
284T	3.434	13.782	14.134	14.360	16.213	1.939	0.500	1.591	3.150	4.625	1.875	11.933	2.670	9.500			6311-Z-C3	6211-Z-C3
284TS							0.374	1.416	2.480	3.250	1.625							
284/6T	3.847						0.500	1.591	3.150	4.625	1.875			10.250				
284/6TS							0.374	1.416	2.480	3.250	1.625							
324T	3.867	15.492	15.669	15.895	17.669	2.252	1.845	3.937	5.250	2.125	13.394	3.658	10.500	NPT2"			6312-Z-C3	6212-Z-C3
324TS							1.591	2.756	3.750	1.875								
324/6T	4.359	15.492				0.500	1.845	3.937	5.250	2.125			11.250					
324/6TS							1.591	2.756	3.750	1.875								
364/5T	4.845	18.409	18.406	18.632	19.804	2.795	0.625	2.020	4.331	5.875	2.375	15.583	4.256	12.000	NPT3"	UNC3/4"	6314-C3	
364/5TS							0.500	1.591	1.969	3.750	1.875			6316-C3				
404/5T	5.654	19.409	18.504	18.604	19.803	2.795	0.750	2.449	5.512	7.250	2.875	15.583	5.256	13.500			6314-C3	
404/5TS							0.500	1.845	2.756	4.250	2.125			6319-C3				
444/5T	6.819	21.945	22.467	22.693	24.402	3.543	0.875	2.878	7.087	8.500	3.375	18.711	4.878	15.750	2xNPT3"	6314-Z-C3		
444/5TS							0.625	2.021	4.331	4.750	2.375			6314-C3	6212-Z-C3			



ODP – Cast Iron - Three Phase - General Purpose- continued

Frame 254T to 444/5TS



“C” FLANGE DIMENSIONS



NEMA	BA	AJ	AK	BD	BF		BB	BC	AH	C	HH					
FRAMES					NUMBER	TAP SIZE										
254TC	4.750	7.252	8.500	9.019	4	UNC1/2"-13	0.250	0.250	3.750	21.037	8.876					
254/6TC										22.785	8.876					
284TC	4,750	9.000	10.500	11.295					UNC1/2"-13	4.375	23.158	9.500				
284TSC										3.000	21.783					
284/6TC										4.375	24.658	10.250				
284/6TSC										3.000	23.283					
324TC						5.250				11.000	12.500	14.023	UNC5/8"-11	5.000	25.807	10.500
324TSC														3.500	24.307	
324/6TC	5.000	27.307	11.250													
324/6TSC	3.500	25.807														
364/5TC	5.875	11.000	12.500	14.095					8					5.625	29.725	12.000
364/5TSC														3.500	27.600	
404/5TC	6.625				14.095	8	7.000	34.100		13.500						
404/5TSC							4.000	31.100								
444/5TC	7.500						14.000	16.000		18.024	8.250	38.325	15.750			
444/5TSC											4.500	34.358				




ODP – Cast Iron - Three Phase - General Purpose

“D” FLANGE DIMENSIONS

NEMA	BA	AJ	AK	BD	BF		BB	C	HH	
FRAMES					NUMBER	TAP SIZE				
254TD	4.750	12.500	11.000	13.934	4	0.810	0.250	21.037	8.876	
254/6TD								22.785	9.750	
284TD				4.750					23.158	9.500
284TSD								21.783		
284/6TD								24.658	10.250	
284/6TSD								23.283		
324TD	5.250	16.000	14.000					25.807	10.500	
324TSD								24.307		
324/6TD								27.307	11.250	
324/6TSD								25.807		
364/5TD	5.875				17.633	8	0.810	0.250	29.725	12.000
364/5TSD									27.600	
404/5TD	6.625	20.000	18.000	21.571	34.100				13.500	
404/5TSD					31.100					
444/5TD	7.500				22.105				38.325	15.750
444/5TSD									34.358	



FRAME	TERMINAL BOX	
	LL	LM
254/6	7.813	7.494
284/6	8.571	8.993
324/6	8.993	9.921
364/5	10.591	11.262
404/5		
444/5	14.940	15.063



Explosion Proof - Three Phase


Frame	2E	2F	A	AA	AB	B	BA	C	D	G	Hole H	J
143T	5.500	4.000	6.457	NPT 3/4"	6.811	5.157	2.250	12.760	3.500	0.429	0.344	1.496
145T		5.000				6.142		13.752				
182T	7.500	4.500	8.661		8.240	5.945	2.750	14.862	4.500	0.787	0.406	1.890
184T		5.500				6.969		15.862				
213T	8.500		7.000	9.764	NPT 1"	9.252	7.402	3.500	17.952	5.250		0.827
215T		8.252	8.898				19.450					
254T	10.000	8.252	12.126	NPT 1 1/2"	11.063	10.000	4.250	23.175	6.250	0.817	0.531	2.520
256T		10.000				11.732		24.923				
284T	11.000	9.500	13.780		11.850	11.575	4.750	26.407	7.000	1.024		3.150
284TS		11.000						25.033				
286T						13.071		27.905				
286TS								26.531				
324T	12.500	10.500	15.157	NPT 2"	12.961	5.250	29.602	8.000	1.307	0.657	3.228	
324TS							12.000					28.102
326T		14.567										31.106
326TS							29.606					
364/5T	14.000	11.250/12.250	17.165	NPT 3"	16.654	15.394	5.875	33.701	9.000		1.480	3.150
364/5TS		16.000				12.250/13.752		19.921				
404/5T	38.074		10.000				1.812					
404/5TS	35.074											
444/5T	18.000		14.500/16.500	21.929	2xNPT 3"		21.732		20.079	7.500	43.797	11.000
444/5TS		20.000	40.047									
447T			20.984			47.339						
447TS						43.589						
449T			32.126			54.996						
449TS		51.246										
504/5T	20.000	16.000/18.000	24.724	21.850		21.969	8.500	49.445	12.500	2.146	1.250	4.724
504/5TS								46.875				
586/7T	23.000	22.000/25.000	29.528	25.787		29.921	10.00	61.389	14.500	2.492	1.181	5.236
586/7TS								54.514				

TEFC – Explosion Proof *continued*

Frames 143T to 586/7TS

Frame	K	O	P	T	Shaft end						Bearings		
					d1	ES	N-W	R	S	U	D.E.	N.D.E	
143T	1.654	7.000	7.000	*	A 4	1.575	2.250	0.765	0.187	0.875	6205 ZZ	6204 ZZ	
145T													
182T	1.969	9.421	8.909	1.772		1.969	2.750	0.984	0.250	1.125	6307 ZZ	6206 ZZ	
184T													
213T	2.165	11.156	10.709			2.480	3.375	1.203	0.313	1.375	6308 ZZ	6207 ZZ	
215T													
254T	2.559	12.352	12.224	2.087		2.756	4.000	1.406	0.375	1.625	6309 ZZ-C3	6209 ZZ-C3	
256T													
284T	2.953	14.362	14.094	2.441		3.149	4.622	1.594	0.500	1.875	6311 ZZ-C3	6211 ZZ-C3	
284TS						2.480	3.250	1.406	0.375	1.625			
286T						3.149	4.622	1.594	0.500	1.875			
286TS						2.480	3.250	1.406	0.375	1.625			
324T	3.346	15.992	15.697	2.795		3.937	5.250	1.844	0.500	2.125	6312 ZZ-C3	6212 ZZ-C3	
324TS						2.756	3.750	1.594		1.875			
326T						3.937	5.250	1.844		2.125			
326TS						2.756	3.750	1.594		1.875			
364/5T	4.134	18.898	18.583	DUNC 3/4"-10	4.330	5.874	2.019	0.625	2.375	6314 C3	6314 C3		
364/5TS					1.968	3.748	1.591	0.500	1.875				
404/5T	5.433	19.843			5.512	7.250	2.449	0.750	2.875	6217 C3			
404/5TS					2.756	4.250	1.842	0.500	2.125	6314 C3			
444/5T	5.591	23.622	24.016		3.543	7.087	8.500	2.880	0.875	3.375	6219 C3	6316 C3	
444/5TS						3.000	4.750	2.021	0.625	2.375	6314 C3	6314 C3	
447T						7.087	8.500	2.880	0.875	3.375	6319 C3	6316 C3	
447TS						3.000	4.750	2.021	0.625	2.375	6314 C3	6314 C3	
449T	7.104					7.087	8.500	2.880	0.875	3.375	6322 C3	6319 C3	
449TS						3.000	4.750	2.021	0.625	2.375	6314 C3	6314 C3	
504/5T	5.984	25.197	24.212			8.661	10.630	3.134	0.875	3.625	6319 C3	6316 C3	
504/5TS						3.000	4.750	2.021	0.625	2.375	6316 C3		
586/7T	7.874	30.428	30.709	4.291		DUNC 7/8"-9	8.661	11.625	3.312	1000.000	3.875	6322 C3	6319 C3
586/7TS						DUNC 3/4"-10	3.000	4.750	2.021	0.625	2.375	6314 C3	6314 C3

Frames 143T to 586/7TS




Fractional - Three Phase - TEFC - NEMA Premium®


Frame	2E	J	A	P	AB	AH	2F	B	BA	CH	U	N-W	Key Length	R	D
48	4.236	1.835	6.142	6.693	5.52	1.689	2.748	3.543	2.5	1.417	0.5	1.5	1.26	0.451	3
W56	4.874	1.62	6.535	6.693	5.52	2.063	3	4.016	2.75	1.417	0.625	1.874	1.417	0.517	3.5
56	4.874	1.732	6.535	7.638	5.882	2.062	3	4.016	2.75	1.377	0.625	1.874	1.417	0.517	3.5
56H	4.874	1.732	6.535	7.638	5.882	2.062	3.000/5.000	6.496	2.75	1.377	0.625	1.874	1.417	0.517	3.5

Frame	H1	G	HB	O	HD	HK	Hole H	C	LL	LM	S	AA	T	DE	NDE
48	1.22	0.075	1.559	5.83	6.354	2.65	0.343		3.835	3.697		0.881"	0.524	6203 ZZ	6202 ZZ
W56	1.22	0.12	2.055	6.33	6.854	2.65	0.343		3.835	3.697	0.187	0.881"	0.524	6203 ZZ	6202 ZZ
56	1.22	0.12	1.783	6.724	7.327	2.638	0.343		4.543	4.106	0.187	0.881"	0.603	6203 ZZ	6202 ZZ
56H	1.22	0.12	1.783	6.724	7.327	2.638	0.343		4.543	4.106	0.187	0.881"	0.603	6204 ZZ	6202 ZZ


Frame 48



Frame W56




Frame 56 - 56H




Fractional - Three Phase - TEFC - NEMA Premium® - C-Face

Frame	Type	Flange	Size	AJ	AK	BD	S	T	AH	Angle	BF Number
W56	C	C	FC-149	5.874	4.5	6.47	UNC 3/8"x16-2B	0.157	2.063	45°	4
48	C	C	FC-95	3.748	3	4.74	UNC 1/4"x20-2B	0.157	1.689	45°	4
56	C	C	FC-149	5.874	4.5	6.45	UNC 3/8"x16-2B	0.157	2.062	45°	4
56H	C	C	FC-149	5.874	4.5	6.45	UNC 3/8"x16-2B	0.157	2.062	45°	4


Frame W56



Frame 48



Frame 56/56H




Fractional - Three Phase - TEFC - Standard Efficiency


Frame	2E	J	A	P	AB	AH	2F	B	BA	CH	U	d1	N-W	Key Length	R	D
48	4.236	1.835	6.142	6.693	5.52	1.689	2.748	3.543	2.5	1.417	0.5	A 3,15	1.5	1.26	0.451	3
W56	4.874	1.62	6.535	6.693	5.52	2.063	3	4.016	2.75	1.417	0.625	A 3,15	1.874	1.417	0.517	3.5
56	4.874	1.732	6.535	7.638	5.882	2.062	3	4.016	2.75	1.377	0.625	A 3,15	1.874	1.417	0.517	3.5
56H	4.874	1.732	6.535	7.638	5.882	2.062	3.000/5.000	6.496	2.75	1.377	0.625	A 3,15	1.874	1.417	0.517	3.5

Frame	H1	G	HB	O	HD	HK	Hole H	C	LL	LM	AJ	S	AA	T	DE	NDE
48	1.22	0.075	1.559	5.83	6.354	2.65	0.343	-	3.835	3.697	5.874		0.881"	0.524	6203 ZZ	6202 ZZ
W56	1.22	0.12	2.055	6.33	6.854	2.65	0.343	-	3.835	3.697	3.748	0.187	0.881"	0.524	6203 ZZ	6202 ZZ
56	1.22	0.12	1.783	6.724	7.327	2.638	0.343	-	4.543	4.106	5.874	0.187	0.881"	0.603	6203 ZZ	6202 ZZ
56H	1.22	0.12	1.783	6.724	7.327	2.638	0.343	-	4.543	4.106	5.874	0.187	0.881"	0.603	6204 ZZ	6202 ZZ


Frame 48



Frame W56




Frame 56 - 56H




Fractional - Three Phase - TEFC - Standard Efficiency - C-Face

Frame	Type	Flange	Size	BB	AJ	AK	BD	S	T	AH	Angle	BF Number
W56	C	C	FC-149	0.157	5.874	4.5	6.47	UNC 3/8"x16-2B	0.157	2.063	45°	4
48	C	C	FC-95	0.157	3.748	3	4.74	UNC 1/4"x20-2B	0.157	1.689	45°	4
56	C	C	FC-149	0.157	5.874	4.5	6.45	UNC 3/8"x16-2B	0.157	2.062	45°	4
56H	C	C	FC-149	0.157	5.874	4.5	6.45	UNC 3/8"x16-2B	0.157	2.062	45°	4


Frame W56



Frame 48



Frame 56/56H





Fractional - Three Phase - ODP - Premium Efficiency




Frame	2E	J	A	P	AB	AH	2F	B	BA	CH	U	N-W	Key Length	R	D
48	4.236	1.835	6.142	5.709	5.52	1.689	2.748	3.543	2.5	1.22	0.5	1.5	1.26	0.451	3
W56	4.874	1.62	6.535	5.709	5.52	2.063	3	4.016	2.75	1.22	0.625	1.874	1.417	0.517	3.5
56	4.874	1.732	6.535	6.456	3.323	2.062	3	4.016	2.75	1.377	0.625	1.874	1.417	0.517	3.5
56H	4.874	1.732	6.535	6.456	5.882	2.062	3.000/5.000	6.496	2.75	1.377	0.625	1.874	1.417	0.517	3.5

Frame	H1	G	HB	O	HD	HK	Hole H	C	LL	LM	S	AA	T	DE	NDE
48	1.22	0.075	1.559	5.83	6.354	2.65	0.343		3.835	3.697		NPT 1/2"	0.524	6203 ZZ	6202 ZZ
W56	1.22	0.12	2.055	6.33	6.854	2.65	0.343		3.835	3.697	0.187	NPT 1/2"	0.524	6203 ZZ	6202 ZZ
56	1.22	0.12	1.784	6.724	6.728	2.629	0.343		4.563	4.09	0.187	NPT 1/2"	0.004	6203 ZZ	6202 ZZ
56H	1.22	0.12	1.783	6.724	6.728	2.638	0.343		4.543	4.106	0.187	NPT 1/2"	0.004	6204 ZZ	6202 ZZ




Frame 48



Frame W56




Frame 56 - 56H




Fractional - Three Phase - ODP - Premium Efficiency - C-Face

Frame	Type	Flange	Size	AJ	AK	BD	S	T	AH	Angle	BF Number
W56	C	C	FC-149	5.874	4.5	6.47	UNC 3/8"x16-2B	0.157	2.063	45°	4
48	C	C	FC-95	3.748	3	4.74	UNC 1/4"x20-2B	0.157	1.689	45°	4
56	C	C	FC-149	5.874	4.5	6.45	UNC 3/8"x16-2B	0.157	2.062	45°	4
56H	C	C	FC-149	5.874	4.5	6.45	UNC 3/8"x16-2B	0.157	2.062	45°	4


Frame 48



Frame W56



Frame 56 - 56H





Fractional - Three Phase - ODP - Standard Efficiency




Frame	2E	J	A	P	AB	AH	2F	B	BA	CH	U	N-W	Key Length	R	D
48	4.236	1.835	6.142	5.709	5.52	1.689	2.748	3.543	2.5	1.22	0.5	1.5	1.26	0.451	3
W56	4.874	1.62	6.535	5.709	5.52	2.063	3	4.016	2.75	1.22	0.625	1.874	1.417	0.517	3.5
56	4.874	1.732	6.535	6.456	3.323	2.062	3	4.016	2.75	1.377	0.625	1.874	1.417	0.517	3.5
56H	4.874	1.732	6.535	6.456	5.882	2.062	3.000/5.000	6.496	2.75	1.377	0.625	1.874	1.417	0.517	3.5

Frame	H1	G	HB	O	HD	HK	Hole H	C	LL	LM	S	AA	T	DE	NDE
48	1.22	0.075	1.559	5.83	6.354	2.65	0.343		3.835	3.697		NPT 1/2"	0.524	6203 ZZ	6202 ZZ
W56	1.22	0.12	2.055	6.33	6.854	2.65	0.343		3.835	3.697	0.187	NPT 1/2"	0.524	6203 ZZ	6202 ZZ
56	1.22	0.12	1.784	6.724	6.728	2.629	0.343		4.563	4.09	0.187	NPT 1/2"	0.004	6203 ZZ	6202 ZZ
56H	1.22	0.12	1.783	6.724	6.728	2.638	0.343		4.543	4.106	0.187	NPT 1/2"	0.004	6204 ZZ	6202 ZZ




Frame 48



Frame W56





Frame 56 - 56H






Fractional - Three Phase - ODP - Standard Efficiency - C-Face

Frame	Type	Flange	Size	AJ	AK	BD	BB	S	T	AH	Angle	BF Number
W56	C	C	FC-149	5.874	4.5	6.47	0.157	UNC 3/8"x16-2B	0.157	2.063	45°	4
48	C	C	FC-95	3.748	3	4.74	0.157	UNC 1/4"x20-2B	0.157	1.689	45°	4
56	C	C	FC-149	5.874	4.5	6.45	0.157	UNC 3/8"x16-2B	0.157	2.062	45°	4
56H	C	C	FC-149	5.874	4.5	6.45	0.157	UNC 3/8"x16-2B	0.157	2.062	45°	4




Frame 48



Frame W56



Frame 56 - 56H



Cooling Tower Motors - Three Phase - TEFC

Frame	2E	J	A	P	AB	AH	2F	B	BA	CH	U	N-W	Key Length	R	D
143T	5.5	1.437	6.457	6.85	6.26	2.125	4	5.157	2.25	0.708	0.875	2.25	1.575	0.771	3.5
143/5T	5.5	1.437	6.457	6.85	6.26	2.125	4.000/5.000	6.142	2.25	0.708	0.875	2.25	1.575	0.771	3.5
145T	5.5	1.437	6.457	6.85	6.26	2.125	5	6.142	2.25	0.708	0.875	2.25	1.575	0.771	3.5
182T	7.5	1.614	8.661	8.504	7.565	2.625	4.5	5.945	2.75	1.22	1.125	2.75	1.969	0.984	4.5
182/4T	7.5	1.614	8.661	8.504	7.565	2.625	4.500/5.500	6.969	2.75	1.22	1.125	2.75	1.969	0.984	4.5
213T	8.5	1.779	9.764	10.669	8.667	3.125	5.5	7.362	3.5	1.22	1.375	3.375	2.48	1.203	5.25
213/5T	8.5	1.779	9.764	10.669	8.667	3.125	5.500/7.000	8.858	3.5	1.22	1.375	3.375	2.48	1.203	5.25
215T	8.5	1.779	9.764	10.669	8.667	3.125	7	8.858	3.5	1.22	1.375	3.375	2.48	1.203	5.25
254T	10	2.539	12.126	12.48	10.483	3.75	8.252	10	4.25	1.85	1.625	4	2.756	1.416	6.25
254/6T	10	2.539	12.126	12.48	10.483	3.75	8.252/10.000	11.732	4.25	1.85	1.625	4	2.756	1.416	6.25
256T	10	2.539	12.126	12.48	10.483	3.75	10	11.732	4.25	1.85	1.625	4	2.756	1.416	6.25
284TS	11	3.11	13.78	13.78	11.073	3	9.5	11.575	4.75	2.244	1.625	3.25	2.48	1.416	7
284T	11	3.11	13.78	13.78	11.073	4.375	9.5	11.575	4.75	2.244	1.875	4.622	3.149	1.594	7
284/6T	11	3.11	13.78	13.78	11.073	4.375	9.500/11.000	13.071	4.75	2.244	1.875	4.622	3.149	1.594	7
284/6TS	11	3.11	13.78	13.78	11.073	3	9.500/11.000	13.071	4.75	2.244	1.625	3.25	2.48	1.416	7
324T	12.5	3.189	15.157	14.961	12.575	5	10.5	13.071	5.25	2.638	2.125	5.25	3.937	1.844	8
324TS	12.5	3.189	15.157	14.961	12.575	3.5	10.5	13.071	5.25	2.638	1.875	3.75	2.756	1.594	8
324/6TS	12.5	3.189	15.157	14.961	12.575	3.5	12	14.567	5.25	2.638	1.875	3.75	2.756	1.594	8
324/6T	12.5	3.189	15.157	14.961	12.575	5	10.500/12.000	14.567	5.25	2.638	2.125	5.25	3.937	1.844	8
326T	12.5	3.189	15.157	14.961	12.575	5	12	14.567	5.25	2.638	2.125	5.25	3.937	1.844	8
326TS	12.5	3.189	15.157	14.961	12.575	3.5	12	14.567	5.25	2.638	1.875	3.75	2.756	1.594	8
364/5T	14.016	3.15	17.165	17.914	16.016	5.625	11.260/12.244	15.512	5.875	3.189	2.375	5.874	4.33	2.019	9
364/5TS	14.016	3.15	17.165	17.914	16.016	3.5	11.260/12.244	15.512	5.875	3.189	1.875	3.748	1.968	1.591	9
404/5T	15.984	3.937	19.921	19.134	16.016	7	12.244/13.740	18.386	6.625	3.189	2.875	7.25	5.512	2.449	10
404/5TS	15.984	3.937	19.921	19.134	16.016	4	12.244/13.740	18.386	6.625	3.189	2.125	4.25	2.756	1.842	10
444/5T	18	3.937	21.929	23.583	18.57	8.25	14.500/16.500	20.315	7.5	3.583	3.375	8.5	7.087	2.88	11
444/5TS	18	3.937	21.929	23.583	18.57	4.5	14.500/16.500	20.315	7.5	3.583	2.375	4.75	3	2.021	11
445/7T	18	3.937	21.929	23.583	20.559	8.25	16.500/20.000	23.897	7.5	3.583	3.375	8.5	7.087	2.88	11
445/7TS	18	3.937	21.929	23.583	20.559	4.5	16.500/20.000	23.897	7.5	3.583	2.375	4.75	3	2.021	11
447/9T	18	3.937	21.929	23.583	20.559	8.25	20.000/25.000	31.535	7.5	3.583	3.375	8.5	7.087	2.88	11
447/9TS	18	3.937	21.929	23.583	20.559	4.5	20.000/25.000	31.535	7.5	3.583	2.375	4.75	3	2.021	11
L447/9T	18	3.937	21.929	25.866	23.72	8.25	20.000/25.000	31.535	7.5	3.583	3.375	8.5	7.087	2.88	11
L447/9TS	18	3.937	21.929	25.866	23.72	4.5	20.000/25.000	31.535	7.5	3.583	2.375	4.75	3	2.021	11
504/5T	20	4.724	24.724	25.866	20.599	10.375	16.000/18.000	24.449	8.5	3.583	3.625	10.63	8.661	3.134	12.5
504/5TS	20	4.724	24.724	25.866	20.599	4.5	16.000/18.000	24.449	8.5	3.583	2.375	4.75	3	2.021	12.5
586/7T	23	5.512	29.528	28.977	23.189	11.375	22.000/25.000	29.921	10	3.583	3.875	11.625	8.661	3.312	14.5
586/7TS	23	5.512	29.528	28.977	23.189	4.5	22.000/25.000	29.921	10	3.583	2.375	4.75	3	2.021	14.5
588/9T	23	5.512	29.528	28.977	27.44	11.375	28.000/32.000	37.98	10	3.583	3.875	11.625	8.661	3.312	14.5
588/9TS	23	5.512	29.528	28.977	27.44	4.5	28.000/32.000	37.98	10	3.583	2.375	4.75	3	2.021	14.5

continued on next page




Cooling Tower Motors - Three Phase - TEFC - continued


Frame	G	HB	O	HD	HF	HH	HK	Hole H	C	LL	LM	S	AA	T	DE	NDE
143T	0.354	1.787	7.122		3.5	4.25	2.638	0.344	12.346	4.528	4.094	0.187	NPT 3/4"		6205 2RS	6204 2RS
143/5T	0.354	1.787	7.122		3.5	4.75	2.638	0.344	13.358	4.528	4.094	0.187	NPT 3/4"		6205 2RS	6204 2RS
145T	0.354	1.787	7.122		3.5	4.75	2.638	0.344	13.358	4.528	4.094	0.187	NPT 3/4"		6205 2RS	6204 2RS
182T	0.394	2.236	9.343	11.115	4.5	5	3.15	0.406	14.86	5.512	5.236	0.25	NPT 1"	1.772	6207 2RS	6206 2RS
182/4T	0.394	2.236	9.343	11.115	4.5	5.5	3.15	0.406	15.86	5.512	5.236	0.25	NPT 1"	1.772	6207 2RS	6206 2RS
213T	0.669	2.985	10.508	12.613	5.25	6.25	3.15	0.406	18.021	5.512	5.236	0.313	NPT 1"	2.105	6308 2RS	6207 2RS
213/5T	0.669	2.985	10.508	12.613	5.25	7	3.15	0.406	19.517	5.512	5.236	0.313	NPT 1"	2.105	6308 2RS	6207 2RS
215T	0.669	2.985	10.508	12.613	5.25	7	3.15	0.406	19.517	5.512	5.236	0.313	NPT 1"	2.105	6308 2RS	6207 2RS
254T	0.827	3.061	12.598	14.685	6.565	8.376	3.976	0.531	23.213	7.815	7.48	0.375	NPT 1 1/2"	2.087	6309 2RS-C3	6209 2RS-C3
254/6T	0.827	3.061	12.598	14.685	6.565	9.25	3.976	0.531	24.945	7.815	7.48	0.375	NPT 1 1/2"	2.087	6309 2RS-C3	6209 2RS-C3
256T	0.827	3.061	12.598	14.685	6.565	9.25	3.976	0.531	24.945	7.815	7.48	0.375	NPT 1 1/2"	2.087	6309 2RS-C3	6209 2RS-C3
284TS	1.023	3.535	14.067	16.154	7	9.5	3.976	0.531	25.061	7.815	7.48	0.375	NPT 1 1/2"	2.087	6311 2RS-C3	6211 2RS-C3
284T	1.023	3.535	14.067	16.154	7	9.5	3.976	0.531	26.433	7.815	7.48	0.5	NPT 1 1/2"	2.087	6311 2RS-C3	6211 2RS-C3
284/6T	1.023	3.535	14.067	16.154	7	10.25	3.976	0.531	27.929	7.815	7.48	0.5	NPT 1 1/2"	2.087	6311 2RS-C3	6211 2RS-C3
324T	1.3	4.811	15.953	18.394	8.708	10.5	4.705	0.657	29.62	9.055	8.661	0.5	NPT 2"	2.441	6312 2RS-C3	6212 2RS-C3
324/6TS	1.3	4.811	15.953	18.394	8.708	11.25	4.705	0.657	29.616	9.055	8.661	0.5	NPT 2"	2.441	6312 2RS-C3	6212 2RS-C3
324/6T	1.3	4.811	15.953	18.394	8.708	11.25	4.705	0.657	31.116	9.055	8.661	0.5	NPT 2"	2.441	6312 2RS-C3	6212 2RS-C3
326T	1.3	4.811	15.953	18.394	8.708	11.25	4.705	0.657	31.116	9.055	8.661	0.5	NPT 2"	2.441	6312 2RS-C3	6212 2RS-C3
364/5T	1.48	4.251	17.957	21.535		11.988	6.024	0.66	34.251	10.591	11.267	0.625	NPT 3"	3.578	6314 2RS-C3	6314 2RS-C3
404/5T	1.811	5.252	19.566	23.11		13.496	6.024	0.81	39.73	10.591	11.267	0.75	NPT 3"	3.544	6316 2RS-C3	6314 2RS-C3
444/5T	1.63	5.687	22.795			15.748	5.97	0.81	44.95	12.362	12.283	0.875	2xNPT 3"		6319 C3	6316 C3

Cooling Tower Motors - Three Phase - TEFC - *continued*

Frames 143 to 213/5




Frames 182 to 213/5




Cooling Tower Motors - Three Phase - TEFC - *continued*

Frames 254 to 326



Frames 364/5 to 445/7




Cooling Tower Motors - Three Phase - TEAO

Frame	2E	J	A	P	AB	AH	2F	B	BA	CH	U	N-W	Key Length	R	D
143T	5.5	1.437	6.457	6.85	6.26	2.125	4	5.157	2.25	0.708	0.875	2.25	1.575	0.771	3.5
143/5T	5.5	1.437	6.457	6.85	6.26	2.125	4.000/5.000	6.142	2.25	0.708	0.875	2.25	1.575	0.771	3.5
145T	5.5	1.437	6.457	6.85	6.26	2.125	5	6.142	2.25	0.708	0.875	2.25	1.575	0.771	3.5
182T	7.5	1.614	8.661	8.504	7.565	2.625	4.5	5.945	2.75	1.22	1.125	2.75	1.969	0.984	4.5
182/4T	7.5	1.614	8.661	8.504	7.565	2.625	4.500/5.500	6.969	2.75	1.22	1.125	2.75	1.969	0.984	4.5
213T	8.5	1.779	9.764	10.669	8.667	3.125	5.5	7.362	3.5	1.22	1.375	3.375	2.48	1.203	5.25
213/5T	8.5	1.779	9.764	10.669	8.667	3.125	5.500/7.000	8.858	3.5	1.22	1.375	3.375	2.48	1.203	5.25
215T	8.5	1.779	9.764	10.669	8.667	3.125	7	8.858	3.5	1.22	1.375	3.375	2.48	1.203	5.25
254T	10	2.539	12.126	12.48	10.483	3.75	8.252	10	4.25	1.85	1.625	4	2.756	1.416	6.25
254/6T	10	2.539	12.126	12.48	10.483	3.75	8.252/10.000	11.732	4.25	1.85	1.625	4	2.756	1.416	6.25
256T	10	2.539	12.126	12.48	10.483	3.75	10	11.732	4.25	1.85	1.625	4	2.756	1.416	6.25
284T	11	3.11	13.78	13.78	11.073	4.375	9.5	11.575	4.75	2.244	1.875	4.622	3.149	1.594	7
284TS	11	3.11	13.78	13.78	11.073	3	9.5	11.575	4.75	2.244	1.625	3.25	2.48	1.416	7
284/6T	11	3.11	13.78	13.78	11.073	4.375	9.500/11.000	13.071	4.75	2.244	1.875	4.622	3.149	1.594	7
324T	12.5	3.189	15.157	14.961	12.575	5	10.5	13.071	5.25	2.638	2.125	5.25	3.937	1.844	8
324/6T	12.5	3.189	15.157	14.961	12.575	5	10.500/12.000	14.567	5.25	2.638	2.125	5.25	3.937	1.844	8
326T	12.5	3.189	15.157	14.961	12.575	5	12	14.567	5.25	2.638	2.125	5.25	3.937	1.844	8
364/5T	14.016	3.15	17.165	17.914	16.016	5.625	11.260/12.244	15.512	5.875	3.189	2.375	5.874	4.33	2.019	9


Frame	G	HB	O	HF	HH	HK	Hole H	C	LL	LM	S	AA	T	DE	NDE
143T	0.354	1.787	7.122	3.5	4.25	2.638	0.344	12.353	4.528	4.094	0.187	NPT 3/4"		6205 2RS	6204 2RS
143/5T	0.354	1.787	7.122	3.5	4.75	2.638	0.344	13.338	4.528	4.094	0.187	NPT 3/4"		6205 2RS	6204 2RS
145T	0.354	1.787	7.122	3.5	4.75	2.638	0.344	13.338	4.528	4.094	0.187	NPT 3/4"		6205 2RS	6204 2RS
182T	0.394	2.236	9.343	4.5	5	3.15	0.406	14.298	5.512	5.236	0.25	NPT 1"	1.772	6207 2RS	6206 2RS
182/4T	0.394	2.236	9.343	4.5	5.5	3.15	0.406	15.298	5.512	5.236	0.25	NPT 1"	1.772	6207 2RS	6206 2RS
213T	0.669	2.985	10.508	5.25	6.25	3.15	0.406	17.239	5.512	5.236	0.313	NPT 1"	2.105	6308 2RS	6207 2RS
213/5T	0.669	2.985	10.508	5.25	7	3.15	0.406	18.739	5.512	5.236	0.313	NPT 1"	2.105	6308 2RS	6207 2RS
215T	0.669	2.985	10.508	5.25	7	3.15	0.406	18.739	5.512	5.236	0.313	NPT 1"	2.105	6308 2RS	6207 2RS
254T	0.827	3.061	12.598	6.565	8.376	3.976	0.531	21.594	7.815	7.48	0.375	NPT 1 1/2"	2.087	6309 2RS-C3	6209 2RS-C3
254/6T	0.827	3.061	12.598	6.565	9.25	3.976	0.531	23.343	7.815	7.48	0.375	NPT 1 1/2"	2.087	6309 2RS-C3	6209 2RS-C3
256T	0.827	3.061	12.598	6.565	9.25	3.976	0.531	23.343	7.815	7.48	0.375	NPT 1 1/2"	2.087	6309 2RS-C3	6209 2RS-C3
284T	1.023	3.535	14.067	7	9.5	3.976	0.531	25.418	7.815	7.48	0.5	NPT 1 1/2"	2.087	6311 2RS-C3	6211 2RS-C3
284/6T	1.023	3.535	14.067	7	10.25	3.976	0.531	26.918	7.815	7.48	0.5	NPT 1 1/2"	2.087	6311 2RS-C3	6211 2RS-C3
324T	1.3	4.811	15.953	8.708	10.5	4.705	0.657	28.575	9.055	8.661	0.5	NPT 2"	2.441	6312 2RS-C3	6212 2RS-C3
324/6T	1.3	4.811	15.953	8.708	11.25	4.705	0.657	30.071	9.055	8.661	0.5	NPT 2"	2.441		
326T	1.3	4.811	15.953	8.708	11.25	4.705	0.657	30.071	9.055	8.661	0.5	NPT 2"	2.441	6312 2RS-C3	6212 2RS-C3
364/5T	1.48	4.251	17.957		11.988	6.024	0.66	29.39	10.591	11.267	0.625	NPT 3"	3.578	6314 2RS-C3	6314 2RS-C3

Cooling Tower Motors - Three Phase - TEAO - *continued*


Frame 143 to 145




Frame 182 to 213/5



Frames 254 to 326



Frames 364 to 445/7




CCP - JM - Three Phase - TEFC - Rolled Steel

Frame	2E	J	A	P	AB	AH	2F	B	BA	C	CH	U	EL	EM	EP	EQ
143/5JM	5.5	1.732	6.535	7.638	5.873	4.267	4.000/5.000	6.496	2.75		1.377	0.875	1.156	1	1.179	0.63
182/4JM	7.5	1.299	8.661	9.435	6.696	4.258	4.500/5.500	6.299	3.5		1.377	0.875	1.25	1	1.376	0.63
213/5JM	8.5	1.575	9.449	10.965	7.973	4.258	5.500/7.000	7.953	4.25		1.929	0.875	1.25	1	1.769	0.63
254/6JM	10	1.693	11.417	13.18	9.448	5.25	8.252/10.000	11.417	4.75		1.929	1.249	1.75	1.375	1.769	0.63

Frame	Key Length	ET	R	D	G	HB	O	HD	HK	Hole H	LL	LM	S	AA	T	DE	NDE
143/5JM	1.575	2.88	0.771	3.5	0.12	1.784	6.724	7.327	2.629	0.343	4.563	4.09	0.187	1.118"	0.603	6206 ZZ	6203 ZZ
182/4JM	1.575	2.88	0.771	4.5	0.167	2.784	8.557	9.218	2.629	0.406	4.563	4.09	0.187	1.118"	0.661	6207 ZZ	6205 ZZ
213/5JM	1.575	2.88	0.771	5.25	0.167	2.982	10.144	10.905	3.022	0.406	5.551	5.25	0.187	1.377"	0.761	6209 ZZ	6206 ZZ
254/6JM	2.559	3.006	1.11	6.25	0.187	3.631	12.01	12.84	3.645	0.53	6.299	6.017	0.25	1.732"	0.83	6309 Z-C3	6208 Z-C3

Frame	Type	Flange	Size	AJ	AK	BD	S	T	AH	Angle	BF Number
143/5JM	C	C	FC-149	5.874	4.5	6.45	UNC 3/8"x16	0.157	4.267	45°	4
182/4JM	C	C	FC-149	5.874	4.5	6.496	UNC 3/8"x16	0.157	4.258	45°	4
213/5JM	C	C	FC-184	7.25	8.5	9.401	UNC 1/2"x13	0.25	4.258	45°	4
254/6JM	C	C	FC-184	7.25	8.5	11.084	UNC 1/2"x13	0.25	5.25	45°	4


Frame 143/5JM




Drawings on next page

CCP - JM - Three Phase - TEFC - Rolled Steel - *continued*

Frame 182/4JM



Frames 213/5JM to 254/6JM





CCP - JM - Three Phase - TEFC - Cast Iron

Frame	2E	J	A	P	AB	AH	2F	B	BA	CH	U	d1	EL	EM	EP
143JM	5.5	1.437	6.457	7.047	6.26	4.258	4	5.157	2.56	0.719	0.874	EUNC 3/8"-16	1.156	1	1.179
143/5JM	5.5	1.437	6.457	7.047	6.26	4.258	4.000/5.000	6.142	2.56	0.719	0.874	EUNC 3/8"-16	1.156	1	1.179
145JM	5.5	1.437	6.457	7.047	6.26	4.258	5	6.142	2.56	0.719	0.874	EUNC 3/8"-16	1.156	1	1.179
182JM	7.5	1.614	8.661	8.74	7.565	4.258	4.5	5.945	2.75	1.337	0.874	EUNC 3/8"-16	1.25	1	1.376
184JM	7.5	1.614	8.661	8.74	7.565	4.258	5.5	6.969	2.75	1.337	0.874	EUNC 3/8"-16	1.25	1	1.376
182/4JM	7.5	1.614	8.661	8.74	7.565	4.258	4.500/5.500	6.969	2.75	1.337	0.874	EUNC 3/8"-16	1.25	1	1.376
213JM	8.5	1.779	9.764	10.669	8.606	4.258	5.5	7.362	3.5	1.22	0.874	EUNC 3/8"-16	1.25	1	1.77
213/5JM	8.5	1.779	9.764	10.669	8.606	4.258	5.500/7.000	8.858	3.5	1.22	0.874	EUNC 3/8"-16	1.25	1	1.77
215JM	8.5	1.779	9.764	10.669	8.606	4.258	7	8.858	3.5	1.22	0.874	EUNC 3/8"-16	1.25	1	1.77
254JM	10	2.539	12.126	12.953	10.483	5.25	8.252	10	4.25	1.85	1.249	EUNC 1/2"-13	1.75	1.375	1.75
254JM	10	2.539	12.126	12.953	10.483	5.25	8.252	10	4.25	1.85	1.249	EUNC 1/2"-13	1.75	1.375	1.75
256JM	10	2.539	12.126	12.953	10.483	5.25	10	11.732	4.25	1.85	1.249	EUNC 1/2"-13	1.75	1.375	1.75
254/6JM	10	2.539	12.126	12.953	10.483	5.25	8.252/10.000	11.732	4.25	1.85	1.249	EUNC 1/2"-13	1.75	1.375	1.75
284JM	11	3.11	13.78	14.173	11.073	5.25	9.5	11.575	4.75	2.244	1.249	EUNC 1/2"-13	1.75	1.375	2.163
284/6JM	11	3.11	13.78	14.173	11.073	5.25	9.500/11.000	13.071	4.75	2.244	1.249	EUNC 1/2"-13	1.75	1.375	2.163
286JM	11	3.11	13.78	14.173	11.073	5.25	11	13.071	4.75	2.244	1.249	EUNC 1/2"-13	1.75	1.375	2.163
324JM	12.5	3.189	15.157	15.827	12.575	5.25	10.5	13.071	5.25	2.638	1.249	EUNC 1/2"-13	1.75	1.375	2.36
324/6JM	12.5	3.189	15.157	15.827	12.575	5.25	10.500/12.000	14.567	5.25	2.638	1.249	EUNC 1/2"-13	1.75	1.375	2.36
326JM	12.5	3.189	15.157	15.827	12.575	5.25	12	14.567	5.25	2.638	1.249	EUNC 1/2"-13	1.75	1.375	2.36
364/5JM	14.016	3.15	17.165	17.914	16.016	5.25	11.260/12.244	15.512	5.875	3.189	1.249	EUNC 1/2"-13	1.75	1.375	2.756


Frame	EQ	ET	R	D	HB	O	HH	HK	Hole H	C	LL	LM	S	T	DE	NDE
143JM	0.63	2.88	0.768	3.5	1.787	7.122	4.25	2.638	0.344	14.691	4.528	4.094	0.187		6206 ZZ	6204 ZZ
143/5JM	0.63	2.88	0.767	3.5	1.787	7.122	4.75	2.638	0.344	15.675	4.528	4.094	0.187		6206 ZZ	6204 ZZ
145JM	0.63	2.88	0.767	3.5	1.787	7.122	4.75	2.638	0.344	15.675	4.528	4.094	0.187		6206 ZZ	6204 ZZ
182JM	0.63	2.88	0.768	4.5	2.236	9.343	5	3.15	0.406	16.412	5.512	5.236	0.187	1.772	6307 ZZ	6206 ZZ
184JM	0.63	2.88	0.768	4.5	2.236	9.343	5.5	3.15	0.406	17.411	5.512	5.236	0.187	1.772	6307 ZZ	6206 ZZ
182/4JM	0.63	2.88	0.768	4.5	2.236	9.343	5.5	3.15	0.406	17.411	5.512	5.236	0.187	1.772	6307 ZZ	6206 ZZ
213JM	0.63	2.88	0.768	5.25	2.985	10.508	6.25	3.15	0.406	18.852	5.512	5.236	0.187	2.105	6309 Z-C3	6207 ZZ
213/5JM	0.63	2.88	0.768	5.25	2.985	10.508	7	3.15	0.406	20.392	5.512	5.236	0.187	2.105	6309 Z-C3	6207 ZZ
215JM	0.63	2.88	0.768	5.25	2.985	10.508	7	3.15	0.406	20.392	5.512	5.236	0.187	2.105	6309 Z-C3	6207 ZZ
254JM	0.63	3.006	1.11	6.25	3.061	12.598	8.376	3.976	0.531	24.478	7.815	7.48	0.25	2.087	6309 C3	6209 C3
254JM	0.63	3.006	1.11	6.25	3.061	12.598	8.376	3.976	0.531	24.478	7.815	7.48	0.25	2.087	6309 C3	6209 C3
256JM	0.63	3.006	1.11	6.25	3.061	12.598	9.25	3.976	0.531	26.226	7.815	7.48	0.25	2.087	6309 C3	6209 C3
254/6JM	0.63	3.006	1.11	6.25	3.061	12.598	9.25	3.976	0.531	26.226	7.815	7.48	0.25	2.087	6309 C3	6209 C3
284JM	0.63	3.006	1.11	7	3.535	14.067	9.5	3.976	0.531	27.165	7.815	7.48	0.25	2.087	6311 C3	6211 C3
284/6JM	0.63	3.006	1.11	7	3.535	14.067	10.25	3.976	0.531	28.7	7.815	7.48	0.25	2.087	6311 C3	6211 C3
286JM	0.63	3.006	1.11	7	3.535	14.067	10.25	3.976	0.531	28.7	7.815	7.48	0.25	2.087	6311 C3	6211 C3
324JM	0.63	3.006	1.11	8	4.811	15.953	10.5	4.705	0.657	28.149	9.055	8.661	0.25	2.441	6312 C3	6212 C3
324/6JM	0.63	3.006	1.11	8	4.811	15.953	11.25	4.705	0.657	29.645	9.055	8.661	0.25	2.441	6312 C3	6212 C3
326JM	0.63	3.006	1.11	8	4.811	15.953	11.25	4.705	0.657	29.645	9.055	8.661	0.25	2.441	6312 C3	6212 C3
364/5JM	0.63	3.006	1.11	9	4.251	17.716	11.988	6.024	0.66	33.832	10.591	11.267	0.25	3.819	6314 C3	6314 C3

continued on next page


CCP - JM - Three Phase - TEFC - Cast Iron - *continued*

Frame	Type	Flange	Size	AJ	AK	BD	S	T	AH	Angle	BF Number
143JM	C	C	FC-149	5.874	4.5	6.496	UNC 3/8"x16	0.157	4.258	45°	4
145JM	C	C	FC-149	5.874	4.5	6.496	UNC 3/8"x16	0.157	4.258	45°	4
143/5JM	C	C	FC-149	5.874	4.5	6.496	UNC 3/8"x16	0.157	4.258	45°	4
182JM	C	C	FC-149	5.874	4.5	6.496	UNC 3/8"x16	0.157	4.258	45°	4
184JM	C	C	FC-149	5.874	4.5	6.496	UNC 3/8"x16	0.157	4.258	45°	4
182/4JM	C	C	FC-149	5.874	4.5	6.496	UNC 3/8"x16	0.157	4.258	45°	4
213JM	C	C	FC-184	7.252	8.5	8.858	UNC 1/2"x13	0.248	4.258	45°	4
213/5JM	C	C	FC-184	7.252	8.5	8.858	UNC 1/2"x13	0.248	4.258	45°	4
215JM	C	C	FC-184	7.252	8.5	8.858	UNC 1/2"x13	0.248	4.258	45°	4
254JM	C	C	FC-184	7.252	8.5	8.858	UNC 1/2"x13	0.248	5.25	45°	4
256JM	C	C	FC-184	7.252	8.5	8.858	UNC 1/2"x13	0.248	5.25	45°	4
254/6JM	C	C	FC-184	7.252	8.5	8.858	UNC 1/2"x13	0.248	5.25	45°	4
284JM	C	C	FC-279	11	12.5	13.593	UNC 5/8"x11	0.248	5.25	45°	4
286JM	C	C	FC-279	11	12.5	13.593	UNC 5/8"x11	0.248	5.25	45°	4
284/6JM	C	C	FC-279	11	12.5	13.593	UNC 5/8"x11	0.248	5.25	45°	4
324JM	C	C	FC-279	11	12.5	13.593	UNC 5/8"x11	0.248	5.25	45°	4
326JM	C	C	FC-279	11	12.5	13.593	UNC 5/8"x11	0.248	5.25	45°	4
324/6JM	C	C	FC-279	11	12.5	13.593	UNC 5/8"x11	0.248	5.25	45°	4
364/5JM	C	C	FC-279	11	12.5	15.562	UNC 5/8"x11	0.248	5.25	45°	8


Frames 143JM to 215JM



Frames 254JM to 326JM



Frame 364/5JM




CCP - JP - Three Phase - TEFC - Rolled Steel

Frame	2E	J	A	P	AB	AH	2F	B	BA	CH	U	d1	EL	EM	EP
143/5JP	5.5	1.732	6.535	7.638	5.873	7.319	4.000/5.000	6.496	2.75	1.377	0.875	EUNC 3/8"-16	1.156	1	1.179
182/4JP	7.5	1.299	8.661	9.435	6.696	7.319	4.500/5.500	6.299	3.5	1.377	0.875	EUNC 3/8"-16	1.25	1	1.376
213/5JP	8.5	1.575	9.449	10.965	7.973	8.13	5.500/7.000	7.953	4.25	1.929	1.25	EUNC 1/2"-13	1.75	1.375	1.769
254/6JP	10	1.693	11.417	13.18	9.448	8.13	8.252/10.000	11.417	4.75	1.929	1.249	EUNC 1/2"-13	1.75	1.375	1.769

Frame	Key Length	ET	Width	R	D	G	HB	O	HK	Hole H	LL	LM	S	AA	T	DE	NDE
143/5JP	1.654	5.941	0.187	0.771	3.5	0.12	1.784	6.724	2.629	0.343	4.563	4.09	0.187	1.118"	0.603	6206 ZZ	6203 ZZ
182/4JP	1.654	5.941	0.187	0.771	4.5	0.167	2.784	8.557	2.629	0.406	4.563	4.09	0.187	1.118"	0.661	6207 ZZ	6205 ZZ
213/5JP	2.56	5.886	0.25	1.11	5.25	0.167	2.982	10.144	3.022	0.406	5.551	5.25	0.25	1.377"	0.761	6209 ZZ	6206 ZZ
254/6JP	2.559	5.886	0.25	1.11	6.25	0.187	3.631	12.01	3.645	0.53	6.299	6.017	0.25	1.732"	0.83	6309 Z-C3	6208 Z-C3


Frame	Type	Flange	Size	BB	AJ	AK	BD	S	T	AH	Angle	BF Number
143/5JP	C	C	FC-149	0.157	5.874	4.5	6.45	UNC 3/8"x16	0.157	7.319	45°	4
182/4JP	C	C	FC-149	0.157	5.874	4.5	6.496	UNC 3/8"x16	0.138	7.319	45°	4
213/5JP	C	C	FC-184	0.25	7.25	8.5	9.401	UNC 1/2"x13	0.25	8.13	45°	4
254/6JP	C	C	FC-184	0.25	7.25	8.5	11.084	UNC 1/2"x13	0.25	8.13	45°	4

Frames 143/5JP




CCP - JP - Three Phase - TEFC - Rolled Steel - *continued*

Frames 182/4JP



Frames 213-254/6JP



CCP - JP - Three Phase - TEFC - Cast Iron


Frame	2E	J	A	P	AB	AH	2F	B	BA	CH	U	EL	EM	EP	EQ	Key Length
143JP	5.5	1.437	6.457	7.047	6.26	7.319	4	5.157	2.56	0.719	0.874	1.156	1	1.179	1.563	1.654
143/5JP	5.5	1.437	6.457	7.047	6.26	7.319	4.000/5.000	6.142	2.56	0.719	0.874	1.156	1	1.179	1.563	1.654
145JP	5.5	1.437	6.457	7.047	6.26	7.319	5	6.142	2.56	0.719	0.874	1.156	1	1.179	1.563	1.654
182JP	7.5	1.614	8.661	8.74	7.565	7.319	4.5	5.945	2.75	1.337	0.874	1.25	1	1.376	1.563	1.575
182/4JP	7.5	1.614	8.661	8.74	7.565	7.319	4.500/5.500	6.969	2.75	1.337	0.874	1.25	1	1.376	1.563	1.575
213JP	8.5	1.779	9.764	10.669	8.606	8.13	5.5	7.362	3.5	1.22	1.249	1.75	1.375	1.77	2.382	2.48
213/5JP	8.5	1.779	9.764	10.669	8.606	8.13	5.500/7.000	8.858	3.5	1.22	1.249	1.75	1.375	1.77	2.382	2.48
215JP	8.5	1.779	9.764	10.669	8.606	8.13	7	8.858	3.5	1.22	1.249	1.75	1.375	1.77	2.382	2.48
254JP	10	2.539	12.126	12.953	10.483	8.13	8.252	10	4.25	1.85	1.249	1.75	1.375	1.77	2.382	2.48
254/6JP	10	2.539	12.126	12.953	10.483	8.13	8.252/10.000	11.732	4.25	1.85	1.249	1.75	1.375	1.77	2.382	2.48
256JP	10	2.539	12.126	12.953	10.483	8.13	10	11.732	4.25	1.85	1.249	1.75	1.375	1.77	2.382	2.48
284JP	11	3.11	13.78	14.173	11.073	8.13	9.5	11.575	4.75	2.244	1.249	1.75	1.375	2.163	2.382	2.48
284/6JP	11	3.11	13.78	14.173	11.073	8.13	9.500/11.000	13.071	4.75	2.244	1.249	1.75	1.375	2.163	2.382	2.48
324JP	12.5	3.189	15.157	15.827	12.575	8.13	10.5	13.071	5.25	2.638	1.249	1.75	1.375	2.36	2.402	2.48
326JP	12.5	3.189	15.157	15.827	12.575	8.13	12	14.567	5.25	2.638	1.249	1.75	1.375	2.36	2.402	2.48
324/6JP	12.5	3.189	15.157	15.827	12.575	8.13	10.500/12.000	14.567	5.25	2.638	1.249	1.75	1.375	2.36	2.402	2.48
364/5JP	14.016	3.15	17.165	17.914	16.016	8.13	11.260/12.244	15.512	5.875	3.189	1.624	2.125	1.75	2.756	2.382	2.48
404/5JP	15.984	3.937	19.921	19.134	16.016	8.13	12.244/13.740	18.386	6.625	3.189	1.624	2.125	1.75	2.756	2.382	2.48

Frame	ET	R	D	G	HB	O	HH	HK	Hole H	C	LL	LM	S	AA	DE	NDE
143JP	5.941	0.768	3.5	0.354	1.787	7.122	4.25	2.638	0.344	17.752	4.528	4.094	0.187	NPT 3/4"	6206 ZZ	6204 ZZ
143/5JP	5.941	0.768	3.5	0.354	1.787	7.122	4.75	2.638	0.344	18.736	4.528	4.094	0.187	NPT 3/4"	6206 ZZ	6204 ZZ
145JP	5.941	0.768	3.5	0.354	1.787	7.122	4.75	2.638	0.344	18.736	4.528	4.094	0.187	NPT 3/4"	6206 ZZ	6204 ZZ
182JP	5.941	0.768	4.5	0.394	2.236	9.343	5	3.15	0.406	19.475	5.512	5.236	0.187	NPT 1"	6307 ZZ	6206 ZZ
182/4JP	5.941	0.768	4.5	0.394	2.236	9.343	5.5	3.15	0.406	20.475	5.512	5.236	0.187	NPT 1"	6307 ZZ	6206 ZZ
213JP	5.886	1.11	5.25	0.669	2.985	10.508	6.25	3.15	0.406	22.804	5.512	5.236	0.25	NPT 1"	6309 Z-C3	6207 ZZ
213/5JP	5.886	1.11	5.25	0.669	2.985	10.508	7	3.15	0.406	24.264	5.512	5.236	0.25	NPT 1"	6309 Z-C3	6207 ZZ
215JP	5.886	1.11	5.25	0.669	2.985	10.508	7	3.15	0.406	24.264	5.512	5.236	0.25	NPT 1"	6309 Z-C3	6207 ZZ
254JP	5.886	1.11	6.25	0.827	3.061	12.598	8.376	3.976	0.531	27.358	7.815	7.48	0.25	NPT 1 1/2"	6309 C3	6209 C3
254/6JP	5.886	1.11	6.25	0.827	3.061	12.598	9.25	3.976	0.531	29.106	7.815	7.48	0.25	NPT 1 1/2"	6309 C3	6209 C3
256JP	5.886	1.11	6.25	0.827	3.061	12.598	9.25	3.976	0.531	29.106	7.815	7.48	0.25	NPT 1 1/2"	6309 C3	6209 C3
284JP	5.886	1.11	7	1.023	3.535	14.067	9.5	3.976	0.531	30.079	7.815	7.48	0.25	NPT 1 1/2"	6311 C3	6211 C3
284/6JP	5.886	1.11	7	1.023	3.535	14.067	10.25	3.976	0.531	31.575	7.815	7.48	0.25	NPT 1 1/2"	6311 C3	6211 C3
324JP	5.906	1.11	8	1.3	4.811	15.953	10.5	4.705	0.657	32.525	9.055	8.661	0.25	NPT 2"	6312 C3	6212 C3
326JP	5.906	1.11	8	1.3	4.811	15.953	11.25	4.705	0.657	34.021	9.055	8.661	0.25	NPT 2"	6312 C3	6212 C3
324/6JP	5.906	1.11	8	1.3	4.811	15.953	11.25	4.705	0.657	34.021	9.055	8.661	0.25	NPT 2"	6312 C3	6212 C3
364/5JP	5.886	1.413	9	1.48	4.251	17.716	11.988	6.024	0.66	35.916	10.591	11.267	0.375	NPT 3"	6314 C3	6314 C3
404/5JP	5.886	1.413	10	1.811	5.252	19.566	13.496	6.024	0.81	38.911	10.591	11.267	0.375	NPT 3"	6314 C3	6314 C3

CCP - JP - Three Phase - TEFC - Cast Iron - *continued*

Frame	Type	Flange	Size	AJ	AK	BD	S	T	AH	Angle	BF Number
143JP	C	C	FC-149	5.874	4.5	6.496	UNC 3/8"x16	0.157	7.319	45°	4
143/5JP	C	C	FC-149	5.874	4.5	6.496	UNC 3/8"x16	0.157	7.319	45°	4
145JP	C	C	FC-149	5.874	4.5	6.496	UNC 3/8"x16	0.157	7.319	45°	4
182JP	C	C	FC-149	5.874	4.5	6.496	UNC 3/8"x16	0.157	7.319	45°	4
182/4JP	C	C	FC-149	5.874	4.5	6.496	UNC 3/8"x16	0.157	7.319	45°	4
213JP	C	C	FC-184	7.252	8.5	8.858	UNC 1/2"x13	0.248	8.13	45°	4
213/5JP	C	C	FC-184	7.252	8.5	8.858	UNC 1/2"x13	0.248	8.13	45°	4
215JP	C	C	FC-184	7.252	8.5	8.858	UNC 1/2"x13	0.248	8.13	45°	4
254JP	C	C	FC-184	7.252	8.5	8.858	UNC 1/2"x13	0.248	8.13	45°	4
254/6JP	C	C	FC-184	7.252	8.5	8.858	UNC 1/2"x13	0.248	8.13	45°	4
256JP	C	C	FC-184	7.252	8.5	8.858	UNC 1/2"x13	0.248	8.13	45°	4
284JP	C	C	FC-279	11	12.5	13.593	UNC 5/8"x11	0.248	8.13	45°	4
284/6JP	C	C	FC-279	11	12.5	13.593	UNC 5/8"x11	0.248	8.13	45°	4
324JP	C	C	FC-279	11	12.5	13.593	UNC 5/8"x11	0.248	8.13	45°	4
326JP	C	C	FC-279	11	12.5	13.593	UNC 5/8"x11	0.248	8.13	45°	4
324/6JP	C	C	FC-279	11	12.5	13.593	UNC 5/8"x11	0.248	8.13	45°	4
364/5JP	C	C	FC-279	11	12.5	15.562	UNC 5/8"x11	0.248	8.13	45°	8
404/5JP	C	C	FC-279	11	12.5	15.562	UNC 5/8"x11	0.248	8.13	45°	8


Frames 143JP to 213/5JP




Drawings on next page

CCP - JP - Three Phase - TEFC - Cast Iron - *continued*

Frames 254JP to 326JP



Frames 364/5JP to 404/5JP



CCP - JM - Three Phase - ODP - Rolled Steel

Frame	2E	J	A	P	AB	AH	2F	B	BA	CH	U	EL	EM	EP	EQ
143/5JM	5.5	1.732	6.535	6.467	5.873	4.267	4.000/5.000	6.496	2.75	1.377	0.8745	1.156	1	1.179	0.63
182/4JM	7.5	1.299	8.661	8.114	6.696	4.258	4.500/5.500	6.299	3.5	1.377	0.8745	1.25	1	1.376	0.63
213/5JM	8.5	1.575	9.449	9.846	7.973	4.258	5.500/7.000	7.953	4.25	1.929	0.8745	1.25	1	1.769	0.63
254/6JM	10	1.693	11.417	11.558	9.448	5.25	8.252/10.000	11.417	4.75	1.929	1.249	1.75	1.375	1.769	0.63

Frame	ET	R	D	G	HB	O	HD	HK	Hole H	C	LL	LM	S	AA	DE	NDE
143/5JM	2.88	0.771	3.5	0.12	1.784	6.724	6.728	2.629	0.343		4.563	4.09	0.187	1.118"	6206 ZZ	6203 ZZ
182/4JM	2.88	0.771	4.5	0.167	2.784	8.557	8.557	2.629	0.406		4.563	4.09	0.187	1.118"	6207 ZZ	6205 ZZ
213/5JM	2.88	0.771	5.25	0.167	2.982	10.144	10.173	3.022	0.406		5.551	5.25	0.187	1.377"	6209 ZZ	6206 ZZ
254/6JM	3.006	1.11	6.25	0.187	3.631	12.01	12.029	3.645	0.53		6.299	6.017	0.25	1.732"	6309 Z-C3	6208 Z-C3

Frame	Type	Flange	Size	AJ	AK	BD	S	T	AH	Angle	BF Number
143/5JM	C	C	FC-149	5.874	4.5	6.45	UNC 3/8"x16	0.157	4.267	45°	4
182/4JM	C	C	FC-149	5.874	4.5	6.496	UNC 3/8"x16	0.138	4.258	45°	4
213/5JM	C	C	FC-184	7.25	8.5	9.401	UNC 1/2"x13	0.25	4.258	45°	4
254/6JM	C	C	FC-184	7.25	8.5	11.084	UNC 1/2"x13	0.25	5.25	45°	4

CCP - JP - Three Phase - ODP - Rolled Steel


Frame	2E	J	A	P	AB	AH	2F	B	BA	CH	U	EL	EM	EP	EQ
143/5JP	5.5	1.732	6.535	6.467	5.873	7.319	4.000/5.000	6.496	2.75	1.377	0.875	1.156	1	1.179	1.563
182/4JP	7.5	1.299	8.661	8.114	6.696	7.319	4.500/5.500	6.299	3.5	1.377	0.875	1.25	1	1.376	1.563
213/5JP	8.5	1.575	9.449	9.846	7.973	8.13	5.500/7.000	7.953	4.25	1.929	1.25	1.75	1.375	1.769	2.374
254/6JP	10	1.693	11.417	11.558	9.448	8.13	8.252/10.000	11.417	4.75	1.929	1.249	1.75	1.375	1.769	2.382

Frame	Key Length	ET	R	D	G	HB	O	HD	HK	Hole H	C	LL	LM	S	AA	DE	NDE
143/5JP	1.654	5.941	0.771	3.5	0.12	1.784	6.724	6.728	2.629	0.343	-	4.563	4.09	0.187	1.118"	6206 ZZ	6203 ZZ
182/4JP	1.654	5.941	0.771	4.5	0.167	2.784	8.557	8.557	2.629	0.406	-	4.563	4.09	0.187	1.118"	6207 ZZ	6205 ZZ
213/5JP	2.56	5.886	1.11	5.25	0.167	2.982	10.144	10.173	3.022	0.406	-	5.551	5.25	0.25	1.377"	6209 ZZ	6206 ZZ
254/6JP	2.559	5.886	1.11	6.25	0.187	3.631	12.01	12.029	3.645	0.53		6.299	6.017	0.25	1.732"	6309 Z-C3	6208 Z-C3


Frame	Type	Flange	Size	AJ	AK	BD	S	T	AH	Angle	BF Number
143/5JP	C	C	FC-149	5.874	4.5	6.45	UNC 3/8"x16	0.157	7.319	45°	4
182/4JP	C	C	FC-149	5.874	4.5	6.496	UNC 3/8"x16	0.138	7.319	45°	4
213/5JP	C	C	FC-184	7.25	8.5	9.401	UNC 1/2"x13	0.25	8.13	45°	4
254/6JP	C	C	FC-184	7.25	8.5	11.084	UNC 1/2"x13	0.25	8.13	45°	4

Drawings on next page

Frame 143




Frame 182



CCP - JM and JP - Three Phase - ODP - Rolled Steel - *continued*

Frame 213 to 256



CCP - JM and JP - Three Phase - ODP - Cast Iron


NEMA FRAMES	MOUNTING				A	B	D	G	J	K	O	P	P WITH PROTECTION SCREEN	P WITH DRIP COVER
	2E	2F	H	BA										
254 JM/JP	10.000	8.250	0.530	4.980	11.496	9.507	6.250	0.630	1.526	3.012	12.337	12.598	12.824	14.913
254/6 JM/JP		8.250				11.200			1.485	3.563				
		10.000												
284 JM/JP	11.000	9.500	0.530	5.000	13.780	11.032	7.000	0.787	2.496	3.434	13.782	14.134	14.360	16.213
284/6 JM/JP		9.500				12.529			3.847					
		11.000												
324 JM/JP	12.500	10.500	0.660	5.500	15.157	12.176	8.000	0.974	2.802	3.867	15.492	15.669	15.895 15.895	17.669
324/6 JM/JP		10.500				13.554			4.359					
		12.000												
364/5 JM/JP	14.000	11.250	0.810	5.875	17.165	15.323	9.000	1.181	3.524	4.845	18.409	18.406	18.632	19.804
		12.250												
404/5 JP	16.000	12.250							0.810	6.625	19.921			
		13.750												

NEMA FRAMES	T	AB	HB	HH	CH	AA	BEARINGS		NEMA "C" FLANGE						
							D.E.	O.D.E.	AJ	AK	BB	BD	BF		
													Qty.	Tap Size	Bolt Depth
254 JM/JP	2.023	10.462	2.360	9.106	1.831	NPT1.1/2"	6309-Z-C3	6209-Z-C3	7.252	8.500		9.019	4.000	UNC1/2"x13	0.787
254/6 JM/JP				9.980											
284 JM/JP	1.939	11.933	2.670	9.750	1.870	NPT2"	6311-Z-C3	6211-Z-C3	11.000	12.500	0.250	14.023	4.000	UNC5/8"x11	0.945
284/6 JM/JP				10.500											
324 JM/JP	2.252	13.394	3.658	10.750	1.870	NPT2"	6312-Z-C3	6212-Z-C3	11.000	12.500	0.250	14.023	4.000	UNC5/8"x11	0.945
324/6 JM/JP	2.265			11.500											
364/5 JM/JP	2.795	15.583	4.256	12.000	2.461	NPT3"	6314-C3	6212-Z-C3	11.000	12.500	0.250	14.095	8.000	UNC5/8"x11	0.945
404/5 JP			5.256	13.500	2.382		6316-C3								

NEMA	SHAFT END - TYPE JM														C
FRAMES	LENGTHS				DIAMETERS				KEYWAY			THREADED HOLE			JM
	AH	ER	EQ	ET	U	EM	EL	EP	S	R	ES	d1 (UNC)	T1	T2	
254 JM	5.250	5.250	0.630	3.002	1.250	1.375	1.750	1.764	0.250	1.110	2.480	1/2"x13-2B	1.100	1.500	22.517
254/6 JM															24.264
284 JM															24.033
284/6 JM								2.157							25.533
324 JM															26.057
324/6 JM								2.354							27.557
364/5 JM		5.500						2.753							29.270

NEMA	SHAFT END - TYPE JP														C
FRAMES	LENGTHS				DIAMETERS				KEYWAY			THREADED HOLE			JP
	AH	ER	EQ	ET	U	EM	EL	EP	S	R	ES	d1 (UNC)	T1	T2	
254 JP	8.130	8.380	2.382	5.886	1.250	1.375	1.750	1.764	0.250	1.110	2.480	1/2"x13-2B	1.100	1.500	25.398
254/6 JP															27.146
284 JP								2.157							26.913
284/6 JP															28.413
324 JP															28.937
324/6 JP								2.354							30.437
364/5 JP					1.625	1.750	2.125	2.753	0.375	1.413					32.150
404/5 JP															35.152

CCP - JM and JP - Three Phase - ODP - Cast Iron



IEC Metric Motors - Cast Iron Frames

Frame	A	AA	AB	AC	AD	B	BB	C	CA	D	D1	D2	DA	E	EA	ES	F
63	100	25.5	116	125	123	80	95	40	78	11j6	EM4	EM3	9j6	23	20	14	4
71	112	28.5	132	141	131	90	113.5	45	88	14j6	DM5	EM4	11j6	30	23	18	5
80	125	30.5	149	159	140	100	125.5	50	93	19j6	DM6	DM4	14j6	40	30	28	6
90S	140	37	164	184	159	100	131	56	135	24j6	DM8	DM6	16j6	50	40	36	8
90L	140	37	164	184	159	125	156	56	135	24j6	DM8	DM6	16j6	50	40	36	8
L90S	140	37	164	184	159	100	131	56	135	24j6	DM8	DM6	16j6	50	40	36	8
L90L	140	37	164	184	159	125	156	56	135	24j6	DM8	DM6	16j6	50	40	36	8
100L	160	40	188	206	169	140	173	63	118	28j6	DM10	DM8	22j6	60	50	45	8
L100L	160	40	188	206	169	140	173	63	162	28j6	DM10	DM8	22j6	60	50	45	8
112M	190	40.5	220	215	192	140	177	70	128	28j6	DM10	DM8	24j6	60	50	45	8
L112M	190	40.5	220	215	192	140	177	70	158	28j6	DM10	DM8	24j6	60	50	45	8
132S	216	45.5	248	274	220	140	187	89	150	38k6	DM12	DM10	28j6	80	60	63	10
132M	216	45.5	248	274	220	178	225	89	150	38k6	DM12	DM10	28j6	80	60	63	10
132M/L	216	45.5	248	274	220	178/203	250	89	150	38k6	DM12	DM10	28j6	80	60	63	10
160M	254	64	308	329	266	210	254	108	174	42k6	DM16	DM16	42k6	110	110	80	12
160L	254	64	308	329	266	254	298	108	174	42k6	DM16	DM16	42k6	110	110	80	12
180M	279	78	350	360	281	241	294	121	200	48k6	DM16	DM16	48k6	110	110	80	14
180L	279	78	350	360	281	279	332	121	200	48k6	DM16	DM16	48k6	110	110	80	14
200L	318	82	385	402	319	305	370	133	222	55m6	DM20	DM20	48k6	110	110	80	16
225S/M	356	80	436	455	410	286/311	412	149	319/294	60m6	DM20	DM20	60m6	140	140	125	18
250S/M	406	100	506	486	410	311/349	467	168	354/316	65m6	DM20	DM20	60m6	140	140	125	18
280S/M	457	100	557	599	445	368/419	517	190	385/334	75m6	DM20	DM20	65m6	140	140	125	20
315S/M	508	120	630	657	525	406/457	621	216	443	80m6	DM20	DM20	65m6	170	140	160	22
315L	508	120	630	657	589	508	752	216	502	80m6	DM20	DM20	65m6	170	140	160	22
355M/L	610	140	750	736	609	560/630	760	254	483/413	100m6	DM24	DM20	80m6	210	170	200	28


Frame	FA	G	GB	GD	GF	H	HA	HB	HC	HD	HF	HH	HK	K	L	LC	LL	LM	S1	DE	NDE
63	3	8.5	7.2	4	3	63	7	25.5	130	156.3	68.5	80	59	7	216	241	108.5	99	2xM20x1,5	6201 ZZ	6201 ZZ
71	4	11	8.5	5	4	71	7	33	145	163.8	76	90	59	7	250	276	108.5	99	2xM20x1,5	6202 ZZ	6202 ZZ
80	5	15.5	11	6	5	80	8	43.5	163	174.3	87	100	59	10	277	313	108.5	99	2xM20x1,5	6204 ZZ	6203 ZZ
90S	5	20	13	7	5	90	9	45	182	182.4	90	106	67	10	305	350	115	104	2xM25x1,5	6205 ZZ	6204 ZZ
90L	5	20	13	7	5	90	9	45	182	182.4	90	118.5	67	10	329	375	115	104	2xM25x1,5	6205 ZZ	6204 ZZ
L90S	5	20	13	7	5	90	9	45	182	182.4	90	106	67	10			115	104	2xM25x1,5	6205 ZZ	6204 ZZ
L90L	5	20	13	7	5	90	9	45	182	182.4	90	118.5	67	10			115	104	2xM25x1,5	6205 ZZ	6204 ZZ
100L	6	24	18.5	7	6	100	10	61.5	205	244	106.4	133	67	12	376	431	115	104		6206 ZZ	6205 ZZ
L100L	6	24	18.5	7	6	100	10	61.5	205	244	106.4	133	67	12			115	104		6206 ZZ	6205 ZZ
112M	8	24	20	7	7	112	10	54.5	226	280	112	140	80	12	394	448	140	133	2xM32x1,5	6207 ZZ	6206 ZZ
L112M	8	24	20	7	7	112	10	54.5	226	280	112	140	80	12			140	133	2xM32x1,5	6207 ZZ	6206 ZZ
132S	8	33	24	8	7	132	16	75	274	319	132	159	80	12	452	519	140	133	2xM32x1,5	6308 ZZ	6207 ZZ
132M	8	33	24	8	7	132	16	75	274	319	132	178	80	12	489	557	140	133	2xM32x1,5	6308 ZZ	6207 ZZ
132M/L	8	33	24	8	7	132	16	75	274	319	132	190.5	80	12	515	582	140	133	2xM32x1,5	6308 ZZ	6207 ZZ
160M	12	37	37	8	8	160	22	79	331	374	168	213	101	14.5	598	712	198.5	190	2xM40x1,5	6309 C3	6209 C3
160L	12	37	37	8	8	160	22	79	331	374	168	235	101	14.5	642	756	198.5	190	2xM40x1,5	6309 C3	6209 C3
180M	14	42.5	42.5	9	9	180	28	92	366	413	180	241.5	101	14.5	664	782	198.5	190	2xM40x1,5	6311 C3	6211 C3
180L	14	42.5	42.5	9	9	180	28	92	366	413	180	260.5	101	14.5	702	820	198.5	190	2xM40x1,5	6311 C3	6211 C3
200L	14	49	42.5	10	9	200	30	119	407	464	218	285.5	119.5	18.5	767	880	230	220	2xM50x1,5	6312 C3	6212 C3
225S/M	18	53	53	11	11	225	34	254	453	541	421	212	153	18.5	886	1034	269	285	2xM50x1,5	6314 C3	6314 C3
250S/M	18	58	53	11	11	250	43	297	493	583	463	214	153	24	965	1113	269	285	2xM63x1,5	6314 C3	6314 C3
280S/M	18	67.5	58	12	11	280	42	386	580	700	572	266	151	24	1071	1223	314	312	2xM63x1,5	6316 C3	6316 C3
315S/M	18	71	58	14	11	315	48	386	644	768	592	264	176	28	1274	1426	379	382	2xM63x1,5	6319 C3	6316 C3
315L	18	71	58	14	11	315	48	336	644	774	575	284	220	28	1389	1536	404	436	2xM63x1,5	6319 C3	6316 C3
355M/L	22	90	71	16	14	355	50	461	723	898	700	339	220	28	1482	1677	404	436	2xM63x1,5	6322 C3	6319 C3

Dimensions measured in millimeters.


Drawings on next page

IEC Metric Motors - Cast Iron Frames - *continued*


Frames 63 to 132M/L



Frames 160L to 200L



Frames 225S/M to 355M/L




IEC Metric Motors - Cast Iron Frames - Additional Flange Detail

Frame	Type	Flange	Size	LA	M	N	P	S	T	Angle	Holes
63	C	FC	FC-95	4.5	95.2	76.2	143	UNC 1/4"x20	4	45°	4
63	C	C-90	C-90	9.5	75	60	90	M5	2.5	45°	4
71	C	FC	FC-95	10	95.2	76.2	143	UNC 1/4"x20	4	45°	4
71	C	C-105	C-105	8	85	70	105	M6	2.5	45°	4
80	C	FC	FC-95	10	95.2	76.2	143	UNC 1/4"x20	4	45°	4
80	C	C-120	C-120	10.5	100	80	120	M6	3	45°	4
90S	C	FC	FC-149	15	149.2	114.3	165	UNC 3/8"x16	4	45°	4
90S	C	C-140	C-140	10.5	115	95	140	M8	3	45°	4
90L	C	FC	FC-149	15	149.2	114.3	165	UNC 3/8"x16	4	45°	4
90L	C	C-140	C-140	10.5	115	95	140	M8	3	45°	4
100L	C	FC	FC-149	12	149.2	114.3	165	UNC 3/8"x16	4	45°	4
100L	C	C-160	C-160	12	130	110	160	M8	3.5	45°	4
112M	C	FC	FC-184	13.5	184.2	215.9	225	UNC 1/2"x13	6.3	45°	4
112M	C	C-160	C-160	13.5	130	110	160	M8	3.5	45°	4
L90S	C	FC	FC-149	15	149.2	114.3	165	UNC 3/8"x16	4	45°	4
L90S	C	C-140	C-140	10.5	115	95	140	M8	3	45°	4
L100L	C	FC	FC-149	12	149.2	114.3	165	UNC 3/8"x16	4	45°	4
L100L	C	C-160	C-160	12	130	110	160	M8	3.5	45°	4
L90L	C	FC	FC-149	15	149.2	114.3	165	UNC 3/8"x16	4	45°	4
L90L	C	C-140	C-140	10.5	115	95	140	M8	3	45°	4
132S	C	FC	FC-184	9	184.2	215.9	225	UNC 1/2"x13	6.3	45°	4
132S	C	C-200	C-200	15.5	165	130	200	M10	3.5	45°	4
132M	C	FC	FC-184	9	184.2	215.9	225	UNC 1/2"x13	6.3	45°	4
132M	C	C-200	C-200	15.5	165	130	200	M10	3.5	45°	4
L112M	C	FC	FC-184	13.5	184.2	215.9	225	UNC 1/2"x13	6.3	45°	4
L112M	C	C-160	C-160	13.5	130	110	160	M8	3.5	45°	4
160M	C	FC	FC-184		184.2	215.9	225	UNC 1/2"x13	6.3	45°	4
160M	C	C-250	C-250	19	215	180	249	M12x1,75	6.3	45°	4
132M/L	C	FC	FC-184	9	184.2	215.9	225	UNC 1/2"x13	6.3	45°	4
132M/L	C	C-200	C-200	15.5	165	130	200	M10	3.5	45°	4
160L	C	FC	FC-184		184.2	215.9	225	UNC 1/2"x13	6.3	45°	4
160L	C	C-250	C-250	19	215	180	249	M12x1,75	6.3	45°	4
180M	C	FC	FC-228	13.5	228.6	266.7	280	UNC 1/2"x13	6.3	45°	4
180L	C	FC	FC-228	13.5	228.6	266.7	280	UNC 1/2"x13	6.3	45°	4
200L	C	FC	FC-228	13.5	228.6	266.7	280	UNC 1/2"x13	6.3	45°	4
225S/M	C	FC	FC-279	18.5	279.4	317.5	395	UNC 5/8"x11	6.3	22°30'	8
250S/M	C	FC	FC-355	18.5	355.6	406.4	455	UNC 5/8"x11	6.3	22°30'	8
280S/M	C	FC	FC-355	18.5	355.6	406.4	455	UNC 5/8"x11	6.3	22°30'	8
315S/M	C	FC	FC-368	18.5	368.3	419.1	455	UNC 5/8"x11	6.3	22°30'	8
315L	C	FC	FC-368	18.5	368.3	419.1	455	UNC 5/8"x11	6.3	22°30'	8
355M/L	C	FC	FC-368	33.5	368.3	419.1	455	UNC 5/8"x11	6.3	22°30'	8

Dimensions in mm


FC & C-DIN Flanges



IEC Metric Motors - Cast Iron Frames - Additional Flange Detail

Frame	Type	Flange	Size	LA	M	N	P	S	T	Angle	Holes
63	F	FF	FF-115	5.5	115	95	140	10	3	45°	4
71	F	FF	FF-130	7	130	110	160	10	3.5	45°	4
80	F	FF	FF-165	9	165	130	200	12	3.5	45°	4
90S	F	FF	FF-165	10	165	130	200	12	3.5	45°	4
90L	F	FF	FF-165	10	165	130	200	12	3.5	45°	4
100L	F	FF	FF-215	12.5	215	180	250	15	4	45°	4
112M	F	FF	FF-215	12.5	215	180	250	15	4	45°	4
L90S	F	FF	FF-165	10	165	130	200	12	3.5	45°	4
L100L	F	FF	FF-215	12.5	215	180	250	15	4	45°	4
L90L	F	FF	FF-165	10	165	130	200	12	3.5	45°	4
132S	F	FF	FF-265	12	265	230	300	15	4	45°	4
132M	F	FF	FF-265	12	265	230	300	15	4	45°	4
L112M	F	FF	FF-215	12.5	215	180	250	15	4	45°	4
160M	F	FF	FF-300	18	300	250	350	19	5	45°	4
132M/L	F	FF	FF-265	12	265	230	300	15	4	45°	4
160L	F	FF	FF-300	18	300	250	350	19	5	45°	4
180M	F	FF	FF-300	18	300	250	350	19	5	45°	4
180L	F	FF	FF-300	18	300	250	350	19	5	45°	4
200L	F	FF	FF-350	18	350	300	400	19	5	45°	4
225S/M	F	FF	FF-400	18	400	350	450	19	5	22°30'	8
250S/M	F	FF	FF-500	18	500	450	550	19	5	22°30'	8
280S/M	F	FF	FF-500	18	500	450	550	19	5	22°30'	8
315S/M	F	FF	FF-600	22	600	550	660	24	6	22°30"	8
315L	F	FF	FF-600	22	600	550	660	24	6	22°30'	8
355M/L	F	FF	FF-740	22	740	680	800	24	6	22°30'	8

Dimensions in mm



Part Number	List Price	Pages
1311017191	\$1,820	A-141
1311017192	\$1,736	A-141
1311017195	\$1,803	A-141
1311017196	\$1,852	A-141
1311087110	\$1,683	A-137
1311087111	\$1,706	A-137
1311087113	\$2,005	A-137
1311087114	\$1,981	A-137
1311087115	\$1,619	A-137
1311087117	\$1,663	A-138
1311087118	\$1,688	A-138
1311087119	\$1,962	A-138
1311087120	\$1,985	A-138
1311087121	\$1,544	A-137
1311087122	\$1,526	A-138
1311087123	\$1,601	A-138
1311087124	\$1,642	A-137
1311087125	\$1,626	A-138
1311087130	\$1,886	A-137
1311087133	\$1,694	A-137
1311087138	\$1,875	A-137
1311087152	\$1,879	A-138
1311087159	\$1,794	A-137
1311731426	\$803	A-266
1312200400	\$879	A-266
1313007404	\$851	A-266
1313087152	\$1,958	A-137
1313087153	\$1,976	A-137
1313087154	\$1,658	A-137
1313087156	\$1,601	A-137
1313087161	\$1,581	A-138
1313171403	\$837	A-266
1321087112	\$1,591	A-137
1321087113	\$1,483	A-137
1321087115	\$1,439	A-137
1321087117	\$1,465	A-138
1321087119	\$1,615	A-137
1321087121	\$1,421	A-138
1321087124	\$1,595	A-138
1321087125	\$1,572	A-138
1321087158	\$1,891	A-138
1323087110	\$1,460	A-137
1323087114	\$1,443	A-138
.12180S1B48CH-S	\$222	A-25;A-164
.12180S1B48-S	\$201	A-23;A-162;A-179
.16180S1ASPRB48Z-S	\$260	A-24;A-163;A-180
.16180S1ASPRB048Z-S	\$272	A-24;A-163;A-180
.16180S1B48CH-S	\$231	A-25;A-164
.16180S1B48-S	\$208	A-23;A-162;A-179
.16360S1B48CH-S	\$237	A-25;A-164
.16360S1B48-S	\$216	A-23;A-162;A-179

Part Number	List Price	Pages
.1809EP3EAL80-W22	\$540	A-82;A-248
.1809EP3WAL80-W22	\$540	A-82;A-248
.1812EP3EAL71-W22	\$338	A-82;A-248
.1818EP3EAL63-W22	\$267	A-82;A-248
.1836EP3EAL63-W22	\$280	A-82;A-248
.2509EP3EAL80-W22	\$583	A-82;A-248
.2509EP3WAL80-W22	\$583	A-82;A-248
.2512EP3EAL71-W22	\$363	A-82;A-248
.25120T3E56C-S	\$316	A-56;A-170
.25120T3E56-S	\$288	A-50;A-169
.2518EP3EAL71-W22	\$282	A-82;A-248
.2518ES1BW56C-S	\$288	A-21;A-160
.2518ES1BW56-S	\$267	A-19;A-159;A-178
.2518ES3E56C-S	\$270	A-42;A-167
.2518ES3E56-S	\$249	A-32;A-166
.2518ES3EBMW56CFL-S	\$966	A-79;A-281
.2518ES3EBMW56-S	\$928	A-78;A-280
.2518ES3H56C-S	\$270	A-42;A-167
.25180S1ASPRB48Z-S	\$262	A-24;A-163;A-180
.25180S1ASPRB048Z-S	\$274	A-24;A-163;A-180
.25180S1BRBFBOW56-S	\$283	A-180
.25180S1BRBFBW56-S	\$271	A-180
.25180S1BSPRB048Z-S	\$274	A-24;A-163;A-180
.25180T1B48CH-S	\$269	A-25;A-164
.25180T1B48-S	\$241	A-23;A-162;A-179
.25180T1BW56CFL-S	\$269	A-165
.25180T1BW56C-S	\$269	A-25;A-164
.25180T1BW56-S	\$241	A-23;A-162;A-179
.25180T3E48-S	\$235	A-50;A-169
.25180T3E56CFL-S	\$263	A-60;A-171
.25180T3E56C-S	\$263	A-56;A-170
.25180T3E56-S	\$235	A-50;A-169
.25180T3H56CFL-S	\$263	A-60;A-171
.2536EP3EAL63-W22	\$286	A-82;A-248
.2536ES1BW56C-S	\$280	A-21;A-160
.2536ES1BW56-S	\$257	A-19;A-159;A-178
.2536ES3E56C-S	\$258	A-42;A-167
.2536ES3E56-S	\$237	A-32;A-166
.25360T1B48CH-S	\$277	A-25;A-164
.25360T1B48-S	\$253	A-23;A-162;A-179
.25360T1BW56C-S	\$281	A-25;A-164
.25360T1BW56-S	\$253	A-23;A-162;A-179
.25360T3E56C-S	\$259	A-56;A-170
.25360T3E56-S	\$231	A-50;A-169
.3312AS1BPFFC48Z-S	\$322	A-263
.33120T3E56C-S	\$361	A-56;A-170
.33120T3E56-S	\$333	A-50;A-169
.3318AS1BPFF48-S	\$311	A-263
.3318AS1BPFFC48Z-S	\$287	A-263
.3318AS1BRBPF48-S	\$325	A-263
.3318EP3ESS56C	\$675	A-142

Part Number	List Price	Pages
.3318EP3ESS56CFL	\$667	A-143
.3318ES1BRBPF48	\$325	A-178
.3318ES1BW56CFL-S	\$304	A-22;A-160
.3318ES1BW56C-S	\$304	A-21;A-160
.3318ES1BW56-S	\$283	A-19;A-159;A-178
.3318ES1RAD56NZ	\$363	A-263
.3318ES1RFDW56-S	\$284	A-19;A-22;A-159;A-161;A-262
.3318ES3E56CFL-S	\$274	A-46;A-168
.3318ES3E56C-S	\$274	A-42;A-167
.3318ES3E56-S	\$253	A-32;A-166
.3318ES3EBMW56CFL-S	\$1,015	A-79;A-281
.3318ES3EBMW56-S	\$977	A-78;A-280
.3318OS1AEC56	\$156	A-181
.3318OS1BRBFBOW56-S	\$293	A-180
.3318OS1BRBFBW56-S	\$281	A-180
.3318OS1BSPRB48Z-S	\$272	A-24;A-163;A-180
.3318OS1BSPRBO48Z-S	\$284	A-24;A-163;A-180
.3318OS1BSPRBOW56-S	\$288	A-24;A-163;A-180
.3318OS1BSPRBW56-S	\$276	A-24;A-163;A-180
.3318OT1B48CH-S	\$299	A-25;A-164
.3318OT1B48-S	\$275	A-23;A-162;A-179
.3318OT1BRBOW56-S	\$325	A-24;A-163;A-180
.3318OT1BW56CFL-S	\$303	A-26;A-165
.3318OT1BW56C-S	\$303	A-25;A-164
.3318OT1BW56-S	\$275	A-23;A-162;A-179
.3318OT3E56CFL-S	\$284	A-60;A-171
.3318OT3E56C-S	\$284	A-56;A-170
.3318OT3E56-S	\$256	A-50;A-169
.3318OT3ERB56-S	\$314	A-60;A-171;A-181
.3318OT3H56CFL-S	\$284	A-60;A-171
.3318OT3H56-S	\$269	A-50;A-169
.3318XS1B56	\$670	A-121;A-174
.3318XS1B56C	\$816	A-121;A-174
.3318XS3E56	\$713	A-123;A-175
.3318XS3E56C	\$877	A-127;A-175
.3336ES1BJPRW56C-S	\$282	A-202
.3336ES1BJPRW56J-S	\$296	A-202
.3336ES1BJPW56C-S	\$263	A-202
.3336ES1BJPW56J-S	\$282	A-202
.3336ES1BW56CFL-S	\$288	A-22;A-160
.3336ES1BW56C-S	\$288	A-21;A-160
.3336ES1BW56-S	\$267	A-19;A-159;A-178
.3336ES3E56CFL-S	\$270	A-46;A-168
.3336ES3E56C-S	\$270	A-42;A-167
.3336ES3E56-S	\$249	A-32;A-166
.3336ES3EJP56J-S	\$259	A-204
.3336ES3EJPR56C-S	\$257	A-204
.3336ES3EJPR56J-S	\$268	A-204
.3336ES3H56CFL-S	\$270	A-46;A-168
.3336ES3H56C-S	\$270	A-42;A-167

Part Number	List Price	Pages
.3336OS1BJPRW56C-S	\$237	A-203
.3336OS1BJPRW56J-S	\$255	A-203
.3336OS1BJPW56J-S	\$254	A-203
.3336OS3EJP56J-S	\$224	A-205
.3336OS3EJPR56C-S	\$220	A-205
.3336OS3EJPR56J-S	\$229	A-205
.3336OT1B48CH-S	\$282	A-25;A-164
.3336OT1B48-S	\$256	A-23;A-162;A-179
.3336OT1BOW56CFL-S	\$302	A-26;A-165
.3336OT1BW56CFL-S	\$285	A-26;A-165
.3336OT1BW56C-S	\$285	A-25;A-164
.3336OT1BW56-S	\$257	A-162;A-179
.3336OT3E56CFL-S	\$270	A-60;A-171
.3336OT3E56C-S	\$270	A-56;A-170
.3336OT3E56-S	\$242	A-50;A-169
.3336XS1B56	\$612	A-121;A-174
.3336XS1B56C	\$737	A-121;A-174
.3336XS3E56	\$650	A-123;A-175
.3336XS3E56C	\$821	A-127;A-175
.3382OS1AEC56	\$188	A-181
.3709EP3EAL90S-W22	\$662	A-82;A-248
.3709EP3WAL90S/L-W22	\$662	A-82;A-248
.3712EP3EAL80-W22	\$378	A-82;A-248
.3718EP3EAL71FF-W22	\$340	A-85;A-118;A-251
.3718EP3EAL71-W22	\$290	A-82;A-248
.3736EP3EAL71-W22	\$309	A-82;A-248
.5012EP3ESS56C	\$760	A-142
.5012EP3ESS56CFL	\$752	A-143
.5012ES1B56CFL-S	\$535	A-22;A-160
.5012ES1B56C-S	\$535	A-21;A-160
.5012ES1B56-S	\$512	A-19;A-159;A-178
.5012ES3E56CFL-S	\$440	A-168
.5012ES3E56C-S	\$440	A-42;A-167
.5012ES3E56-S	\$417	A-32;A-166
.5012ES3H56CFL-S	\$441	A-168
.5012OT3E56C-S	\$377	A-56;A-170
.5012OT3E56-S	\$349	A-50;A-169
.5018AS1BPFW56-S	\$336	A-263
.5018AS1BRBPFW56-S	\$350	A-263
.5018EP3ESS56C	\$696	A-142
.5018EP3ESS56CFL	\$689	A-143
.5018ES1BOW56C-S	\$348	A-21;A-160
.5018ES1BRBPF48C56	\$350	A-178
.5018ES1BW56CFL-S	\$333	A-22;A-160
.5018ES1BW56C-S	\$333	A-21;A-160
.5018ES1BW56-S	\$312	A-19;A-159;A-178
.5018ES1RAD56NZ	\$409	A-263
.5018ES1RFDW56-S	\$308	A-19;A-22;A-159;A-161;A-262
.5018ES3E56CFL-S	\$311	A-46;A-168
.5018ES3E56C-S	\$311	A-42;A-167

Part Number	List Price	Pages
.5018ES3E56-S	\$287	A-32;A-166
.5018ES3EBMW56CFL-S	\$1,143	A-79;A-281
.5018ES3EBMW56-S	\$1,105	A-78;A-280
.5018ES3H56CFL-S	\$312	A-46;A-168
.5018ES3H56C-S	\$263	A-42;A-167
.5018ES3H56-S	\$288	A-32;A-166
.5018NT3EHW56C	\$644	A-147
.5018NT3EHW56CFL	\$625	A-148
.5018NT3FVD56C-S	\$599	A-115;A-268
.5018OS1AEC56	\$164	A-181
.5018OS1BRBFBOW56-S	\$325	A-180
.5018OS1BRBFBW56-S	\$313	A-180
.5018OS1BSPRB48Z-S	\$299	A-24;A-163;A-180
.5018OS1BSPRB048Z-S	\$311	A-24;A-163;A-180
.5018OS1BSPRBOW56-S	\$316	A-24;A-163;A-180
.5018OS1BSPRBW56-S	\$304	A-24;A-163;A-180
.5018OS1DEC56	\$166	A-181
.5018OT1B48-S	\$318	A-23;A-162;A-179
.5018OT1BOW56C-S	\$352	A-25;A-164
.5018OT1BRBOW56-S	\$368	A-24;A-163;A-180
.5018OT1BW56CFL-S	\$335	A-26;A-165
.5018OT1BW56C-S	\$335	A-25;A-164
.5018OT1BW56-S	\$307	A-23;A-162;A-179
.5018OT3E56CFL-S	\$324	A-60;A-171
.5018OT3E56C-S	\$324	A-56;A-170
.5018OT3E56-S	\$296	A-50;A-169
.5018OT3ERB56-S	\$354	A-60;A-171;A-181
.5018OT3H56CFL-S	\$324	A-60;A-171
.5018OT3H56-S	\$311	A-50;A-169
.5018XS1B56	\$739	A-121;A-174
.5018XS1B56C	\$817	A-121;A-174
.5018XS3E56	\$741	A-123;A-175
.5018XS3E56C	\$926	A-127;A-175
.5036EP3ESS56C	\$618	A-142
.5036EP3ESS56CFL	\$611	A-143
.5036ES1BJPRW56C-S	\$299	A-202
.5036ES1BJPRW56J-S	\$305	A-202
.5036ES1BJPW56C-S	\$284	A-202
.5036ES1BJPW56J-S	\$300	A-202
.5036ES1BOLW56-S	\$316	A-19;A-22;A-159;A-161;A-178
.5036ES1BW56CFL-S	\$313	A-22;A-160
.5036ES1BW56C-S	\$313	A-21;A-160
.5036ES1BW56-S	\$284	A-19;A-159;A-178
.5036ES1E143JP-W22	\$668	A-210
.5036ES3E56CFL-S	\$282	A-168
.5036ES3E56C-S	\$282	A-167
.5036ES3E56-S	\$258	A-32;A-166
.5036ES3EJP56J-S	\$267	A-204
.5036ES3EJPR56C-S	\$270	A-204
.5036ES3EJPR56J-S	\$282	A-204

Part Number	List Price	Pages
.5036ES3H56C-S	\$281	A-42;A-167
.5036OS1BCDW56-S	\$224	A-23;A-26;A-162;A-165;A-272
.5036OS1BJPRW56C-S	\$255	A-203
.5036OS1BJPRW56J-S	\$258	A-203
.5036OS1BJPW56J-S	\$258	A-203
.5036OS3EJP56J-S	\$236	A-205
.5036OS3EJPR56C-S	\$224	A-205
.5036OS3EJPR56J-S	\$241	A-205
.5036OS3HJP56J-S	\$236	A-205
.5036OT1B48CH-S	\$300	A-25;A-164
.5036OT1B48-S	\$276	A-23;A-162;A-179
.5036OT1BOW56CFL-S	\$327	A-26;A-165
.5036OT1BW56CFL-S	\$310	A-26;A-165
.5036OT1BW56C-S	\$310	A-25;A-164
.5036OT1BW56-S	\$282	A-23;A-162;A-179
.5036OT3E56CFL-S	\$286	A-60;A-171
.5036OT3E56C-S	\$286	A-56;A-170
.5036OT3E56-S	\$258	A-50;A-169
.5036XS1B56	\$636	A-121;A-174
.5036XS1B56C	\$717	A-121;A-174
.5036XS3E56	\$782	A-123;A-175
.5036XS3E56C	\$856	A-127;A-175
.5036XS3EJPR56J	\$810	A-168;A-203
.5082OS1AEC56	\$199	A-181
.5082OS1DEC56	\$220	A-181
.5509EP3EAL90L-W22	\$696	A-82;A-248
.5509EP3WAL90S/L-W22	\$696	A-82;A-248
.5512EP3EAL80-W22	\$405	A-82;A-248
.5518EP3EAL80FF-W22	\$383	A-85;A-118;A-251
.5518EP3EAL80-W22	\$333	A-82;A-248
.5536EP3EAL71FF-W22	\$366	A-85;A-118;A-251
.5536EP3EAL71-W22	\$316	A-82;A-248
.7509ET3EAL100L-W22	\$869	A-82;A-248
.7512EP3ESS56C	\$868	A-142
.7512EP3ESS56CFL	\$862	A-143
.7512ES1B56CFL-S	\$669	A-22;A-160
.7512ES1B56C-S	\$669	A-21;A-160
.7512ES1B56-S	\$648	A-19;A-159;A-178
.7512ES3E56CFL-S	\$449	A-46;A-168
.7512ES3E56C-S	\$449	A-42;A-167
.7512ES3E56-S	\$427	A-32;A-166
.7512ES3H56CFL-S	\$450	A-46;A-168
.7512ET3EAL90S-W22	\$537	A-82;A-248
.7512ET3WAL90S-W22	\$537	A-82;A-248
.7512OT3E56C-S	\$412	A-56;A-170
.7512OT3E56-S	\$384	A-50;A-169
.7518AS1BPF56-S	\$385	A-263
.7518AS1BRBPF56-S	\$400	A-263
.7518EP3ESS56C	\$798	A-142
.7518EP3ESS56CFL	\$787	A-143

Part Number	List Price	Pages
.7518ES1B56CFL-S	\$370	A-22;A-160
.7518ES1B56C-S	\$370	A-21;A-160
.7518ES1B56-S	\$348	A-19;A-159;A-178
.7518ES1BRBPF56	\$433	A-178
.7518ES1RAD56NZ	\$447	A-263
.7518ES1RFD56-S	\$357	A-19;A-22;A-159;A-161;A-262
.7518ES3E56CFL-S	\$332	A-46;A-168
.7518ES3E56C-S	\$332	A-42;A-167
.7518ES3E56-S	\$311	A-32;A-166
.7518ES3EBMW56CFL-S	\$1,339	A-79;A-281
.7518ES3EBMW56-S	\$1,301	A-78;A-280
.7518ES3H56CFL-S	\$333	A-46;A-168
.7518ES3H56C-S	\$333	A-42;A-167
.7518ET3EAL90S/LFF-W	\$479	A-85;A-118;A-251
.7518ET3EAL90S/L-W22	\$420	A-82;A-248
.7518ET3WAL90S/LFF-W	\$479	A-85;A-118;A-251
.7518ET3WAL90S/L-W22	\$420	A-82;A-248
.7518NT3EHW56C	\$720	A-147
.7518NT3EHW56CFL	\$699	A-148
.7518NT3FVD56C-S	\$636	A-115;A-268
.7518OS1AEC56	\$201	A-181
.7518OS1BRBFB0W56-S	\$379	A-180
.7518OS1BRBFBW56-S	\$367	A-180
.7518OS1DEC56	\$201	A-181
.7518OT1B56CFL-S	\$415	A-26;A-165
.7518OT1B56C-S	\$415	A-25;A-164
.7518OT1B56-S	\$387	A-23;A-162;A-179
.7518OT1BRB056-S	\$434	A-24;A-163;A-180
.7518OT3E56CFL-S	\$358	A-60;A-171
.7518OT3E56C-S	\$358	A-56;A-170
.7518OT3E56-S	\$330	A-50;A-169
.7518OT3ERB56-S	\$388	A-60;A-171;A-181
.7518OT3H56CFL-S	\$358	A-60;A-171
.7518OT3H56C-S	\$358	A-56;A-170
.7518OT3H56-S	\$347	A-50;A-169
.7518XS1B56	\$868	A-121;A-174
.7518XS1B56C	\$912	A-121;A-174
.7518XS3E56	\$817	A-123;A-175
.7518XS3E56C	\$944	A-127;A-175
.7536AS1RAF56Z-S	\$395	A-264
.7536AS3EAF56Z-S	\$402	A-264
.7536EP3ESS56C	\$681	A-142
.7536EP3ESS56CFL	\$674	A-143
.7536ES1B56CFL-S	\$353	A-22;A-160
.7536ES1B56C-S	\$353	A-21;A-160
.7536ES1B56-S	\$297	A-19;A-159;A-178
.7536ES1BJP56C-S	\$320	A-202
.7536ES1BJP56J-S	\$330	A-202
.7536ES1BJPR56C-S	\$341	A-202
.7536ES1BJPR56J-S	\$336	A-202

Part Number	List Price	Pages
.7536ES1BOL56-S	\$329	A-19;A-22;A-159;A-161;A-178
.7536ES3E56CFL-S	\$311	A-46;A-168
.7536ES3E56C-S	\$311	A-42;A-167
.7536ES3E56-S	\$287	A-32;A-166
.7536ES3EJP56J-S	\$301	A-204
.7536ES3EJPR56C-S	\$293	A-204
.7536ES3EJPR56J-S	\$319	A-204
.7536ES3H56CFL-S	\$312	A-46;A-168
.7536ES3H56C-S	\$310	A-42;A-167
.7536ES3H56-S	\$288	A-32;A-166
.7536ES3HJP56J-S	\$301	A-204
.7536ET3WAL80-W22	\$397	A-82;A-248
.7536OS1BCDW56-S	\$237	A-23;A-26;A-162;A-165;A-272
.7536OS1BJPRW56C-S	\$297	A-203
.7536OS1BJPRW56J-S	\$296	A-203
.7536OS1BJPW56J-S	\$296	A-203
.7536OS3EJP56J-S	\$271	A-205
.7536OS3EJPR56C-S	\$257	A-205
.7536OS3EJPR56J-S	\$278	A-205
.7536OS3HJP56J-S	\$271	A-205
.7536OS3HJPR56C-S	\$257	A-205
.7536OS3HJPR56J-S	\$277	A-205
.7536OT1B56CFL-S	\$348	A-26;A-165
.7536OT1B56C-S	\$348	A-25;A-164
.7536OT1B56-S	\$320	A-23;A-162;A-179
.7536OT1B056CFL-S	\$365	A-26;A-165
.7536OT3E56CFL-S	\$333	A-60;A-171
.7536OT3E56C-S	\$333	A-56;A-170
.7536OT3E56-S	\$305	A-50;A-169
.7536XS1B56	\$717	A-121;A-174
.7536XS1B56C	\$773	A-121;A-174
.7536XS3E56	\$815	A-123;A-175
.7536XS3E56C	\$884	A-127;A-175
.7536XS3EJPR56J	\$835	A-168;A-203
.7582OS1AEC56	\$251	A-181
.7582OS1DEC56	\$267	A-181
00109ET3E182T-W22	\$1,043	A-32;A-93
00109ET3EBM182T-W22	\$2,594	A-76;A-278
00109ET3H182T-W22	\$1,043	A-32;A-93
00109ST3QIE182T-W22	\$2,006	A-69;A-104
00109XT3E182T	\$1,974	A-123
00112ET3E145JM-S	\$700	A-212
00112ET3E145JM-W22	\$700	A-212
00112ET3E145JP-S	\$714	A-216
00112ET3E145JP-W22	\$714	A-216
00112ET3E145TC-S	\$554	A-42
00112ET3E145TC-W22	\$636	A-42;A-100
00112ET3E145T-S	\$529	A-32
00112ET3E145T-SG	\$669	A-61;A-182
00112ET3E145T-W22	\$608	A-32;A-93

Part Number	List Price	Pages
00112ET3E56CFL-S	\$528	A-46;A-168
00112ET3E56C-S	\$525	A-42;A-167
00112ET3E56-S	\$497	A-32;A-166
00112ET3EAL100L-W22	\$746	A-82;A-248
00112ET3EBM145T-W22	\$1,587	A-76;A-278
00112ET3ECT145TF1-W2	\$728	A-190
00112ET3ECT145T-W22	\$728	A-190
00112ET3ER145TC-S	\$554	A-46
00112ET3ER145TC-W22	\$655	A-46;A-102
00112ET3H145T-S	\$529	A-32
00112ET3H145T-SG	\$669	A-61;A-182
00112ET3H145T-W22	\$608	A-32;A-93
00112ET3H56CFL-S	\$528	A-46;A-168
00112ET3PCT145TF1-W2	\$728	A-190
00112ET3PCT145T-W22	\$728	A-190
00112ET3VR145TC-S	\$554	A-46
001120T3E145JM-S	\$550	A-221
001120T3E145JMV-S	\$605	A-224
001120T3E145JP-S	\$550	A-225
001120T3E145T-S	\$446	A-50
001120T3E145T-SG	\$586	A-65;A-186
001120T3E56C-S	\$486	A-56;A-170
001120T3E56-S	\$458	A-50;A-169
001120T3H145T-S	\$446	A-50
001120T3H145T-SG	\$586	A-65;A-186
00112ST3HIE145T-W22	\$1,062	A-69;A-104
00112ST3QIE145TC-W22	\$1,112	A-73;A-108
00112ST3QIE145T-W22	\$1,062	A-69;A-104
00112XT3E145T	\$988	A-123
00112XT3E145TC	\$1,107	A-127
00112XT3H145T	\$988	A-123
00118AS1BPF56-S	\$410	A-263
00118AS1BPFH56-S	\$445	A-263
00118AS1BRBPF56-S	\$435	A-263
00118AT3PCT143T-W22	\$666	A-193
00118EG3E143T-W22	\$580	A-87
00118ES1B56CFL-S	\$424	A-22;A-160
00118ES1B56C-S	\$424	A-21;A-160
00118ES1B56-S	\$401	A-19;A-159;A-178
00118ES1B056C-S	\$439	A-21;A-160
00118ES1BRBPDF56	\$469	A-178
00118ES1E143T-S	\$531	0
00118ES1ER143TC-S	\$559	A-22
00118ES1RAD56N	\$481	A-263
00118ES1RFD143T-S	\$400	A-19;A-22;A-262
00118ES1RFD56-S	\$394	A-19;A-22;A-159;A-161;A-262
00118ET3E143HP-W22	\$619	A-244
00118ET3E143JM-S	\$613	A-212
00118ET3E143JM-SG	\$764	A-230
00118ET3E143JM-W22	\$613	A-212
00118ET3E143JP-S	\$624	A-216

Part Number	List Price	Pages
00118ET3E143JP-SG	\$764	A-231
00118ET3E143JP-W22	\$624	A-216
00118ET3E143TC-S	\$484	A-42
00118ET3E143TC-W22	\$555	A-42;A-100
00118ET3E143T-S	\$459	A-32
00118ET3E143T-SG	\$599	A-61;A-182
00118ET3E143T-W22	\$527	A-32;A-93
00118ET3E56CFL-S	\$407	A-46;A-168
00118ET3E56C-S	\$407	A-42;A-167
00118ET3E56-S	\$379	A-32;A-166
00118ET3EAL90S-W22	\$470	A-82;A-248
00118ET3EBM143TC-S	\$1,767	A-79;A-281
00118ET3EBM143T-S	\$1,729	A-78;A-280
00118ET3EBM143T-W22	\$1,494	A-76;A-278
00118ET3EBM56CFL-S	\$1,542	A-79;A-281
00118ET3EBM56C-S	\$1,542	A-79;A-281
00118ET3EBM56-S	\$1,504	A-78;A-280
00118ET3EBMR143TC-S	\$1,767	A-79;A-281
00118ET3ECT143TF1-W2	\$647	A-190
00118ET3ECT143T-W22	\$647	A-190
00118ET3EPM143/5Y-W2	\$594	A-199
00118ET3ER143TC-S	\$484	A-46
00118ET3ER143TC-W22	\$572	A-46;A-102
00118ET3ESS143TC	\$1,042	A-142
00118ET3ESS143TCFL	\$1,028	A-143
00118ET3ESS56C	\$994	A-142
00118ET3ESS56CFL	\$981	A-143
00118ET3H143JM-S	\$613	A-212
00118ET3H143JM-SG	\$764	A-230
00118ET3H143JM-W22	\$613	A-212
00118ET3H143TC-S	\$484	A-42
00118ET3H143TC-W22	\$555	A-42;A-100
00118ET3H143T-S	\$459	A-32
00118ET3H143T-SG	\$599	A-61;A-182
00118ET3H143T-W22	\$527	A-32;A-93
00118ET3H56CFL-S	\$407	A-46;A-168
00118ET3H56C-S	\$407	A-42;A-167
00118ET3H56-S	\$379	A-32;A-166
00118ET3HBM143T-W22	\$1,494	A-76;A-278
00118ET3PCT143T-W22	\$647	A-190
00118ET3V143JM-S	\$613	A-212
00118ET3V143T-SG	\$599	A-61;A-182
00118ET3WAL90S-W22	\$470	A-82;A-248
00118NT3EHW143TC	\$859	A-147
00118NT3EHW56C	\$843	A-147
00118NT3EHW56CFL	\$815	A-148
00118NT3EHW143TC	\$830	A-148
00118NT3ESS143TC	\$1,026	A-142
00118NT3ESS143TCFL	\$1,014	A-143
00118NT3ESS56C	\$834	A-142

Part Number	List Price	Pages
00118NT3ESS56CFL	\$824	A-143
00118NT3FVD143TC-W22	\$697	A-115;A-268
00118NT3FVD56C-S	\$681	A-115;A-268
001180S1BRBFB056-S	\$408	A-180
001180S1BRBFBW56-S	\$396	A-180
001180T1B56CFL-S	\$449	A-26;A-165
001180T1B56C-S	\$449	A-25;A-164
001180T1B56-S	\$421	A-23;A-162;A-179
001180T1B056-S	\$438	A-23;A-26;A-162;A-165;A-179
001180T1BRB056-S	\$468	A-24;A-163;A-180
001180T3E143JM-S	\$486	A-221
001180T3E143JM-SG	\$626	A-232
001180T3E143JMV-S	\$541	A-224
001180T3E143JP-S	\$486	A-225
001180T3E143JP-SG	\$626	A-233
001180T3E143TC-S	\$424	A-56
001180T3E143TC-SG	\$564	A-65;A-186
001180T3E143T-S	\$390	A-50;A-273
001180T3E143T-SG*	\$530	A-65;A-186
001180T3E56CFL-S	\$378	A-60;A-171
001180T3E56C-S	\$378	A-56;A-170
001180T3E56-S	\$350	A-50;A-169
001180T3ECD143T-S	\$398	A-273
001180T3ER143TC-S	\$479	A-60
001180T3ERB56-S	\$408	A-60;A-171;A-181
001180T3H143JM-S	\$486	A-221
001180T3H143JM-SG	\$626	A-232
001180T3H143TC-S	\$424	A-56
001180T3H143T-S	\$390	A-50
001180T3H143T-SG	\$530	A-65;A-186
001180T3H56CFL-S	\$378	A-60;A-171
001180T3P143TC-S	\$424	A-56
001180T3P143T-S	\$390	A-50;A-273
001180T3V143JM-S	\$486	A-221
001180T3V143T-SG	\$530	A-65;A-186
00118ST3HIE143T-W22	\$922	A-69;A-104
00118ST3QIE143TC-W22	\$972	A-73;A-108
00118ST3QIE143T-W22	\$922	A-69;A-104
00118ST3QIER143TC-W2	\$1,000	A-75;A-109
00118XS1B56	\$988	A-121;A-174
00118XS1B56C	\$1,036	A-121;A-174
00118XT3E143T	\$901	A-123
00118XT3E143TC	\$1,054	A-127
00118XT3E56	\$922	A-123;A-175
00118XT3E56C	\$1,007	A-127;A-175
00118XT3ER143TC	\$1,072	A-128
00118XT3H143T	\$901	A-123
00136AS1RAF56Z-S	\$459	A-264
00136AS3EAF56Z-S	\$435	A-264

Part Number	List Price	Pages
00136EG3E143T-W22	\$569	A-87
00136ES1B143T-S	\$553	A-19
00136ES1B56CFL-S	\$378	A-22;A-160
00136ES1B56C-S	\$378	A-21;A-160
00136ES1B56-S	\$376	A-19;A-159;A-178
00136ES1BJP56C-S	\$344	A-202
00136ES1BJP56J-S	\$374	A-202
00136ES1BJPR56C-S	\$357	A-202
00136ES1BJPR56J-S	\$386	A-202
00136ES1BOL56-S	\$408	A-19;A-22;A-159;A-161;A-178
00136ES1E143JM-W22	\$682	A-209
00136ET3E143TC-W22	\$566	A-42;A-100
00136ET3E143T-S	\$420	A-32
00136ET3E143T-SG	\$560	A-61;A-182
00136ET3E143T-W22	\$538	A-32;A-93
00136ET3EAL80-W22	\$444	A-82;A-248
00136ET3EJPRW56C-S	\$425	A-204
00136ET3EJPRW56J-S	\$429	A-204
00136ET3EJPW56J-S	\$434	A-204
00136ET3EPM143/5Y-W2	\$565	A-199
00136ET3ER143TC-W22	\$577	A-46;A-102
00136ET3ESS56C	\$836	A-142
00136ET3ESS56CFL	\$827	A-143
00136ET3EW56CFL-S	\$420	A-46;A-168
00136ET3EW56C-S	\$420	A-42;A-167
00136ET3EW56-S	\$392	A-32;A-166
00136ET3H143T-S	\$420	A-32
00136ET3H143T-SG	\$560	A-61;A-182
00136ET3H143T-W22	\$538	A-32;A-93
00136ET3HJPW56J-S	\$434	A-204
00136ET3HW56C-S	\$420	A-42;A-167
00136ET3HW56-S	\$392	A-32;A-166
00136ET3WAL80-W22	\$444	A-82;A-248
00136NT3ESS56C	\$912	A-142
00136NT3ESS56CFL	\$898	A-143
001360S1BCD56-S	\$278	A-23;A-26;A-162;A-165;A-272
001360S1BJP56J-S	\$334	A-203
001360S1BJPR56C-S	\$317	A-203
001360S1BJPR56J-S	\$334	A-203
001360S3EJP56J-S	\$286	A-205
001360S3EJPR56C-S	\$274	A-205
001360S3EJPR56J-S	\$287	A-205
001360S3HJP56J-S	\$286	A-205
001360T1B56CFL-S	\$375	A-26;A-165
001360T1B56C-S	\$375	A-25;A-164
001360T1B56-S	\$347	A-23;A-162;A-179
001360T1B056CFL-S	\$392	A-26;A-165
001360T3E143T-S	\$385	A-50
001360T3E56CFL-S	\$383	A-60;A-171

Part Number	List Price	Pages
001360T3E56C-S	\$383	A-56;A-170
001360T3E56-S	\$355	A-50;A-169
00136XS1B56	\$774	A-121;A-174
00136XS1B56C	\$814	A-121;A-174
00136XT3E143T	\$886	A-123
00136XT3E56	\$858	A-123;A-175
00136XT3E56C	\$924	A-127;A-175
00136XT3EJPR56J	\$1,030	A-168;A-203
00152ES1E182T-W22	\$1,100	A-19
00152ET3E182JM-S	\$909	A-212
00152ET3E182JM-W22	\$909	A-212
00152ET3E182JP-S	\$924	A-216
00152ET3E182JP-W22	\$924	A-216
00152ET3E182TC-S	\$690	A-42
00152ET3E182TC-W22	\$792	A-42;A-100
00152ET3E182T-S	\$656	A-33
00152ET3E182T-SG	\$826	A-61;A-182
00152ET3E182T-W22	\$754	A-33;A-93
00152ET3EAL112M-W22	\$923	A-82;A-248
00152ET3EBM182T-W22	\$2,264	A-76;A-278
00152ET3ECT182T-W22	\$903	A-190
00152ET3EPM182/4Y-W2	\$820	A-199
00152ET3ER182TC-S	\$690	A-46
00152ET3ER182TC-W22	\$816	A-46;A-102
00152ET3H182T-S	\$656	A-33
00152ET3H182T-SG	\$826	A-61;A-182
00152ET3H182T-W22	\$754	A-33;A-93
00152ET3PCT182T-W22	\$903	A-190
00152ET3WAL100LFF-W2	\$882	A-85;A-118;A-251
00152ET3WAL100L-W22	\$812	A-82;A-248
00152ET3WAL112M-W22	\$923	A-82;A-248
00152OT3E182JM-S	\$769	A-221
00152OT3E182JMV-S	\$827	A-224
00152OT3E182JP-S	\$729	A-225
00152OT3E182T-S	\$588	A-50
00152OT3E182T-SG	\$758	A-65;A-186
00152ST3HIE182T-W22	\$1,286	A-69;A-104
00152ST3QIE182TC-W22	\$1,351	A-73;A-108
00152ST3QIE182T-W22	\$1,286	A-69;A-104
00152XT3E182T	\$1,105	A-123
00152XT3E182TC	\$1,270	A-127
00152XT3H182T	\$1,105	A-123
00156AP3EAF143TZ-S	\$498	A-264
00156AS1RAF143TZ-S	\$643	A-264
00156AS1RAF56Z-S	\$601	A-264
00156EG3E143T-W22	\$597	A-87
00156ES1B143T-S	\$602	A-19
00156ES1B56CFL-S	\$454	A-22;A-160
00156ES1B56C-S	\$454	A-21;A-160
00156ES1B56-S	\$432	A-19;A-159;A-178
00156ES1BJP56C-S	\$412	A-202

Part Number	List Price	Pages
00156ES1BJP56J-S	\$425	A-202
00156ES1BJPR56C-S	\$432	A-202
00156ES1BJPR56J-S	\$438	A-202
00156ES1BOL56-S	\$463	A-19;A-22;A-159;A-161;A-178
00156ES1E143JM-W22	\$729	A-209
00156ES1E143JP-W22	\$729	A-210
00156ET3E143HP-W22	\$573	A-244
00156ET3E143JM-S	\$710	A-212
00156ET3E143JM-SG	\$850	A-230
00156ET3E143JM-W22	\$710	A-212
00156ET3E143JP-S	\$649	A-216
00156ET3E143JP-SG	\$850	A-231
00156ET3E143JP-W22	\$649	A-216
00156ET3E143TC-S	\$497	A-42
00156ET3E143TC-W22	\$571	A-42;A-100
00156ET3E143T-S	\$473	A-33
00156ET3E143T-SG	\$613	A-61;A-182
00156ET3E143T-W22	\$543	A-33;A-93
00156ET3E56CFL-S	\$461	A-46;A-168
00156ET3E56C-S	\$461	A-42;A-167
00156ET3E56-S	\$433	A-33;A-166
00156ET3EAL90S-W22	\$504	A-82;A-248
00156ET3EBM143T-W22	\$1,501	A-76;A-278
00156ET3EJP56J-S	\$473	A-204
00156ET3EJPR56C-S	\$455	A-204
00156ET3EJPR56J-S	\$468	A-204
00156ET3EPM143/5Y-W2	\$613	A-199
00156ET3ER143TC-S	\$497	A-46
00156ET3ER143TC-W22	\$588	A-46;A-102
00156ET3ESS143TCFL	\$1,117	A-143
00156ET3ESS56C	\$1,023	A-142
00156ET3ESS56CFL	\$1,017	A-143
00156ET3H143JM-SG	\$850	A-230
00156ET3H143TC-W22	\$571	A-42;A-100
00156ET3H143T-S	\$473	A-33
00156ET3H143T-SG	\$613	A-61;A-182
00156ET3H143T-W22	\$543	A-33;A-93
00156ET3H56C-S	\$461	A-42;A-167
00156ET3HJP56J-S	\$473	A-204
00156ET3HJPR56J-S	\$468	A-204
00156ET3WAL90S-W22	\$504	A-82;A-248
00156OS1BCD56-S	\$311	A-23;A-26;A-162;A-165;A-272
00156OS1BJP56J-S	\$382	A-203
00156OS1BJPR56C-S	\$338	A-203
00156OS1BJPR56J-S	\$382	A-203
00156OS3EJP56J-S	\$296	A-205
00156OS3EJPR56C-S	\$290	A-205
00156OS3EJPR56J-S	\$305	A-205
00156OS3HJP56J-S	\$296	A-205



Part Number	List Price	Pages
001560S3HJPR56C-S	\$290	A-205
001560T1B56CFL-S	\$421	A-26;A-165
001560T1B56C-S	\$421	A-25;A-164
001560T1B56-S	\$393	A-23;A-162;A-179
001560T1B056CFL-S	\$438	A-26;A-165
001560T1BRB056-S	\$450	A-24;A-163;A-180
001560T3E143JM-S	\$534	A-221
001560T3E143JM-SG	\$674	A-232
001560T3E143JMV-S	\$589	A-224
001560T3E143JP-S	\$534	A-225
001560T3E143JP-SG	\$674	A-233
001560T3E143JPV-S	\$589	A-228
001560T3E143TC-S	\$476	A-56
001560T3E143T-S	\$442	A-50;A-273
001560T3E143T-SG	\$582	A-65;A-186
001560T3E56CFL-S	\$408	A-60;A-171
001560T3E56C-S	\$408	A-56;A-170
001560T3E56-S	\$380	A-50;A-169
001560T3ER143TC-S	\$531	A-60
001560T3H143JM-SG	\$674	A-232
001560T3H143TC-S	\$476	A-56
001560T3H143T-S	\$442	A-50
001560T3V143JM-S	\$534	A-221
001560T3V143JP-S	\$534	A-225
00156ST3HIE143T-W22	\$981	A-69;A-104
00156ST3QIE143TC-W22	\$1,031	A-73;A-108
00156ST3QIE143T-W22	\$981	A-69;A-104
00156XS1C56	\$1,121	A-121;A-174
00156XS1C56C	\$1,274	A-121;A-174
00156XT3E143T	\$916	A-123
00156XT3E143TC	\$1,069	A-127
00156XT3E56	\$1,050	A-123;A-175
00156XT3E56C	\$1,038	A-127;A-175
00156XT3EJPR56J	\$1,105	A-168;A-203
00156XT3H143T	\$916	A-123
00158AS1BPF56-S	\$458	A-263
00158AS1BPFH56-S	\$484	A-263
00158AS1BRBPF56-S	\$477	A-263
00158AT3PCT145T-W22	\$696	A-193
00158EG3EL145T-W22	\$606	A-87
00158ES1B145T-S	\$612	A-19
00158ES1B56CFL-S	\$478	A-22;A-160
00158ES1B56C-S	\$478	A-21;A-160
00158ES1B56-S	\$456	A-19;A-159;A-178
00158ES1B056C-S	\$493	A-21;A-160
00158ES1E145JM-W22	\$754	A-209
00158ES1E145T-S	\$611	A-19
00158ES1RAD56N	\$597	A-263
00158ES1RFD145T-S	\$504	A-19;A-22;A-262
00158ES1RFD56H-S	\$502	A-19;A-22;A-159;A-161;A-262

Part Number	List Price	Pages
00158ET3E145HP-W22	\$663	A-244
00158ET3E145JM-S	\$643	A-212
00158ET3E145JM-SG	\$793	A-230
00158ET3E145JM-W22	\$643	A-212
00158ET3E145JP-S	\$653	A-216
00158ET3E145JP-SG	\$793	A-231
00158ET3E145JP-W22	\$653	A-216
00158ET3E145TC-S	\$504	A-42
00158ET3E145TC-W22	\$579	A-42;A-100
00158ET3E145T-S	\$480	A-33
00158ET3E145T-SG	\$620	A-61;A-182
00158ET3E145T-W22	\$551	A-33;A-93
00158ET3E56CFL-S	\$463	A-46;A-168
00158ET3E56C-S	\$463	A-42;A-167
00158ET3E56-S	\$435	A-33;A-166
00158ET3EAL90LFF-W22	\$583	A-85;A-118;A-251
00158ET3EAL90L-W22	\$524	A-82;A-248
00158ET3EBM145TC-S	\$1,904	A-79;A-281
00158ET3EBM145T-S	\$1,866	A-78;A-280
00158ET3EBM145T-W22	\$1,569	A-76;A-278
00158ET3EBM56CFL-S	\$1,856	A-79;A-281
00158ET3EBMR145TC-S	\$1,904	A-79;A-281
00158ET3ECT145TF1-W2	\$676	A-190
00158ET3ECT145T-W22	\$676	A-190
00158ET3EHW145TC	\$880	A-147
00158ET3EHW56C	\$860	A-147
00158ET3EHW56CFL	\$830	A-148
00158ET3EHW145TC	\$850	A-148
00158ET3EPM143/5Y-W2	\$617	A-199
00158ET3ER145TC-S	\$504	A-46
00158ET3ER145TC-W22	\$596	A-46;A-102
00158ET3ESB145TCZ1-S	\$1,489	A-283
00158ET3ESS145TC	\$1,082	A-142
00158ET3ESS145TCFL	\$1,066	A-143
00158ET3ESS56C	\$1,041	A-142
00158ET3ESS56CFL	\$1,034	A-143
00158ET3H145JM-S	\$643	A-212
00158ET3H145JM-SG	\$793	A-230
00158ET3H145JM-W22	\$643	A-212
00158ET3H145TC-S	\$504	A-42
00158ET3H145TC-W22	\$579	A-42;A-100
00158ET3H145T-S	\$480	A-33
00158ET3H145T-SG	\$620	A-61;A-182
00158ET3H145T-W22	\$551	A-33;A-93
00158ET3H56C-S	\$463	A-42;A-167
00158ET3PCT145TF1-W2	\$676	A-190
00158ET3PCT145T-W22	\$676	A-190
00158ET3V145JM-S	\$643	A-212
00158ET3V145T-SG	\$620	A-61;A-182
00158ET3W90L-W22	\$537	A-82
00158ET3WAL90LFF-W22	\$583	A-85;A-118;A-251

Part Number	List Price	Pages
00158ET3WAL90L-W22	\$524	A-82;A-248
00158NT3FVD145TC-W22	\$705	A-115;A-268
001580T1B56CFL-S	\$551	A-26;A-165
001580T1B56C-S	\$551	A-25;A-164
001580T1B56-S	\$523	A-23;A-162;A-179
001580T1B056-S	\$541	A-23;A-26;A-162;A-165;A-179
001580T1BRB056-S	\$570	A-24;A-163;A-180
001580T3E145JM-S	\$553	A-221
001580T3E145JM-SG	\$693	A-232
001580T3E145JMV-S	\$608	A-224
001580T3E145JP-S	\$553	A-225
001580T3E145JP-SG	\$693	A-233
001580T3E145TC-S	\$483	A-56
001580T3E145TC-SG	\$623	A-65;A-186
001580T3E145T-S	\$449	A-50;A-273
001580T3E145T-SG	\$589	A-65;A-186
001580T3E56CFL-S	\$389	A-60;A-171
001580T3E56C-S	\$389	A-56;A-170
001580T3E56-S	\$361	A-50;A-169
001580T3ECD145T-S	\$458	A-273
001580T3ER145TC-S	\$538	A-60
001580T3ERB56-S	\$419	A-60;A-171;A-181
001580T3H145JM-S	\$553	A-221
001580T3H145JM-SG	\$693	A-232
001580T3H145TC-S	\$483	A-56
001580T3H145T-S	\$449	A-50
001580T3H145T-SG	\$589	A-65;A-186
001580T3H56CFL-S	\$389	A-60;A-171
001580T3P145TC-S	\$483	A-56
001580T3P145T-S	\$449	A-50;A-273
001580T3V145JM-S	\$553	A-221
001580T3V145TC-SG	\$623	A-65;A-186
001580T3V145T-SG	\$589	A-65;A-186
00158ST3HIE145T-W22	\$981	A-69;A-104
00158ST3QIE145TC-W22	\$1,031	A-73;A-108
00158ST3QIE145T-W22	\$981	A-69;A-104
00158ST3QIER145TC-W2	\$1,061	A-75;A-109
00158XS1C56H	\$1,324	A-121;A-174
00158XS1C56HC	\$1,420	A-121;A-174
00158XT3E145T	\$963	A-123
00158XT3E145TC	\$1,116	A-127
00158XT3E56H	\$1,003	A-123;A-175
00158XT3E56HC	\$1,011	A-127;A-175
00158XT3ER145TC	\$1,135	A-128
00158XT3H145T	\$963	A-123
00158XT3H145TC	\$1,024	A-127
00159ET3E184T-W22	\$1,207	A-33;A-93
00159ET3EBM184T-W22	\$2,703	A-76;A-278
00159ET3H184T-W22	\$1,207	A-33;A-93
00159ET3YAL112M-W22	\$1,001	A-82;A-248
00159ST3QIE184TC-W22	\$2,081	A-73;A-108

Part Number	List Price	Pages
00159ST3QIE184T-W22	\$2,016	A-69;A-104
00159XT3E184T	\$1,901	A-123
001820S1AEC56	\$364	A-181
001820S1DEC56	\$389	A-181
00209ET3E213T-W22	\$1,848	A-33;A-93
00209ET3EBM213T-W22	\$3,345	A-76;A-278
00209ET3H213T-W22	\$1,848	A-33;A-93
00209ET3YAL132S-W22	\$1,412	A-82;A-248
00209ST3QIE213TC-W22	\$2,781	A-73;A-108
00209ST3QIE213T-W22	\$2,701	A-69;A-104
00209XT3E213T	\$2,439	A-123
00212AT3ECT184TF1-W2	\$1,010	A-193
00212AT3ECT184T-W22	\$1,010	A-193
00212AT3HCT184TF1-W2	\$1,010	A-193
00212AT3HCT184T-W22	\$1,010	A-193
00212AT3PCT184TF1-W2	\$1,010	A-193
00212AT3PCT184T-W22	\$1,010	A-193
00212ES1E213T-W22	\$1,209	A-20
00212ET3E184JM-S	\$1,021	A-212
00212ET3E184JM-W22	\$1,021	A-212
00212ET3E184JP-S	\$1,040	A-216
00212ET3E184JP-W22	\$1,040	A-216
00212ET3E184TC-S	\$747	A-43
00212ET3E184TC-W22	\$857	A-43;A-100
00212ET3E184T-S	\$713	A-33
00212ET3E184T-SG	\$883	A-61;A-182
00212ET3E184T-W22	\$819	A-33;A-93
00212ET3EAL132S-W22	\$1,166	A-82;A-248
00212ET3EBM184T-W22	\$2,369	A-76;A-278
00212ET3ECT184T-W22	\$981	A-190
00212ET3EHW184TC-S	\$1,410	A-147
00212ET3ER184TC-S	\$747	A-46
00212ET3ER184TC-W22	\$883	A-46;A-102
00212ET3H184T-S	\$713	A-33
00212ET3H184T-SG	\$883	A-61;A-182
00212ET3H184T-W22	\$819	A-33;A-93
00212ET3PCT184T-W22	\$981	A-190
00212ET3YAL132S-W22	\$1,166	A-82;A-248
002120T3E184JM-S	\$816	A-221
002120T3E184JMV-S	\$874	A-224
002120T3E184JP-S	\$863	A-225
002120T3E184TC-S	\$635	A-56
002120T3E184T-S	\$597	A-50
002120T3E184T-SG	\$767	A-65;A-186
002120T3ER184TC-S	\$635	A-60
002120T3H184TC-S	\$635	A-56
002120T3H184T-S	\$597	A-50
00212ST3HIE184T-W22	\$1,363	A-69;A-104
00212ST3QIE184TC-W22	\$1,428	A-73;A-108
00212ST3QIE184T-W22	\$1,363	A-69;A-104
00212XT3E184T	\$1,158	A-123



Part Number	List Price	Pages
00212XT3E184TC	\$1,323	A-127
00212XT3H184T	\$1,158	A-123
00218AT3ECT145TF1-W2	\$775	A-193
00218AT3ECT145T-W22	\$775	A-193
00218AT3PCT145T-W22	\$775	A-193
00218EG3EL145T-W22	\$673	A-87
00218ES1B145TC-S	\$643	A-21
00218ES1B145T-S	\$615	A-20
00218ES1E145JM-W22	\$814	A-209
00218ES1E145JP-W22	\$814	A-210
00218ES1E145T-S	\$615	A-20
00218ES1RFD145T-S	\$578	A-20;A-22;A-262
00218ES1RFD182T	\$790	A-22
00218ES1RFD182T-W22	\$790	A-20;A-262
00218ES1RFD184T-S	\$790	A-262
00218ES1RFD56H-S	\$529	A-20;A-22;A-159;A-161;A-262
00218ET3E145HP-W22	\$730	A-244
00218ET3E145JM-S	\$707	A-212
00218ET3E145JM-SG	\$858	A-230
00218ET3E145JM-W22	\$707	A-212
00218ET3E145JP-S	\$718	A-216
00218ET3E145JP-SG	\$858	A-231
00218ET3E145JP-W22	\$718	A-216
00218ET3E145TC-S	\$558	A-43
00218ET3E145TC-W22	\$640	A-43;A-100
00218ET3E145T-S	\$533	A-33
00218ET3E145T-SG	\$673	A-61;A-182
00218ET3E145T-W22	\$612	A-33;A-93
00218ET3E56CFL-S	\$506	A-46;A-168
00218ET3E56C-S	\$506	A-43;A-167
00218ET3E56-S	\$478	A-33;A-166
00218ET3EAL100LFF-W2	\$700	A-85;A-118;A-251
00218ET3EAL100L-W22	\$630	A-82;A-248
00218ET3EBM145TC-S	\$1,959	A-79;A-281
00218ET3EBM145T-S	\$1,921	A-78;A-280
00218ET3EBM145T-W22	\$1,594	A-76;A-278
00218ET3EBM56CFL-S	\$1,925	A-79;A-281
00218ET3EBMR145TC-S	\$1,959	A-79;A-281
00218ET3ECT145TF1-W2	\$752	A-190
00218ET3ECT145T-W22	\$752	A-190
00218ET3EHW145TC	\$1,060	A-147
00218ET3EHW56C	\$1,035	A-147
00218ET3EHW56CFL	\$995	A-148
00218ET3EHW145TC	\$1,020	A-148
00218ET3EPM143/5Y-W2	\$685	A-199
00218ET3ER145TC-S	\$558	A-46
00218ET3ER145TC-W22	\$659	A-46;A-102
00218ET3ESB145TCZ1-S	\$1,612	A-283
00218ET3ESB145TCZ2-S	\$1,612	A-283
00218ET3ESS145TC	\$1,257	A-142

Part Number	List Price	Pages
00218ET3ESS145TCFL	\$1,198	A-143
00218ET3ESS56C	\$1,164	A-142
00218ET3ESS56CFL	\$1,154	A-143
00218ET3H145JM-S	\$707	A-212
00218ET3H145JM-SG	\$858	A-230
00218ET3H145JM-W22	\$707	A-212
00218ET3H145TC-S	\$558	A-43
00218ET3H145TC-W22	\$640	A-43;A-100
00218ET3H145T-S	\$533	A-33
00218ET3H145T-SG	\$673	A-61;A-182
00218ET3H145T-W22	\$612	A-33;A-93
00218ET3HCT145T-W22	\$752	A-190
00218ET3PCT145TF1-W2	\$752	A-190
00218ET3PCT145T-W22	\$752	A-190
00218ET3V145JM-S	\$707	A-212
00218ET3V145T-SG	\$673	A-61;A-182
00218ET3W100L-W22	\$645	A-82
00218ET3WAL100LFF-W2	\$700	A-85;A-118;A-251
00218ET3WAL100L-W22	\$630	A-82;A-248
00218NT3FVD145TC-W22	\$928	A-115;A-268
002180T1B56CFL-S	\$654	A-26;A-165
002180T1B56C-S	\$654	A-25;A-164
002180T1B56-S	\$626	A-23;A-162;A-179
002180T1BRB056H-S	\$616	A-24;A-163;A-181
002180T3E145JM-S	\$607	A-221
002180T3E145JM-SG	\$747	A-232
002180T3E145JMV-S	\$662	A-224
002180T3E145JP-S	\$607	A-225
002180T3E145JP-SG	\$747	A-233
002180T3E145TC-S	\$526	A-56
002180T3E145TC-SG	\$666	A-65;A-186
002180T3E145T-S	\$492	A-50;A-273
002180T3E145T-SG	\$632	A-65;A-186
002180T3E56CFL-S	\$399	A-60;A-171
002180T3E56C-S	\$399	A-56;A-170
002180T3E56-S	\$371	A-50;A-169
002180T3ECD145T-S	\$502	A-273
002180T3ER145TC-S	\$581	A-60
002180T3H145JM-S	\$607	A-221
002180T3H145JM-SG	\$747	A-232
002180T3H145TC-S	\$526	A-56
002180T3H145T-S	\$492	A-50
002180T3H145T-SG	\$632	A-65;A-186
002180T3H56CFL-S	\$399	A-60;A-171
002180T3P145T-S	\$492	A-50;A-273
002180T3V145JM-S	\$607	A-221
002180T3V145TC-S	\$526	A-56
002180T3V145T-SG	\$632	A-65;A-186
00218ST3HIE145T-W22	\$1,023	A-69;A-104
00218ST3QIE145TC-W22	\$1,073	A-73;A-108
00218ST3QIE145T-W22	\$1,023	A-69;A-104

Part Number	List Price	Pages
00218ST3QIER145TC-W2	\$1,104	A-75;A-109
00218XT3E145T	\$995	A-123
00218XT3E145TC	\$1,148	A-127
00218XT3E56H	\$1,090	A-123;A-175
00218XT3E56HC	\$1,162	A-127;A-175
00218XT3ER145TC	\$1,168	A-128
00218XT3H145T	\$995	A-123
00218XT3H145TC	\$1,148	A-127
00226EP3QCT213VF1-W2	\$2,021	A-195
00226EP3QCT213V-W22	\$2,021	A-195
00236AP3EAF143TZ-S	\$578	A-264
00236AS1RAF143TZ-S	\$783	A-264
00236EG3E145T-W22	\$650	A-87
00236ES1B145T-S	\$641	A-20
00236ES1B56CFL-S	\$589	A-22;A-160
00236ES1B56C-S	\$589	A-21;A-160
00236ES1B56-S	\$561	A-20;A-159;A-178
00236ES1BJP56C-S	\$487	A-202
00236ES1BJP56J-S	\$486	A-202
00236ES1BJPR56C-S	\$494	A-202
00236ES1BJPR56J-S	\$498	A-202
00236ES1BOL56-S	\$592	A-20;A-22;A-159;A-161;A-178
00236ES1E145JP-W22	\$770	A-210
00236ES1E145T-S	\$640	A-20
00236ET3E145HP-W22	\$581	A-244
00236ET3E145JM-S	\$683	A-212
00236ET3E145JM-SG	\$834	A-230
00236ET3E145JM-W22	\$683	A-212
00236ET3E145JP-S	\$694	A-216
00236ET3E145JP-SG	\$834	A-231
00236ET3E145JP-W22	\$694	A-216
00236ET3E145TC-W22	\$619	A-43;A-100
00236ET3E145T-S	\$514	A-33
00236ET3E145T-SG	\$654	A-61;A-182
00236ET3E145T-W22	\$591	A-33;A-93
00236ET3E56CFL-S	\$517	A-46;A-168
00236ET3E56C-S	\$517	A-43;A-167
00236ET3E56-S	\$489	A-33;A-166
00236ET3EAL90L-W22	\$756	A-82;A-248
00236ET3EBM145T-W22	\$1,501	A-76;A-278
00236ET3EJP56J-S	\$535	A-204
00236ET3EJPR56C-S	\$490	A-204
00236ET3EJPR56J-S	\$525	A-204
00236ET3EPM143/5Y-W2	\$661	A-199
00236ET3ER145TC-S	\$539	A-46
00236ET3ER145TC-W22	\$638	A-46;A-102
00236ET3ESS145TC	\$1,290	A-142
00236ET3ESS145TCFL	\$1,275	A-143
00236ET3ESS56C	\$1,146	A-142
00236ET3ESS56CFL	\$1,139	A-143

Part Number	List Price	Pages
00236ET3H145JM-S	\$683	A-212
00236ET3H145JM-SG	\$834	A-230
00236ET3H145JM-W22	\$683	A-212
00236ET3H145TC-S	\$539	A-43
00236ET3H145TC-W22	\$619	A-43;A-100
00236ET3H145T-S	\$514	A-33
00236ET3H145T-SG	\$654	A-61;A-182
00236ET3H145T-W22	\$591	A-33;A-93
00236ET3H56C-S	\$517	A-43;A-167
00236ET3HJP56J-S	\$535	A-204
00236ET3HJPR56J-S	\$525	A-204
00236ET3V145JM-S	\$683	A-212
00236ET3WAL90LFF-W22	\$815	A-85;A-118;A-251
00236ET3WAL90L-W22	\$756	A-82;A-248
00236OS1BCD56-S	\$372	A-23;A-26;A-162;A-165;A-272
00236OS1BJP56J-S	\$438	A-203
00236OS1BJPR56C-S	\$424	A-203
00236OS1BJPR56J-S	\$438	A-203
00236OS3EJP56J-S	\$316	A-205
00236OS3EJPR56C-S	\$311	A-205
00236OS3EJPR56J-S	\$321	A-205
00236OS3HJP56J-S	\$316	A-205
00236OS3HJPR56C-S	\$311	A-205
00236OS3HJPR56J-S	\$321	A-205
00236OT1B56CFL-S	\$513	A-26;A-165
00236OT1B56C-S	\$513	A-25;A-164
00236OT1B56-S	\$485	A-23;A-162;A-179
00236OT1B056CFL-S	\$530	A-26;A-165
00236OT3E145JM-S	\$580	A-221
00236OT3E145JM-SG	\$720	A-232
00236OT3E145JMV-S	\$635	A-224
00236OT3E145JP-S	\$580	A-225
00236OT3E145JP-SG	\$720	A-233
00236OT3E145JPV-S	\$635	A-228
00236OT3E145TC-S	\$521	A-56
00236OT3E145T-S	\$487	A-50;A-273
00236OT3E145T-SG	\$627	A-65;A-186
00236OT3E56CFL-S	\$464	A-60;A-171
00236OT3E56C-S	\$464	A-56;A-170
00236OT3E56-S	\$436	A-50;A-169
00236OT3ER145TC-S	\$576	A-60
00236OT3H145JM-S	\$580	A-221
00236OT3H145JM-SG	\$720	A-232
00236OT3H145TC-S	\$521	A-56
00236OT3H145T-S	\$487	A-50
00236OT3V145JM-S	\$580	A-221
00236OT3V145JM-SG	\$720	A-232
00236OT3V145JP-S	\$580	A-225
00236ST3HIE145T-W22	\$1,023	A-69;A-104
00236ST3QIE145TC-W22	\$1,073	A-73;A-108

Part Number	List Price	Pages
00236ST3QIE145T-W22	\$1,023	A-69;A-104
00236XS1C56H	\$1,408	A-121;A-174
00236XS1C56HC	\$1,457	A-121;A-174
00236XT3E145T	\$935	A-123
00236XT3E145TC	\$1,045	A-127
00236XT3E56H	\$1,171	A-123;A-175
00236XT3E56HC	\$1,125	A-127;A-175
00236XT3EJPR56J	\$1,153	A-168;A-203
00236XT3H145T	\$935	A-123
00289EP3PCT145VF1-W2	\$929	A-195
00289EP3PCT145V-W22	\$929	A-195
00309ET3E215TC-W22	\$2,166	A-43;A-100
00309ET3E215T-W22	\$2,115	A-34;A-93
00309ET3EAL132M-W22	\$1,610	A-83;A-249
00309ET3EBM215T-W22	\$3,740	A-76;A-278
00309ET3H215T-W22	\$2,115	A-34;A-93
00309ET3YAL132M-W22	\$1,610	A-83;A-249
00309ST3QIE215TC-W22	\$2,963	A-73;A-108
00309ST3QIE215T-W22	\$2,883	A-69;A-104
00309XT3E215T	\$2,805	A-123
00312AT3ECT213TF1-W2	\$1,369	A-193
00312AT3ECT213T-W22	\$1,369	A-193
00312AT3HCT213T-W22	\$1,369	A-193
00312AT3PCT213TF1-W2	\$1,369	A-193
00312AT3PCT213T-W22	\$1,369	A-193
00312EG3E213T-W22	\$1,242	A-87
00312ES1E215T-W22	\$1,327	A-20
00312ES3EOW215T-W22	\$1,027	A-270
00312ET3E213JM-S	\$1,423	A-212
00312ET3E213JM-W22	\$1,423	A-212
00312ET3E213JP-S	\$1,449	A-216
00312ET3E213JP-W22	\$1,449	A-216
00312ET3E213TC-W22	\$1,180	A-43;A-100
00312ET3E213T-S	\$983	A-34
00312ET3E213T-SG	\$1,183	A-61;A-182
00312ET3E213T-W22	\$1,129	A-34;A-93
00312ET3EAL132M-W22	\$1,247	A-83;A-249
00312ET3EBM213T-W22	\$3,220	A-76;A-278
00312ET3ECT213T-W22	\$1,329	A-190
00312ET3EHW213TC-S	\$1,850	A-147
00312ET3ER213TC-S	\$1,028	A-47
00312ET3ER213TC-W22	\$1,203	A-47;A-102
00312ET3H213T-S	\$983	A-34
00312ET3H213T-SG	\$1,183	A-61;A-182
00312ET3H213T-W22	\$1,129	A-34;A-93
00312ET3HCT213T-W22	\$1,329	A-190
00312ET3PCT213T-W22	\$1,329	A-190
00312ET3YAL132M-W22	\$1,247	A-83;A-249
00312OT3E213JM-S	\$1,105	A-221
00312OT3E213JMV-S	\$1,187	A-224
00312OT3E213JP-S	\$1,095	A-225

Part Number	List Price	Pages
00312OT3E213TC-S	\$826	A-56
00312OT3E213T-S	\$775	A-51
00312OT3E213T-SG	\$975	A-65;A-186
00312OT3H213TC-S	\$826	A-56
00312OT3H213T-S	\$775	A-51
00312OT3H213T-SG	\$975	A-65;A-186
00312ST3HIE213T-W22	\$1,537	A-69;A-104
00312ST3QIE213TC-W22	\$1,617	A-73;A-108
00312ST3QIE213T-W22	\$1,537	A-69;A-104
00312XT3E213T	\$1,792	A-123
00312XT3E213TC	\$1,868	A-127
00312XT3H213T	\$1,792	A-123
00318AT3ECT182TF1-W2	\$804	A-193
00318AT3ECT182T-W22	\$804	A-193
00318AT3HCT182T-W22	\$804	A-193
00318AT3PCT182TF1-W2	\$804	A-193
00318AT3PCT182T-W22	\$804	A-193
00318EG3E182T-W22	\$729	A-87
00318ES1B184JM-W22	\$1,182	A-209
00318ES1B184JP-W22	\$1,182	A-210
00318ES1B184TC	\$913	A-21
00318ES1C184TC	\$913	A-21
00318ES1C184T-W22	\$875	A-20
00318ES1DFD182T-S	\$915	A-262
00318ES1DFD184T	\$915	A-22
00318ES1DFD184T-W22	\$915	A-20;A-262
00318ES1E184JM-W22	\$1,182	A-209
00318ES1E184JP-W22	\$1,182	A-210
00318ES1E184TC	\$913	A-21
00318ES1E184T-W22	\$874	A-20
00318ES1ER184TC	\$912	A-22
00318ET3E182HP-W22	\$923	A-244
00318ET3E182JM-S	\$1,022	A-212
00318ET3E182JM-SG	\$1,211	A-230
00318ET3E182JMV-S	\$1,080	A-212
00318ET3E182JM-W22	\$1,022	A-212
00318ET3E182JP-S	\$1,041	A-216
00318ET3E182JP-SG	\$1,211	A-231
00318ET3E182JP-W22	\$1,041	A-216
00318ET3E182TC-S	\$610	A-43
00318ET3E182TC-SG	\$780	A-61;A-182
00318ET3E182TC-W22	\$700	A-43;A-100
00318ET3E182T-S	\$577	A-34
00318ET3E182T-SG	\$747	A-61;A-182
00318ET3E182T-W22	\$663	A-34;A-93
00318ET3EAL100L-W22	\$672	A-83;A-249
00318ET3EBM182TC-S	\$2,189	A-79;A-281
00318ET3EBM182T-S	\$2,117	A-78;A-280
00318ET3EBM182T-W22	\$2,052	A-76;A-278
00318ET3EBMR182TC-S	\$2,189	A-79;A-281

Part Number	List Price	Pages
00318ET3ECT182TF1-W2	\$781	A-190
00318ET3ECT182T-W22	\$781	A-190
00318ET3EHW182TC-S	\$1,380	A-147
00318ET3EHW182T-S	\$1,315	A-148
00318ET3EHW182TC-S	\$1,259	A-148
00318ET3EPM182/4Y-W2	\$735	A-199
00318ET3ER182TC-S	\$610	A-47
00318ET3ER182TC-W22	\$721	A-47;A-102
00318ET3ESS182TC	\$1,908	A-142
00318ET3ESS182TCFL	\$1,892	A-143
00318ET3H182JM-S	\$1,022	A-212
00318ET3H182JM-SG	\$1,211	A-230
00318ET3H182JM-W22	\$1,022	A-212
00318ET3H182JP-S	\$1,041	A-216
00318ET3H182JP-W22	\$1,041	A-216
00318ET3H182TC-S	\$610	A-43
00318ET3H182TC-W22	\$700	A-43;A-100
00318ET3H182T-S	\$577	A-34
00318ET3H182T-SG	\$747	A-61;A-182
00318ET3H182T-W22	\$663	A-34;A-93
00318ET3HCT182TF1-W2	\$781	A-190
00318ET3HCT182T-W22	\$781	A-190
00318ET3PCT182TF1-W2	\$781	A-190
00318ET3PCT182T-W22	\$781	A-190
00318ET3V182JM-S	\$1,022	A-212
00318ET3V182T-SG	\$747	A-61;A-182
00318ET3WAL100LFF-W2	\$742	A-85;A-118;A-251
00318ET3WAL100L-W22	\$672	A-83;A-249
00318NT3FVD182TC-W22	\$1,150	A-115;A-268
00318OS1B184T	\$690	A-23
00318OS1C184T	\$690	A-23
00318OS1CCDOL184T	\$687	A-23;A-272
003180T3E182JM-S	\$665	A-221
003180T3E182JM-SG	\$835	A-232
003180T3E182JMV-S	\$723	A-224
003180T3E182JP-S	\$665	A-225
003180T3E182JP-SG	\$835	A-233
003180T3E182TC-S	\$562	A-56
003180T3E182TC-SG	\$732	A-65;A-186
003180T3E182T-S	\$524	A-51;A-273
003180T3E182T-SG	\$694	A-65;A-186
003180T3E56Z-S	\$481	A-51;A-169
003180T3ER182TC-S	\$620	A-60
003180T3H182JM-S	\$665	A-221
003180T3H182JM-SG	\$835	A-232
003180T3H182JP-S	\$665	A-225
003180T3H182TC-S	\$562	A-56
003180T3H182T-S	\$524	A-51
003180T3H182T-SG	\$694	A-65;A-186
003180T3P182T-S	\$524	A-51;A-273
003180T3V182JM-S	\$665	A-221

Part Number	List Price	Pages
003180T3V182JM-SG	\$835	A-232
003180T3V182TC-S	\$562	A-56
003180T3V182TC-SG	\$732	A-65;A-186
003180T3V182T-S	\$524	A-51
003180T3V182T-SG	\$694	A-65;A-186
00318ST3HIE182T-W22	\$1,224	A-69;A-104
00318ST3QIE182TC-W22	\$1,289	A-73;A-108
00318ST3QIE182T-W22	\$1,224	A-69;A-104
00318ST3QIER182TC-W2	\$1,326	A-75;A-109
00318XT3E182JP	\$1,586	A-128;A-219
00318XT3E182T	\$1,208	A-123
00318XT3E182TC	\$1,373	A-127
00318XT3ER182TC	\$1,397	A-128
00318XT3H182JP	\$1,586	A-128;A-219
00318XT3H182T	\$1,208	A-123
00318XT3H182TC	\$1,373	A-127
00326EP3QCT215V-W22	\$2,125	A-195
00336AP1DGD145TZ-S	\$910	A-264
00336AP3EAF145TZ-S	\$659	A-264
00336AP3EGD145TZ-S	\$750	A-264
00336AS1RAF145TZ-S	\$818	A-264
00336EG3E182T-W22	\$839	A-87
00336ES1B145T-S	\$830	A-20
00336ES1B182T-W22	\$882	A-20
00336ES1C145JM-W22	\$1,076	A-209
00336ES1DJP56C-S	\$548	A-202
00336ES1DJP56J-S	\$557	A-202
00336ES1DJPR56C-S	\$555	A-202
00336ES1DJPR56J-S	\$573	A-202
00336ES1E145JP-W22	\$1,076	A-210
00336ES1E145TC-S	\$858	A-21
00336ES1E145T-S	\$829	A-20
00336ES1E182T-W22	\$879	A-20
00336ES3ESA80SL	\$969	A-282
00336ES3ESA80SR	\$969	A-282
00336ET3E145HP-W22	\$863	A-244
00336ET3E145JM-S	\$897	A-212
00336ET3E145JM-W22	\$764	A-212
00336ET3E145JP-S	\$915	A-216
00336ET3E145JP-W22	\$915	A-216
00336ET3E145TC-S	\$674	A-43
00336ET3E182HP-W22	\$925	A-244
00336ET3E182JM-S	\$918	A-212
00336ET3E182JM-SG	\$1,103	A-230
00336ET3E182JM-W22	\$918	A-212
00336ET3E182JP-S	\$933	A-216
00336ET3E182JP-SG	\$1,103	A-231
00336ET3E182JP-W22	\$933	A-216
00336ET3E182TC-S	\$698	A-43
00336ET3E182TC-W22	\$802	A-43;A-100
00336ET3E182T-S	\$665	A-34

Part Number	List Price	Pages
00336ET3E182T-SG	\$835	A-61;A-182
00336ET3E182T-W22	\$763	A-34;A-93
00336ET3E56CFL-S	\$606	A-47;A-168
00336ET3E56C-S	\$606	A-43;A-167
00336ET3E56-S	\$578	A-34;A-166
00336ET3EAL100L-W22	\$805	A-83;A-249
00336ET3EBM182T-W22	\$2,290	A-76;A-278
00336ET3EHW182TC-S	\$1,409	A-147
00336ET3EHW182T-S	\$1,340	A-148
00336ET3EJP56J-S	\$634	A-204
00336ET3EJPR56C-S	\$602	A-204
00336ET3EJPR56J-S	\$624	A-204
00336ET3EPM182/4Y-W2	\$847	A-199
00336ET3ER145TC-W22	\$677	A-47;A-102
00336ET3ER182TC-S	\$698	A-47
00336ET3ER182TC-W22	\$826	A-47;A-102
00336ET3ESS145TCFL	\$1,858	A-143
00336ET3ESS182TC	\$1,989	A-142
00336ET3ESS182TCFL	\$1,974	A-143
00336ET3H145JM-S	\$897	A-212
00336ET3H145JM-W22	\$764	A-212
00336ET3H182JM-S	\$918	A-212
00336ET3H182JM-SG	\$1,103	A-230
00336ET3H182JM-W22	\$918	A-212
00336ET3H182JP-W22	\$933	A-216
00336ET3H182TC-S	\$698	A-43
00336ET3H182TC-W22	\$802	A-43;A-100
00336ET3H182T-S	\$665	A-34
00336ET3H182T-SG	\$835	A-61;A-182
00336ET3H182T-W22	\$763	A-34;A-93
00336ET3H56CFL-S	\$606	A-47;A-168
00336ET3H56C-S	\$606	A-43;A-167
00336ET3HJP56J-S	\$634	A-204
00336ET3WAL100L-W22	\$805	A-83;A-249
00336OS1B182JM	\$977	A-220
00336OS1B182T	\$607	A-23
00336OS1C182T	\$606	A-23
00336OS1CCD56-S	\$432	A-23;A-26;A-162;A-165;A-272
00336OS1DJP56J-S	\$499	A-203
00336OS1DJPR56C-S	\$482	A-203
00336OS1DJPR56J-S	\$499	A-203
00336OS3EJP56J-S	\$339	A-205
00336OS3EJPR56C-S	\$332	A-205
00336OS3EJPR56J-S	\$350	A-205
00336OS3HJP56J-S	\$339	A-205
00336OT1B56CFL-S	\$596	A-26;A-165
00336OT1B56C-S	\$596	A-25;A-164
00336OT1B56-S	\$568	A-23;A-162;A-179
00336OT1B056CFL-S	\$613	A-26;A-165
00336OT3E145JM-S	\$660	A-221
00336OT3E145JM-SG	\$800	A-232

Part Number	List Price	Pages
00336OT3E145JMV-S	\$715	A-224
00336OT3E145JP-S	\$660	A-225
00336OT3E145JP-SG	\$800	A-233
00336OT3E145JPV-S	\$715	A-228
00336OT3E145TC-S	\$579	A-56
00336OT3E145T-S	\$545	A-51;A-273
00336OT3E145T-SG	\$685	A-65;A-186
00336OT3E56CFL-S	\$513	A-60;A-171
00336OT3E56C-S	\$513	A-56;A-170
00336OT3E56-S	\$485	A-51;A-169
00336OT3ER145TC-S	\$634	A-60
00336OT3H145JM-S	\$660	A-221
00336OT3H145JM-SG	\$800	A-232
00336OT3H145JP-S	\$660	A-225
00336OT3H145TC-S	\$579	A-56
00336OT3H145T-S	\$545	A-51
00336OT3V145JM-S	\$660	A-221
00336OT3V145JM-SG	\$800	A-232
00336OT3V145JP-S	\$660	A-225
00336OT3V145TC-S	\$579	A-56
00336ST3HIE182T-W22	\$1,267	A-69;A-104
00336ST3QIE182TC-W22	\$1,332	A-73;A-108
00336ST3QIE182T-W22	\$1,267	A-69;A-104
00336XT3E182T	\$1,192	A-123
00336XT3E182TC	\$1,262	A-127
00336XT3H182T	\$1,192	A-123
00389EP3PCT182VF1-W2	\$1,369	A-195
00389EP3PCT182V-W22	\$1,369	A-195
00389EP3QCT182VF1-W2	\$1,369	A-195
00389EP3QCT182V-W22	\$1,369	A-195
00409ET3Y160M-W22	\$1,947	A-83;A-117;A-249
00412ET3EAL132M-W22	\$1,254	A-83;A-249
00412ET3YAL132MFF-W2	\$1,333	A-85;A-118;A-251
00412ET3YAL132M-W22	\$1,254	A-83;A-249
00418ET3EAL112M-W22	\$679	A-83;A-249
00418ET3YAL112MFF-W2	\$749	A-85;A-118;A-251
00418ET3YAL112M-W22	\$679	A-83;A-249
00436ET3EAL112M-W22	\$874	A-83;A-249
00436ET3YAL112MFF-W2	\$944	A-85;A-118;A-251
00436ET3YAL112M-W22	\$874	A-83;A-249
00456AP1DGD145TZ-S	\$1,025	A-264
00456AP3EGD145TZ-S	\$795	A-264
00456AP3EGD182Z-S	\$827	A-264
00509ES3EOW256T-W22	\$2,242	A-270
00509ET3E254T-W22	\$3,301	A-34;A-93
00509ET3EBM254T-W22	\$5,641	A-76;A-278
00509ET3H254T-W22	\$3,301	A-34;A-93
00509ET3Y160M-W22	\$2,244	A-83;A-117;A-249
00509ST3QIE254TC-W22	\$4,363	A-73;A-108
00509ST3QIE254T-W22	\$4,243	A-69;A-104
00509XT3E254T	\$3,953	A-123

Part Number	List Price	Pages
00512AT3ECT215TF1-W2	\$1,563	A-193
00512AT3ECT215T-W22	\$1,563	A-193
00512AT3HCT215TF1-W2	\$1,563	A-193
00512AT3HCT215T-W22	\$1,563	A-193
00512AT3PCT215TF1-W2	\$1,563	A-193
00512AT3PCT215T-W22	\$1,563	A-193
00512EG3EL215T-W22	\$1,465	A-87
00512ES1E215T-W22	\$1,588	A-20
00512ES3EOW215T-W22	\$1,170	A-270
00512ET3E215JM-S	\$1,769	A-213
00512ET3E215JM-W22	\$1,769	A-213
00512ET3E215JP-S	\$1,801	A-216
00512ET3E215JP-W22	\$1,801	A-216
00512ET3E215TC-S	\$1,206	A-43
00512ET3E215TC-W22	\$1,384	A-43;A-100
00512ET3E215T-S	\$1,160	A-34
00512ET3E215T-SG	\$1,360	A-61;A-182
00512ET3E215T-W22	\$1,332	A-34;A-93
00512ET3EBM215T-W22	\$3,406	A-76;A-278
00512ET3ECT215TF1-W2	\$1,517	A-190
00512ET3ECT215T-W22	\$1,517	A-190
00512ET3EHW215TC-S	\$2,185	A-147
00512ET3ER215TC-S	\$1,206	A-47
00512ET3ER215TC-W22	\$1,426	A-47;A-102
00512ET3H215T-S	\$1,160	A-34
00512ET3H215T-SG	\$1,360	A-61;A-182
00512ET3H215T-W22	\$1,332	A-34;A-93
00512ET3HCT215T-W22	\$1,517	A-190
00512ET3PCT215T-W22	\$1,517	A-190
00512ET3Y132M/L-W22	\$1,760	A-83;A-117;A-249
00512OT3E215JM-S	\$1,319	A-221
00512OT3E215JMV-S	\$1,401	A-224
00512OT3E215JP-S	\$1,321	A-225
00512OT3E215TC-S	\$1,108	A-57
00512OT3E215T-S	\$1,057	A-51
00512OT3E215T-SG	\$1,257	A-65;A-186
00512OT3H215TC-S	\$1,108	A-57
00512OT3H215T-S	\$1,057	A-51
00512ST3HIE215T-W22	\$1,901	A-69;A-104
00512ST3QIE215TC-W22	\$1,981	A-73;A-108
00512ST3QIE215T-W22	\$1,901	A-69;A-104
00512XT3E215T	\$1,899	A-123
00512XT3E215TC	\$1,975	A-127
00512XT3H215T	\$1,899	A-123
00518AT3ECT184TF1-W2	\$921	A-193
00518AT3ECT184T-W22	\$921	A-193
00518AT3HCT184TF1-W2	\$921	A-193
00518AT3HCT184T-W22	\$921	A-193
00518AT3PCT184TF1-W2	\$921	A-193
00518AT3PCT184T-W22	\$921	A-193
00518EG3EL184T-W22	\$849	A-87

Part Number	List Price	Pages
00518EP3EHP184TYZ7F3	\$819	A-276
00518ES1B184JM-W22	\$1,430	A-209
00518ES1B184JP-W22	\$1,430	A-210
00518ES1C184TC-W22	\$1,103	A-21
00518ES1C184T-W22	\$1,066	A-20
00518ES1DFD184T	\$1,074	A-22
00518ES1DFD184T-S	\$1,074	A-262
00518ES1DFD184T-W22	\$1,074	A-20;A-262
00518ES1DFD215T	\$1,205	A-22
00518ES1DFD215T-S	\$1,205	A-262
00518ES1DFD215T-W22	\$1,205	A-20;A-262
00518ES1DFD215Z	\$1,205	A-22
00518ES1DFD215Z-W22	\$1,205	A-20;A-262
00518ES1E184JP-W22	\$1,430	A-210
00518ES1E184TC	\$1,103	A-21
00518ES1E184T-W22	\$1,064	A-20
00518ES1EID184TC-W22	\$1,153	A-265
00518ES3ESA90LL	\$1,701	A-282
00518ES3ESA90LR	\$1,701	A-282
00518ET3E184HP-W22	\$1,045	A-244
00518ET3E184JM-S	\$1,141	A-213
00518ET3E184JM-SG	\$1,331	A-230
00518ET3E184JMV-S	\$1,199	A-213
00518ET3E184JM-W22	\$1,141	A-213
00518ET3E184JP-S	\$1,161	A-216
00518ET3E184JP-SG	\$1,331	A-231
00518ET3E184JP-W22	\$1,161	A-216
00518ET3E184TC-S	\$706	A-43
00518ET3E184TC-SG	\$876	A-61;A-182
00518ET3E184TC-W22	\$810	A-43;A-100
00518ET3E184T-S	\$672	A-34
00518ET3E184T-SG	\$842	A-61;A-182
00518ET3E184T-SRT	\$840	A-34
00518ET3E184T-W22	\$772	A-34;A-93
00518ET3EAL132S-W22	\$932	A-83;A-249
00518ET3EBM184TC-S	\$2,564	A-79;A-281
00518ET3EBM184T-S	\$2,492	A-78;A-280
00518ET3EBM184T-W22	\$2,291	A-76;A-278
00518ET3EBMR184TC-S	\$2,564	A-79;A-281
00518ET3ECT184TF1-W2	\$894	A-190
00518ET3ECT184T-W22	\$894	A-190
00518ET3EHW184TC-S	\$1,728	A-147
00518ET3EHW184T-S	\$1,640	A-148
00518ET3EHW184TC-S	\$1,592	A-148
00518ET3EID184TC-W22	\$860	A-265
00518ET3EPM182/4Y-W2	\$855	A-199
00518ET3ER184TC-S	\$706	A-47
00518ET3ER184TC-W22	\$834	A-47;A-102
00518ET3ESS184TC	\$2,230	A-142
00518ET3ESS184TCFL	\$2,215	A-143
00518ET3H184JM-S	\$1,141	A-213

Part Number	List Price	Pages
00518ET3H184JM-SG	\$1,331	A-230
00518ET3H184JM-W22	\$1,141	A-213
00518ET3H184JP-S	\$1,161	A-216
00518ET3H184JP-W22	\$1,161	A-216
00518ET3H184TC-S	\$706	A-43
00518ET3H184TC-W22	\$810	A-43;A-100
00518ET3H184T-S	\$672	A-34
00518ET3H184T-SG	\$842	A-61;A-182
00518ET3H184T-SRT	\$840	A-34
00518ET3H184T-W22	\$772	A-34;A-93
00518ET3HBM184T-W22	\$2,291	A-76;A-278
00518ET3HCT184TF1-W2	\$894	A-190
00518ET3HCT184T-W22	\$894	A-190
00518ET3P184JM-S	\$1,141	A-213
00518ET3P184JM-W22	\$1,141	A-213
00518ET3P184T-S	\$672	A-34
00518ET3P184T-W22	\$772	A-34;A-93
00518ET3PCT184TF1-W2	\$894	A-190
00518ET3PCT184T-W22	\$894	A-190
00518ET3V184JM-S	\$1,141	A-213
00518ET3V184T-SG	\$842	A-61;A-182
00518ET3Y132S-W22	\$953	A-83;A-249
00518ET3YAL132SFF-W2	\$1,011	A-85;A-118;A-251
00518ET3YAL132S-W22	\$932	A-83;A-249
00518NT3FVD184TC-W22	\$1,373	A-115;A-268
005180S1C184T	\$725	A-24
005180S1CCD184T	\$682	A-23;A-272
005180S1CCDOL184T	\$721	A-23;A-272
005180T3E184JM-S	\$849	A-221
005180T3E184JM-SG	\$1,019	A-232
005180T3E184JMV-S	\$907	A-224
005180T3E184JP-S	\$848	A-225
005180T3E184JP-SG	\$1,019	A-233
005180T3E184TC-S	\$668	A-57
005180T3E184TC-SG	\$838	A-65;A-186
005180T3E184T-S	\$630	A-51;A-273
005180T3E184T-SG	\$800	A-65;A-186
005180T3ER184TC-S	\$726	A-60
005180T3H184JM-S	\$849	A-221
005180T3H184JM-SG	\$1,019	A-232
005180T3H184JP-S	\$848	A-225
005180T3H184TC-S	\$668	A-57
005180T3H184T-S	\$630	A-51
005180T3H184T-SG	\$800	A-65;A-186
005180T3P184T-S	\$630	A-51;A-273
005180T3V184JM-S	\$849	A-221
005180T3V184TC-S	\$668	A-57
005180T3V184TC-SG	\$838	A-65;A-186
005180T3V184T-S	\$630	A-51
005180T3V184T-SG	\$800	A-65;A-186
00518ST3H1E184T-W22	\$1,371	A-69;A-104

Part Number	List Price	Pages
00518ST3QAP184T-W22	\$1,371	A-111
00518ST3QIE184TC-W22	\$1,436	A-73;A-108
00518ST3QIE184T-W22	\$1,371	A-69;A-104
00518ST3QIER184TC-W2	\$1,478	A-75;A-109
00518XT3E184JP	\$1,609	A-128;A-219
00518XT3E184T	\$1,220	A-123
00518XT3E184TC	\$1,385	A-127
00518XT3ER184TC	\$1,409	A-128
00518XT3H184JP	\$1,609	A-128;A-219
00518XT3H184T	\$1,220	A-123
00518XT3H184TC	\$1,385	A-127
00526EP3QCT254VF1-W2	\$2,424	A-195
00526EP3QCT254V-W22	\$2,424	A-195
00536EG3E184T-W22	\$960	A-87
00536ES1B184JP-W22	\$1,457	A-210
00536ES1B184T-W22	\$1,040	A-20
00536ES1C184JM-W22	\$1,457	A-209
00536ES1E184JP-W22	\$1,457	A-210
00536ES1E184TC	\$1,077	A-21
00536ES1E184T-W22	\$1,038	A-20
00536ES3ESA80ML	\$1,160	A-282
00536ES3ESA80MR	\$1,160	A-282
00536ET3E184HP-W22	\$1,084	A-244
00536ET3E184JM-S	\$1,075	A-213
00536ET3E184JM-SG	\$1,264	A-230
00536ET3E184JMV-S	\$1,247	A-213
00536ET3E184JM-W22	\$1,075	A-213
00536ET3E184JP-S	\$1,094	A-216
00536ET3E184JP-SG	\$1,264	A-231
00536ET3E184JP-W22	\$1,094	A-216
00536ET3E184TC-SG	\$963	A-61;A-182
00536ET3E184TC-W22	\$911	A-43;A-100
00536ET3E184T-S	\$760	A-34
00536ET3E184T-SG	\$930	A-61;A-182
00536ET3E184T-SRT	\$810	A-34
00536ET3E184T-W22	\$873	A-34;A-93
00536ET3EAL132S-W22	\$1,144	A-83;A-249
00536ET3EBM184T-W22	\$2,343	A-76;A-278
00536ET3EHW184TC-S	\$1,700	A-147
00536ET3EHW184T-S	\$1,628	A-148
00536ET3EHW182TC-S	\$1,600	A-148
00536ET3EPM182/4Y-W2	\$985	A-199
00536ET3ER184TC-S	\$793	A-47
00536ET3ER184TC-W22	\$938	A-47;A-102
00536ET3ESS184TC	\$2,298	A-142
00536ET3ESS184TCFL	\$2,282	A-143
00536ET3H184JM-S	\$1,075	A-213
00536ET3H184JM-SG	\$1,264	A-230
00536ET3H184JM-W22	\$1,075	A-213
00536ET3H184JP-W22	\$1,094	A-216
00536ET3H184TC-S	\$793	A-43

Part Number	List Price	Pages
00536ET3H184TC-W22	\$911	A-43;A-100
00536ET3H184T-S	\$760	A-34
00536ET3H184T-SG	\$930	A-61;A-182
00536ET3H184T-W22	\$873	A-34;A-93
00536ET3P184JM-S	\$1,075	A-213
00536ET3V184JM-S	\$1,075	A-213
00536ET3YAL132SFF-W2	\$1,223	A-85;A-118;A-251
00536ET3YAL132S-W22	\$1,144	A-83;A-249
005360S1B184JM	\$1,383	A-220
005360S1B184T	\$863	A-24
005360S1C184T	\$863	A-24
005360S1CCDW184Y-S	\$526	A-24;A-26;A-272
005360S1D184T	\$862	A-24
005360S1DCD56H-S	\$458	A-24;A-26;A-162;A-165;A-272
005360S1DCD56HZ-S	\$481	A-24;A-26;A-162;A-165;A-272
005360S3ECD56-S	\$412	A-273
005360T3E182JM-S	\$780	A-221
005360T3E182JM-SG	\$962	A-232
005360T3E182JMV-S	\$838	A-224
005360T3E182JP-S	\$792	A-225
005360T3E182JP-SG	\$962	A-233
005360T3E182JPV-S	\$850	A-228
005360T3E182TC-S	\$689	A-57
005360T3E182TC-SG	\$859	A-65;A-186
005360T3E182T-S	\$651	A-51;A-273
005360T3E182T-SG	\$821	A-65;A-186
005360T3ER182TC-S	\$747	A-60
005360T3H182JM-S	\$780	A-221
005360T3H182JM-SG	\$962	A-232
005360T3H182JP-S	\$792	A-225
005360T3H182TC-S	\$689	A-57
005360T3H182T-S	\$651	A-51
005360T3V182JM-S	\$780	A-221
005360T3V182JM-SG	\$962	A-232
005360T3V182JP-S	\$792	A-225
005360T3V182TC-S	\$689	A-57
005360T3V182T-S	\$651	A-51
00536ST3HIE184T-W22	\$1,429	A-69;A-104
00536ST3QIE184TC-W22	\$1,494	A-73;A-108
00536ST3QIE184T-W22	\$1,429	A-69;A-104
00536XT3E184T	\$1,255	A-123
00536XT3E184TC	\$1,325	A-127
00536XT3H184T	\$1,255	A-123
00536XT3H184TC	\$1,325	A-127
00589EP3HCT184VF1-W2	\$1,471	A-195
00589EP3HCT184V-W22	\$1,471	A-195
00589EP3PCT184VF1-W2	\$1,471	A-195
00589EP3PCT184V-W22	\$1,471	A-195
00589EP3PCT215V2F1-W	\$2,262	A-195

Part Number	List Price	Pages
00589EP3QCT184VF1-W2	\$1,471	A-195
00589EP3QCT184V-W22	\$1,471	A-195
00589EP3QCT215V2F1-W	\$2,262	A-195
00589EP3QCT215V2-W22	\$2,262	A-195
00709ET3E256TC-W22	\$3,726	A-43;A-100
00709ET3E256T-W22	\$3,658	A-35;A-94
00709ET3EBM256T-W22	\$6,415	A-76;A-278
00709ET3H256T-W22	\$3,658	A-35;A-94
00709ET3Y160L-W22	\$2,774	A-83;A-117;A-249
00709ST3QIE256TC-W22	\$5,160	A-73;A-108
00709ST3QIE256T-W22	\$5,040	A-69;A-104
00709XT3E256T	\$4,707	A-124
00712AT3ECT254TF1-W2	\$2,506	A-193
00712AT3PCT254TF1-W2	\$2,506	A-193
00712EG3E254T-W22	\$2,272	A-87
00712ES3E0W254T-W22	\$1,688	A-270
00712ET3E254JM-S	\$2,455	A-213
00712ET3E254JM-W22	\$2,455	A-213
00712ET3E254JP-S	\$2,495	A-217
00712ET3E254JP-W22	\$2,495	A-217
00712ET3E254TC-W22	\$2,134	A-43;A-100
00712ET3E254T-S	\$1,799	A-35
00712ET3E254T-SG	\$2,079	A-62;A-183
00712ET3E254T-W22	\$2,065	A-35;A-94
00712ET3EBM254T-W22	\$5,172	A-76;A-278
00712ET3ECT254T-W22	\$2,433	A-191
00712ET3EHW254TC-S	\$3,795	A-147
00712ET3ER254TC-S	\$1,859	A-47
00712ET3H254T-S	\$1,799	A-35
00712ET3H254T-SG	\$2,079	A-62;A-183
00712ET3H254T-W22	\$2,065	A-35;A-94
00712ET3HCT254T-W22	\$2,433	A-191
00712ET3PCT254T-W22	\$2,433	A-191
00712ET3Y160M-W22	\$2,306	A-83;A-117;A-249
007120T3E254JM-S	\$1,985	A-221
007120T3E254JM-W40	\$1,985	A-221
007120T3E254JP-S	\$2,113	A-225
007120T3E254JPV-S	\$2,211	A-228
007120T3E254JP-W40	\$2,113	A-225
007120T3E254TC-S	\$1,535	A-57
007120T3E254TC-SG	\$1,815	A-66;A-187
007120T3E254TC-W40	\$1,535	A-57
007120T3E254T-S	\$1,467	A-51
007120T3E254T-SG	\$1,747	A-66;A-187
007120T3E254T-W40	\$1,467	A-51
007120T3H254TC-S	\$1,535	A-57
007120T3H254TC-W40	\$1,535	A-57
007120T3H254T-S	\$1,467	A-51
007120T3H254T-SG	\$1,747	A-66;A-187
00712ST3HIE254T-W22	\$2,544	A-69;A-104
00712ST3QIE254TC-W22	\$2,664	A-73;A-108

Part Number	List Price	Pages
00712ST3QIE254T-W22	\$2,544	A-69;A-104
00712XT3E254T	\$2,483	A-124
00712XT3H254T	\$2,483	A-124
00718AT3ECT213TF1-W2	\$1,332	A-193
00718AT3ECT213T-W22	\$1,332	A-193
00718AT3HCT213TF1-W2	\$1,332	A-193
00718AT3HCT213T-W22	\$1,332	A-193
00718AT3PCT213TF1-W2	\$1,332	A-193
00718AT3PCT213T-W22	\$1,332	A-193
00718EG3E213T-W22	\$1,198	A-87
00718EP3EHP213TYZ7F3	\$1,054	A-276
00718ES1C215JM-W22	\$1,766	A-209
00718ES1DFD213T-S	\$1,463	A-262
00718ES1DFD215T	\$1,463	A-22
00718ES1DFD215T-W22	\$1,463	A-20;A-262
00718ES1DFD215Z	\$1,463	A-22
00718ES1DFD215Z-W22	\$1,463	A-20;A-262
00718ES1E215JP-W22	\$1,762	A-210
00718ES1E215TC	\$1,410	A-21
00718ES1E215T-W22	\$1,359	A-20
00718ES1EID215TC-W22	\$1,471	A-265
00718ES3ESA90LL	\$1,855	A-282
00718ES3ESA90LR	\$1,855	A-282
00718ET3E213HP-W22	\$1,371	A-244
00718ET3E213JM-S	\$1,519	A-213
00718ET3E213JM-SG	\$1,743	A-230
00718ET3E213JM-W22	\$1,519	A-213
00718ET3E213JP-S	\$1,543	A-217
00718ET3E213JP-SG	\$1,743	A-231
00718ET3E213JP-W22	\$1,543	A-217
00718ET3E213TC-S	\$994	A-43
00718ET3E213TC-SG	\$1,194	A-62;A-183
00718ET3E213TC-W22	\$1,141	A-43;A-100
00718ET3E213T-S	\$948	A-35
00718ET3E213T-SG	\$1,148	A-62;A-183
00718ET3E213T-W22	\$1,089	A-35;A-94
00718ET3EAL132M-W22	\$1,110	A-83;A-249
00718ET3EBM213TC-S	\$4,702	A-79;A-281
00718ET3EBM213T-S	\$4,563	A-78;A-280
00718ET3EBM213T-W22	\$2,903	A-76;A-278
00718ET3EBMR213TC-S	\$4,702	A-79;A-281
00718ET3ECT213TF1-W2	\$1,293	A-191
00718ET3ECT213T-W22	\$1,293	A-191
00718ET3EHW213TC-S	\$2,230	A-147
00718ET3EHW213T-S	\$2,046	A-148
00718ET3EHW213TC-S	\$2,011	A-148
00718ET3EID213TC-W22	\$1,202	A-265
00718ET3EPM213/5Y-W2	\$1,240	A-199
00718ET3ER213TC-S	\$994	A-47
00718ET3ER213TC-W22	\$1,175	A-47;A-102
00718ET3ESS213TC	\$3,228	A-142

Part Number	List Price	Pages
00718ET3ESS213TCFL	\$3,207	A-143
00718ET3H213JM-S	\$1,519	A-213
00718ET3H213JM-SG	\$1,743	A-230
00718ET3H213JM-W22	\$1,519	A-213
00718ET3H213JP-S	\$1,543	A-217
00718ET3H213JP-SG	\$1,743	A-231
00718ET3H213JP-W22	\$1,543	A-217
00718ET3H213TC-W22	\$1,141	A-43;A-100
00718ET3H213T-S	\$948	A-35
00718ET3H213T-SG	\$1,148	A-62;A-183
00718ET3H213T-W22	\$1,089	A-35;A-94
00718ET3HCT213TF1-W2	\$1,293	A-191
00718ET3HCT213T-W22	\$1,293	A-191
00718ET3P213JM-S	\$1,519	A-213
00718ET3P213T-S	\$948	A-35
00718ET3P213T-W22	\$1,089	A-35;A-94
00718ET3PCT213TF1-W2	\$1,293	A-191
00718ET3PCT213T-W22	\$1,293	A-191
00718ET3V213JM-S	\$1,519	A-213
00718ET3V213JP-S	\$1,543	A-217
00718ET3V213T-SG	\$1,148	A-62;A-183
00718ET3Y132M-W22	\$1,135	A-83
00718ET3YAL132MFF-W2	\$1,189	A-85;A-118;A-251
00718ET3YAL132M-W22	\$1,110	A-83;A-249
00718NT3FVD213TC-W22	\$1,803	A-115;A-268
00718OS1CCD215T	\$961	A-23;A-272
00718OS1F215T	\$961	A-24
00718OT3E213JM-S	\$1,119	A-221
00718OT3E213JM-SG	\$1,320	A-232
00718OT3E213JMV-S	\$1,201	A-224
00718OT3E213JP-S	\$1,120	A-225
00718OT3E213JP-SG	\$1,320	A-233
00718OT3E213TC-S	\$961	A-57
00718OT3E213TC-SG	\$1,161	A-66;A-187
00718OT3E213T-S	\$910	A-51;A-273
00718OT3E213T-SG	\$1,110	A-66;A-187
00718OT3ER213TC-S	\$1,043	A-60
00718OT3H213JM-S	\$1,120	A-221
00718OT3H213JM-SG	\$1,320	A-232
00718OT3H213JP-S	\$1,120	A-225
00718OT3H213JP-SG	\$1,320	A-233
00718OT3H213TC-S	\$961	A-57
00718OT3H213T-S	\$910	A-51
00718OT3H213T-SG	\$1,110	A-66;A-187
00718OT3P213T-S	\$910	A-51;A-273
00718OT3V213JM-S	\$1,119	A-221
00718OT3V213JP-S	\$1,120	A-225
00718OT3V213JP-SG	\$1,320	A-233
00718OT3V213TC-S	\$961	A-57
00718OT3V213TC-SG	\$1,161	A-66;A-187

Part Number	List Price	Pages
007180T3V213T-SG	\$1,110	A-66;A-187
00718ST3HIE213T-W22	\$1,646	A-69;A-104
00718ST3QAP213T-W22	\$1,870	A-111
00718ST3QIE213TC-W22	\$1,726	A-73;A-108
00718ST3QIE213T-W22	\$1,646	A-69;A-104
00718ST3QIER213TC-W2	\$1,776	A-75;A-109
00718XT3E213T	\$1,897	A-124
00718XT3E213TC	\$2,080	A-127
00718XT3ER213TC	\$2,118	A-128
00718XT3H213T	\$1,897	A-124
00718XT3H213TC	\$2,080	A-127
00726EP3QCT256V-W22	\$2,496	A-195
00736AP1DGD182TZ-S	\$1,296	A-264
00736AP3EGD184TZ-S	\$933	A-264
00736EG3E213T-W22	\$1,238	A-87
00736ES1B213T-W22	\$1,552	A-20
00736ES1C213JM-W22	\$1,641	A-209
00736ES1E213JP-W22	\$1,641	A-210
00736ES1E213TC-W22	\$1,598	A-21
00736ES1E213T-W22	\$1,548	A-20
00736ES3ESA80LL	\$1,642	A-282
00736ES3ESA80LR	\$1,642	A-282
00736ES3HSA80LL	\$1,642	A-282
00736ES3HSA80LR	\$1,642	A-282
00736ET3E184HP-W22	\$1,331	A-244
00736ET3E184JM-S	\$1,313	A-213
00736ET3E184JM-W22	\$1,313	A-213
00736ET3E184JP-S	\$1,339	A-217
00736ET3E184JP-W22	\$1,339	A-217
00736ET3E184TC-S	\$985	A-43
00736ET3E184TC-W22	\$1,112	A-43;A-100
00736ET3E184T-W22	\$1,074	A-35;A-94
00736ET3E213HP-W22	\$1,440	A-244
00736ET3E213JM-S	\$1,419	A-213
00736ET3E213JM-SG	\$1,645	A-230
00736ET3E213JM-W22	\$1,419	A-213
00736ET3E213JP-S	\$1,445	A-217
00736ET3E213JP-SG	\$1,645	A-231
00736ET3E213JP-W22	\$1,445	A-217
00736ET3E213TC-SG	\$1,225	A-62;A-183
00736ET3E213TC-W22	\$1,177	A-43;A-100
00736ET3E213T-S	\$980	A-35
00736ET3E213T-SG	\$1,180	A-62;A-183
00736ET3E213T-SRG	\$1,298	A-62;A-183
00736ET3E213T-SRT	\$1,078	A-35
00736ET3E213T-W22	\$1,125	A-35;A-94
00736ET3EAL132S-W22	\$1,292	A-83;A-249
00736ET3EBM213T-W22	\$3,002	A-76;A-278
00736ET3EHW184TC-S	\$2,082	A-147
00736ET3EHW184T-S	\$1,978	A-148

Part Number	List Price	Pages
00736ET3EHW213TC-S	\$2,214	A-147
00736ET3EHW213T-S	\$2,040	A-148
00736ET3EHW213TC-S	\$2,010	A-148
00736ET3EPM213/5Y-W2	\$1,248	A-199
00736ET3ER213TC-S	\$1,025	A-47
00736ET3ER213TC-W22	\$1,212	A-47;A-102
00736ET3ESS213TC	\$3,377	A-142
00736ET3ESS213TCFL	\$3,356	A-143
00736ET3H184JM-S	\$1,313	A-213
00736ET3H184JM-W22	\$1,313	A-213
00736ET3H184TC-W22	\$1,112	A-43;A-100
00736ET3H213JM-S	\$1,419	A-213
00736ET3H213JM-SG	\$1,645	A-230
00736ET3H213JM-W22	\$1,419	A-213
00736ET3H213JP-S	\$1,445	A-217
00736ET3H213JP-W22	\$1,445	A-217
00736ET3H213TC-S	\$1,025	A-43
00736ET3H213TC-W22	\$1,177	A-43;A-100
00736ET3H213T-S	\$980	A-35
00736ET3H213T-SG	\$1,180	A-62;A-183
00736ET3H213T-W22	\$1,125	A-35;A-94
00736ET3V213JM-S	\$1,419	A-213
00736ET3YAL132SFF-W2	\$1,371	A-85;A-118;A-251
00736ET3YAL132S-W22	\$1,292	A-83;A-249
00736OP3EFP184JMV-S	\$993	A-238
00736OP3EFP184TC-S	\$734	A-237
00736OP3HFP184JMV-S	\$993	A-238
00736OP3HFP184TC-S	\$734	A-237
00736OP3VFP184JMV-S	\$993	A-238
00736OP3VFP184TC-S	\$734	A-237
00736OS1C184T	\$961	A-24
00736OS1C213JM	\$1,567	A-220
00736OT3E184JM-S	\$1,086	A-221
00736OT3E184JM-SG	\$1,256	A-232
00736OT3E184JMV-S	\$1,144	A-224
00736OT3E184JP-S	\$1,086	A-225
00736OT3E184JP-SG	\$1,256	A-233
00736OT3E184JPV-S	\$1,144	A-228
00736OT3E184TC-S	\$958	A-57
00736OT3E184TC-SG	\$1,128	A-66;A-187
00736OT3E184T-S	\$920	A-51;A-273
00736OT3E184T-SG	\$1,090	A-66;A-187
00736OT3ER184TC-S	\$1,016	A-60
00736OT3H184JM-S	\$1,086	A-221
00736OT3H184JM-SG	\$1,256	A-232
00736OT3H184JMV-S	\$1,144	A-224
00736OT3H184JP-S	\$1,086	A-225
00736OT3H184TC-S	\$958	A-57
00736OT3H184T-S	\$920	A-51
00736OT3V184JM-S	\$1,086	A-221

Part Number	List Price	Pages
007360T3V184JMV-S	\$1,144	A-224
007360T3V184JP-S	\$1,086	A-225
007360T3V184JPV-S	\$1,144	A-228
00736ST3HIE213T-W22	\$1,751	A-69;A-104
00736ST3QIE213TC-W22	\$1,831	A-73;A-108
00736ST3QIE213T-W22	\$1,751	A-69;A-104
00736XT3E213T	\$1,646	A-124
00736XT3E213TC	\$1,722	A-127
00736XT3H213T	\$1,646	A-124
00789EP3HCT213V-W22	\$1,672	A-195
00789EP3PCT213VF1-W2	\$1,672	A-195
00789EP3PCT213V-W22	\$1,672	A-195
00789EP3PCT254V2F1-W	\$2,808	A-195
00789EP3PCT254V2-W22	\$2,808	A-195
00789EP3QCT213VF1-W2	\$1,672	A-195
00789EP3QCT213V-W22	\$1,672	A-195
00789EP3QCT254V2F1-W	\$2,808	A-195
00789EP3QCT254V2-W22	\$2,808	A-195
01009ES3E0W286T-W22	\$3,437	A-270
01009ET3E284T-W22	\$4,634	A-35;A-94
01009ET3H284T-W22	\$4,634	A-35;A-94
01009ST3QIE284TC-W22	\$6,136	A-73;A-108
01009ST3QIE284T-W22	\$5,936	A-70;A-105
01009XT3E284T	\$5,668	A-124
01012AT3ECT256TF1-W2	\$2,919	A-194
01012AT3PCT256TF1-W2	\$2,919	A-194
01012AT3PCT256T-W22	\$2,919	A-194
01012EG3E256T-W22	\$2,636	A-87
01012ES3E0W256T-W22	\$2,070	A-270
01012ET3E256JM-S	\$2,979	A-213
01012ET3E256JM-W22	\$2,979	A-213
01012ET3E256JP-S	\$3,103	A-217
01012ET3E256JP-W22	\$3,103	A-217
01012ET3E256TC-W22	\$2,465	A-44;A-100
01012ET3E256T-S	\$2,088	A-35
01012ET3E256T-SG	\$2,368	A-62;A-183
01012ET3E256T-W22	\$2,396	A-35;A-94
01012ET3EBM256T-W22	\$5,759	A-76;A-278
01012ET3ECT256TF1-W2	\$2,751	A-191
01012ET3ECT256T-W22	\$2,751	A-191
01012ET3EHW256TC-S	\$4,345	A-147
01012ET3ER256TC-S	\$2,148	A-47
01012ET3H256T-S	\$2,088	A-35
01012ET3H256T-SG	\$2,368	A-62;A-183
01012ET3H256T-W22	\$2,396	A-35;A-94
01012ET3HCT256T-W22	\$2,751	A-191
01012ET3PCT256T-W22	\$2,751	A-191
010120T3E256JM-S	\$2,298	A-222
010120T3E256JM-W40	\$2,298	A-222
010120T3E256JP-S	\$2,298	A-225
010120T3E256JPV-S	\$2,396	A-228

Part Number	List Price	Pages
010120T3E256JP-W40	\$2,298	A-225
010120T3E256TC-S	\$1,785	A-57
010120T3E256TC-W40	\$1,785	A-57
010120T3E256T-S	\$1,717	A-51
010120T3E256T-SG	\$1,997	A-66;A-187
010120T3E256T-W40	\$1,717	A-51
010120T3H256TC-S	\$1,785	A-57
010120T3H256TC-W40	\$1,785	A-57
010120T3H256T-S	\$1,717	A-51
010120T3H256T-SG	\$1,997	A-66;A-187
01012ST3HIE256T-W22	\$2,834	A-70;A-105
01012ST3QIE256TC-W22	\$2,954	A-73;A-108
01012ST3QIE256T-W22	\$2,834	A-70;A-105
01012XT3E256T	\$2,900	A-124
01012XT3H256T	\$2,900	A-124
01018AT3ECT215TF1-W2	\$1,519	A-194
01018AT3ECT215T-W22	\$1,519	A-194
01018AT3HCT215TF1-W2	\$1,519	A-194
01018AT3HCT215T-W22	\$1,519	A-194
01018AT3PCT215TF1-W2	\$1,519	A-194
01018AT3PCT215T-W22	\$1,519	A-194
01018EG3EL215T-W22	\$1,400	A-87
01018EP3EHP215TYZ7F3	\$1,244	A-276
01018ES1C215JM-W22	\$2,057	A-209
01018ES1DFD215T	\$1,692	A-22
01018ES1DFD215T-S	\$1,692	A-262
01018ES1DFD215T-W22	\$1,692	A-20;A-262
01018ES1E215JM-W22	\$2,057	A-209
01018ES1E215JP-W22	\$2,057	A-210
01018ES1E215TC	\$1,633	A-21
01018ES1E215T-W22	\$1,579	A-20
01018ES1EID215TC-W22	\$1,694	A-265
01018ES3ESA90LL	\$2,176	A-282
01018ES3ESA90LR	\$2,176	A-282
01018ET3E215HP-W22	\$1,641	A-244
01018ET3E215JM-S	\$1,792	A-213
01018ET3E215JM-SG	\$2,023	A-230
01018ET3E215JM-W22	\$1,792	A-213
01018ET3E215JP-S	\$1,823	A-217
01018ET3E215JP-SG	\$2,023	A-231
01018ET3E215JP-W22	\$1,823	A-217
01018ET3E215TC-S	\$1,354	A-44
01018ET3E215TC-SG	\$1,354	A-62;A-183
01018ET3E215TC-W22	\$1,325	A-44;A-100
01018ET3E215T-S	\$1,110	A-35
01018ET3E215T-SG	\$1,310	A-62;A-183
01018ET3E215T-W22	\$1,273	A-35;A-94
01018ET3EBM215TC-S	\$5,128	A-79;A-281
01018ET3EBM215T-S	\$4,989	A-78;A-280
01018ET3EBM215T-W22	\$3,474	A-76;A-278

Part Number	List Price	Pages
01018ET3EBMR215TC-S	\$5,128	A-79;A-281
01018ET3ECT215TF1-W2	\$1,475	A-191
01018ET3ECT215T-W22	\$1,475	A-191
01018ET3EHW215TC-S	\$2,568	A-147
01018ET3EHW215T-S	\$2,350	A-148
01018ET3EHW215TC-S	\$2,394	A-148
01018ET3EID215TC-W22	\$1,386	A-265
01018ET3EPM213/5Y-W2	\$1,450	A-199
01018ET3ER215TC-S	\$1,154	A-47
01018ET3ER215TC-W22	\$1,366	A-47;A-102
01018ET3ESS215TC	\$3,499	A-142
01018ET3ESS215TCFL	\$3,477	A-143
01018ET3H215JM-S	\$1,792	A-213
01018ET3H215JM-SG	\$2,023	A-230
01018ET3H215JM-W22	\$1,792	A-213
01018ET3H215JP-S	\$1,823	A-217
01018ET3H215JP-SG	\$2,023	A-231
01018ET3H215JP-W22	\$1,823	A-217
01018ET3H215TC-S	\$1,154	A-44
01018ET3H215TC-W22	\$1,325	A-44;A-100
01018ET3H215T-S	\$1,110	A-35
01018ET3H215T-SG	\$1,310	A-62;A-183
01018ET3H215T-W22	\$1,273	A-35;A-94
01018ET3HBM215T-W22	\$3,474	A-76;A-278
01018ET3HCT215TF1-W2	\$1,475	A-191
01018ET3HCT215T-W22	\$1,475	A-191
01018ET3HR215TC-S	\$1,154	A-47
01018ET3P215T-W22	\$1,273	A-35;A-94
01018ET3PCT215TF1-W2	\$1,475	A-191
01018ET3PCT215T-W22	\$1,475	A-191
01018ET3V215JM-S	\$1,792	A-213
01018ET3V215JP-S	\$1,823	A-217
01018ET3V215T-SG	\$1,310	A-62;A-183
01018NT3FVD215TC-W22	\$2,157	A-115;A-268
01018OS1CCD215T	\$1,468	A-23;A-272
01018OT3E215JM-S	\$1,364	A-222
01018OT3E215JM-SG	\$1,566	A-232
01018OT3E215JMV-S	\$1,446	A-224
01018OT3E215JP-S	\$1,366	A-225
01018OT3E215JP-SG	\$1,566	A-233
01018OT3E215TC-S	\$1,153	A-57
01018OT3E215TC-SG	\$1,353	A-66;A-187
01018OT3E215T-S	\$1,102	A-51;A-273
01018OT3E215T-SG	\$1,302	A-66;A-187
01018OT3ER215TC-S	\$1,235	A-60
01018OT3H215JM-S	\$1,366	A-222
01018OT3H215JM-SG	\$1,566	A-232
01018OT3H215JMV-S	\$1,448	A-224
01018OT3H215JP-S	\$1,366	A-225
01018OT3H215JP-SG	\$1,566	A-233
01018OT3H215TC-S	\$1,153	A-57

Part Number	List Price	Pages
01018OT3H215T-S	\$1,102	A-51
01018OT3H215T-SG	\$1,302	A-66;A-187
01018OT3P215T-S	\$1,102	A-51;A-273
01018OT3V215JP-S	\$1,366	A-225
01018OT3V215JP-SG	\$1,566	A-233
01018OT3V215TC-S	\$1,153	A-57
01018OT3V215TC-SG	\$1,353	A-66;A-187
01018OT3V215T-SG	\$1,302	A-66;A-187
01018ST3HIE215T-W22	\$1,760	A-70;A-105
01018ST3QAP215T-W22	\$1,962	A-111
01018ST3QIE215TC-W22	\$1,840	A-73;A-108
01018ST3QIE215T-W22	\$1,760	A-70;A-105
01018ST3QIER215TC-W2	\$1,893	A-75;A-109
01018XT3E215T	\$1,997	A-124
01018XT3E215TC	\$2,180	A-127
01018XT3ER215TC	\$2,220	A-128
01018XT3H215T	\$1,997	A-124
01018XT3H215TC	\$2,180	A-127
01026EP3QCT284V-W22	\$3,017	A-195
01036AP1DGD182TZ-S	\$1,338	A-264
01036AP3EGD184TZ-S	\$1,123	A-264
01036EG3E215T-W22	\$1,465	A-87
01036ES1C215JP-W22	\$2,172	A-210
01036ES1E215JP-W22	\$2,172	A-210
01036ES1E215TC	\$1,970	A-21
01036ES1E215T-W22	\$1,916	A-20
01036ES3ESA90LL	\$1,953	A-282
01036ES3ESA90LR	\$1,953	A-282
01036ES3HSA90LL	\$1,953	A-282
01036ES3HSA90LR	\$1,953	A-282
01036ET3E215HP-W22	\$1,727	A-244
01036ET3E215JM-S	\$1,769	A-213
01036ET3E215JM-SG	\$2,001	A-230
01036ET3E215JM-W22	\$1,769	A-213
01036ET3E215JP-S	\$1,801	A-217
01036ET3E215JP-SG	\$2,001	A-231
01036ET3E215JP-W22	\$1,801	A-217
01036ET3E215TC-S	\$1,205	A-44
01036ET3E215TC-SG	\$1,405	A-62;A-183
01036ET3E215TC-W22	\$1,383	A-44;A-100
01036ET3E215T-S	\$1,160	A-35
01036ET3E215T-SG	\$1,360	A-62;A-183
01036ET3E215T-SRG	\$1,496	A-62;A-183
01036ET3E215T-SRT	\$1,276	A-35
01036ET3E215T-W22	\$1,332	A-35;A-94
01036ET3EBM215T-W22	\$3,492	A-76;A-278
01036ET3EHW215TC-S	\$2,650	A-147
01036ET3EHW215TC-S	\$2,442	A-148
01036ET3EPM213/5Y-W2	\$1,477	A-199
01036ET3ER215TC-S	\$1,205	A-47
01036ET3ER215TC-W22	\$1,424	A-47;A-102

Part Number	List Price	Pages
01036ET3ESS215TC	\$3,625	A-142
01036ET3ESS215TCFL	\$3,604	A-143
01036ET3H215JM-S	\$1,769	A-213
01036ET3H215JM-SG	\$2,001	A-230
01036ET3H215JM-W22	\$1,769	A-213
01036ET3H215JP-S	\$1,801	A-217
01036ET3H215JP-W22	\$1,801	A-217
01036ET3H215TC-S	\$1,205	A-44
01036ET3H215TC-W22	\$1,383	A-44;A-100
01036ET3H215T-S	\$1,160	A-35
01036ET3H215T-SG	\$1,360	A-62;A-183
01036ET3H215T-W22	\$1,332	A-35;A-94
01036ET3V215JM-S	\$1,769	A-213
010360P3EFP213JMV-S	\$1,201	A-238
010360P3EFP213TC-S	\$901	A-237
010360P3HFP213JMV-S	\$1,201	A-238
010360P3HFP213TC-S	\$901	A-237
010360P3VFP213JMV-S	\$1,201	A-238
010360S1C215JM	\$2,067	A-220
010360T3E213JM-S	\$1,289	A-222
010360T3E213JM-SG	\$1,489	A-232
010360T3E213JMV-S	\$1,371	A-224
010360T3E213JP-S	\$1,289	A-225
010360T3E213JP-SG	\$1,489	A-233
010360T3E213JPV-S	\$1,371	A-228
010360T3E213TC-S	\$1,132	A-57
010360T3E213TC-SG	\$1,332	A-66;A-187
010360T3E213T-S	\$1,081	A-51;A-273
010360T3E213T-SG	\$1,281	A-66;A-187
010360T3ER213TC-S	\$1,214	A-60
010360T3H213JM-S	\$1,289	A-222
010360T3H213JM-SG	\$1,489	A-232
010360T3H213JMV-S	\$1,371	A-224
010360T3H213JP-S	\$1,289	A-225
010360T3H213JP-SG	\$1,489	A-233
010360T3H213JPV-S	\$1,371	A-228
010360T3H213TC-S	\$1,132	A-57
010360T3H213T-S	\$1,081	A-51
010360T3V213JM-S	\$1,289	A-222
010360T3V213JMV-S	\$1,371	A-224
010360T3V213JP-S	\$1,289	A-225
010360T3V213JPV-S	\$1,371	A-228
010360T3V213TC-S	\$1,132	A-57
01036ST3HIE215T-W22	\$1,920	A-70;A-105
01036ST3QIE215TC-W22	\$2,000	A-73;A-108
01036ST3QIE215T-W22	\$1,920	A-70;A-105
01036XT3E215T	\$1,727	A-124
01036XT3E215TC	\$1,803	A-127
01036XT3H215T	\$1,727	A-124
01036XT3H215TC	\$1,803	A-127
01089EP3HCT215VF1-W2	\$1,891	A-195

Part Number	List Price	Pages
01089EP3HCT215V-W22	\$1,891	A-195
01089EP3PCT215VF1-W2	\$1,891	A-195
01089EP3PCT215V-W22	\$1,891	A-195
01089EP3PCT256V2F1-W	\$3,052	A-195
01089EP3PCT256V2-W22	\$3,052	A-195
01089EP3QCT215VF1-W2	\$1,891	A-195
01089EP3QCT215V-W22	\$1,891	A-195
01089EP3QCT256V2F1-W	\$3,052	A-195
01089EP3QCT256V2-W22	\$3,052	A-195
01109ET3Y180L-W22	\$4,031	A-83;A-117;A-249
01112ET3Y160L-W22	\$3,160	A-83;A-117;A-249
01118ET3Y160MFF-W22	\$1,843	A-85;A-118;A-251
01118ET3Y160M-W22	\$1,726	A-83;A-117;A-249
01136ET3Y160MFF-W22	\$2,219	A-85;A-118;A-251
01136ET3Y160M-W22	\$2,102	A-83;A-117;A-249
01218ES1DFD215T-W22	\$1,889	A-262
01218ES1E215TC	\$1,827	A-21
01218ES1E215T-W22	\$1,776	A-20
01218ES1EID215TC-W22	\$1,888	A-265
01236ES1C215T-W22	\$2,015	A-20
01509ES3EOW324T-W22	\$4,293	A-270
01509ET3E286T-W22	\$5,368	A-36;A-94
01509ET3H286T-W22	\$5,368	A-36;A-94
01509ET3Y200L-W22	\$5,158	A-83;A-117;A-249
01509ST3QIE286TC-W22	\$6,942	A-73;A-108
01509ST3QIE286T-W22	\$6,742	A-70;A-105
01509XT3E286T	\$7,102	A-124
01512AT3ECT284TF1-W2	\$3,965	A-194
01512EG3E284T-W22	\$3,620	A-87
01512ES3EOW284T-W22	\$2,679	A-270
01512ET3E284JM-W22	\$3,912	A-214
01512ET3E284JP-W22	\$3,972	A-217
01512ET3E284TC-W22	\$3,388	A-44;A-100
01512ET3E284TS-W22	\$3,291	A-36;A-94
01512ET3E284TS-W22G	\$3,601	A-62;A-183
01512ET3E284T-W22	\$3,291	A-36;A-94
01512ET3E284T-W22G	\$3,601	A-62;A-183
01512ET3ECT284T-W22	\$3,850	A-191
01512ET3EPM284/6Y-W2	\$3,652	A-199
01512ET3H284TC-W22	\$3,388	A-44;A-100
01512ET3H284TS-W22	\$3,291	A-36;A-94
01512ET3H284TS-W22G	\$3,601	A-62;A-183
01512ET3H284T-W22	\$3,291	A-36;A-94
01512ET3PCT284T-W22	\$3,850	A-191
01512ET3Y180L-W22	\$3,884	A-83;A-117;A-249
015120T3E284JM-W40	\$3,164	A-222
015120T3E284JPV-W40	\$3,399	A-228
015120T3E284JP-W40	\$3,163	A-226
015120T3E284TC-W40	\$2,497	A-57
015120T3E284T-W40	\$2,412	A-51
015120T3E284T-W40G	\$2,722	A-66;A-187

Part Number	List Price	Pages
015120T3H284TC-W40	\$2,497	A-57
015120T3H284T-W40	\$2,412	A-51
01512ST3HIE284T-W22	\$4,203	A-70;A-105
01512ST3QIE284TC-W22	\$4,403	A-73;A-108
01512ST3QIE284T-W22	\$4,203	A-70;A-105
01512XT3E284T	\$4,048	A-124
01512XT3H284T	\$4,048	A-124
01515EP30FP254T-W22	\$1,811	A-242
01518AT3ECT254TF1-W2	\$2,186	A-194
01518AT3ECT254T-W22	\$2,186	A-194
01518AT3HCT254TF1-W2	\$2,186	A-194
01518AT3HCT254T-W22	\$2,186	A-194
01518AT3PCT254TF1-W2	\$2,186	A-194
01518AT3PCT254T-W22	\$2,186	A-194
01518EG3E254T-W22	\$2,033	A-87
01518ET3E254HP-W22	\$2,463	A-244
01518ET3E254JM-S	\$2,609	A-214
01518ET3E254JM-SG	\$2,933	A-230
01518ET3E254JM-W22	\$2,609	A-214
01518ET3E254JP-S	\$2,653	A-217
01518ET3E254JP-SG	\$2,933	A-231
01518ET3E254JP-W22	\$2,653	A-217
01518ET3E254TC-S	\$1,670	A-44
01518ET3E254TC-SG	\$1,950	A-62;A-183
01518ET3E254TC-W22	\$1,917	A-44;A-100
01518ET3E254T-S	\$1,610	A-36
01518ET3E254T-SG	\$1,890	A-62;A-183
01518ET3E254T-W22	\$1,848	A-36;A-94
01518ET3E254T-W22G	\$2,128	A-62;A-183
01518ET3EBM254T-S	\$6,985	A-78;A-280
01518ET3EBM254T-W22	\$5,205	A-76;A-278
01518ET3ECT254TF1-W2	\$2,122	A-191
01518ET3ECT254T-W22	\$2,122	A-191
01518ET3EHW254TC-S	\$4,826	A-147
01518ET3EHW254T-S	\$4,602	A-148
01518ET3EID254TC-W22	\$1,996	A-265
01518ET3ER254TC-S	\$1,670	A-47
01518ET3ER254TC-W22	\$1,975	A-47;A-102
01518ET3H254JM-S	\$2,609	A-214
01518ET3H254JM-SG	\$2,933	A-230
01518ET3H254JM-W22	\$2,609	A-214
01518ET3H254JP-S	\$2,653	A-217
01518ET3H254JP-W22	\$2,653	A-217
01518ET3H254TC-S	\$1,670	A-44
01518ET3H254TC-W22	\$1,917	A-44;A-100
01518ET3H254T-S	\$1,610	A-36
01518ET3H254T-SG	\$1,890	A-62;A-183
01518ET3H254T-W22	\$1,848	A-36;A-94
01518ET3HBM254T-W22	\$5,205	A-76;A-278
01518ET3HCT254TF1-W2	\$2,122	A-191
01518ET3HCT254T-W22	\$2,122	A-191

Part Number	List Price	Pages
01518ET3HR254TC-S	\$1,670	A-47
01518ET3P254T-S	\$1,610	A-36
01518ET3P254T-W22	\$1,848	A-36;A-94
01518ET3PCT254TF1-W2	\$2,122	A-191
01518ET3PCT254T-W22	\$2,122	A-191
01518ET3V254JM-S	\$2,609	A-214
01518ET3V254JP-S	\$2,653	A-217
01518ET3V254T-SG	\$1,890	A-62;A-183
01518ET3Y160LFF-W22	\$2,235	A-85;A-118;A-251
01518ET3Y160L-W22	\$2,118	A-83;A-117;A-249
01518NT3FVD254TC-W22	\$2,567	A-115;A-268
01518OT3E254JM-S	\$1,995	A-222
01518OT3E254JM-SG	\$2,275	A-232
01518OT3E254JMV-S	\$2,147	A-224
01518OT3E254JM-W40	\$1,995	A-222
01518OT3E254JP-S	\$1,995	A-226
01518OT3E254JP-SG	\$2,275	A-233
01518OT3E254JP-W40	\$1,995	A-226
01518OT3E254TC-S	\$1,545	A-57
01518OT3E254TC-SG	\$1,825	A-66;A-187
01518OT3E254TC-W40	\$1,545	A-57
01518OT3E254T-S	\$1,477	A-51;A-273
01518OT3E254T-SG	\$1,757	A-66;A-187
01518OT3E254T-W40	\$1,477	A-51
01518OT3ER254TC-S	\$1,643	A-60
01518OT3H254JM-S	\$1,995	A-222
01518OT3H254JM-SG	\$2,275	A-232
01518OT3H254JM-W40	\$1,995	A-222
01518OT3H254JP-S	\$1,995	A-226
01518OT3H254JP-W40	\$1,995	A-226
01518OT3H254TC-S	\$1,545	A-57
01518OT3H254TC-W40	\$1,545	A-57
01518OT3H254T-S	\$1,477	A-51;A-273
01518OT3H254T-SG	\$1,757	A-66;A-187
01518OT3H254T-W40	\$1,477	A-51
01518OT3P254T-S	\$1,477	A-51;A-273
01518OT3P254T-W40	\$1,477	A-51
01518OT3V254JM-S	\$1,995	A-222
01518OT3V254JM-W40	\$1,995	A-222
01518OT3V254JPV-S	\$2,093	A-228
01518OT3V254TC-S	\$1,545	A-57
01518OT3V254TC-W40	\$1,545	A-57
01518OT3V254T-S	\$1,477	A-51
01518OT3V254T-SG	\$1,757	A-66;A-187
01518ST3HIE254T-W22	\$2,257	A-70;A-105
01518ST3QAP254T-W22	\$2,524	A-111
01518ST3QIE254TC-W22	\$2,377	A-73;A-108
01518ST3QIE254T-W22	\$2,257	A-70;A-105
01518XT3E254T	\$2,653	A-124
01518XT3E254TC	\$2,976	A-127
01518XT3ER254TC	\$3,029	A-128

Part Number	List Price	Pages
01518XT3H254T	\$2,653	A-124
01518XT3H254TC	\$2,976	A-127
01526EP3HCT286VF1-W2	\$3,274	A-196
01526EP3HCT286V-W22	\$3,274	A-196
01526EP3PCT286VF1-W2	\$3,274	A-196
01526EP3PCT286V-W22	\$3,274	A-196
01526EP3QCT286VF1-W2	\$3,274	A-196
01526EP3QCT286V-W22	\$3,274	A-196
01530EP30FP254T-W22	\$1,788	A-242
01536AP1DGD215TZ-S	\$2,024	A-264
01536AP3EGD215TZ-S	\$1,408	A-264
01536EG3E254T-W22	\$2,006	A-87
01536ET3E215HP-W22	\$2,240	A-244
01536ET3E215JM-S	\$2,058	A-214
01536ET3E215JM-SG	\$2,258	A-230
01536ET3E215JM-W22	\$2,058	A-214
01536ET3E215JP-S	\$2,099	A-217
01536ET3E215JP-W22	\$2,099	A-217
01536ET3E215TC-W22	\$1,748	A-44;A-100
01536ET3E215T-W22	\$1,697	A-36;A-94
01536ET3E254HP-W22	\$2,462	A-244
01536ET3E254JM-S	\$2,214	A-214
01536ET3E254JM-SG	\$2,909	A-230
01536ET3E254JM-W22	\$2,214	A-214
01536ET3E254JP-S	\$2,629	A-217
01536ET3E254JP-SG	\$2,909	A-231
01536ET3E254JP-W22	\$2,629	A-217
01536ET3E254TC-SG	\$1,929	A-62;A-183
01536ET3E254TC-W22	\$1,893	A-44;A-100
01536ET3E254T-S	\$1,589	A-36
01536ET3E254T-SG	\$1,869	A-62;A-183
01536ET3E254T-W22	\$1,824	A-36;A-94
01536ET3E254T-W22G	\$2,104	A-62;A-183
01536ET3EBM254T-W22	\$4,745	A-76;A-278
01536ET3EHW215TC-S	\$3,250	A-147
01536ET3EHW254TC-S	\$4,859	A-147
01536ET3EHW215TC-S	\$3,052	A-148
01536ET3ER254TC-S	\$1,649	A-47
01536ET3ER254TC-W22	\$1,950	A-47;A-102
01536ET3H215JM-S	\$2,058	A-214
01536ET3H215JM-SG	\$2,258	A-230
01536ET3H215JM-W22	\$2,058	A-214
01536ET3H215JP-S	\$2,099	A-217
01536ET3H254JM-S	\$2,214	A-214
01536ET3H254JM-SG	\$2,909	A-230
01536ET3H254JM-W22	\$2,214	A-214
01536ET3H254JP-W22	\$2,629	A-217
01536ET3H254TC-S	\$1,649	A-44
01536ET3H254TC-W22	\$1,893	A-44;A-100
01536ET3H254T-S	\$1,589	A-36
01536ET3H254T-SG	\$1,869	A-62;A-183

Part Number	List Price	Pages
01536ET3H254T-W22	\$1,824	A-36;A-94
01536ET3V215JM-S	\$2,058	A-214
01536ET3V254JM-S	\$2,214	A-214
01536ET3V254JP-S	\$2,629	A-217
01536ET3Y160M-W22	\$2,413	A-83;A-117;A-249
01536OP3EFP215JMV-S	\$1,617	A-238
01536OP3EFP215TC-S	\$1,283	A-237
01536OP3HFP215JMV-S	\$1,617	A-238
01536OP3VFP215JMV-S	\$1,617	A-238
01536OP3VFP215TC-S	\$1,283	A-237
01536OT3E215JM-S	\$1,707	A-222
01536OT3E215JM-SG	\$1,907	A-232
01536OT3E215JMV-S	\$1,789	A-224
01536OT3E215JP-S	\$1,707	A-226
01536OT3E215JP-SG	\$1,907	A-233
01536OT3E215JPV-S	\$1,789	A-228
01536OT3E215TC-S	\$1,543	A-57
01536OT3E215TC-SG	\$1,743	A-66;A-187
01536OT3E215T-S	\$1,492	A-51
01536OT3E215T-SG	\$1,692	A-66;A-187
01536OT3ER215TC-S	\$1,625	A-60
01536OT3H215JM-S	\$1,707	A-222
01536OT3H215JM-SG	\$1,907	A-232
01536OT3H215JMV-S	\$1,789	A-224
01536OT3H215JP-S	\$1,707	A-226
01536OT3H215JP-SG	\$1,907	A-233
01536OT3H215JPV-S	\$1,789	A-228
01536OT3H215TC-S	\$1,543	A-57
01536OT3H215T-S	\$1,492	A-51
01536OT3V215JM-S	\$1,707	A-222
01536OT3V215JMV-S	\$1,789	A-224
01536OT3V215JP-S	\$1,707	A-226
01536OT3V215JPV-S	\$1,789	A-228
01536OT3V215TC-S	\$1,543	A-57
01536ST3HIE254T-W22	\$2,428	A-70;A-105
01536ST3QIE254TC-W22	\$2,548	A-73;A-108
01536ST3QIE254T-W22	\$2,428	A-70;A-105
01536XT3E254T	\$2,387	A-124
01536XT3E254TC	\$2,490	A-127
01536XT3H254T	\$2,387	A-124
01589EP3HCT254VF1-W2	\$2,572	A-196
01589EP3HCT254V-W22	\$2,572	A-196
01589EP3PCT254VF1-W2	\$2,572	A-196
01589EP3PCT254V-W22	\$2,572	A-196
01589EP3PCT284V2F1-W	\$3,878	A-196
01589EP3PCT284V2-W22	\$3,878	A-196
01589EP3QCT254VF1-W2	\$2,572	A-196
01589EP3QCT254V-W22	\$2,572	A-196
01589EP3QCT284V2F1-W	\$3,878	A-196
01589EP3QCT284V2-W22	\$3,878	A-196
01809ET3Y225S/M-W22	\$5,902	A-83;A-117;A-249

Part Number	List Price	Pages
01812ET3Y200L-W22	\$4,886	A-83;A-117;A-249
01818ET3Y180M-W22	\$2,689	A-83;A-117;A-249
01836ET3Y160L-W22	\$2,925	A-83;A-117;A-249
02009ES3EOW326T-W22	\$4,872	A-270
02009ET3E286T-W22	\$5,854	A-36;A-94
02009ET3E324T-W22	\$6,339	A-36;A-94
02009ET3H324T-W22	\$6,339	A-36;A-94
02009ST3QIE324TC-W22	\$8,494	A-73;A-108
02009ST3QIE324T-W22	\$8,269	A-70;A-105
02009XT3E324T	\$8,390	A-124
02012AT3ECT286TF1-W2	\$4,576	A-194
02012EG3E286T-W22	\$4,358	A-87
02012ES3EOW286T-W22	\$3,162	A-270
02012ET3E286JM-W22	\$4,940	A-214
02012ET3E286JP-W22	\$5,015	A-218
02012ET3E286TC-W22	\$4,060	A-44;A-101
02012ET3E286T-W22	\$3,962	A-36;A-94
02012ET3E286T-W22G	\$4,272	A-62;A-183
02012ET3ECT286T-W22	\$4,635	A-191
02012ET3EPM284/6Y-W2	\$4,437	A-199
02012ET3H286T-W22	\$3,962	A-36;A-94
02012ET3H286T-W22G	\$4,272	A-62;A-183
02012ET3PCT286T-W22	\$4,635	A-191
020120T3E286JM-W40	\$3,872	A-222
020120T3E286JP-W40	\$3,871	A-226
020120T3E286TC-W40	\$3,119	A-58
020120T3E286T-W40	\$3,034	A-52
020120T3E286T-W40G	\$3,344	A-66;A-187
020120T3H286TC-W40	\$3,119	A-58
020120T3H286T-W40	\$3,034	A-52
02012ST3HIE286T-W22	\$4,773	A-70;A-105
02012ST3QIE286TC-W22	\$4,973	A-73;A-108
02012ST3QIE286T-W22	\$4,773	A-70;A-105
02012XT3E286T	\$4,444	A-124
02012XT3H286T	\$4,444	A-124
02015EP30FP256T-W22	\$2,157	A-242
020150P30FP256T-W40	\$1,831	A-241
02018AT3ECT256TF1-W2	\$2,625	A-194
02018AT3ECT256T-W22	\$2,625	A-194
02018AT3HCT256TF1-W2	\$2,625	A-194
02018AT3HCT256T-W22	\$2,625	A-194
02018AT3PCT256TF1-W2	\$2,625	A-194
02018AT3PCT256T-W22	\$2,625	A-194
02018EG3E256T-W22	\$2,421	A-87
02018ET3E256HP-W22	\$2,721	A-244
02018ET3E256JM-S	\$2,857	A-214
02018ET3E256JM-SG	\$3,188	A-230
02018ET3E256JM-W22	\$2,857	A-214
02018ET3E256JP-S	\$2,908	A-218
02018ET3E256JP-SG	\$3,188	A-231
02018ET3E256JP-W22	\$2,908	A-218

Part Number	List Price	Pages
02018ET3E256TC-S	\$1,978	A-44
02018ET3E256TC-SG	\$2,258	A-62;A-183
02018ET3E256TC-W22	\$2,270	A-44;A-101
02018ET3E256T-S	\$1,918	A-36
02018ET3E256T-SG	\$2,198	A-62;A-183
02018ET3E256T-W22	\$2,201	A-36;A-94
02018ET3EBM256T-S	\$9,080	A-78;A-280
02018ET3EBM256T-W22	\$5,771	A-76;A-278
02018ET3ECT256TF1-W2	\$2,549	A-191
02018ET3ECT256T-W22	\$2,549	A-191
02018ET3EHW256TC-S	\$5,830	A-147
02018ET3EHW256T-S	\$5,571	A-148
02018ET3EID256TC-W22	\$2,349	A-265
02018ET3ER256TC-S	\$1,978	A-47
02018ET3ER256TC-W22	\$2,338	A-47;A-102
02018ET3H256JM-S	\$2,857	A-214
02018ET3H256JM-SG	\$3,188	A-230
02018ET3H256JM-W22	\$2,857	A-214
02018ET3H256JP-S	\$2,908	A-218
02018ET3H256JP-W22	\$2,908	A-218
02018ET3H256TC-S	\$1,978	A-44
02018ET3H256TC-W22	\$2,270	A-44;A-101
02018ET3H256T-S	\$1,918	A-36
02018ET3H256T-SG	\$2,198	A-62;A-183
02018ET3H256T-W22	\$2,201	A-36;A-94
02018ET3HCT256TF1-W2	\$2,549	A-191
02018ET3HCT256T-W22	\$2,549	A-191
02018ET3P256T-W22	\$2,201	A-36;A-94
02018ET3PCT256TF1-W2	\$2,549	A-191
02018ET3PCT256T-W22	\$2,549	A-191
02018ET3V256JM-S	\$2,857	A-214
02018ET3V256JP-S	\$2,908	A-218
02018ET3V256T-SG	\$2,198	A-62;A-183
02018NT3FVD256TC-W22	\$3,747	A-115;A-268
020180P3EFP256T-W40	\$1,526	A-235
020180T3E256JM-S	\$2,413	A-222
020180T3E256JM-SG	\$2,693	A-232
020180T3E256JMV-S	\$2,580	A-224
020180T3E256JM-W40	\$2,413	A-222
020180T3E256JP-S	\$2,413	A-226
020180T3E256JP-SG	\$2,693	A-233
020180T3E256JPV-S	\$2,580	A-228
020180T3E256JP-W40	\$2,413	A-226
020180T3E256TC-S	\$1,900	A-58
020180T3E256TC-SG	\$2,180	A-66;A-187
020180T3E256TC-W40	\$1,900	A-58
020180T3E256T-S	\$1,832	A-52;A-273
020180T3E256T-SG	\$2,112	A-66;A-187
020180T3E256T-W40	\$1,832	A-52
020180T3ER256TC-S	\$1,998	A-60
020180T3H256JM-S	\$2,413	A-222

Part Number	List Price	Pages
020180T3H256JM-SG	\$2,693	A-232
020180T3H256JM-W40	\$2,413	A-222
020180T3H256JP-S	\$2,413	A-226
020180T3H256JP-W40	\$2,413	A-226
020180T3H256TC-S	\$1,900	A-58
020180T3H256TC-W40	\$1,900	A-58
020180T3H256T-S	\$1,832	A-52
020180T3H256T-SG	\$2,112	A-66;A-187
020180T3H256T-W40	\$1,832	A-52
020180T3P256T-S	\$1,832	A-52
020180T3P256T-W40	\$1,832	A-52
020180T3V256TC-S	\$1,900	A-58
020180T3V256TC-SG	\$2,180	A-66;A-187
020180T3V256TC-W40	\$1,900	A-58
020180T3V256T-S	\$1,832	A-52
020180T3V256T-SG	\$2,112	A-66;A-187
02018ST3HIE256T-W22	\$2,597	A-70;A-105
02018ST3QAP256T-W22	\$2,881	A-111
02018ST3QIE256TC-W22	\$2,717	A-73;A-108
02018ST3QIE256T-W22	\$2,597	A-70;A-105
02018XT3E256T	\$3,008	A-124
02018XT3E256TC	\$3,331	A-127
02018XT3ER256TC	\$3,391	A-128
02018XT3H256T	\$3,008	A-124
02018XT3H256TC	\$3,111	A-127
02026EP3QCT324V-W22	\$4,101	A-196
02030EP30FP256T-W22	\$2,334	A-242
020300P30FP256T-W40	\$1,690	A-241
02036EG3E256T-W22	\$2,620	A-87
02036ET3E254HP-W22	\$2,738	A-244
02036ET3E256HP-W22	\$2,955	A-244
02036ET3E256JM-S	\$2,965	A-214
02036ET3E256JM-SG	\$3,298	A-230
02036ET3E256JM-W22	\$2,965	A-214
02036ET3E256JP-S	\$3,018	A-218
02036ET3E256JP-SG	\$3,298	A-231
02036ET3E256JP-W22	\$3,018	A-218
02036ET3E256TC-SG	\$2,416	A-62;A-183
02036ET3E256TC-W22	\$2,451	A-44;A-101
02036ET3E256T-S	\$2,076	A-36
02036ET3E256T-SG	\$2,356	A-62;A-183
02036ET3E256T-W22	\$2,382	A-36;A-94
02036ET3E256T-W22G	\$2,662	A-62;A-183
02036ET3EBM256T-W22	\$5,768	A-76;A-278
02036ET3EHW256TC-S	\$5,772	A-147
02036ET3ER256TC-S	\$2,136	A-47
02036ET3ER256TC-W22	\$2,525	A-47;A-102
02036ET3H256JM-S	\$2,965	A-214
02036ET3H256JM-SG	\$3,298	A-230
02036ET3H256JM-W22	\$2,965	A-214
02036ET3H256JP-S	\$3,018	A-218

Part Number	List Price	Pages
02036ET3H256JP-W22	\$3,018	A-218
02036ET3H256TC-S	\$2,136	A-44
02036ET3H256TC-W22	\$2,451	A-44;A-101
02036ET3H256T-S	\$2,076	A-36
02036ET3H256T-SG	\$2,356	A-62;A-183
02036ET3H256T-W22	\$2,382	A-36;A-94
02036ET3V256JM-S	\$2,965	A-214
020360P3EFP254JMV-S	\$2,092	A-238
020360P3EFP254TC-S	\$1,469	A-237
020360P3EFP254TC-W40	\$1,469	A-237
020360P3EFP254T-W40	\$1,469	A-235
020360P3HFP254JMV-S	\$2,092	A-238
020360P3HFP254TC-S	\$1,469	A-237
020360P3HFP254TC-W40	\$1,469	A-237
020360P3VFP254JMV-S	\$2,092	A-238
020360P3VFP254TC-S	\$1,469	A-237
020360P3VFP254TC-W40	\$1,469	A-237
020360T3E254JM-S	\$2,107	A-222
020360T3E254JM-SG	\$2,387	A-232
020360T3E254JMV-S	\$2,205	A-224
020360T3E254JM-W40	\$2,107	A-222
020360T3E254JP-S	\$2,106	A-226
020360T3E254JP-SG	\$2,387	A-233
020360T3E254JPV-S	\$2,204	A-228
020360T3E254JP-W40	\$2,106	A-226
020360T3E254TC-S	\$1,828	A-58
020360T3E254TC-SG	\$2,108	A-66;A-187
020360T3E254TC-W40	\$1,828	A-58
020360T3E254T-S	\$1,760	A-52;A-273
020360T3E254T-SG	\$2,040	A-66;A-187
020360T3E254T-W40	\$1,760	A-52
020360T3ER254TC-S	\$1,926	A-60
020360T3H254JM-S	\$2,107	A-222
020360T3H254JM-SG	\$2,387	A-232
020360T3H254JMV-S	\$2,205	A-224
020360T3H254JM-W40	\$2,107	A-222
020360T3H254JP-S	\$2,106	A-226
020360T3H254JPV-S	\$2,204	A-228
020360T3H254JP-W40	\$2,106	A-226
020360T3H254TC-S	\$1,828	A-58
020360T3H254TC-W40	\$1,828	A-58
020360T3H254T-S	\$1,760	A-52
020360T3H254T-W40	\$1,760	A-52
020360T3V254JM-S	\$2,107	A-222
020360T3V254JMV-S	\$2,205	A-224
020360T3V254JM-W40	\$2,107	A-222
020360T3V254JP-S	\$2,106	A-226
020360T3V254JPV-S	\$2,204	A-228
020360T3V254JP-W40	\$2,106	A-226
02036ST3HIE256T-W22	\$2,957	A-70;A-105
02036ST3QIE256TC-W22	\$3,077	A-73;A-108

Part Number	List Price	Pages
02036ST3QIE256T-W22	\$2,957	A-70;A-105
02036XT3E256T	\$3,083	A-124
02036XT3H256T	\$3,083	A-124
02089EP3HCT256VF1-W2	\$2,923	A-196
02089EP3HCT256V-W22	\$2,923	A-196
02089EP3PCT256VF1-W2	\$2,923	A-196
02089EP3PCT256V-W22	\$2,923	A-196
02089EP3PCT286V2F1-W	\$4,827	A-196
02089EP3PCT286V2-W22	\$4,827	A-196
02089EP3QCT256VF1-W2	\$2,923	A-196
02089EP3QCT256V-W22	\$2,923	A-196
02089EP3QCT286V2F1-W	\$4,827	A-196
02089EP3QCT286V2-W22	\$4,827	A-196
02209ET3Y225S/M-W22	\$7,506	A-83;A-117;A-249
02212ET3Y200L-W22	\$4,924	A-83;A-117;A-249
02218ET3Y180LFF-W22	\$3,361	A-85;A-118;A-251
02218ET3Y180L-W22	\$3,225	A-83;A-117;A-249
02236ET3Y180M-W22	\$3,492	A-83;A-117;A-249
02509ET3E326T-W22	\$7,315	A-36;A-95
02509ET3H326T-W22	\$7,315	A-36;A-95
02509ST3QIE326TC-W22	\$9,063	A-73;A-108
02509ST3QIE326T-W22	\$8,838	A-70;A-105
02509XT3E326T	\$10,512	A-124
02512AT3ECT324TF1-W2	\$5,709	A-194
02512AT3HCT324TF1-W2	\$5,709	A-194
02512EG3E324T-W22	\$5,211	A-87
02512ES3EOW324T-W22	\$3,887	A-270
02512ET3E324JM-W22	\$5,546	A-214
02512ET3E324JP-W22	\$5,972	A-218
02512ET3E324TC-W22	\$4,858	A-44;A-101
02512ET3E324T-W22	\$4,737	A-36;A-95
02512ET3E324T-W22G	\$5,137	A-62;A-183
02512ET3ECT324T-W22	\$5,543	A-191
02512ET3EPM324/6Y-W2	\$5,353	A-199
02512ET3H324T-W22	\$4,737	A-36;A-95
02512ET3H324T-W22G	\$5,137	A-62;A-183
02512ET3PCT324T-W22	\$5,543	A-191
025120T3E324JM-W40	\$4,306	A-222
025120T3E324JP-W40	\$4,306	A-226
025120T3E324TC-W40	\$3,619	A-58
025120T3E324T-W40	\$3,519	A-52
025120T3E324T-W40G	\$3,919	A-66;A-187
02512ST3HIE324T-W22	\$5,211	A-70;A-105
02512ST3QIE324TC-W22	\$5,436	A-73;A-108
02512ST3QIE324T-W22	\$5,211	A-70;A-105
02512XT3E324T	\$5,375	A-124
02512XT3H324T	\$5,375	A-124
02515EP30FP284TS-W22	\$2,688	A-242
025150P30FP284TS-W40	\$2,069	A-241
02518AT3ECT284TF1-W2	\$3,333	A-194
02518AT3ECT284T-W22	\$3,333	A-194

Part Number	List Price	Pages
02518AT3HCT284TF1-W2	\$3,333	A-194
02518AT3HCT284T-W22	\$3,333	A-194
02518AT3PCT284TF1-W2	\$3,333	A-194
02518AT3PCT284T-W22	\$3,333	A-194
02518EG3E284T-W22	\$3,017	A-87
02518ET3E284HPH-W22	\$3,624	A-244
02518ET3E284HP-W22	\$3,624	A-244
02518ET3E284JM-W22	\$3,734	A-214
02518ET3E284JP-W22	\$3,797	A-218
02518ET3E284TC-W22	\$2,840	A-44;A-101
02518ET3E284TS-W22	\$2,743	A-36;A-95
02518ET3E284T-W22	\$2,743	A-36;A-95
02518ET3E284T-W22G	\$3,053	A-62;A-183
02518ET3EBM284T-W22	\$6,796	A-76;A-278
02518ET3ECT284TF1-W2	\$3,236	A-191
02518ET3ECT284T-W22	\$3,236	A-191
02518ET3EID284TC-W22	\$2,947	A-265
02518ET3EPM284/6Y-W2	\$3,071	A-199
02518ET3ER284TC-W22	\$2,925	A-47;A-102
02518ET3H284JM-W22	\$3,734	A-214
02518ET3H284JP-W22	\$3,797	A-218
02518ET3H284TC-W22	\$2,840	A-44;A-101
02518ET3H284T-W22	\$2,743	A-36;A-95
02518ET3H284T-W22G	\$3,053	A-62;A-183
02518ET3HCT284TF1-W2	\$3,236	A-191
02518ET3HCT284T-W22	\$3,236	A-191
02518ET3PCT284TF1-W2	\$3,236	A-191
02518ET3PCT284T-W22	\$3,236	A-191
02518ET3V284T-W22G	\$3,053	A-62;A-183
025180P3EFP284TS-W40	\$1,799	A-235
025180P3VFP284TS-W40	\$1,799	A-235
025180T3E284JMV-W40	\$3,137	A-224
025180T3E284JM-W40	\$2,912	A-222
025180T3E284JP-G	\$3,221	A-233
025180T3E284JPV-W40	\$3,137	A-228
025180T3E284JP-W40	\$2,911	A-226
025180T3E284TC-W40	\$2,245	A-58
025180T3E284TC-W40G	\$2,555	A-66;A-187
025180T3E284TS-W40	\$2,160	A-52
025180T3E284T-W40	\$2,160	A-52
025180T3E284T-W40G	\$2,470	A-66;A-187
025180T3H284JM-W40	\$2,912	A-222
025180T3H284JP-W40	\$2,911	A-226
025180T3H284TC-W40	\$2,245	A-58
025180T3H284TS-W40	\$2,160	A-52
025180T3H284T-W40	\$2,160	A-52
025180T3H284T-W40G	\$2,470	A-66;A-187
025180T3P284T-W40	\$2,160	A-52
025180T3V284TC-W40	\$2,245	A-58
025180T3V284TS-W40	\$2,160	A-52
025180T3V284T-W40G	\$2,470	A-66;A-187

Part Number	List Price	Pages
02518ST3HIE284T-W22	\$2,926	A-70;A-105
02518ST3QAP284T-W22	\$3,236	A-111
02518ST3QIE284TC-W22	\$3,126	A-73;A-108
02518ST3QIE284T-W22	\$2,926	A-70;A-105
02518XT3E284T	\$3,886	A-124
02518XT3E284TC	\$4,262	A-127
02518XT3ER284TC	\$4,340	A-128
02518XT3H284T	\$3,886	A-124
02518XT3H284TC	\$4,262	A-127
02526EP3QCT326V-W22	\$6,222	A-196
02530EP30FP284TS-W22	\$2,938	A-242
025300P30FP256T-W40	\$2,051	A-241
02536EG3E284TS-W22	\$3,298	A-87
02536ET3E256HP-W22	\$3,336	A-244
02536ET3E256JM-S	\$3,231	A-214
02536ET3E256JM-W22	\$3,231	A-214
02536ET3E256JP-S	\$3,296	A-218
02536ET3E256JP-W22	\$3,296	A-218
02536ET3E256T-S	\$2,487	A-36
02536ET3E284HPH-W22	\$3,627	A-244
02536ET3E284HP-W22	\$3,627	A-244
02536ET3E284JM-W22	\$3,619	A-214
02536ET3E284JP-W22	\$3,679	A-218
02536ET3E284TSC-W22	\$3,096	A-44;A-101
02536ET3E284TS-W22	\$2,998	A-36;A-95
02536ET3E284TS-W22G	\$3,308	A-62;A-183
02536ET3EHW256TC-S	\$6,887	A-147
02536ET3ER284TSC-W22	\$3,187	A-47;A-102
02536ET3H256JM-S	\$3,231	A-214
02536ET3H256JM-W22	\$3,231	A-214
02536ET3H256JP-S	\$3,296	A-218
02536ET3H256JP-W22	\$3,296	A-218
02536ET3H284JM-W22	\$3,619	A-214
02536ET3H284JP-W22	\$3,679	A-218
02536ET3H284TSC-W22	\$3,096	A-44;A-101
02536ET3H284TS-W22	\$2,998	A-36;A-95
02536ET3H284TS-W22G	\$3,308	A-62;A-183
02536ET3V256JM-S	\$3,231	A-214
025360P3EFP256JMV-S	\$2,352	A-238
025360P3EFP256TC-S	\$1,783	A-237
025360P3EFP256TC-W40	\$1,783	A-237
025360P3EFP256T-S	\$1,783	A-235
025360P3EFP256T-W40	\$1,783	A-235
025360P3HFP256JMV-S	\$2,352	A-238
025360P3HFP256T-S	\$1,783	A-235
025360P3HFP256T-W40	\$1,783	A-235
025360P3VFP256JMV-S	\$2,352	A-238
025360P3VFP256TC-S	\$1,783	A-237
025360P3VFP256TC-W40	\$1,783	A-237
025360P3VFP256T-S	\$1,783	A-235
025360T3E256JM-S	\$2,598	A-222

Part Number	List Price	Pages
025360T3E256JM-SG	\$2,879	A-232
025360T3E256JMV-S	\$2,696	A-224
025360T3E256JM-W40	\$2,598	A-222
025360T3E256JP-S	\$2,599	A-226
025360T3E256JP-SG	\$2,879	A-233
025360T3E256JPV-S	\$2,697	A-228
025360T3E256JP-W40	\$2,599	A-226
025360T3E256TC-S	\$2,207	A-58
025360T3E256TC-SG	\$2,487	A-66;A-187
025360T3E256TC-W40	\$2,207	A-58
025360T3E256T-S	\$2,139	A-52;A-273
025360T3E256T-SG	\$2,419	A-66;A-187
025360T3E256T-W40	\$2,139	A-52
025360T3H256JM-S	\$2,598	A-222
025360T3H256JM-SG	\$2,879	A-232
025360T3H256JMV-S	\$2,696	A-224
025360T3H256JM-W40	\$2,598	A-222
025360T3H256JP-S	\$2,599	A-226
025360T3H256JPV-S	\$2,697	A-228
025360T3H256JP-W40	\$2,599	A-226
025360T3H256TC-S	\$2,207	A-58
025360T3H256TC-W40	\$2,207	A-58
025360T3H256T-S	\$2,139	A-52
025360T3H256T-W40	\$2,139	A-52
025360T3V256JMV-S	\$2,696	A-224
025360T3V256JP-S	\$2,599	A-226
025360T3V256JPV-S	\$2,697	A-228
025360T3V256JP-W40	\$2,599	A-226
02536ST3HIE284TS-W22	\$3,368	A-70;A-105
02536ST3QIE284TSC-W2	\$3,568	A-73;A-108
02536ST3QIE284TS-W22	\$3,368	A-70;A-105
02536XT3E284TS	\$4,188	A-124
02536XT3H284TS	\$4,188	A-124
02589EP3HCT286VF1-W2	\$4,199	A-196
02589EP3HCT286V-W22	\$4,199	A-196
02589EP3PCT286VF1-W2	\$4,199	A-196
02589EP3PCT324V2F1-W	\$5,826	A-196
02589EP3PCT324V2-W22	\$5,826	A-196
02589EP3QCT286VF1-W2	\$4,199	A-196
02589EP3QCT286V-W22	\$4,199	A-196
02589EP3QCT324V2F1-W	\$5,826	A-196
02589EP3QCT324V2-W22	\$5,826	A-196
03009ET3E364T-W22	\$11,215	A-37;A-95
03009ET3Y250S/M-W22	\$8,858	A-84;A-117;A-250
03009ST3QIE364TC-W22	\$13,524	A-73;A-108
03009ST3QIE364T-W22	\$13,149	A-70;A-105
03009XT3E364T	\$15,071	A-124
03012AT3PCT326TF1-W2	\$6,246	A-194
03012EG3E326T-W22	\$5,800	A-87
03012ES3EOW326T-W22	\$4,515	A-270
03012ET3E326JM-W22	\$6,686	A-214

Part Number	List Price	Pages
03012ET3E326JP-W22	\$6,690	A-218
03012ET3E326TC-W22	\$5,394	A-44;A-101
03012ET3E326TC-W22G	\$5,794	A-63;A-184
03012ET3E326T-W22	\$5,273	A-37;A-95
03012ET3E326T-W22G	\$5,673	A-63;A-184
03012ET3ECT326T-W22	\$6,064	A-192
03012ET3EPM324/6Y-W2	\$5,906	A-199
03012ET3ER326TSC-W22	\$5,768	A-47;A-102
03012ET3H326T-W22	\$5,273	A-37;A-95
03012ET3H326T-W22G	\$5,673	A-63;A-184
03012ET3PCT326T-W22	\$6,064	A-192
03012ET3Y225S/M-W22	\$7,689	A-84;A-117;A-250
03012OT3E326JM-W40	\$4,741	A-222
03012OT3E326JP-W40	\$4,980	A-226
03012OT3E326TC-W40	\$3,990	A-58
03012OT3E326T-W40	\$3,890	A-52
03012OT3E326T-W40G	\$4,290	A-67;A-188
03012OT3H326T-W40	\$3,890	A-52
03012ST3HIE326T-W22	\$5,359	A-70;A-105
03012ST3QIE326TC-W22	\$5,584	A-73;A-108
03012ST3QIE326T-W22	\$5,359	A-70;A-105
03012XT3E326T	\$6,196	A-124
03012XT3H326T	\$6,196	A-124
03015EP30FP286TS-W22	\$3,159	A-242
030150P30FP286TS-W40	\$2,425	A-241
03018AT3ECT286TF1-W2	\$3,850	A-194
03018AT3ECT286T-W22	\$3,850	A-194
03018AT3HCT286TF1-W2	\$3,850	A-194
03018AT3HCT286T-W22	\$3,850	A-194
03018AT3PCT286TF1-W2	\$3,850	A-194
03018AT3PCT286T-W22	\$3,850	A-194
03018EG3E286T-W22	\$3,545	A-87
03018ET3E286HPH-W22	\$3,967	A-244
03018ET3E286HP-W22	\$3,967	A-244
03018ET3E286JM-W22	\$4,096	A-214
03018ET3E286JP-W22	\$4,167	A-218
03018ET3E286TC-W22	\$3,321	A-44;A-101
03018ET3E286TC-W22G	\$3,632	A-63;A-184
03018ET3E286TS-W22	\$3,223	A-37;A-95
03018ET3E286T-W22	\$3,223	A-37;A-95
03018ET3E286T-W22G	\$3,533	A-63;A-184
03018ET3EBM286T-W22	\$7,276	A-76;A-278
03018ET3ECT286TF1-W2	\$3,738	A-192
03018ET3ECT286T-W22	\$3,738	A-192
03018ET3EPM284/6Y-W2	\$3,610	A-199
03018ET3ER286TC-W22	\$3,421	A-47;A-102
03018ET3H286JM-W22	\$4,096	A-214
03018ET3H286JP-W22	\$4,167	A-218
03018ET3H286TC-W22	\$3,321	A-44;A-101
03018ET3H286T-W22	\$3,223	A-37;A-95
03018ET3H286T-W22G	\$3,533	A-63;A-184

Part Number	List Price	Pages
03018ET3HCT286TF1-W2	\$3,738	A-192
03018ET3HCT286T-W22	\$3,738	A-192
03018ET3PCT286TF1-W2	\$3,738	A-192
03018ET3PCT286T-W22	\$3,738	A-192
03018ET3V286T-W22G	\$3,533	A-63;A-184
03018ET3Y200L-W22	\$4,312	A-84;A-117;A-250
030180P3EFP286JMV-W4	\$3,175	A-238
030180P3EFP286TS-W40	\$2,108	A-235
030180P3HFP286JMV-W4	\$3,403	A-238
030180P3VFP286TS-W40	\$2,108	A-235
030180T3E286JM-W40	\$3,368	A-222
030180T3E286JPV-W40	\$3,609	A-228
030180T3E286JP-W40	\$3,367	A-226
030180T3E286TC-W40	\$2,615	A-58
030180T3E286TC-W40G	\$2,925	A-67;A-188
030180T3E286TS-W40	\$2,530	A-52
030180T3E286T-W40	\$2,530	A-52
030180T3E286T-W40G	\$2,840	A-67;A-188
030180T3H286JMV-W40	\$3,610	A-224
030180T3H286JM-W40	\$3,368	A-222
030180T3H286JP-W40	\$3,367	A-226
030180T3H286TC-W40	\$2,615	A-58
030180T3H286TS-W40	\$2,530	A-52
030180T3H286T-W40	\$2,530	A-52
030180T3H286T-W40G	\$2,840	A-67;A-188
030180T3P286T-W40	\$2,530	A-52
030180T3V286JP-W40	\$3,367	A-226
030180T3V286TC-W40	\$2,615	A-58
030180T3V286TS-W40	\$2,590	A-52
030180T3V286T-W40G	\$2,840	A-67;A-188
03018ST3HIE286T-W22	\$3,509	A-70;A-105
03018ST3QAP286T-W22	\$3,824	A-111
03018ST3QIE286TC-W22	\$3,709	A-73;A-108
03018ST3QIE286T-W22	\$3,509	A-70;A-105
03018XT3E286T	\$4,296	A-124
03018XT3E286TC	\$4,672	A-128
03018XT3ER286TC	\$4,758	A-128
03018XT3H286T	\$4,296	A-124
03026EP3QCT364V-W22	\$7,435	A-197
03030EP30FP286TS-W22	\$3,490	A-242
030300P30FP284TS-W40	\$2,338	A-241
03036EG3E286TS-W22	\$3,917	A-87
03036ET3E286HPH-W22	\$4,365	A-244
03036ET3E286HP-W22	\$4,365	A-244
03036ET3E286JM-W22	\$4,539	A-214
03036ET3E286JP-W22	\$4,614	A-218
03036ET3E286TSC-W22	\$3,659	A-44;A-101
03036ET3E286TS-W22	\$3,561	A-37;A-95
03036ET3E286TS-W22G	\$3,871	A-63;A-184
03036ET3ER286TSC-W22	\$3,767	A-47;A-102
03036ET3H286JM-W22	\$4,539	A-214



Part Number	List Price	Pages
03036ET3H286JP-W22	\$4,614	A-218
03036ET3H286TSC-W22	\$3,659	A-44;A-101
03036ET3H286TS-W22	\$3,561	A-37;A-95
03036ET3H286TS-W22G	\$3,871	A-63;A-184
03036ET3Y200L-W22	\$4,877	A-84;A-117;A-250
03036OP3EFP284JMV-W4	\$2,954	A-238
03036OP3EFP284TSC-W4	\$2,033	A-237
03036OP3EFP284TS-W40	\$2,033	A-235
03036OP3HFP284JMV*	\$3,181	A-238
03036OP3HFP284JMV-W4	\$3,181	A-238
03036OP3HFP284TS-W40	\$2,033	A-235
03036OP3VFP284JMV-W4	\$2,954	A-238
03036OP3VFP284TSC-W4	\$2,033	A-237
03036OP3VFP284TS-W40	\$2,033	A-235
03036OT3E284JM-W40	\$3,185	A-222
03036OT3E284JPV*	\$3,422	A-228
03036OT3E284JPV-W40	\$3,422	A-228
03036OT3E284JP-W40	\$3,185	A-226
03036OT3E284TSC-W40	\$2,572	A-58
03036OT3E284TS-W40	\$2,487	A-52
03036OT3E284TS-W40G	\$2,797	A-67;A-188
03036OT3H284JMV-W40	\$3,422	A-224
03036OT3H284JM-W40	\$3,185	A-222
03036OT3H284JPV-W40	\$3,422	A-228
03036OT3H284JP-W40	\$3,185	A-226
03036OT3H284TSC-W40	\$2,572	A-58
03036OT3H284TS-W40	\$2,487	A-52
03036OT3V284JM-W40	\$3,185	A-222
03036OT3V284JPV*	\$3,422	A-228
03036OT3V284JPV-W40	\$3,422	A-228
03036OT3V284JP-W40	\$3,185	A-226
03036OT3V284TSC-W40	\$2,572	A-58
03036OT3V284TS-W40	\$2,487	A-52
03036ST3HIE286TS-W22	\$3,799	A-70;A-105
03036ST3QIE286TSC-W2	\$3,999	A-73;A-108
03036ST3QIE286TS-W22	\$3,799	A-70;A-105
03036XT3E286TS	\$4,262	A-124
03036XT3H286TS	\$4,262	A-124
03089EP3HCT324VF1-W2	\$4,725	A-197
03089EP3HCT324V-W22	\$4,725	A-197
03089EP3PCT324VF1-W2	\$4,725	A-197
03089EP3PCT324V-W22	\$4,725	A-197
03089EP3PCT326V2F1-W	\$6,995	A-197
03089EP3PCT326V2-W22	\$6,995	A-197
03089EP3QCT324VF1-W2	\$4,725	A-197
03089EP3QCT324V-W22	\$4,725	A-197
03089EP3QCT326V2F1-W	\$6,995	A-197
03089EP3QCT326V2-W22	\$6,995	A-197
03709ET3Y280S/M-W22	\$11,751	A-84;A-117;A-250
03712ET3Y250S/M-W22	\$9,947	A-84;A-117;A-250
03718ET3Y225S/MFF-W22	\$7,774	A-85;A-118;A-251

Part Number	List Price	Pages
03718ET3Y225S/M-W22	\$6,984	A-84;A-117;A-250
03736ET3Y200LFF-W22	\$5,789	A-85;A-118;A-251
03736ET3Y200L-W22	\$5,487	A-84;A-117;A-250
04009ET3E365T-W22	\$12,194	A-37;A-95
04009ST3QIE365TC-W22	\$15,284	A-74;A-109
04009ST3QIE365T-W22	\$14,909	A-70;A-105
04009XT3E365T	\$15,505	A-125
04012EG3E364T-W22	\$8,012	A-87
04012ES3EOW365T-W22	\$6,290	A-270
04012ET3E364JM-W22	\$8,807	A-215
04012ET3E364JP-W22	\$9,268	A-218
04012ET3E364TC-W22	\$7,576	A-44;A-101
04012ET3E364T-W22	\$7,284	A-37;A-95
04012ET3E364T-W22G	\$8,124	A-63;A-184
04012ET3ECT364T-W22	\$8,376	A-192
04012ET3H364T-W22	\$7,284	A-37;A-95
04012ET3H364T-W22G	\$8,124	A-63;A-184
04012ET3PCT364T-W22	\$8,376	A-192
040120T3E364JM-W40	\$6,696	A-223
040120T3E364JP-W40	\$7,444	A-227
040120T3E364TC-W40	\$5,938	A-58
040120T3E364T-W40	\$5,544	A-53
040120T3E364T-W40G	\$6,384	A-67;A-188
040120T3H364T-W40	\$5,544	A-53
04012ST3HIE364T-W22	\$8,636	A-70;A-105
04012ST3QIE364TC-W22	\$9,011	A-74;A-109
04012ST3QIE364T-W22	\$8,636	A-70;A-105
04012XT3E364T	\$10,576	A-125
04012XT3H364T	\$10,576	A-125
04015EP30FP324TS-W22	\$3,969	A-242
040150P30FP324TS-W40	\$3,050	A-241
04018AT3ECT324TF1-W2	\$4,949	A-194
04018AT3ECT324T-W22	\$4,949	A-194
04018AT3HCT324TF1-W2	\$4,949	A-194
04018AT3HCT324T-W22	\$4,949	A-194
04018AT3PCT324TF1-W2	\$4,949	A-194
04018AT3PCT324T-W22	\$4,949	A-194
04018EG3E324T-W22	\$4,596	A-87
04018ET3E324HP-W22	\$5,247	A-244
04018ET3E324JM-W22	\$5,316	A-215
04018ET3E324JP-W22	\$5,413	A-218
04018ET3E324TC-W22	\$4,300	A-44;A-101
04018ET3E324TSC-W22	\$4,300	A-44;A-101
04018ET3E324TS-W22	\$4,178	A-37;A-95
04018ET3E324T-W22	\$4,178	A-37;A-95
04018ET3E324T-W22G	\$4,578	A-63;A-184
04018ET3ECT324TF1-W2	\$4,805	A-192
04018ET3ECT324T-W22	\$4,805	A-192
04018ET3EPM324/6Y-W2	\$4,638	A-199
04018ET3ER324TC-W22	\$4,429	A-47;A-102
04018ET3H324JM-W22	\$5,316	A-215

Part Number	List Price	Pages
04018ET3H324JP-W22	\$5,413	A-218
04018ET3H324TC-W22	\$4,300	A-44;A-101
04018ET3H324T-W22	\$4,178	A-37;A-95
04018ET3H324T-W22G	\$4,578	A-63;A-184
04018ET3HCT324TF1-W2	\$4,805	A-192
04018ET3HCT324T-W22	\$4,805	A-192
04018ET3P324T-W22	\$4,178	A-37;A-95
04018ET3PCT324TF1-W2	\$4,805	A-192
04018ET3PCT324T-W22	\$4,805	A-192
04018ET3V324T-W22G	\$4,578	A-63;A-184
04018OP3EFP324JMV-W4	\$3,621	A-238
04018OP3EFP324TC-W40	\$2,752	A-237
04018OP3EFP324TS-W40	\$2,652	A-235
04018OP3HFP324JMV-W4	\$3,621	A-238
04018OP3HFP324TS-W40	\$2,652	A-235
04018OP3VFP324TS-W40	\$2,652	A-235
04018OT3E324JMV-W40	\$4,431	A-224
04018OT3E324JM-W40	\$3,797	A-223
04018OT3E324JPV-W40	\$4,077	A-228
04018OT3E324JP-W40	\$3,797	A-226
04018OT3E324TC-W40	\$3,195	A-58
04018OT3E324TC-W40G	\$3,595	A-67;A-188
04018OT3E324TSC-W40	\$3,195	A-58
04018OT3E324TS-W40	\$3,095	A-53
04018OT3E324TS-W40G	\$3,372	A-67;A-188
04018OT3E324T-W40	\$3,095	A-53
04018OT3E324T-W40G	\$3,495	A-67;A-188
04018OT3H324JM-W40	\$3,797	A-223
04018OT3H324JP-W40	\$3,797	A-226
04018OT3H324TC-W40	\$3,195	A-58
04018OT3H324TS-W40	\$3,095	A-53
04018OT3H324T-W40	\$3,095	A-53
04018OT3H324T-W40G	\$3,495	A-67;A-188
04018OT3P324T-W40	\$3,095	A-53
04018OT3V324JPV-W40	\$4,077	A-228
04018OT3V324JP-W40	\$3,797	A-226
04018OT3V324TC-W40G	\$3,595	A-67;A-188
04018OT3V324TS-W40	\$3,095	A-53
04018OT3V324T-W40G	\$3,495	A-67;A-188
04018ST3HIE324T-W22	\$4,692	A-70;A-105
04018ST3QAP324T-W22	\$5,095	A-111
04018ST3QIE324TC-W22	\$4,917	A-74;A-109
04018ST3QIE324T-W22	\$4,692	A-70;A-105
04018XT3E324T	\$5,380	A-125
04018XT3E324TC	\$5,919	A-128
04018XT3ER324TC	\$6,027	A-128
04018XT3H324T	\$5,380	A-125
04026EP3QCT365VF1-W2	\$9,302	A-197
04026EP3QCT365V-W22	\$9,302	A-197
04030EP30FP324TS-W22	\$4,489	A-242
04030OP30FP286TS-W40	\$3,171	A-241

Part Number	List Price	Pages
04036EG3E324TS-W22	\$5,198	A-87
04036ET3E286JM-W22	\$5,368	A-215
04036ET3E286JP-W22	\$5,475	A-218
04036ET3E324HP-W22	\$5,457	A-244
04036ET3E324JM-W22	\$5,534	A-215
04036ET3E324JP-W22	\$5,628	A-218
04036ET3E324TSC-W22	\$4,845	A-44;A-101
04036ET3E324TS-W22	\$4,725	A-37;A-95
04036ET3E324TS-W22G	\$5,125	A-63;A-184
04036ET3ER324TSC-W22	\$4,988	A-47;A-102
04036ET3H286JM-W22	\$5,368	A-215
04036ET3H286JP-W22	\$5,475	A-218
04036ET3H324JM-W22	\$5,534	A-215
04036ET3H324JP-W22	\$5,628	A-218
04036ET3H324TSC-W22	\$4,845	A-44;A-101
04036ET3H324TS-W22	\$4,725	A-37;A-95
04036ET3H324TS-W22G	\$5,125	A-63;A-184
04036OP3EFP286JMV-W4	\$3,611	A-238
04036OP3EFP286TSC-W4	\$2,757	A-237
04036OP3EFP286TS-W40	\$2,757	A-235
04036OP3HFP286JMV-W4	\$3,611	A-238
04036OP3HFP286TSC-W4	\$2,757	A-237
04036OP3HFP286TS-W40	\$2,757	A-235
04036OP3VFP286JMV-W4	\$3,611	A-238
04036OP3VFP286TSC-W4	\$2,757	A-237
04036OP3VFP286TS-W40	\$2,757	A-235
04036OT3E286JMV-W40	\$4,066	A-224
04036OT3E286JM-W40	\$3,811	A-223
04036OT3E286JPV*	\$4,066	A-228
04036OT3E286JPV-W40	\$4,066	A-228
04036OT3E286JP-W40	\$3,811	A-226
04036OT3E286TSC-W40	\$3,393	A-58
04036OT3E286TSC-W40G	\$3,703	A-67;A-188
04036OT3E286TS-W40	\$3,308	A-53
04036OT3E286TS-W40G	\$3,618	A-67;A-188
04036OT3H286JMV*	\$4,066	A-224
04036OT3H286JMV-W40	\$4,066	A-224
04036OT3H286JM-W40	\$3,811	A-223
04036OT3H286JP-W40	\$3,811	A-226
04036OT3H286TSC-W40	\$3,393	A-58
04036OT3H286TS-W40	\$3,308	A-53
04036OT3P286TS-W40	\$3,308	A-53
04036OT3V286JPV*	\$4,066	A-228
04036OT3V286JPV-W40	\$4,066	A-228
04036OT3V286JP-W40	\$3,811	A-226
04036OT3V286TS-W40	\$3,308	A-53
04036ST3HIE324TS-W22	\$5,306	A-70;A-105
04036ST3QIE324TSC-W2	\$5,531	A-74;A-109
04036ST3QIE324TS-W22	\$5,306	A-70;A-105
04036XT3E324TS	\$5,583	A-125
04036XT3H324TS	\$5,583	A-125

Part Number	List Price	Pages
04089EP3HCT326VF1-W2	\$5,464	A-197
04089EP3HCT326V-W22	\$5,464	A-197
04089EP3PCT326VF1-W2	\$5,464	A-197
04089EP3PCT326V-W22	\$5,464	A-197
04089EP3PCT364V2F1-W	\$8,720	A-197
04089EP3PCT364V2-W22	\$8,720	A-197
04089EP3QCT326VF1-W2	\$5,464	A-197
04089EP3QCT326V-W22	\$5,464	A-197
04089EP3QCT364V2F1-W	\$8,720	A-197
04089EP3QCT364V2-W22	\$8,720	A-197
04509ET3Y280S/M-W22	\$12,815	A-84;A-117;A-250
04512ET3Y280S/M-W22	\$11,023	A-84;A-117;A-250
04518ET3Y225S/M-W22	\$7,391	A-84;A-117;A-250
04536ET3Y225S/M-W22	\$7,961	A-84;A-117;A-250
05009ET3E404T-W22	\$17,648	A-37;A-95
05009ET3EKD404T-W22	\$17,648	A-113
05009ST3QIE404TC-W22	\$19,856	A-74;A-109
05009ST3QIE404T-W22	\$19,331	A-71;A-106
05009XT3E404T	\$22,443	A-125
05012EG3E365T-W22	\$9,370	A-87
05012ES3E0W404T-W22	\$8,172	A-270
05012ET3E365JM-W22	\$10,551	A-215
05012ET3E365JP-W22	\$10,748	A-218
05012ET3E365TC-W22	\$8,960	A-44;A-101
05012ET3E365T-W22	\$8,518	A-37;A-95
05012ET3E365T-W22G	\$9,358	A-63;A-184
05012ET3ECT365T-W22	\$9,625	A-192
05012ET3H365T-W22	\$8,518	A-37;A-95
05012ET3H365T-W22G	\$9,358	A-63;A-184
05012ET3PCT365T-W22	\$9,625	A-192
05012OT3E365JM-W40	\$7,666	A-223
05012OT3E365JP-W40	\$7,666	A-227
05012OT3E365TC-W40	\$6,786	A-58
05012OT3E365T-W40	\$6,392	A-53
05012OT3E365T-W40G	\$7,232	A-67;A-188
05012OT3V365T-W40	\$6,392	A-53
05012ST3HIE365T-W22	\$9,369	A-71;A-106
05012ST3QIE365TC-W22	\$9,744	A-74;A-109
05012ST3QIE365T-W22	\$9,369	A-71;A-106
05012XT3E365T	\$11,197	A-125
05012XT3H365T	\$11,197	A-125
05015EP30FP326TS-W22	\$4,845	A-242
05015OP30FP326TS-W40	\$3,588	A-241
05018AT3ECT326T-W22	\$6,041	A-194
05018AT3HCT326T-W22	\$6,041	A-194
05018AT3PCT326T-W22	\$6,041	A-194
05018EG3E326T-W22	\$5,610	A-87
05018ET3E326HP-W22	\$6,009	A-244
05018ET3E326JM-W22	\$6,513	A-215
05018ET3E326JP-W22	\$6,624	A-218
05018ET3E326JP-W22G	\$7,024	A-231

Part Number	List Price	Pages
05018ET3E326TC-W22	\$5,221	A-44;A-101
05018ET3E326TSC-W22	\$5,221	A-44;A-101
05018ET3E326TS-W22	\$5,100	A-37;A-95
05018ET3E326T-W22	\$5,100	A-37;A-95
05018ET3E326T-W22G	\$5,500	A-63;A-184
05018ET3ECT326TF1-W2	\$5,865	A-192
05018ET3ECT326T-W22	\$5,865	A-192
05018ET3EPM324/6Y-W2	\$5,661	A-199
05018ET3ER326TC-W22	\$5,378	A-47;A-102
05018ET3H326JM-W22	\$6,513	A-215
05018ET3H326JP-W22	\$6,624	A-218
05018ET3H326TC-W22	\$5,221	A-44;A-101
05018ET3H326T-W22	\$5,100	A-37;A-95
05018ET3H326T-W22G	\$5,500	A-63;A-184
05018ET3HCT326TF1-W2	\$5,865	A-192
05018ET3HCT326T-W22	\$5,865	A-192
05018ET3PCT326T-W22	\$5,865	A-192
05018ET3V326T-W22G	\$5,500	A-63;A-184
05018OP3EFP326JMV-W4	\$4,393	A-238
05018OP3EFP326JPV-W4	\$4,500	A-240
05018OP3EFP326TC-W40	\$3,135	A-237
05018OP3EFP326TS-W40	\$3,015	A-235
05018OP3HFP326JMV-W4	\$4,527	A-238
05018OP3HFP326JPV-W4	\$4,394	A-240
05018OP3VFP326JPV-W4	\$4,500	A-240
05018OP3VFP326TS-W40	\$3,015	A-235
05018OT3E326JM-W40	\$4,877	A-223
05018OT3E326JPV-W40	\$5,190	A-229;A-239
05018OT3E326JP-W40	\$4,878	A-227
05018OT3E326TC-G*	\$4,288	A-188
05018OT3E326TC-W40	\$3,888	A-58
05018OT3E326TC-W40G	\$4,288	A-67;A-188
05018OT3E326TSC-W40	\$3,888	A-58
05018OT3E326TS-W40	\$3,788	A-53
05018OT3E326T-W40	\$3,788	A-53
05018OT3E326T-W40G	\$4,188	A-67;A-188
05018OT3G326TS-W40	\$3,788	A-53
05018OT3H326JMV-W40	\$5,189	A-224
05018OT3H326JM-W40	\$4,877	A-223
05018OT3H326JP-W40	\$4,878	A-227
05018OT3H326TC-W40	\$3,888	A-58
05018OT3H326TS-W40	\$3,788	A-53
05018OT3H326T-W40	\$3,788	A-53
05018OT3H326T-W40G	\$4,188	A-67;A-188
05018OT3P326T-W40	\$3,788	A-53
05018OT3V326JPV-W40	\$5,190	A-229;A-239
05018OT3V326TS-W40	\$3,788	A-53
05018OT3V326T-W40G	\$4,188	A-67;A-188
05018ST3HIE326T-W22	\$5,233	A-71;A-106
05018ST3QAP326T-W22	\$5,617	A-111
05018ST3QIE326TC-W22	\$5,458	A-74;A-109

Part Number	List Price	Pages
05018ST3QIE326T-W22	\$5,233	A-71;A-106
05018XT3E326T	\$6,545	A-125
05018XT3E326TC	\$7,084	A-128
05018XT3ER326TC	\$7,215	A-128
05018XT3H326T	\$6,545	A-125
05026EP3QCT365VF1-W2	\$11,051	A-197
05026EP3QCT365V-W22	\$11,051	A-197
05030EP30FP326TS-W22	\$5,050	A-242
050300P30FP324TS-W40	\$3,662	A-241
05036EG3E326TS-W22	\$5,848	A-87
05036ET3E326HP-W22	\$6,681	A-244
05036ET3E326JM-W22	\$6,622	A-215
05036ET3E326JP-W22	\$6,733	A-218
05036ET3E326TSC-W22	\$5,437	A-44;A-101
05036ET3E326TS-W22	\$5,316	A-37;A-95
05036ET3E326TS-W22G	\$5,716	A-63;A-184
05036ET3H326JP-W22	\$6,733	A-218
05036ET3H326TS-W22	\$5,316	A-37;A-95
05036ET3H326TS-W22G	\$5,716	A-63;A-184
050360P3EFP324JMV-W4	\$4,394	A-238
050360P3EFP324JPV*	\$4,372	A-240
050360P3EFP324JPV-W4	\$4,372	A-240
050360P3EFP324TSC-W4	\$3,184	A-237
050360P3EFP324TS-W40	\$3,184	A-235
050360P3HFP324JMV*	\$4,394	A-238
050360P3HFP324JMV-W4	\$4,394	A-238
050360P3HFP324JPV*	\$4,372	A-240
050360P3HFP324JPV-W4	\$4,372	A-240
050360P3HFP324TS-W40	\$3,184	A-235
050360P3JFP324TS-W40	\$3,184	A-235
050360P3VFP324JMV-W4	\$4,664	A-238
050360P3VFP324JPV*	\$4,372	A-240
050360P3VFP324JPV-W4	\$4,372	A-240
050360P3VFP324TSC-W4	\$3,184	A-237
050360P3VFP324TS-W40	\$3,184	A-235
050360T3E324JMV-W40	\$4,911	A-224
050360T3E324JM-W40	\$4,607	A-223
050360T3E324JPV*	\$4,911	A-229;A-239
050360T3E324JPV-W40	\$4,911	A-229;A-239
050360T3E324JP-W40	\$4,607	A-227
050360T3E324TSC-W40	\$3,920	A-58
050360T3E324TSC-W40G	\$4,197	A-67;A-188
050360T3E324TS-W40	\$3,820	A-53
050360T3E324TS-W40G	\$4,097	A-67;A-188
050360T3G324JM-W40	\$4,607	A-223
050360T3G324JP-W40	\$4,607	A-227
050360T3H324JMV-W40	\$4,911	A-224
050360T3H324JM-W40	\$4,607	A-223
050360T3H324JPV-W40	\$4,911	A-229;A-239
050360T3H324JP-W40	\$4,607	A-227
050360T3H324TSC*	\$3,920	A-58

Part Number	List Price	Pages
050360T3H324TSC-W40	\$3,920	A-58
050360T3H324TS-W40	\$3,820	A-53
050360T3V324JMV-W40	\$4,911	A-224
050360T3V324JPV*	\$4,911	A-229;A-239
050360T3V324JPV-W40	\$4,911	A-229;A-239
050360T3V324JP-W40	\$4,607	A-227
050360T3V324TS-W40	\$3,820	A-53
05036ST3HIE326TS-W22	\$5,970	A-71;A-106
05036ST3QIE326TSC-W2	\$6,195	A-74;A-109
05036ST3QIE326TS-W22	\$5,970	A-71;A-106
05036XT3E326TS	\$6,582	A-125
05036XT3H326TS	\$6,582	A-125
05089EP3HCT364VF1-W2	\$7,526	A-197
05089EP3HCT364V-W22	\$7,526	A-197
05089EP3PCT364VF1-W2	\$7,526	A-197
05089EP3PCT364V-W22	\$7,526	A-197
05089EP3PCT365V2F1-W	\$11,093	A-197
05089EP3PCT365V2-W22	\$11,093	A-197
05089EP3QCT364VF1-W2	\$7,526	A-197
05089EP3QCT364V-W22	\$7,526	A-197
05089EP3QCT365V2F1-W	\$11,093	A-197
05089EP3QCT365V2-W22	\$11,093	A-197
05509ET3Y315S/M-W22	\$15,379	A-84;A-117;A-250
05512ET3Y280S/M-W22	\$13,622	A-84;A-117;A-250
05518ET3Y250S/M-W22	\$8,961	A-84;A-117;A-250
05536ET3Y250S/M-W22	\$9,847	A-84;A-117;A-250
06009ET3E405T-W22	\$20,443	A-37;A-95
06009ET3EKD405T-W22	\$20,443	A-113
06009ST3QIE405T-W22	\$22,579	A-71;A-106
06009XT3E405T	\$26,900	A-125
06012EG3E404T-W22	\$11,547	A-87
06012ES3EOW405T-W22	\$9,414	A-270
06012ET3E404JP-W22	\$12,444	A-218
06012ET3E404T-W22	\$10,497	A-37;A-95
06012ET3E404T-W22G	\$11,697	A-63;A-184
06012ET3ECT404T-W22	\$11,861	A-192
06012ET3ERB404T-W22	\$10,497	A-37;A-95;A-113
06012ET3G404T-W22	\$10,497	A-37;A-95
06012ET3H404T-W22	\$10,497	A-37;A-95
06012ET3H404T-W22G	\$11,697	A-63;A-184
06012ET3PCT404T-W22	\$11,861	A-192
060120T3E404JP-W40	\$9,462	A-227
060120T3E404T-W40	\$7,562	A-53
060120T3E404T-W40G	\$8,762	A-67;A-188
06012ST3HIE404T-W22	\$11,790	A-71;A-106
06012ST3QIE404TC-W22	\$12,315	A-74;A-109
06012ST3QIE404T-W22	\$11,790	A-71;A-106
06012XT3E404T	\$13,196	A-125
06012XT3H404T	\$13,196	A-125
06015EP30FP364TS-W22	\$7,020	A-242
060150P30FP365TS-W40	\$4,455	A-241

Part Number	List Price	Pages
06018AT3ECT364T-W22	\$8,752	A-194
06018EG3E364T-W22	\$8,128	A-87
06018ET3E364HP-W22	\$8,525	A-244
06018ET3E364JM-W22	\$8,912	A-215
06018ET3E364JP-W22	\$9,619	A-218
06018ET3E364TC-W22	\$7,831	A-45;A-101
06018ET3E364TS-W22	\$7,389	A-37;A-95
06018ET3E364T-W22	\$7,389	A-37;A-95
06018ET3E364T-W22G	\$8,229	A-63;A-184
06018ET3ECT364TF1-W2	\$8,497	A-192
06018ET3ECT364T-W22	\$8,497	A-192
06018ET3ER364TC-W22	\$8,053	A-47;A-102
06018ET3G364T-W22	\$7,389	A-37;A-95
06018ET3H364JM-W22	\$8,912	A-215
06018ET3H364JP-W22	\$9,619	A-218
06018ET3H364TC-W22	\$7,831	A-45;A-101
06018ET3H364T-W22	\$7,389	A-37;A-95
06018ET3H364T-W22G	\$8,229	A-63;A-184
06018ET3HCT364TF1-W2	\$8,497	A-192
06018ET3HCT364T-W22	\$8,497	A-192
06018ET3PCT364T-W22	\$8,497	A-192
06018OP3EFP364JPV-W4	\$6,142	A-240
06018OP3EFP364TS-W40	\$3,703	A-235
06018OP3HFP364TS-W40	\$3,703	A-235
06018OP3VFP364JPV-W4	\$6,142	A-240
06018OP3VFP364TS-W40	\$3,703	A-235
06018OT3E364JM-W40	\$5,994	A-223
06018OT3E364JPV-W40	\$6,365	A-229;A-239
06018OT3E364JP-W40	\$5,994	A-227
06018OT3E364TC-W40	\$4,837	A-58
06018OT3E364TC-W40G	\$5,677	A-67;A-188
06018OT3E364TS-W40	\$4,443	A-53
06018OT3E364T-W40	\$4,443	A-53
06018OT3E364T-W40G	\$5,283	A-67;A-188
06018OT3G364JM-W40	\$5,994	A-223
06018OT3G364JP-W40	\$5,994	A-227
06018OT3G364TS-W40	\$4,443	A-53
06018OT3G364T-W40	\$4,443	A-53
06018OT3H364JM-W40	\$5,994	A-223
06018OT3H364JP-W40	\$5,994	A-227
06018OT3H364TC-W40	\$4,837	A-58
06018OT3H364TS-W40	\$4,443	A-53
06018OT3H364T-W40	\$4,443	A-53
06018OT3H364T-W40G	\$5,283	A-67;A-188
06018OT3V364JPV-W40	\$6,365	A-229;A-239
06018OT3V364TS-W40	\$4,443	A-53
06018ST3HIE364T-W22	\$8,044	A-71;A-106
06018ST3QAP364T-W22	\$8,535	A-111
06018ST3QIE364T-W22	\$8,044	A-71;A-106
06018XT3E364T	\$10,460	A-125
06018XT3E364TC	\$11,116	A-128

Part Number	List Price	Pages
06018XT3H364T	\$10,460	A-125
06030EP30FP364TS-W22	\$7,174	A-242
06030OP30FP326TS-W40	\$4,610	A-241
06036EG3E364TS-W22	\$8,307	A-87
06036ET3E326HP-W22	\$8,632	A-244
06036ET3E326JM-W22	\$7,699	A-215
06036ET3E326JP-W22	\$7,853	A-218
06036ET3E364HP-W22	\$9,484	A-244
06036ET3E364JM-W22	\$8,261	A-215
06036ET3E364JP-W22	\$10,252	A-218
06036ET3E364TSC-W22	\$7,994	A-45;A-101
06036ET3E364TS-W22	\$7,552	A-37;A-95
06036ET3E364TS-W22G	\$8,392	A-63;A-184
06036ET3G364TS-W22	\$7,552	A-37;A-95
06036ET3H364JM-W22	\$8,261	A-215
06036ET3H364JP-W22	\$10,252	A-218
06036ET3H364TSC-W22	\$7,994	A-45;A-101
06036ET3H364TS-W22	\$7,552	A-37;A-95
06036ET3H364TS-W22G	\$8,392	A-63;A-184
06036OP3EFP326JMV-W4	\$5,171	A-238
06036OP3EFP326JPV*	\$5,105	A-240
06036OP3EFP326JPV-W4	\$5,105	A-240
06036OP3EFP326TSC-W4	\$4,448	A-237
06036OP3EFP326TS-W40	\$4,008	A-235
06036OP3HFP326JMV*	\$5,305	A-238
06036OP3HFP326JMV-W4	\$5,305	A-238
06036OP3HFP326JPV*	\$5,105	A-240
06036OP3HFP326JPV-W4	\$5,105	A-240
06036OP3HFP326TS-W40	\$4,008	A-235
06036OP3JFP326TS-W40	\$4,008	A-235
06036OP3VFP326JMV-W4	\$5,171	A-238
06036OP3VFP326JPV*	\$5,105	A-240
06036OP3VFP326JPV-W4	\$5,105	A-240
06036OP3VFP326TS*	\$4,008	A-235
06036OP3VFP326TS-W40	\$4,008	A-235
06036OT3E326JM-W40	\$5,432	A-223
06036OT3E326JPV*	\$5,761	A-229;A-239
06036OT3E326JPV-W40	\$5,761	A-229;A-239
06036OT3E326JP-W40	\$5,432	A-227
06036OT3E326TSC-W40	\$4,681	A-58
06036OT3E326TS-W40	\$4,581	A-53
06036OT3E326TS-W40G	\$4,858	A-67;A-188
06036OT3G326JM-W40	\$5,432	A-223
06036OT3G326JP-W40	\$5,432	A-227
06036OT3G326TS-W40	\$4,581	A-53
06036OT3H326JMV-W40	\$5,761	A-224
06036OT3H326JM-W40	\$5,432	A-223
06036OT3H326JP-W40	\$5,432	A-227
06036OT3H326TS-W40	\$4,581	A-53
06036OT3V326JPV*	\$5,761	A-229;A-239
06036OT3V326JPV-W40	\$5,761	A-229;A-239

Part Number	List Price	Pages
060360T3V326JP-W40	\$5,432	A-227
060360T3V326TS-W40	\$4,581	A-53
06036ST3HIE364TS-W22	\$8,665	A-71;A-106
06036ST3QIE364TS-W22	\$8,665	A-71;A-106
06036XT3E364TS	\$9,988	A-125
06036XT3H364TS	\$9,988	A-125
06089EP3PCT365VF1-W2	\$11,068	A-197
06089EP3PCT365V-W22	\$11,068	A-197
06089EP3QCT365VF1-W2	\$11,068	A-197
06089EP3QCT365V-W22	\$11,068	A-197
07509ET3E444T-W22	\$23,334	A-38;A-96
07509ET3GKD444T-W22	\$23,334	A-113
07509ET3QRB444TF2-W2	\$23,334	A-96;A-113
07509ET3Y315S/M-W22	\$18,647	A-84;A-117;A-250
07509ST3QIE444T-W22	\$23,457	A-71;A-106
07509XT3E444T	\$29,094	A-125
07512EG3E405T-W22	\$13,264	A-87
07512ES3E0W444T-W22	\$14,976	A-270
07512ET3E405JP-W22	\$14,005	A-219
07512ET3E405T-W22	\$12,058	A-38;A-96
07512ET3E405T-W22G	\$13,258	A-63;A-184
07512ET3ECT405T-W22	\$13,626	A-192
07512ET3ERB405T-W22	\$12,058	A-38;A-96;A-113
07512ET3G405T-W22	\$12,058	A-38;A-96
07512ET3GRB405T-W22	\$12,058	A-38;A-96;A-113
07512ET3H405TC-W22	\$12,549	A-45;A-101
07512ET3H405T-W22	\$12,058	A-38;A-96
07512ET3H405T-W22G	\$13,258	A-63;A-184
07512ET3PCT405T-W22	\$13,626	A-192
07512ET3Y315S/M-W22	\$16,479	A-84;A-117;A-250
075120T3E405JP-W40	\$9,762	A-227
075120T3E405T-W40	\$8,358	A-54
075120T3E405T-W40G	\$9,558	A-67;A-188
07512ST3HIE405T-W22	\$12,866	A-71;A-106
07512ST3QIE405T-W22	\$12,866	A-71;A-106
07512ST3QIERB405T-W2	\$12,866	A-71;A-106
07512XT3E405T	\$13,836	A-125
07515EP30FP365TS-W22	\$8,270	A-242
075150P30FP365TS-W40	\$5,423	A-241
07518AT3ECT365T-W22	\$10,222	A-194
07518EG3E365T-W22	\$9,576	A-87
07518ET3E365HP-W22	\$9,352	A-244
07518ET3E365JM-W22	\$10,057	A-215
07518ET3E365JP-W22	\$10,235	A-219
07518ET3E365TC-W22	\$9,148	A-45;A-101
07518ET3E365TC-W22G	\$9,988	A-63;A-184
07518ET3E365TS-W22	\$8,705	A-38;A-96
07518ET3E365T-W22	\$8,705	A-38;A-96
07518ET3E365T-W22G	\$9,545	A-63;A-184
07518ET3ECT365TF1-W2	\$9,924	A-192
07518ET3ECT365T-W22	\$9,924	A-192

Part Number	List Price	Pages
07518ET3ER365TC-W22	\$9,408	A-47;A-102
07518ET3G365T-W22	\$8,705	A-38;A-96
07518ET3H365JM-W22	\$10,057	A-215
07518ET3H365JP-W22	\$10,235	A-219
07518ET3H365TC-W22	\$9,148	A-45;A-101
07518ET3H365T-W22	\$8,705	A-38;A-96
07518ET3H365T-W22G	\$9,545	A-63;A-184
07518ET3HCT365T-W22	\$9,924	A-192
07518ET3PCT365T-W22	\$9,924	A-192
07518ET3Y280S/M-W22	\$12,353	A-84;A-117;A-250
075180P3EFP365JPV*	\$6,967	A-240
075180P3EFP365JPV-W4	\$6,967	A-240
075180P3EFP365TC-W40	\$5,109	A-237
075180P3EFP365TS-W40	\$4,715	A-235
075180P3HFP365TS-W40	\$4,715	A-235
075180P3VFP365JPV-W4	\$6,967	A-240
075180P3VFP365TS-W40	\$4,715	A-235
075180T3E365JM-W40	\$6,932	A-223
075180T3E365JPV-W40	\$7,331	A-229;A-239
075180T3E365JP-W40	\$6,932	A-227
075180T3E365TC-W40	\$6,052	A-59
075180T3E365TC-W40G	\$6,892	A-67;A-188
075180T3E365TS-W40	\$5,658	A-54
075180T3E365T-W40	\$5,658	A-54
075180T3E365T-W40G	\$6,498	A-67;A-188
075180T3ERB365T-W40	\$6,632	A-54
075180T3G365JM-W40	\$6,932	A-223
075180T3G365JP-W40	\$6,932	A-227
075180T3G365TS-W40	\$5,658	A-54
075180T3G365T-W40	\$5,658	A-54
075180T3GRB365T-W40	\$6,632	A-54
075180T3H365JM-W40	\$6,932	A-223
075180T3H365JP-W40	\$6,932	A-227
075180T3H365TC-W40	\$6,052	A-59
075180T3H365TS-W40	\$5,658	A-54
075180T3H365T-W40	\$5,658	A-54
075180T3H365T-W40G	\$6,498	A-67;A-188
075180T3V365JPV-W40	\$7,331	A-229;A-239
075180T3V365TS-W40	\$5,658	A-54
07518ST3HIE365T-W22	\$9,289	A-71;A-106
07518ST3QAP365T-W22	\$9,772	A-111
07518ST3QIE365T-W22	\$9,289	A-71;A-106
07518ST3QIERB365T-W2	\$10,019	A-71;A-106
07518XT3E365T	\$11,125	A-125
07518XT3E365TC	\$11,781	A-128
07518XT3H365T	\$11,125	A-125
07530EP30FP365TS-W22	\$8,636	A-242
075300P30FP365TS-W40	\$5,836	A-241
07536EG3E365TS-W22	\$10,000	A-87
07536ET3E365HP-W22	\$10,977	A-244
07536ET3E365JM-W22	\$11,124	A-215

Part Number	List Price	Pages
07536ET3E365JP-W22	\$11,321	A-219
07536ET3E365TSC-W22	\$9,533	A-45;A-101
07536ET3E365TS-W22	\$9,091	A-38;A-96
07536ET3E365TS-W22G	\$9,931	A-63;A-184
07536ET3G365JP-W22	\$11,321	A-219
07536ET3G365TS-W22	\$9,091	A-38;A-96
07536ET3H365JM-W22	\$11,124	A-215
07536ET3H365JP-W22	\$11,321	A-219
07536ET3H365TS-W22	\$9,091	A-38;A-96
07536ET3H365TS-W22G	\$9,931	A-63;A-184
07536ET3Y280S/M-W22	\$12,472	A-84;A-117;A-250
075360P3EFP364JPV-W4	\$7,525	A-240
075360P3EFP364TS-W40	\$5,074	A-235
075360P3HFP364JPV-W4	\$7,525	A-240
075360P3HFP364TS-W40	\$5,074	A-235
075360P3JFP364TS-W40	\$5,074	A-235
075360P3VFP364JPV-W4	\$7,525	A-240
075360P3VFP364TS-W40	\$5,074	A-235
075360T3E364JM-W40	\$6,951	A-223
075360T3E364JPV*	\$8,121	A-229;A-239
075360T3E364JPV-W40	\$8,121	A-229;A-239
075360T3E364JP-W40	\$7,699	A-227
075360T3E364TSC-RFW4	\$6,812	A-275
075360T3E364TSC-W40	\$6,193	A-59
075360T3E364TSC-W40G	\$6,566	A-67;A-188
075360T3E364TS-RFVFD	\$8,509	A-275
075360T3E364TS-RFW40	\$6,379	A-275
075360T3E364TS-W40	\$5,799	A-54
075360T3E364TS-W40G	\$6,172	A-67;A-188
075360T3G364JM-W40	\$6,951	A-223
075360T3G364JP-W40	\$7,699	A-227
075360T3G364TS-W40	\$5,799	A-54
075360T3H364JMV-W40	\$7,351	A-224
075360T3H364JM-W40	\$6,951	A-223
075360T3H364JPV-W40	\$8,121	A-229;A-239
075360T3H364JP-W40	\$7,699	A-227
075360T3H364TS-W40	\$5,799	A-54
075360T3V364JPV-W40	\$8,121	A-229;A-239
075360T3V364JP-W40	\$7,699	A-227
075360T3V364TS-W40	\$5,799	A-54
07536ST3HIE365TS-W22	\$10,210	A-71;A-106
07536ST3QIE365TS-W22	\$10,210	A-71;A-106
07536XT3E365TS	\$11,285	A-125
07536XT3H365TS	\$11,285	A-125
07589EP3PCT404VF1-W2	\$14,226	A-197
07589EP3PCT404V-W22	\$14,226	A-197
07589EP3QCT404VF1-W2	\$14,226	A-197
07589EP3QCT404V-W22	\$14,226	A-197
09009ET3Y315S/M-W22	\$21,288	A-84;A-117;A-250
09012ET3Y315S/M-W22	\$19,448	A-84;A-117;A-250
09018ET3Y280S/M-W22	\$15,220	A-84;A-117;A-250

Part Number	List Price	Pages
09036ET3Y280S/M-W22	\$16,720	A-84;A-117;A-250
10009ET3E445T-W22	\$26,988	A-38;A-96
10009ET3G445T-W22	\$26,988	A-38;A-96
10009ET3GKD445T-W22	\$26,988	A-113
10009ST3QIE445T-W22	\$24,681	A-71;A-106
10009ST3QIERB445T-W2	\$24,681	A-71;A-106
10009XT3E445T	\$31,191	A-125
10009XT3G445T	\$31,191	A-125
10012EG3E444T-W22	\$17,194	A-87
10012ES3E0W445T-W22	\$18,074	A-270
10012ET3E444T-W22	\$15,631	A-38;A-96
10012ET3E444T-W22G	\$17,181	A-63;A-184
10012ET3ECT444T-W22	\$17,194	A-192
10012ET3ERB444T-W22	\$15,631	A-38;A-96;A-113
10012ET3G444T-W22	\$15,631	A-38;A-96
10012ET3GRB444T-W22	\$15,631	A-38;A-96;A-113
10012ET3H444T-W22	\$15,631	A-38;A-96
10012ET3H444T-W22G	\$17,181	A-63;A-184
10012ET3PCT444T-W22	\$17,194	A-192
100120T3E444T-W40	\$11,863	A-54
100120T3E444T-W40G	\$13,463	A-67;A-188
100120T3G444T-W40	\$11,863	A-54
10012ST3HIE444T-W22	\$17,933	A-71;A-106
10012ST3QIE444T-W22	\$17,933	A-71;A-106
10012ST3QIERB444T-W2	\$17,933	A-71;A-106
10012XT3E444T	\$21,032	A-125
10012XT3G444T	\$21,032	A-125
10015EP30FP405TS-W22	\$11,105	A-242
100150P30FP405TS-W40	\$6,975	A-241
10018AT3ECT405TF1-W2	\$11,412	A-194
10018AT3ECT405T-W22	\$11,412	A-194
10018EG3E405T-W22	\$12,858	A-87
10018ET3E405HPH-W22	\$11,222	A-245
10018ET3E405HP-W22	\$11,222	A-245
10018ET3E405JM-W22	\$12,300	A-215
10018ET3E405JP-W22	\$12,411	A-219
10018ET3E405TC-W22	\$12,179	A-45;A-101
10018ET3E405TSC-W22	\$12,179	A-45;A-101
10018ET3E405TS-W22	\$11,689	A-38;A-96
10018ET3E405T-W22	\$11,689	A-38;A-96
10018ET3E405T-W22G	\$12,889	A-63;A-184
10018ET3ECT405T-W22	\$13,092	A-192
10018ET3ERB405T-W22	\$11,689	A-38;A-96;A-113
10018ET3G405HPH-W22	\$11,222	A-245
10018ET3G405HP-W22	\$11,222	A-245
10018ET3G405JM-W22	\$12,300	A-215
10018ET3G405JP-W22	\$12,411	A-219
10018ET3G405T-W22	\$11,689	A-38;A-96
10018ET3GRB405T-W22	\$11,689	A-38;A-96;A-113
10018ET3H405TC-W22	\$12,179	A-45;A-101
10018ET3H405T-W22	\$11,689	A-38;A-96

Part Number	List Price	Pages
10018ET3H405T-W22G	\$12,889	A-63;A-184
10018ET3HRB405T-W22	\$11,689	A-38;A-96;A-113
10018ET3PCT405T-W22	\$13,092	A-192
100180P3EFP404JPV*	\$8,825	A-240
100180P3EFP404JPV-W4	\$8,825	A-240
100180P3EFP404TC-W40	\$6,510	A-237
100180P3EFP404TS-W40	\$6,065	A-236
100180P3EFP404T-W40	\$6,065	A-236
100180P3HFP404TC-W40	\$6,510	A-237
100180P3HFP404TS-W40	\$6,065	A-236
100180P3VFP404JPV-W4	\$8,825	A-240
100180P3VFP404TC-W40	\$6,510	A-237
100180P3VFP404TS-W40	\$6,065	A-236
100180T3E404JPV-W40	\$9,237	A-229;A-239
100180T3E404JP-W40	\$8,783	A-227
100180T3E404TC-W40	\$7,587	A-59
100180T3E404TSC-W40	\$7,587	A-59
100180T3E404TS-W40	\$7,141	A-54
100180T3E404TS-W40G	\$7,751	A-67;A-188
100180T3E404T-W40	\$7,141	A-54
100180T3E404T-W40G	\$8,341	A-67;A-188
100180T3ERB404T-W40	\$7,141	A-54
100180T3G404JP-W40	\$8,783	A-227
100180T3G404TS-W40	\$7,141	A-54
100180T3G404T-W40	\$7,141	A-54
100180T3GRB404T-W40	\$7,141	A-54
100180T3H404TC-W40	\$7,587	A-59
100180T3H404TSC-W40	\$7,587	A-59
100180T3H404T-W40	\$7,141	A-54
100180T3H404T-W40G	\$8,341	A-67;A-188
100180T3V404JPV-W40	\$9,237	A-229;A-239
100180T3V404TS-W40	\$7,141	A-54
10018ST3HIE405T-W22	\$12,471	A-71;A-106
10018ST3HIERB405T-W2	\$12,471	A-71;A-106
10018ST3QIE405T-W22	\$12,471	A-71;A-106
10018ST3QIERB405T-W2	\$12,471	A-71;A-106
10018XT3E405T	\$14,206	A-125
10018XT3E405TC	\$14,993	A-128
10018XT3G405T	\$14,206	A-125
10018XT3H405T	\$14,206	A-125
10030EP30FP405TS-W22	\$11,402	A-242
10030OP30FP365TS-W40	\$7,075	A-241
10036EG3E405TS-W22	\$13,202	A-87
10036ET3E405HPH-W22	\$12,908	A-245
10036ET3E405HP-W22	\$12,908	A-245
10036ET3E405JM-W22	\$13,093	A-215
10036ET3E405JP-W22	\$13,949	A-219
10036ET3E405TS-W22	\$12,002	A-38;A-96
10036ET3E405TS-W22G	\$13,202	A-63;A-184
10036ET3G405HPH-W22	\$12,908	A-245
10036ET3G405HP-W22	\$12,908	A-245

Part Number	List Price	Pages
10036ET3G405JM-W22	\$13,093	A-215
10036ET3G405JP-W22	\$13,949	A-219
10036ET3G405TS-W22	\$12,002	A-38;A-96
10036ET3H405TS-W22	\$12,002	A-38;A-96
100360P3EFP365JPV-W4	\$8,860	A-240
100360P3EFP365TS-W40	\$6,152	A-236
100360P3HFP365JPV-W4	\$8,860	A-240
100360P3HFP365TS-W40	\$6,152	A-236
100360P3JFP365TS-W40	\$6,152	A-236
100360P3VFP365JPV-W4	\$8,860	A-240
100360P3VFP365TS-W40	\$6,152	A-236
100360T3E365JM-W40	\$8,683	A-223
100360T3E365JPV-W40	\$8,609	A-229;A-239
100360T3E365JP-W40	\$8,173	A-227
100360T3E365TS-W40	\$6,644	A-54
100360T3E365TS-W40G	\$7,484	A-67;A-188
100360T3G365JM-W40	\$8,683	A-223
100360T3G365JP-W40	\$8,173	A-227
100360T3G365TSC-RFW4	\$7,742	A-275
100360T3G365TS-RFVFD	\$9,438	A-275
100360T3G365TS-RFW40	\$7,308	A-275
100360T3G365TS-W40	\$6,644	A-54
100360T3H365JPV-W40	\$8,609	A-229;A-239
100360T3H365TS-W40	\$6,644	A-54
100360T3V365JPV-W40	\$8,609	A-229;A-239
100360T3V365TS-W40	\$6,644	A-54
10036ST3HIE405TS-W22	\$12,806	A-71;A-106
10036ST3QIE405TS-W22	\$12,806	A-71;A-106
10036XT3E405TS	\$12,999	A-125
10036XT3G405TS	\$12,999	A-125
10036XT3H405TS	\$12,999	A-125
10089EP3PCT444VF1-W2	\$16,398	A-197
10089EP3PCT444V-W22	\$16,398	A-197
10089EP3QCT444VF1-W2	\$16,398	A-197
10089EP3QCT444V-W22	\$16,398	A-197
11009ET3Y315L-W22	\$27,910	A-84;A-118;A-250
11012ET3Y315S/M-W22	\$22,507	A-84;A-118;A-250
11018ET3Y280S/M-W22	\$17,078	A-84;A-118;A-250
11036ET3Y315S/M-W22	\$21,018	A-84;A-118;A-250
12509ET3G447T-W22	\$28,175	A-39;A-97
12509ET3GKD447T-W22	\$28,175	A-113
12509ST3QIE447T-W22	\$29,733	A-71;A-106
12509ST3QIERB447T-W2	\$29,733	A-71;A-106
12512EG3G445T-W22	\$19,742	A-88
12512ET3E445T-W22	\$17,947	A-39;A-97
12512ET3E445T-W22G	\$19,497	A-64;A-185
12512ET3ERB445T-W22	\$17,947	A-39;A-97;A-113
12512ET3G445T-W22	\$17,947	A-39;A-97
12512ET3GRB445T-W22	\$17,947	A-39;A-97;A-113
12512ET3H445T-W22	\$17,947	A-39;A-97
12512ET3H445T-W22G	\$19,497	A-64;A-185



Part Number	List Price	Pages
125120T3G445T-W40	\$12,753	A-54
125120T3G445T-W40G	\$14,353	A-67;A-188
12512ST3HIE445T-W22	\$20,158	A-71;A-106
12512ST3QIE445T-W22	\$20,158	A-71;A-106
12512ST3QIERB445T-W2	\$20,158	A-71;A-106
12512XT3G445T	\$21,537	A-125
12515EP30FP444TS-W22	\$14,011	A-242
125150P30FP445TS-W40	\$9,336	A-241
12518EG3G444T-W22	\$16,223	A-88
12518ET3E444TC-W22	\$16,218	A-45;A-101
12518ET3E444TC-W22G	\$16,904	A-64;A-185
12518ET3E444TS-W22	\$14,748	A-39;A-97
12518ET3E444T-W22	\$14,748	A-39;A-97
12518ET3E444T-W22G	\$16,298	A-64;A-185
12518ET3ERB444T-W22	\$14,748	A-39;A-97;A-113
12518ET3G444HP-W22	\$15,687	A-245
12518ET3G444TC-W22	\$16,218	A-45;A-101
12518ET3G444TC-W22G	\$17,768	A-64;A-185
12518ET3G444TSC-W22	\$16,218	A-45;A-101
12518ET3G444T-W22	\$14,748	A-39;A-97
12518ET3GRB444T-W22	\$14,748	A-39;A-97;A-113
12518ET3H444TC-W22	\$16,218	A-45;A-101
12518ET3H444T-W22	\$14,748	A-39;A-97
12518ET3H444T-W22G	\$16,298	A-64;A-185
125180P3EFP405TS-W40	\$6,651	A-236
125180P3GFP405TC-W40	\$6,651	A-237
125180P3GFP405TS-W40	\$6,651	A-236
125180P3HFP405TC-W40	\$6,651	A-237
125180P3HFP405TS-W40	\$6,651	A-236
125180P3VFP405TS-W40	\$6,651	A-236
125180T3E405TC-W40	\$8,427	A-59
125180T3E405TC-W40G	\$9,627	A-67;A-188
125180T3E405TSC-W40	\$8,427	A-59
125180T3E405TS-W40	\$7,981	A-54
125180T3E405T-W40	\$7,981	A-54
125180T3E405T-W40G	\$9,181	A-67;A-188
125180T3ERB405T-W40	\$7,981	A-54
125180T3G405JP-W40	\$10,317	A-227
125180T3G405TC-W40	\$8,427	A-59
125180T3G405TSC-W40	\$8,427	A-59
125180T3G405TS-W40	\$7,981	A-54
125180T3G405T-W40	\$7,981	A-54
125180T3GRB405T-W40	\$7,981	A-54
125180T3H405TC-W40	\$8,427	A-59
125180T3H405T-W40	\$7,981	A-54
125180T3H405T-W40G	\$9,181	A-67;A-188
12518ST3HIE444T-W22	\$16,564	A-71;A-106
12518ST3QIE444T-W22	\$16,564	A-71;A-106
12518ST3QIERB444T-W2	\$16,564	A-71;A-106
12518XT3E444T	\$19,961	A-125
12518XT3G444T	\$19,961	A-125

Part Number	List Price	Pages
12530EP30FP444TS-W22	\$14,583	A-242
125300P30FP405TS-W40	\$8,927	A-241
12536EG3G444TS-W22	\$16,885	A-88
12536ET3E444TS-W22	\$15,350	A-39;A-97
12536ET3E444TS-W22G	\$16,900	A-64;A-185
12536ET3G444HP-W22	\$17,969	A-245
12536ET3G444TS-W22	\$15,350	A-39;A-97
12536ET3H444TS-W22	\$15,350	A-39;A-97
12536ET3H444TS-W22G	\$16,900	A-64;A-185
125360P3EFP404TS-W40	\$7,762	A-236
125360P3GFP404TS-W40	\$7,762	A-236
125360P3HFP404TS-W40	\$7,762	A-236
125360P3JFP404TS-W40	\$7,762	A-236
125360P3VFP404TS-W40	\$7,762	A-236
125360T3E404TS-W40	\$8,826	A-54
125360T3E404TS-W40G	\$10,026	A-67;A-188
125360T3G404JP-W40	\$10,563	A-227
125360T3G404TSC-RFW4	\$10,199	A-275
125360T3G404TS-RFVFD	\$11,950	A-275
125360T3G404TS-RFW40	\$9,709	A-275
125360T3G404TS-W40	\$8,826	A-54
125360T3H404TS-W40	\$8,826	A-54
12536ST3HIE444TS-W22	\$18,198	A-71;A-106
12536ST3QIE444TS-W22	\$18,198	A-71;A-106
12536XT3G444TS	\$20,874	A-125
13209ET3Y315L-W22	\$33,687	A-84;A-118;A-250
132108T139**	\$1,696	A-137
132108T140**	\$1,676	A-138
13212ET3Y315S/M-W22	\$25,642	A-84;A-118;A-250
13218ET3Y315S/M-W22	\$19,732	A-84;A-118;A-250
13236ET3Y315S/M-W22	\$23,180	A-84;A-118;A-250
15009ET3G449T-W22	\$30,677	A-39;A-97
15009ET3GKD447T-W22	\$30,677	A-113
15009ST3QIE447T-W22	\$34,755	A-72;A-107
15009ST3QIERB447T-W2	\$34,755	A-72;A-107
15012EG3G449T-W22	\$22,703	A-88
15012ET3E447T-W22	\$20,639	A-39;A-97
15012ET3G447T-W22	\$20,639	A-39;A-97
15012ET3GRB447T-W22	\$20,639	A-39;A-97;A-113
15012ET3H447T-W22	\$20,639	A-39;A-97
15012ET3Y315L-W22	\$28,298	A-84;A-118;A-250
150120T3G445T-W40	\$13,615	A-54
15012ST3HIE447T-W22	\$23,181	A-72;A-107
15012ST3QIE447T-W22	\$23,181	A-72;A-107
15012ST3QIERB447T-W2	\$23,181	A-72;A-107
15012XT3G447T	\$32,370	A-126
15012XT3G504	\$32,370	A-126
15015EP30FP445TS-W22	\$16,549	A-242
150150P30FP445TS-W40	\$10,225	A-241
15018EG3G445T-W22	\$19,162	A-88
15018ET3E445TC-W22	\$18,025	A-45;A-101

Part Number	List Price	Pages
15018ET3E445TC-W22G	\$19,575	A-64;A-185
15018ET3E445T-W22	\$17,420	A-39;A-97
15018ET3G445HP-W22	\$17,845	A-245
15018ET3G445TC-W22	\$18,025	A-45;A-101
15018ET3G445TC-W22G	\$19,575	A-64;A-185
15018ET3G445TS-W22	\$17,420	A-39;A-97
15018ET3G445T-W22	\$17,420	A-39;A-97
15018ET3GRB445T-W22	\$17,420	A-39;A-97;A-113
15018ET3H445T-W22	\$17,420	A-39;A-97
15018ET3HRB445T-W22	\$17,420	A-39;A-97;A-113
15018ET3Y315S/M-W22	\$21,772	A-84;A-118;A-250
15018OP3EFP444TS-W40	\$8,891	A-236
15018OP3GFP444TS-W40	\$8,891	A-236
15018OP3HFP444TS-W40	\$8,891	A-236
15018OT3G444TC-W40	\$11,228	A-59
15018OT3G444TSC-W40	\$11,228	A-59
15018OT3G444TS-W40	\$10,668	A-54
15018OT3G444T-W40	\$10,668	A-54
15018OT3GRB444T-W40	\$10,668	A-54
15018OT3H444TC-W40	\$11,228	A-59
15018OT3H444T-W40	\$10,668	A-54
15018ST3HIE445T-W22	\$18,587	A-72;A-107
15018ST3HIERB445T-W2	\$18,587	A-72;A-107
15018ST3QIE445T-W22	\$18,587	A-72;A-107
15018ST3QIERB445T-W2	\$18,587	A-72;A-107
15018XT3E445T	\$21,557	A-126
15018XT3G445T	\$21,557	A-126
15018XT3H445T	\$21,557	A-126
15030EP30FP445TS-W22	\$17,938	A-242
15030OP30FP445TS-W40	\$13,422	A-241
15036EG3G445TS-W22	\$20,770	A-88
15036ET3E445TS-W22	\$18,882	A-39;A-97
15036ET3G445HP-W22	\$20,517	A-245
15036ET3G445TS-W22	\$18,882	A-39;A-97
15036ET3Y315S/M-W22	\$26,249	A-84;A-118;A-250
15036OP3EFP405TS-W40	\$10,042	A-236
15036OP3GFP405TS-W40	\$10,042	A-236
15036OP3HFP405TS-W40	\$10,042	A-236
15036OP3JFP405TS-W40	\$10,042	A-236
15036OP3VFP405TS-W40	\$10,042	A-236
15036OT3G405JP-W40	\$13,922	A-227
15036OT3G405TSC-RFW4	\$13,048	A-275
15036OT3G405TSC-W40	\$11,862	A-59
15036OT3G405TS-RFVFD	\$14,799	A-275
15036OT3G405TS-RFW40	\$12,558	A-275
15036OT3G405TS-W40	\$11,416	A-54
15036OT3G405TS-W40G	\$12,616	A-67;A-188
15036OT3H405TS-W40	\$11,416	A-54
15036ST3HIE445TS-W22	\$21,433	A-72;A-107
15036ST3QIE445TS-W22	\$21,433	A-72;A-107

Part Number	List Price	Pages
15036XT3G445TS	\$21,320	A-126
18512ET3Y355M/L-W22	\$43,876	A-84;A-118;A-250
18518ET3Y315S/M-W22	\$26,247	A-84;A-118;A-250
18536ET3Y315S/M-W22	\$26,529	A-84;A-118;A-250
20009ET3G449T-W22	\$49,899	A-40;A-98
20009ET3GKD449T-W22	\$49,899	A-113
20009ST3HIE449T-W22	\$57,394	A-72;A-107
20009ST3QIE449T-W22	\$57,394	A-72;A-107
20009ST3QIERB449T-W2	\$57,394	A-72;A-107
20012EG3G449T-W22	\$27,646	A-88
20012ET3E449T-W22	\$25,255	A-40;A-98
20012ET3G447T-W22	\$25,133	A-40;A-98
20012ET3G449T-W22	\$25,255	A-40;A-98
20012ET3G505-W22	\$25,133	A-40;A-98
20012ET3GKD505Z-W22	\$25,133	A-113
20012ET3GRB447T-W22	\$25,133	A-40;A-98;A-113
20012ET3GRB449T-W22	\$25,255	A-40;A-98;A-113
20012ET3H449T-W22	\$25,255	A-40;A-98
20012ET3HKD505Z-W22	\$25,133	A-113
20012ET3XL449-W22MV	\$43,039	A-286
20012ET3XL449-W22MVR	\$43,039	A-286
20012OT3G447/9T-W40	\$23,380	A-55
20012ST3HIE449T-W22	\$27,577	A-72;A-107
20012ST3HIERB449T-W2	\$27,557	A-72;A-107
20012ST3QIE449T-W22	\$27,577	A-72;A-107
20012ST3QIERB449T-W2	\$27,557	A-72;A-107
20012XT3G447T	\$33,613	A-126
20015EP30FP447TS-W22	\$20,043	A-242
20015OP30FP449TS-W40	\$15,362	A-241
20018EG3G449T-W22	\$23,208	A-88
20018ET3E447T-W22	\$21,098	A-40;A-98
20018ET3G447TC-W22	\$21,704	A-45;A-102
20018ET3G447TS-W22	\$21,098	A-40;A-98
20018ET3G447T-W22	\$21,098	A-40;A-98
20018ET3G504-W22	\$21,098	A-40;A-98
20018ET3GRB447T-W22	\$21,098	A-40;A-98;A-113
20018ET3H447T-W22	\$21,098	A-40;A-98
20018ET3HRB447T-W22	\$21,098	A-40;A-98;A-113
20018ET3XL449-W22MV	\$37,790	A-286
20018ET3XL449-W22MVR	\$37,790	A-286
20018OP3GFP445TS-W40	\$10,837	A-236
20018OP3HFP445TS-W40	\$10,837	A-236
20018OT3G445TC-W40	\$13,564	A-59
20018OT3G445TS-W40	\$13,004	A-55
20018OT3G445T-W40	\$13,004	A-55
20018OT3GRB445T-W40	\$13,004	A-55
20018ST3HIE447T-W22	\$23,696	A-72;A-107
20018ST3QIE447T-W22	\$23,696	A-72;A-107
20018ST3QIERB447T-W2	\$23,696	A-72;A-107
20018XT3G447T	\$29,397	A-126
20018XT3G504	\$29,397	A-126

Part Number	List Price	Pages
20030EP30FP447TS-W22	\$22,384	A-242
200300P30FP445TS-W40	\$14,700	A-241
20036EG3G447TS-W22	\$25,918	A-88
20036ET3E447TS-W22	\$23,562	A-40;A-98
20036ET3G447TS-W22	\$23,562	A-40;A-98
20036ET3G504S-W22	\$23,562	A-40;A-98
20036ET3XL449-W22MV	\$38,054	A-286
20036ET3XL449-W22MVR	\$38,054	A-286
200360P3GFP444TS-W40	\$12,782	A-236
200360P3HFP444TS-W40	\$12,782	A-236
200360P3JFP444TS-W40	\$12,782	A-236
200360T3G444TSC-RFW4	\$16,570	A-275
200360T3G444TSC-W40	\$15,064	A-59
200360T3G444TS-RFVFD	\$18,818	A-275
200360T3G444TS-RFW40	\$15,954	A-275
200360T3G444TS-W40	\$14,504	A-55
200360T3H444TS-W40	\$14,504	A-55
20036ST3HIE447TS-W22	\$28,568	A-72;A-107
20036ST3QIE447TS-W22	\$28,568	A-72;A-107
20036XT3G447TS	\$29,446	A-126
22012ET3Y355M/L-W22	\$46,322	A-84;A-118;A-250
22018ET3Y315L-W22	\$36,234	A-84;A-118;A-250
22036ET3Y315L-W22	\$44,212	A-84;A-118;A-250
25009ET3G449T-W22	\$56,168	A-40;A-98
25009ET3GKD586/7-W22	\$56,168	A-113
25012ET3E449T-W22	\$35,555	A-40;A-98
25012ET3G449T-W22	\$35,555	A-40;A-98
25012ET3G586/7-W22	\$39,631	A-40;A-98
25012ET3GKD449T-W22	\$35,555	A-113
25012ET3GKD580Z-W22	\$39,631	A-113
25012ET3GRB449T-W22	\$35,555	A-40;A-98;A-113
25012ET3H449T-W22	\$35,555	A-40;A-98
25012ET3HKD580Z-W22	\$39,631	A-113
25012ET3X5009-W50MV	\$48,810	A-286
250120T3G447/9T-W40	\$27,249	A-55
25012ST3QIE449T-W22	\$39,415	A-72;A-107
25012ST3QIERB449T-W2	\$39,415	A-72;A-107
25012XT3G449T	\$48,048	A-126
25015EP30FP449TS-W22	\$25,463	A-242
250150P30FP449TS-W40	\$20,127	A-241
25018EG3G449T-W22	\$29,388	A-88
25018ET3G447TSC-W22	\$27,795	A-45;A-102
25018ET3G447TS-W22	\$27,189	A-40;A-98
25018ET3G447T-W22	\$26,716	A-40;A-98
25018ET3G449T-W22	\$26,803	A-40;A-98
25018ET3GKD447T-W22	\$26,716	A-113
25018ET3GKD505Z-W22	\$26,716	A-113
25018ET3GRB447T-W22	\$26,716	A-40;A-98;A-113
25018ET3GRB449T-W22	\$26,803	A-40;A-98;A-113
25018ET3H447TS-W22	\$27,189	A-40;A-98
25018ET3H447T-W22	\$26,716	A-40;A-98

Part Number	List Price	Pages
25018ET3HRB447T-W22	\$26,716	A-40;A-98;A-113
25018ET3Q447TSC-W22	\$27,322	A-102
25018ET3X5009-W50MV	\$42,249	A-286
250180P3GFP445TS-W40	\$13,358	A-236
250180P3HFP445TS-W40	\$13,358	A-236
250180T3G445TC-W40	\$16,073	A-59
250180T3G445TS-W40	\$15,513	A-55
250180T3G445T-W40	\$15,513	A-55
250180T3GRB445T-W40	\$15,513	A-55
250180T3H445T-W40	\$15,513	A-55
25018ST3QIE449T-W22	\$30,081	A-72;A-107
25018ST3QIERB449T-W2	\$30,081	A-72;A-107
25018XT3G447T	\$32,866	A-126
25018XT3H447T	\$32,866	A-126
25030EP30FP449TS-W22	\$31,514	A-242
250300P30FP445TS-W40	\$18,003	A-241
25036EG3G447TS-W22	\$32,831	A-88
25036ET3G447TS-W22	\$29,846	A-40;A-98
25036ET3G449TS-W22	\$33,173	A-40;A-98
25036ET3X5009-W50MV	\$42,512	A-286
250360P3GFP445TS-W40	\$15,654	A-236
250360P3HFP445TS-W40	\$15,654	A-236
250360T3G445TSC-RFW4	\$21,497	A-275
250360T3G445TSC-W40	\$19,543	A-59
250360T3G445TS-RFVFD	\$23,745	A-275
250360T3G445TS-RFW40	\$20,881	A-275
250360T3G445TS-W40	\$18,983	A-55
250360T3H445TS-W40	\$18,983	A-55
25036ST3QIE449TS-W22	\$34,663	A-72;A-107
25036XT3G447TS	\$31,124	A-126
26012ET3Y355M/L-W22	\$53,001	A-84;A-118;A-250
26018ET3Y355M/L-W22	\$43,761	A-84;A-118;A-250
26036ET3Y355M/L-W22	\$50,637	A-84;A-118;A-250
30009ET3G449T-W22	\$58,655	A-40;A-98
30009ET3GKD586/7-W22	\$58,655	A-114
30012ET3G449T-W22	\$38,437	A-40;A-98
30012ET3G586/7-W22	\$44,301	A-40;A-98
30012ET3GKD449T-W22	\$38,437	A-40;A-98;A-114
30012ET3GKD580Z-W22	\$44,301	A-114
30012ET3GKD586/7-W22	\$44,301	A-114
30012ET3HKD580Z-W22	\$44,301	A-114
30012ET3X5009-W50MV	\$55,371	A-286
300120T3G447/9T-W40	\$29,853	A-55
30012ST3QIE449T-W22	\$44,648	A-72;A-107
30012ST3QIERB449T-W2	\$44,648	A-72;A-107
30012XT3G449T	\$52,790	A-126
30015EP30FP449TS-W22	\$29,815	A-242
300150P30FP5011TS-W4	\$22,044	A-241
30018ET3G449TC-W22	\$31,990	A-45;A-102
30018ET3G449TS-W22	\$31,384	A-40;A-98
30018ET3G449T-W22	\$31,384	A-40;A-98

Part Number	List Price	Pages
30018ET3GKD449T-W22	\$31,384	A-114
30018ET3GKD580Z-W22	\$39,112	A-114
30018ET3GRB449T-W22	\$31,384	A-40;A-98;A-114
30018ET3HKD580Z-W22	\$39,112	A-114
30018ET3X5009-W50MV	\$47,239	A-286
30018ET3Y355M/L-W22	\$60,292	A-84;A-118;A-250
300180P3GFP447/9TSW4	\$19,168	A-236
300180T3G447/9TS-W40	\$24,878	A-55
300180T3G447/9T-W40	\$24,878	A-55
30018ST3QIE449T-W22	\$36,810	A-72;A-107
30018ST3QIERB449T-W2	\$36,810	A-72;A-107
30018XT3G449T	\$42,566	A-126
30030EP30FP449TS-W22	\$36,356	A-242
300300P30FP449TS-W40	\$23,464	A-241
30036ET3G449TS-W22	\$38,269	A-40;A-98
30036ET3X5009-W50MV	\$51,698	A-286
30036ET3Y355M/L-W22	\$66,321	A-84;A-118;A-250
300360P3GFP445TS-W40	\$19,556	A-236
300360P3HFP445TS-W40	\$19,556	A-236
300360T3G445TSC-RFW4	\$25,139	A-275
300360T3G445TS-RFW40	\$24,523	A-275
300360T3G445TS-W40	\$22,294	A-55
300360T3G449TS-RFVFD	\$27,387	A-275
30036XT3G449TS	\$48,747	A-126
33018ET3Y355M/L-W22	\$64,557	A-84;A-118;A-250
35009ET3G586/7-W22	\$64,873	A-41;A-99
35009ET3GKD586/7-W22	\$64,873	A-114
35012ET3G449T-W22	\$47,633	A-41;A-99
35012ET3GKD580Z-W22	\$50,250	A-114
35012ET3GKD586/7-W22	\$50,250	A-114
35012ET3GRB449T-W22	\$47,633	A-41;A-99;A-114
35012ET3X5009-W50MV	\$61,532	A-286
35012ST3QIE449T-W22	\$52,634	A-72;A-107
35012ST3QIERB449T-W2	\$52,634	A-72;A-107
35012XT3G586/7	\$71,652	A-126
350150P30FP5011TS-W4	\$29,804	A-241
35018ET3G449TS-W22	\$36,517	A-41;A-99
35018ET3G449T-W22	\$36,517	A-41;A-99
35018ET3GKD449T-W22	\$36,517	A-114
35018ET3GKD580Z-W22	\$41,230	A-114
35018ET3GRB449T-W22	\$36,517	A-41;A-99;A-114
35018ET3HKD580Z-W22	\$41,230	A-114
350180P3GFP447/9TSW4	\$22,807	A-236
350180P3HFP447/9TSW4	\$22,807	A-236
350180T3G447/9TS-W40	\$25,174	A-55
350180T3G447/9T-W40	\$25,174	A-55
35018ST3QIE449T-W22	\$44,105	A-72;A-107
35018ST3QIERB449T-W2	\$44,105	A-72;A-107
35018XT3G449T	\$53,222	A-126
350300P30FP449TS-W40	\$25,697	A-241
35036ET3G449TS-W22	\$43,805	A-41;A-99

Part Number	List Price	Pages
350360P3GFP447/9TSW4	\$22,346	A-236
350360P3HFP447/9TSW4	\$22,346	A-236
350360T3G447/9TS-W40	\$25,055	A-55
350360T3G449TSC-RFW4	\$29,637	A-275
350360T3G449TS-RFW40	\$28,813	A-275
35036XT3G449TS	\$65,868	A-126
40009ET3G588/9-W22	\$66,123	A-41;A-99
40012ET3G449T-W22	\$52,307	A-41;A-99
40012ET3G586/7-W22	\$56,201	A-41;A-99
40012ET3GKD580Z-W22	\$58,210	A-114
40012ET3GKD586/7-W22	\$56,201	A-114
40012ET3GRB449T-W22	\$52,307	A-41;A-99;A-114
40012ET3HKD580Z-W22	\$58,210	A-114
40012ET3X5809-W50MV	\$68,812	A-286
40012XT3G586/7	\$75,473	A-126
400150P30FP5011TS-W4	\$32,521	A-241
40018ET3G449TS-W22	\$43,805	A-41;A-99
40018ET3G449T-W22	\$43,805	A-41;A-99
40018ET3GKD580Z-W22	\$45,805	A-114
40018ET3GRB449T-W22	\$43,805	A-41;A-99;A-114
40018ET3H449T-W22	\$43,805	A-41;A-99
40018ET3HKD580Z-W22	\$45,805	A-114
40018ET3X5009-W50MV	\$60,848	A-286
40018ET3X5009-W50MVR	\$60,848	A-286
400180P3HFP447/9TSW4	\$25,570	A-236
400180P3QFP447/9TSW4	\$25,570	A-236
400180T3G447/9TS-W40	\$28,311	A-55
400180T3G447/9T-W40	\$28,311	A-55
40018ST3QIE449T-W22	\$48,396	A-72;A-107
40018ST3QIERB449T-W2	\$48,396	A-72;A-107
40018XT3G586/7	\$61,096	A-126
400300P30FP449TS-W40	\$27,761	A-241
40036ET3G449TS-W22	\$44,605	A-41;A-99
40036ET3X5009-W50MV	\$61,669	A-286
40036ET3X5009-W50MVR	\$61,669	A-286
400360P3GFP447/9TSW4	\$24,140	A-236
400360P3HFP447/9TSW4	\$24,140	A-236
400360T3G447/9TS-W40	\$26,678	A-55
400360T3G449TS-RFW40	\$30,680	A-275
45009ET3G588/9-W22	\$68,715	A-41;A-99
45012ET3G586/7-W22	\$62,251	A-41;A-99
45012ET3GKD580Z-W22	\$63,251	A-114
45012ET3GRB586/7-W22	\$62,251	A-41;A-99;A-114
45018ET3G449T-W22	\$48,010	A-41;A-99
45018ET3GKD580Z-W22	\$48,053	A-114
45018ET3GKD586/7-W22	\$48,053	A-114
45018ET3GRB449T-W22	\$48,010	A-41;A-99;A-114
45018XT3G586/7	\$65,201	A-126
45036ET3G449TS-W22	\$49,610	A-41;A-99
450360P3GFP447/9TSW4	\$26,055	A-236
450360P3HFP447/9TSW4	\$26,055	A-236

Part Number	List Price	Pages
450360T3G447/9TS-W40	\$28,239	A-55
450360T3G449TS-RFW40	\$32,475	A-275
50012ET3G586/7-W22	\$62,962	A-41;A-99
50012ET3GKD580Z-W22	\$65,962	A-114
50012ET3X5809-W50MV	\$89,970	A-286
50012ET3X5809-W50MVR	\$89,970	A-286
50018ET3G449T-W22	\$50,594	A-41;A-99
50018ET3GKD580Z-W22	\$51,611	A-114
50018ET3GRB449T-W22	\$50,594	A-41;A-99;A-114
50018ET3X5009-W50MV	\$76,398	A-286
50018ET3X5009-W50MVR	\$76,398	A-286
50018XT3G586/7	\$70,086	A-126
50036ET3G586/7S-W22	\$56,305	A-41;A-99
50036ET3X5809-W50MV	\$79,517	A-286
50036ET3X5809-W50MVR	\$79,517	A-286
500360P3GFP447/9TSW4	\$27,711	A-236
500360P3HFP447/9TSW4	\$27,711	A-236
500360T3G447/9TS-W40	\$31,476	A-55
500360T3G449TS-RFW40	\$36,197	A-275
550360T3G447/9TS-W40	\$32,629	A-55
60012ET3G588/9-W22	\$71,374	A-41;A-99
60012ET3X5809-W50MV	\$105,217	A-286
60012ET3X5809-W50MVR	\$105,217	A-286
60018ET3G586/7-W22	\$60,316	A-41;A-99
60018ET3X5809-W50MV	\$91,633	A-286
60018ET3X5809-W50MVR	\$91,633	A-286
60036ET3G588/9S-W22	\$64,635	A-41;A-99
60036ET3X5809-W50MV	\$86,864	A-286
60036ET3X5809-W50MVR	\$86,864	A-286
600360T3G447/9TS-W40	\$32,994	A-55
600360T3G449TS-RFW40	\$37,943	A-275
65018ET3G588/9-W22	\$66,701	A-41;A-99
65036ET3G588/9S-W22	\$66,835	A-41;A-99
70012ET3X6808-W50MV	\$117,307	A-286
70012ET3X6808-W50MVR	\$117,307	A-286
70018ET3G588/9-W22	\$71,185	A-41;A-99
70018ET3X6806-W50MV	\$105,814	A-286
70018ET3X6806-W50MVR	\$105,814	A-286
70036ET3G588/9S-W22	\$71,254	A-41;A-99
700360T3G5010S-RF	\$48,993	A-275
700360T3Q5010S-W40	\$42,603	A-55
75018ET3G588/9-W22	\$74,025	A-41;A-99
80018ET3X6808-W50MV	\$114,209	A-286
80018ET3X6808-W50MVR	\$114,209	A-286
800360T3G5010S-RF	\$51,795	A-275
800360T3Q5010S-W40	\$45,039	A-55
ACBF-11	\$20	A-394
ACBF-11 MPW100	\$35	A-394
ACBS-02	\$22	A-394
ACBS-02 MPW100	\$27	A-394
ACBS-11	\$22	A-394

Part Number	List Price	Pages
ACBS-11 MPW100	\$27	A-394
ACBS-20	\$22	A-394
ACBS-20 MPW100	\$27	A-394
AG10250MI60AI	\$12,665	A-301
AG10250MI70AI	\$14,625	A-301
AG10250MI80AI	\$15,561	A-301
AG10250SI50AI	\$11,723	A-301
AG10280MI50AI	\$16,948	A-301
AG10280MI60AI	\$18,802	A-301
AG10315LI90AI	\$35,691	A-301
AG10315MI50AI	\$21,388	A-301
AG10315MI60AI	\$23,985	A-301
AG10315MI70AI	\$26,638	A-301
AG10355MI65AI	\$42,822	A-301
AG10355MI70AI	\$48,750	A-301
AUXTBOXF1W22-A	\$135	A-422
AUXTBOXF1W22-B	\$171	A-422
AUXTBOXF1W22-C	\$270	A-422
AUXTBOXF1W22-D	\$270	A-422
AUXTBOXF2W22-B	\$171	A-422
AUXTBOXF2W22-C	\$270	A-422
AUXTBOXF2W22-D	\$270	A-422
BC10B-CSW	\$5	A-379
BDK-BM140-W22	\$422	A-423
BDK-BM180-W22	\$643	A-423
BDK-BM210-W22	\$770	A-423
BDK-BM250-W22	\$934	A-423
BDK-BM280-W22	\$1,610	A-423
BDK-BM320-W22	\$2,814	A-423
BLK-E140	\$1,149	A-427
BLK-E180	\$1,260	A-427
BLK-E210	\$1,452	A-427
BLK-E250-W22	\$1,573	A-427
BLK-E280	\$1,658	A-427
BLK-E320	\$1,821	A-427
BLK-E360-W22	\$2,038	A-427
BLK-E400-W22	\$2,159	A-427
BLK-E444/5-W22	\$2,561	A-427
BLK-E445/7-447/9-W22	\$2,561	A-427
BLK-E580-W22	\$3,632	A-427
BLK-EL449/500-W22	\$3,025	A-427
BRAKE-E140-W22	\$588	A-423
BRAKE-E180-W22	\$972	A-423
BRAKE-E210-W22	\$1,410	A-423
BRAKE-E250-W22	\$1,985	A-423
BRAKE-E280-W22	\$3,454	A-423
BRAKE-E320-W22	\$5,453	A-423
BRKHDL-BM140-W22	\$78	A-424
BRKHDL-BM180-W22	\$127	A-424
BRKHDL-BM210-W22	\$179	A-424

Part Number	List Price	Pages
BRKHDL-BM250-W22	\$236	A-424
BRKHDL-BM280-W22	\$453	A-424
BRKHDL-BM320-W22	\$602	A-424
CAN-01	\$410	A-339
CCK-01	\$105	A-339
CFW300A01P6S1NB20	\$361	A-325
CFW300A01P6S2NB20	\$323	A-325
CFW300A01P6T2NB20	\$343	A-325
CFW300A02P6S1NB20	\$394	A-325
CFW300A02P6S2NB20	\$348	A-325
CFW300A02P6T2NB20	\$376	A-325
CFW300A04P2S1NB20	\$420	A-325
CFW300A04P2S2NB20	\$371	A-325
CFW300A04P2T2NB20	\$399	A-325
CFW300A06P0S1NB20	\$507	A-325
CFW300A06P0S2NB20	\$461	A-325
CFW300A06P0T2NB20	\$484	A-325
CFW300A07P3S2NB20	\$543	A-325
CFW300A07P3T2NB20	\$571	A-325
CFW300B10P0B2DB20 3	\$648	A-325
CFW300B15P2T2DB20	\$792	A-325
CFW300-CCAN	\$100	A-325
CFW300-CPDP	\$294	A-325
CFW300-CRS232	\$82	A-325
CFW300-CRS485	\$82	A-325
CFW300-CUSB	\$87	A-325
CFW300-IOADR	\$207	A-325
CFW300-IOAENC	\$143	A-325
CFW300-IOAR	\$141	A-325
CFW300-IODR	\$108	A-325
CFW300-KFA	\$90	A-325
CFW300-KFB	\$105	A-325
CFW300-KHMIR	\$256	A-325
CFW300-MMF	\$210	A-325
CFW500A01P0T4DB66DSG2	\$1,095	A-153;A-345
CFW500A01P0T4DB66G2	\$950	A-152;A-344
CFW500A01P0T4NB20	\$582	A-330
CFW500A01P6B2DB66DSG2	\$895	A-153;A-345
CFW500A01P6B2DB66G2	\$775	A-152;A-344
CFW500A01P6B2NB20	\$456	A-330
CFW500A01P6S2NB20	\$451	A-330
CFW500A01P6T4DB66DSG2	\$1,125	A-153;A-345
CFW500A01P6T4DB66G2	\$975	A-152;A-344
CFW500A01P6T4NB20	\$604	A-330
CFW500A02P6B2DB66DSG2	\$920	A-153;A-345
CFW500A02P6B2DB66G2	\$800	A-152;A-344
CFW500A02P6B2NB20	\$467	A-330
CFW500A02P6S2NB20	\$463	A-330
CFW500A02P6T4DB66DSG2	\$1,140	A-153;A-345
CFW500A02P6T4DB66G2	\$990	A-152;A-344
CFW500A02P6T4NB20	\$649	A-330

Part Number	List Price	Pages
CFW500A04P3B2DB66DSG2	\$980	A-153;A-345
CFW500A04P3B2DB66G2	\$850	A-152;A-344
CFW500A04P3B2NB20	\$506	A-330
CFW500A04P3S2NB20	\$499	A-330
CFW500A04P3T4DB66DSG2	\$1,350	A-153;A-345
CFW500A04P3T4DB66G2	\$1,175	A-152;A-344
CFW500A04P3T4NB20	\$799	A-330
CFW500A06P1T4NB20	\$982	A-330
CFW500A06P5T4DB66DSG2	\$1,610	A-153;A-345
CFW500A06P5T4DB66G2	\$1,400	A-152;A-344
CFW500A07P0S2NB20	\$633	A-330
CFW500A07P0T2NB20	\$628	A-330
CFW500A07P3B2DB66DSG2	\$1,170	A-153;A-345
CFW500A07P3B2DB66G2	\$1,015	A-152;A-344
CFW500A09P6T2NB20	\$773	A-330
CFW500A10P0B2DB66DSG2	\$1,255	A-153;A-345
CFW500A10P0B2DB66G2	\$1,095	A-152;A-344
CFW500A10P0T4DB66DSG2	\$1,900	A-153;A-345
CFW500A10P0T4DB66G2	\$1,650	A-152;A-344
CFW500A16P0T2DB66DSG2	\$1,555	A-153;A-345
CFW500A16P0T2DB66G2	\$1,350	A-152;A-344
CFW500B01P7T5DB66	\$1,590	A-152;A-344
CFW500B01P7T5DB66DS	\$1,830	A-153;A-345
CFW500B02P6T4DB20	\$708	A-330
CFW500B03P0T5DB66	\$1,670	A-152;A-344
CFW500B03P0T5DB66DS	\$1,925	A-153;A-345
CFW500B04P3T4DB20	\$892	A-330
CFW500B04P3T5DB66	\$1,890	A-152;A-344
CFW500B04P3T5DB66DS	\$2,175	A-153;A-345
CFW500B06P5T4DB20	\$1,067	A-330
CFW500B07P0T5DB66	\$2,115	A-152;A-344
CFW500B07P0T5DB66DS	\$2,435	A-153;A-345
CFW500B07P3B2DB20	\$678	A-330
CFW500B10P0B2DB20	\$789	A-330
CFW500B10P0T4DB20	\$1,207	A-330
CFW500B10P0T5DB66	\$2,330	A-152;A-344
CFW500B10P0T5DB66DS	\$2,680	A-153;A-345
CFW500B12P0T5DB66	\$2,615	A-152;A-344
CFW500B12P0T5DB66DS	\$3,005	A-153;A-345
CFW500B14P0T4DB66DSG2	\$2,360	A-153;A-345
CFW500B14P0T4DB66G2	\$2,050	A-152;A-344
CFW500B16P0T2DB20	\$842	A-330
CFW500B16P0T4DB66DSG2	\$2,620	A-153;A-345
CFW500B16P0T4DB66G2	\$2,275	A-152;A-344
CFW500B24P0T2DB66DSG2	\$2,245	A-153;A-345
CFW500B24P0T2DB66G2	\$1,950	A-152;A-344
CFW500B24P0T4DB66DSG2	\$3,480	A-153;A-345
CFW500B24P0T4DB66G2	\$3,025	A-152;A-344
CFW500B28P0T2DB66DSG2	\$2,620	A-153;A-345
CFW500B28P0T2DB66G2	\$2,275	A-152;A-344
CFW500B31P0T4DB66DSG2	\$4,200	A-153;A-345

Part Number	List Price	Pages
CFW500B31POT4DB66G2	\$3,650	A-152;A-344
CFW500B33POT2DB66DSG2	\$3,080	A-153;A-345
CFW500B33POT2DB66G2	\$2,675	A-152;A-344
CFW500C01P7T5DB20	\$910	A-330
CFW500C03POT5DB20	\$954	A-330
CFW500C04P3T5DB20	\$1,073	A-330
CFW500C07POT5DB20	\$1,276	A-330
CFW500C10POT5DB20	\$1,621	A-330
CFW500C12POT5DB20	\$1,813	A-330
CFW500C14POT4DB20	\$1,495	A-330
CFW500C16POT4DB20	\$1,684	A-330
CFW500C24POT2DB20	\$1,427	A-330
CFW500-CCAN	\$138	A-331
CFW500-CCHMIR010M	\$72	A-331
CFW500-CCHMIR01M	\$23	A-331
CFW500-CCHMIR02M	\$31	A-331
CFW500-CCHMIR03M	\$41	A-331
CFW500-CCHMIR05M	\$51	A-331
CFW500-CCHMIR075M	\$61	A-331
CFW500-CEMB-TCP	\$499	A-331
CFW500-CEPN-IO	\$499	A-331
CFW500-CETH-IP	\$499	A-331
CFW500-CPDP	\$405	A-331
CFW500-CPDP2	\$445	A-331
CFW500-CRS232	\$138	A-331
CFW500-CRS485	\$143	A-331
CFW500-CUSB	\$210	A-331
CFW500D24POT4DB20	\$2,229	A-330
CFW500D28POT2DB20	\$1,777	A-330
CFW500D31POT4DB20	\$2,783	A-330
CFW500D33POT2DB20	\$2,146	A-330
CFW500D47POT2DB20	\$2,910	A-330
CFW500E39POT4DB20	\$3,346	A-330
CFW500E49POT4DB20	\$4,214	A-330
CFW500E56POT2DB20	\$3,380	A-330
CFW500-ENC	\$210	A-331
CFW500-HMIR 2	\$169	A-331
CFW500-IOAD	\$182	A-331
CFW500-IOD	\$141	A-331
CFW500-IOR	\$125	A-331
CFW500-IOS 1	\$110	A-331
CFW500-KN1A	\$28	A-331
CFW500-KN1B	\$33	A-331
CFW500-KN1C	\$44	A-331
CFW500-KN1D	\$59	A-331
CFW500-KN1E	\$64	A-331
CFW500-KPCSA	\$41	A-331
CFW500-KPCSB	\$44	A-331
CFW500-KPCSC	\$46	A-331
CFW500-KPCSD	\$51	A-331
CFW500-MMF	\$189	A-331

Part Number	List Price	Pages
CFW500-USB02M	\$50	A-331
CFW700A03P6T4DB20	\$1,350	A-337
CFW700A05POT4DB20	\$1,444	A-337
CFW700A06P0B2DB20	\$1,370	A-336
CFW700A07P0B2DB20	\$1,430	A-336
CFW700A07POT2DB20	\$1,350	A-336
CFW700A07POT4DB20	\$1,510	A-337
CFW700A10P0S2DB20	\$1,510	A-336
CFW700A10POT2DB20	\$1,410	A-336
CFW700A10POT4DB20	\$1,600	A-337
CFW700A13POT2DB20	\$1,440	A-336
CFW700A13P5T4DB20	\$1,711	A-337
CFW700A16POT2DB20	\$1,542	A-336
CFW700B02P9T5DB20	\$1,689	A-338
CFW700B04P2T5DB20	\$1,759	A-338
CFW700B07POT5DB20	\$1,874	A-338
CFW700B10POT5DB20	\$2,048	A-338
CFW700B12POT5DB20	\$2,171	A-338
CFW700B17POT4DB20	\$2,055	A-337
CFW700B17POT5DB20	\$2,552	A-338
CFW700B24POT2DB20	\$2,020	A-336
CFW700B24POT4DB20	\$2,455	A-337
CFW700B28POT2DB20	\$2,201	A-336
CFW700B31POT4DB20	\$3,450	A-337
CFW700B33P5T2DB20	\$2,600	A-336
CFW700C22POT5DB20	\$4,235	A-338
CFW700C27POT5DB20	\$4,506	A-338
CFW700C32POT5DB20	\$6,486	A-338
CFW700C38POT4DB20	\$3,888	A-337
CFW700C44POT5DB20	\$7,309	A-338
CFW700C45POT2DB20	\$2,900	A-336
CFW700C45POT4DB20	\$5,000	A-337
CFW700C54POT2DB20	\$3,700	A-336
CFW700C58P5T4DB20	\$5,800	A-337
CFW700C70POT2DB20	\$4,880	A-336
CFW700D0105T2DBN1	\$8,100	A-336
CFW700D22POT5NBN1	\$3,921	A-338
CFW700D27POT5NBN1	\$4,450	A-338
CFW700D32POT5NBN1	\$5,763	A-338
CFW700D44POT5NBN1	\$6,768	A-338
CFW700D70P5T4DBN1	\$6,888	A-337
CFW700D86POT2DBN1	\$6,101	A-336
CFW700D88POT4DBN1	\$8,100	A-337
CFW700E0107T5DB20C3	\$16,240	A-338
CFW700E0107T5NB20C3	\$15,042	A-338
CFW700E0125T5DB20C3	\$16,910	A-338
CFW700E0125T5NB20C3	\$15,662	A-338
CFW700E0150T5DB20C3	\$23,456	A-338
CFW700E0150T5NB20C3	\$21,723	A-338
CFW700E0211T4NB20C3	\$18,787	A-337

Part Number	List Price	Pages
CFW700E105T4DB20C3	\$11,989	A-337
CFW700E105T4NB20C3	\$9,999	A-337
CFW700E142T2DB20C3	\$11,500	A-336
CFW700E142T2NB20C3	\$10,101	A-336
CFW700E142T4DB20C3	\$14,989	A-337
CFW700E142T4NB20C3	\$12,000	A-337
CFW700E180T2DB20C3	\$15,500	A-336
CFW700E180T2NB20C3	\$12,999	A-336
CFW700E180T4DB20C3	\$20,989	A-337
CFW700E180T4NB20C3	\$15,400	A-337
CFW700E211T2DB20C3	\$21,222	A-336
CFW700E211T2NB20C3	\$18,555	A-336
CFW700E211T4DB20C3	\$25,989	A-337
CFW700E53POT5DB20C3	\$9,118	A-338
CFW700E53POT5NB20C3	\$8,446	A-338
CFW700E63POT5DB20C3	\$11,580	A-338
CFW700E63POT5NB20C3	\$10,728	A-338
CFW700E80POT5DB20C3	\$12,091	A-338
CFW700E80POT5NB20C3	\$11,200	A-338
CSW30-SP3PBS	\$535	A-331;A-339
CSW-SP3PBS	\$460	A-331;A-339
DEVICENET-05	\$1,100	A-402
DRCV-E100	\$89	A-420
DRCV-E140	\$89	A-420
DRCV-E180	\$128	A-420
DRCV-E180-S	\$128	A-420
DRCV-E210	\$136	A-420
DRCV-E210-S	\$136	A-420
DRCV-E250-S	\$167	A-420
DRCV-E250-W22	\$167	A-420
DRCV-E280-W22	\$220	A-420
DRCV-E320-W22	\$344	A-420
DRCV-E360-W22	\$393	A-420
DRCV-E400-W22	\$479	A-420
DRCV-E440-W22	\$819	A-420
DRCV-E48/W56-S	\$45	A-420
DRCV-E56/140-S (for Steel Fan Cover)	\$53	A-420
DRCV-E580-W22	\$1,145	A-420
DRCV-EL440-W22	\$952	A-420
DRCV-0140-S	\$53	A-420
DRCV-0180-S	\$128	A-420
DRCV-0210-S	\$136	A-420
DRCV-0250-S	\$167	A-420
DRCV-0250-W40	\$152	A-420
DRCV-0280-W40	\$220	A-420
DRCV-0320-W40	\$366	A-420
DRCV-0360FL-400-W40	\$410	A-420
DRCV-0360-W40	\$410	A-420
DRCV-0444/5FL-W40	\$613	A-420
DRCV-0444/5-W40	\$613	A-420

Part Number	List Price	Pages
DRCV-056-S	\$45	A-420
DRCV-ODP250	\$152	A-420
DRCV-ODP280	\$220	A-420
DRCV-ODP320	\$366	A-420
DRCV-ODP360/400	\$410	A-420
DRCV-ODP440	\$613	A-420
E0.1812EP3WAX71F3-W2	\$476	A-253
E0.1818EP3WAX63F3-W2	\$365	A-253
E0.1836EP3WAX63F3-W2	\$364	A-253
E0.2512EP3WAX71F3-W2	\$483	A-253
E0.2518EP3WAX71F3-W2	\$415	A-253
E0.2536EP3WAX63F3-W2	\$373	A-253
E0.3712EP3WAX80F3-W2	\$507	A-253
E0.3718EP3WAX71F3-W2	\$427	A-253
E0.3736EP3WAX71F3-W2	\$408	A-253
E0.5512EP3WAX80F3-W2	\$523	A-253
E0.5518EP3WAX80F3-W2	\$488	A-253
E0.5536EP3WAX71F3-W2	\$415	A-253
E0.7512EP3WAX90SF3-W	\$660	A-253
E0.7512ET3WAXL90SF3W	\$872	A-253
E0.7512XP3WAX90LF3-W	\$1,199	A-131
E0.7512XT3WAX90LF3-W	\$1,355	A-132;A-258
E0.7518EP3WAX80F3-W2	\$507	A-253
E0.7518ET3WAX80F3-W2	\$670	A-253
E0.7518XP3WAX90SF3-W	\$1,283	A-131
E0.7518XT3WAX80F3-W2	\$1,450	A-132;A-258
E0.7536EP3WAX80F3-W2	\$499	A-253
E0.7536ET3WAX80F3-W2	\$659	A-253
E0.7536XP3WAX90SF3-W	\$1,267	A-131
E0.7536XT3WAX80F3-W2	\$1,432	A-132;A-258
E00112EP3WAX90LF3-W2	\$700	A-253
E00112ET3WAX100LF3-W	\$924	A-253
E00112XP3WAX90LF3-W	\$1,588	A-131
E00112XT3WAX100LF3-W	\$1,794	A-132;A-258
E00118EP3WAX90SF3-W2	\$578	A-253
E00118ET3WAX90SF3-W2	\$763	A-253
E00118XP3WAX90LF3-W	\$1,334	A-131
E00118XT3WAX90LF3-W	\$1,507	A-132;A-258
E00136EP3WAX80F3-W22	\$538	A-253
E00136ET3WAX80F3-W22	\$711	A-253
E00136XP3WAX90SF3-W	\$1,318	A-131
E00136XT3WAX80F3-W2	\$1,489	A-132;A-258
E00152EP3WAX100LF3-W	\$872	A-253
E00152ET3WAX100LF3-W	\$1,152	A-253
E00152XP3WAX100LF3-W	\$1,757	A-131
E00152XT3WAX100LF3-W	\$1,985	A-132;A-258
E00156EP3WAX90SF3-W2	\$614	A-253
E00156ET3WAX90SF3-W2	\$811	A-253
E00156XP3WAX90SF3-W	\$1,371	A-131
E00156XT3WAX90SF3-W	\$1,549	A-132;A-258



Part Number	List Price	Pages
E00158EP3WAX90LF3-W2	\$673	A-253
E00158ET3WAX90LF3-W2	\$889	A-253
E00158XP3WAX100LF3-W	\$1,488	A-131
E00158XT3WAX90LF3-W	\$1,681	A-132;A-258
E00212EP3YAX112MF3-W	\$1,181	A-253
E00212ET3YAX112MF3-W	\$1,561	A-253
E00212XP3YAX112MF3-W	\$2,040	A-131
E00212XT3YAX112MF3-W	\$2,305	A-132;A-258
E00218EP3WAX100LF3-W	\$845	A-253
E00218ET3WAX100LF3-W	\$1,116	A-253
E00218XP3WAX100LF3-W	\$1,783	A-131
E00218XT3WAX100LF3-W	\$2,015	A-132;A-258
E00236EP3WAX90LF3-W2	\$700	A-253
E00236ET3WAX90LF3-W2	\$924	A-253
E00236XP3WAX90LF3-W	\$1,534	A-131
E00236XT3WAX90LF3-W	\$1,733	A-132;A-258
E00312EP3YAX132SF3-W	\$1,684	A-253
E00312ET3YAX132SF3-W	\$2,225	A-253
E00312XP3YAX132SF3-W	\$3,224	A-131
E00312XT3YAX132SF3-W	\$3,643	A-132;A-258
E00318EP3WAX100LF3-W	\$1,016	A-253
E00318ET3WAX100LF3W	\$1,342	A-253
E00318XP3YAX112MF3-W	\$2,137	A-131
E00318XT3WAX100LF3-W	\$2,415	A-132;A-258
E00336EP3WAX100LF3-W	\$916	A-253
E00336ET3WAX100LF3-W	\$1,210	A-253
E00336XP3WAX100LF3-W	\$1,918	A-131
E00336XT3WAX100LF3-W	\$2,167	A-132;A-258
E00412EP3YAX132MF3-W	\$1,910	A-253
E00412ET3YAX132MF3-W	\$2,524	A-253
E00412XP3YAX132MF3-W	\$3,607	A-131
E00412XT3YAX132MF3-W	\$4,076	A-132;A-258
E00418EP3YAX112MF3-W	\$1,388	A-253
E00418ET3YAX112MF3-W	\$1,712	A-253
E00418XP3YAX112MF3-W	\$2,468	A-131
E00418XT3YAX112MF3-W	\$2,789	A-132;A-258
E00436EP3YAX112MF3-W	\$1,174	A-253
E00436ET3YAX112MF3-W	\$1,552	A-253
E00436XP3YAX112MF3-W	\$2,414	A-131
E00436XT3YAX112MF3-W	\$2,728	A-132;A-258
E00512EP3YAX132MF3-W	\$2,312	A-254
E00512ET3YAX132MLF3W	\$3,052	A-254
E00512XP3YAX132MF3-W	\$3,800	A-131
E00512XT3YAX132MF3-W	\$4,294	A-132;A-258
E00518EP3YAX132SF3-W	\$1,798	A-254
E00518ET3YAX132SF3-W	\$2,218	A-254
E00518XP3YAX132SF3-W	\$3,025	A-131
E00518XT3YAX132SF3-W	\$3,418	A-132;A-258
E00536EP3YAX132SF3-W	\$1,613	A-254
E00536ET3YAX132SF3-W	\$2,132	A-254
E00536XP3YAX132SF3-W	\$3,083	A-131

Part Number	List Price	Pages
E00536XT3YAX132SF3-W	\$3,484	A-132;A-258
E00712EP3YAX160MF3-W	\$3,221	A-254
E00712ET3YAX160MF3-W	\$4,256	A-254
E00712XP3YAX160MF3-W	\$5,017	A-131
E00712XT3YAX160MF3-W	\$5,669	A-132;A-258
E00718EP3YAX132MF3-W	\$2,135	A-254
E00718ET3YAX132MF3-W	\$2,634	A-254
E00718XP3YAX132MF3-W	\$3,685	A-131
E00718XT3YAX132MF3-W	\$4,164	A-132;A-258
E00736EP3YAX132SF3-W	\$1,833	A-254
E00736ET3YAX132SF3-W	\$2,422	A-254
E00736XP3YAX132SF3-W	\$3,556	A-131
E00736XT3YAX132SF3-W	\$4,018	A-132;A-258
E01112EP3YAX160LF3-W	\$4,243	A-254
E01112ET3YAX160LF3-W	\$5,607	A-254
E01112XT3YAX160LF3-W	\$5,968	A-132;A-258
E01118EP3YAX160MF3-W	\$3,331	A-254
E01118ET3YAX160MF3-W	\$4,108	A-254
E01118XT3YAX160MF3-W	\$4,691	A-132;A-258
E01136EP3YAX160MF3-W	\$3,150	A-254
E01136ET3YAX160MF3-W	\$4,163	A-254
E01136XT3YAX160MF3-W	\$4,687	A-132;A-258
E01512EP3YAX180LF3-W	\$5,388	A-254
E01512ET3YAX180LF3-W	\$7,119	A-254
E01512XT3YAX180LF3-W	\$7,273	A-132;A-258
E01518EP3YAX160LF3-W	\$3,622	A-254
E01518ET3YAX160LF3-W	\$4,696	A-254
E01518XT3YAX160LF3-W	\$5,207	A-132;A-258
E01536EP3YAX160MF3-W	\$3,398	A-254
E01536ET3YAX160MF3-W	\$4,490	A-254
E01536XT3YAX160MF3-W	\$5,564	A-132;A-258
E01812EP3YAX200LF3-W	\$7,499	A-254
E01812ET3YAX200LF3-W	\$9,910	A-254
E01812XT3YAX200LF3-W	\$9,468	A-132;A-258
E01818EP3YAX180MF3-W	\$5,439	A-254
E01818ET3YAX180MF3-W	\$6,708	A-254
E01818XT3YAX180MF3-W	\$6,847	A-132;A-258
E01836EP3YAX160LF3-W	\$3,960	A-254
E01836ET3YAX160LF3-W	\$5,233	A-254
E01836XT3YAX160LF3-W	\$6,684	A-132;A-258
E02212EP3YAX200LF3-W	\$7,956	A-254
E02212ET3YAX200LF3-W	\$10,539	A-254
E02212XT3YAX200LF3-W	\$10,720	A-132;A-258
E02218EP3YAX180LF3-W	\$5,934	A-254
E02218ET3YAX180LF3-W	\$7,319	A-254
E02218XT3YAX180LF3-W	\$7,578	A-132;A-258
E02236EP3YAX180MF3-W	\$5,140	A-254
E02236ET3YAX180MF3-W	\$6,792	A-254
E02236XT3YAX180MF3-W	\$8,022	A-132;A-258
E03012EP3YAX225SMF3W	\$12,034	A-254
E03012ET3YAX225SMF3W	\$15,902	A-254

Part Number	List Price	Pages
E03012XT3YAX225SMF3W	\$14,618	A-132;A-258
E03018EP3YAX200LF3-W	\$7,716	A-254
E03018ET3YAX200LF3-W	\$10,004	A-254
E03018XT3YAX200LF3-W	\$9,850	A-132;A-258
E03036EP3YAX200LF3-W	\$7,515	A-254
E03036ET3YAX200LF3-W	\$9,931	A-254
E03036XT3YAX200LF3-W	\$9,971	A-132;A-258
E03712EP3YAX250SMF3W	\$13,422	A-254
E03712ET3YAX250SMF3W	\$17,736	A-254
E03712XT3YAX250SMF3W	\$17,149	A-132;A-258
E03718EP3YAX225SMF3W	\$10,284	A-254
E03718ET3YAX225SMF3W	\$13,553	A-254
E03718XT3YAX225SMF3W	\$12,542	A-132;A-258
E03736EP3YAX200LF3-W	\$7,987	A-254
E03736ET3YAX200LF3-W	\$10,554	A-254
E03736XT3YAX200LF3-W	\$12,218	A-132;A-258
E04512EP3YAX280SMF3W	\$20,481	A-255
E04512ET3YAX280SMF3W	\$27,064	A-255
E04512XT3YAX280SMF3W	\$24,345	A-132;A-258
E04518EP3YAX225SMF3W	\$11,696	A-255
E04518ET3YAX225SMF3W	\$15,411	A-255
E04518XT3YAX225SMF3W	\$14,516	A-132;A-258
E04536EP3YAX225SMF3W	\$12,588	A-255
E04536ET3YAX225SMF3W	\$16,634	A-255
E04536XT3YAX225SMF3W	\$19,498	A-132;A-258
E05512EP3YAX280SMF3W	\$20,781	A-255
E05512ET3YAX280SMF3W	\$27,355	A-255
E05512XT3YAX280SMF3W	\$30,872	A-133;A-259
E05518EP3YAX250SMF3W	\$14,354	A-255
E05518ET3YAX250SMF3W	\$18,916	A-255
E05518XT3YAX250SMF3W	\$21,508	A-133;A-259
E05536EP3YAX250SMF3W	\$14,893	A-255
E05536ET3YAX250SMF3W	\$19,680	A-255
E05536XT3YAX250SMF3W	\$24,417	A-133;A-259
E07512EP3YAX315SMF3W	\$23,092	A-255
E07512ET3YAX315SMF3W	\$30,515	A-255
E07512XT3YAX315SMF3W	\$35,180	A-133;A-259
E07518EP3YAX280SMF3W	\$20,544	A-255
E07518ET3YAX280SMF3W	\$27,072	A-255
E07518XT3YAX280SMF3W	\$27,104	A-133;A-259
E07536EP3YAX280SMF3W	\$20,430	A-255
E07536ET3YAX280SMF3W	\$26,996	A-255
E07536XT3YAX280SMF3W	\$34,180	A-133;A-259
E09012EP3YAX315SMF3W	\$27,076	A-255
E09012ET3YAX315SMF3W	\$35,779	A-255
E09012XT3YAX315SMF3W	\$45,340	A-133;A-259
E09018EP3YAX280SMF3W	\$21,307	A-255
E09018ET3YAX280SMF3W	\$28,077	A-255
E09018XT3YAX280SMF3W	\$37,526	A-133;A-259
E09036EP3YAX280SMF3W	\$21,712	A-255
E09036ET3YAX280SMF3W	\$28,691	A-255

Part Number	List Price	Pages
E09036XT3YAX280SMF3W	\$40,751	A-133;A-259
E11012EP3YAX315SMF3W	\$34,367	A-255
E11012ET3YAX315SMF3W	\$45,413	A-255
E11012XT3YAX315SMF3W	\$54,984	A-133;A-259
E11018EP3YAX315SMF3W	\$27,068	A-255
E11018ET3YAX315SMF3W	\$35,670	A-255
E11018XT3YAX315SMF3W	\$42,766	A-133;A-259
E11036EP3YAX315SMF3W	\$26,144	A-255
E11036ET3YAX315SMF3W	\$34,547	A-255
E11036XT3YAX315SMF3W	\$48,322	A-133;A-259
E13212EP3YAX315SMF3W	\$52,853	A-255
E13212ET3YAX315SMF3W	\$76,749	A-255
E13212XT3YAX315SMF3W	\$93,051	A-133;A-259
E13218EP3YAX315SMF3W	\$31,689	A-255
E13218ET3YAX315SMF3W	\$42,877	A-255
E13218XT3YAX315SMF3W	\$51,911	A-133;A-259
E13236EP3YAX315SMF3W	\$29,862	A-255
E13236ET3YAX315SMF3W	\$39,500	A-255
E13236XT3YAX315SMF3W	\$61,092	A-133;A-259
E15012EP3YAX355MLF3W	\$62,660	A-255
E15012ET3YAX315LF3W2	\$82,712	A-255
E15018EP3YAX315SMF3W	\$33,286	A-255
E15018ET3YAX315SMF3W	\$43,938	A-255
E15036EP3YAX315SMF3W	\$31,360	A-255
E15036ET3YAX315SMF3W	\$41,396	A-255
E16012EP3YAX315LF3-W	\$60,176	A-256
E16012EP3YAX355MLF3W	\$65,792	A-256
E16012ET3YAX315LF3-W	\$79,990	A-256
E16012ET3YAX355MLF3W	\$86,940	A-256
E16012XT3YAX315LF3-W	\$101,880	A-133;A-259
E16018EP3YAX315SMF3W	\$36,046	A-256
E16018ET3YAX315SMF3W	\$47,534	A-256
E16018XT3YAX315SMF3W	\$56,646	A-133;A-259
E16036EP3YAX315SMF3W	\$38,870	A-256
E16036ET3YAX315SMF3W	\$51,363	A-256
E16036XT3YAX315SMF3W	\$76,056	A-133;A-259
E20012EP3YAX315LF3-W	\$66,948	A-256
E20012EP3YAX355MLF3W	\$74,007	A-256
E20012ET3YAX355MLF3W	\$97,795	A-256
E20012XT3YAX355MLF3W	\$124,447	A-133;A-259
E20018EP3YAX355MLF3W	\$64,081	A-256
E20018ET3YAX315LF3-W	\$70,770	A-256
E20018ET3YAX355MLF3W	\$76,925	A-256
E20018XT3YAX315LF3-W	\$91,423	A-133;A-259
E20036EP3YAX355MLF3W	\$66,531	A-256
E20036XT3YAX315LF3-W	\$114,087	A-133;A-259
E25012EP3YAX355MLF3W	\$88,256	A-256
E25012ET3YAX355MLF3W	\$111,338	A-256
E25012XT3YAX355MLF3W	\$150,638	A-133;A-259
E25018EP3YAX315LF3-W	\$62,457	A-256
E25018EP3YAX355MLF3W	\$67,456	A-256

Part Number	List Price	Pages
E25018ET3YAX315LF3-W	\$76,550	A-256
E25018ET3YAX355MLF3W	\$83,195	A-256
E25018XT3YAX315LF3-W	\$107,240	A-133;A-259
E25036EP3YAX315LF3-W	\$73,948	A-256
E25036EP3YAX355MLF3W	\$82,191	A-256
E25036XT3YAX315LF3-W	\$125,854	A-133;A-259
E31518XT3YAX355MLF3W	\$122,650	A-133;A-259
E-35	\$350	A-302
ECHS35M-A	\$2,150	A-425
ECHS35RTEBC-D	\$1,845	A-425
ECHSD38-D	\$1,418	A-425
EDP11S003GN12	\$6,510	A-350
EDP11S003GN1201000	\$7,273	A-352
EDP11S003GN1210000	\$8,020	A-351
EDP11S003GN1211000	\$8,783	A-353
EDP11S003GN3R	\$8,341	A-354
EDP11S003GN3R01000	\$9,104	A-356
EDP11S003GN3R10000	\$9,851	A-355
EDP11S003GN3R11000	\$10,614	A-357
EDP11S005GN12	\$6,626	A-350
EDP11S005GN1201000	\$7,389	A-352
EDP11S005GN1210000	\$8,136	A-351
EDP11S005GN1211000	\$8,899	A-353
EDP11S005GN3R	\$8,457	A-354
EDP11S005GN3R01000	\$9,220	A-356
EDP11S005GN3R10000	\$9,967	A-355
EDP11S005GN3R11000	\$10,730	A-357
EDP11S007DN12	\$6,690	A-350
EDP11S007DN1201000	\$7,453	A-352
EDP11S007DN1210000	\$8,200	A-351
EDP11S007DN1211000	\$8,963	A-353
EDP11S007DN3R	\$8,521	A-354
EDP11S007DN3R01000	\$9,284	A-356
EDP11S007DN3R10000	\$10,031	A-355
EDP11S007DN3R11000	\$10,794	A-357
EDP11S007GN12	\$6,690	A-350
EDP11S007GN1201000	\$7,453	A-352
EDP11S007GN1210000	\$8,200	A-351
EDP11S007GN1211000	\$8,963	A-353
EDP11S007GN3R	\$8,521	A-354
EDP11S007GN3R01000	\$9,284	A-356
EDP11S007GN3R10000	\$10,031	A-355
EDP11S007GN3R11000	\$10,794	A-357
EDP11S010DN12	\$6,756	A-350
EDP11S010DN1201000	\$7,519	A-352
EDP11S010DN1210000	\$8,276	A-351
EDP11S010DN1211000	\$9,039	A-353
EDP11S010DN3R	\$8,587	A-354
EDP11S010DN3R01000	\$9,350	A-356
EDP11S010DN3R10000	\$10,107	A-355
EDP11S010DN3R11000	\$10,870	A-357

Part Number	List Price	Pages
EDP11S010GN12	\$6,756	A-350
EDP11S010GN1201000	\$7,519	A-352
EDP11S010GN1210000	\$8,276	A-351
EDP11S010GN1211000	\$9,039	A-353
EDP11S010GN3R	\$8,587	A-354
EDP11S010GN3R01000	\$9,350	A-356
EDP11S010GN3R10000	\$10,107	A-355
EDP11S010GN3R11000	\$10,870	A-357
EDP11S013DN12	\$6,855	A-350
EDP11S013DN1201000	\$7,618	A-352
EDP11S013DN1210000	\$8,375	A-351
EDP11S013DN1211000	\$9,138	A-353
EDP11S013DN3R	\$8,686	A-354
EDP11S013DN3R01000	\$9,449	A-356
EDP11S013DN3R10000	\$10,206	A-355
EDP11S013DN3R11000	\$10,969	A-357
EDP11S013GN12	\$6,855	A-350
EDP11S013GN1201000	\$7,618	A-352
EDP11S013GN1210000	\$8,375	A-351
EDP11S013GN1211000	\$9,138	A-353
EDP11S013GN3R	\$8,686	A-354
EDP11S013GN3R01000	\$9,449	A-356
EDP11S013GN3R10000	\$10,206	A-355
EDP11S013GN3R11000	\$10,969	A-357
EDP11S016DN12	\$7,123	A-350
EDP11S016DN1201000	\$7,886	A-352
EDP11S016DN1210000	\$8,643	A-351
EDP11S016DN1211000	\$9,406	A-353
EDP11S016DN3R	\$8,918	A-354
EDP11S016DN3R01000	\$9,681	A-356
EDP11S016DN3R10000	\$10,438	A-355
EDP11S016DN3R11000	\$11,201	A-357
EDP11S017GN12	\$7,269	A-350
EDP11S017GN1201000	\$8,032	A-352
EDP11S017GN1210000	\$8,867	A-351
EDP11S017GN1211000	\$9,630	A-353
EDP11S017GN3R	\$9,100	A-354
EDP11S017GN3R01000	\$9,863	A-356
EDP11S017GN3R10000	\$10,698	A-355
EDP11S017GN3R11000	\$11,461	A-357
EDP11S024DN12	\$7,664	A-350
EDP11S024DN1201000	\$8,427	A-352
EDP11S024DN1210000	\$9,262	A-351
EDP11S024DN1211000	\$10,025	A-353
EDP11S024DN3R	\$9,459	A-354
EDP11S024DN3R01000	\$10,222	A-356
EDP11S024DN3R10000	\$11,057	A-355
EDP11S024DN3R11000	\$11,820	A-357
EDP11S024GN12	\$7,821	A-350
EDP11S024GN1201000	\$8,584	A-352
EDP11S024GN1210000	\$9,613	A-351

Part Number	List Price	Pages
EDP11S024GN1211000	\$10,376	A-353
EDP11S024GN3R	\$9,652	A-354
EDP11S024GN3R01000	\$10,415	A-356
EDP11S024GN3R10000	\$11,444	A-355
EDP11S024GN3R11000	\$12,207	A-357
EDP11S028DN12	\$8,408	A-350
EDP11S028DN1201000	\$9,171	A-352
EDP11S028DN1210000	\$10,200	A-351
EDP11S028DN1211000	\$10,963	A-353
EDP11S028DN3R	\$10,202	A-354
EDP11S028DN3R01000	\$10,965	A-356
EDP11S028DN3R10000	\$11,994	A-355
EDP11S028DN3R11000	\$12,757	A-357
EDP11S031GN12	\$8,580	A-350
EDP11S031GN1201000	\$9,343	A-352
EDP11S031GN1210000	\$10,483	A-351
EDP11S031GN1211000	\$11,246	A-353
EDP11S031GN3R	\$10,411	A-354
EDP11S031GN3R01000	\$11,174	A-356
EDP11S031GN3R10000	\$12,314	A-355
EDP11S031GN3R11000	\$13,077	A-357
EDP11S033DN12	\$9,108	A-350
EDP11S033DN1201000	\$9,871	A-352
EDP11S033DN1210000	\$11,011	A-351
EDP11S033DN1211000	\$11,774	A-353
EDP11S033DN3R	\$10,902	A-354
EDP11S033DN3R01000	\$11,665	A-356
EDP11S033DN3R10000	\$12,805	A-355
EDP11S033DN3R11000	\$13,568	A-357
EDP11S038GN12	\$9,293	A-350
EDP11S038GN1201000	\$10,056	A-352
EDP11S038GN1210000	\$11,395	A-351
EDP11S038GN1211000	\$12,158	A-353
EDP11S038GN3R	\$11,125	A-354
EDP11S038GN3R01000	\$11,888	A-356
EDP11S038GN3R10000	\$13,227	A-355
EDP11S038GN3R11000	\$13,873	A-357
EDP11S045DN12	\$10,214	A-350
EDP11S045DN1201000	\$10,977	A-352
EDP11S045DN1210000	\$12,316	A-351
EDP11S045DN1211000	\$13,079	A-353
EDP11S045DN3R	\$12,122	A-354
EDP11S045DN3R01000	\$12,885	A-356
EDP11S045DN3R10000	\$14,224	A-355
EDP11S045DN3R11000	\$14,987	A-357
EDP11S045GN12	\$10,422	A-350
EDP11S045GN1201000	\$11,185	A-352
EDP11S045GN1210000	\$12,669	A-351
EDP11S045GN1211000	\$13,432	A-353
EDP11S045GN3R	\$12,369	A-354
EDP11S045GN3R01000	\$13,132	A-356

Part Number	List Price	Pages
EDP11S045GN3R10000	\$14,616	A-355
EDP11S045GN3R11000	\$15,233	A-357
EDP11S054DN12	\$11,491	A-350
EDP11S054DN1201000	\$12,254	A-352
EDP11S054DN1210000	\$13,738	A-351
EDP11S054DN1211000	\$14,501	A-353
EDP11S054DN3R	\$13,400	A-354
EDP11S054DN3R01000	\$14,163	A-356
EDP11S054DN3R10000	\$15,647	A-355
EDP11S054DN3R11000	\$16,410	A-357
EDP11S058GN12	\$12,026	A-350
EDP11S058GN1201000	\$12,789	A-352
EDP11S058GN1210000	\$14,721	A-351
EDP11S058GN1211000	\$15,484	A-353
EDP11S058GN3R	\$13,673	A-354
EDP11S058GN3R01000	\$14,436	A-356
EDP11S058GN3R10000	\$16,368	A-355
EDP11S058GN3R11000	\$16,683	A-357
EDP11S070DN12	\$12,162	A-350
EDP11S070DN1201000	\$12,925	A-352
EDP11S070DN1210000	\$14,857	A-351
EDP11S070DN1211000	\$15,620	A-353
EDP11S070DN3R	\$14,162	A-354
EDP11S070DN3R01000	\$14,925	A-356
EDP11S070DN3R10000	\$16,857	A-355
EDP11S070DN3R11000	\$17,620	A-357
EDP11S070GN12	\$12,729	A-350
EDP11S070GN1201000	\$13,492	A-352
EDP11S070GN1210000	\$15,424	A-351
EDP11S070GN1211000	\$16,187	A-353
EDP11S070GN3R	\$14,451	A-354
EDP11S070GN3R01000	\$15,214	A-356
EDP11S070GN3R10000	\$17,146	A-355
EDP11S070GN3R11000	\$17,909	A-357
EDP11S086DN12	\$14,321	A-350
EDP11S086DN1201000	\$15,084	A-352
EDP11S086DN1210000	\$17,016	A-351
EDP11S086DN1211000	\$17,779	A-353
EDP11S086DN3R	\$16,320	A-354
EDP11S086DN3R01000	\$17,083	A-356
EDP11S086DN3R10000	\$19,015	A-355
EDP11S086DN3R11000	\$19,778	A-357
EDP11S088GN12	\$14,988	A-350
EDP11S088GN1201000	\$15,751	A-352
EDP11S088GN1210000	\$17,876	A-351
EDP11S088GN1211000	\$18,639	A-353
EDP11S088GN3R	\$16,653	A-354
EDP11S088GN3R01000	\$17,416	A-356
EDP11S088GN3R10000	\$19,541	A-355
EDP11S088GN3R11000	\$20,304	A-357
EDP11S105DN12	\$17,164	A-350

Part Number	List Price	Pages
EDP11S105DN1201000	\$17,927	A-352
EDP11S105DN1210000	\$20,052	A-351
EDP11S105DN1211000	\$20,815	A-353
EDP11S105DN3R	\$19,338	A-354
EDP11S105DN3R01000	\$20,101	A-356
EDP11S105DN3R10000	\$22,226	A-355
EDP11S105DN3R11000	\$22,989	A-357
EDP11S105GN12	\$17,964	A-350
EDP11S105GN1201000	\$18,727	A-352
EDP11S105GN1210000	\$21,308	A-351
EDP11S105GN1211000	\$22,071	A-353
EDP11S105GN3R	\$19,733	A-354
EDP11S105GN3R01000	\$20,496	A-356
EDP11S105GN3R10000	\$23,077	A-355
EDP11S105GN3R11000	\$23,840	A-357
EDP11S142DN12	\$19,793	A-350
EDP11S142DN1201000	\$20,556	A-352
EDP11S142DN1210000	\$24,778	A-351
EDP11S142DN1211000	\$25,541	A-353
EDP11S142DN3R	\$21,967	A-354
EDP11S142DN3R01000	\$22,730	A-356
EDP11S142DN3R10000	\$26,952	A-355
EDP11S142DN3R11000	\$27,715	A-357
EDP11S142GN12	\$20,715	A-350
EDP11S142GN1201000	\$21,478	A-352
EDP11S142GN1210000	\$25,700	A-351
EDP11S142GN1211000	\$26,463	A-353
EDP11S142GN3R	\$22,415	A-354
EDP11S142GN3R01000	\$23,178	A-356
EDP11S142GN3R10000	\$27,400	A-355
EDP11S142GN3R11000	\$28,163	A-357
EDP11S180DN12	\$25,116	A-350
EDP11S180DN1201000	\$25,879	A-352
EDP11S180DN1210000	\$31,111	A-351
EDP11S180DN1211000	\$31,874	A-353
EDP11S180DN3R	\$27,290	A-354
EDP11S180DN3R01000	\$28,053	A-356
EDP11S180DN3R10000	\$33,285	A-355
EDP11S180DN3R11000	\$34,048	A-357
EDP11S180GN12	\$26,286	A-350
EDP11S180GN1201000	\$27,049	A-352
EDP11S180GN1210000	\$32,281	A-351
EDP11S180GN1211000	\$33,044	A-353
EDP11S180GN3R	\$27,847	A-354
EDP11S180GN3R01000	\$28,610	A-356
EDP11S180GN3R10000	\$33,842	A-355
EDP11S180GN3R11000	\$34,605	A-357
EDP11S211DN12	\$28,326	A-350
EDP11S211DN1201000	\$29,089	A-352
EDP11S211DN1210000	\$35,651	A-351

Part Number	List Price	Pages
EDP11S211DN1211000	\$36,414	A-353
EDP11S211DN3R	\$30,499	A-354
EDP11S211DN3R01000	\$31,262	A-356
EDP11S211DN3R10000	\$37,824	A-355
EDP11S211DN3R11000	\$38,587	A-357
EDP11S211GN12	\$29,645	A-350
EDP11S211GN1201000	\$30,408	A-352
EDP11S211GN1210000	\$36,970	A-351
EDP11S211GN1211000	\$37,733	A-353
EDP11S211GN3R	\$31,122	A-354
EDP11S211GN3R01000	\$31,885	A-356
EDP11S211GN3R10000	\$38,447	A-355
EDP11S211GN3R11000	\$39,210	A-357
EDP11S242GN12	\$40,755	A-350
EDP11S242GN1201000	\$41,613	A-352
EDP11S242GN1210000	\$53,334	A-351
EDP11S242GN1211000	\$54,097	A-353
EDP11S242GN3R	\$45,693	A-354
EDP11S242GN3R01000	\$46,456	A-356
EDP11S242GN3R10000	\$58,272	A-355
EDP11S242GN3R11000	\$59,035	A-357
EDP11S312GN12	\$45,114	A-350
EDP11S312GN1201000	\$45,972	A-352
EDP11S312GN1210000	\$59,257	A-351
EDP11S312GN1211000	\$60,115	A-353
EDP11S312GN3R	\$50,053	A-354
EDP11S312GN3R01000	\$50,911	A-356
EDP11S312GN3R10000	\$64,196	A-355
EDP11S312GN3R11000	\$65,054	A-357
EDP11S370GN12	\$47,743	A-350
EDP11S370GN1201000	\$48,601	A-352
EDP11S370GN1210000	\$62,146	A-351
EDP11S370GN1211000	\$63,004	A-353
EDP11S370GN3R	\$52,682	A-354
EDP11S370GN3R01000	\$53,540	A-356
EDP11S370GN3R10000	\$67,085	A-355
EDP11S370GN3R11000	\$67,943	A-357
EDP11S477GN12	\$54,585	A-350
EDP11S477GN1201000	\$55,443	A-352
EDP11S477GN1210000	\$76,618	A-351
EDP11S477GN1211000	\$77,476	A-353
EDP11S477GN3R	\$59,523	A-354
EDP11S477GN3R01000	\$60,381	A-356
EDP11S477GN3R10000	\$81,556	A-355
EDP11S477GN3R11000	\$82,414	A-357
EDP11S515GN12	\$66,023	A-350
EDP11S515GN1201000	\$66,881	A-352
EDP11S515GN1210000	\$88,056	A-351
EDP11S515GN1211000	\$88,914	A-353
EDP11S515GN3R	\$71,976	A-354

Part Number	List Price	Pages
EDP11S515GN3R01000	\$72,834	A-356
EDP11S515GN3R10000	\$94,009	A-355
EDP11S515GN3R11000	\$94,867	A-357
EDP11S601GN12	\$71,875	A-350
EDP11S601GN1201000	\$72,733	A-352
EDP11S601GN1210000	\$99,447	A-351
EDP11S601GN1211000	\$100,305	A-353
EDP11S601GN3R	\$77,828	A-354
EDP11S601GN3R01000	\$78,686	A-356
EDP11S601GN3R10000	\$105,400	A-355
EDP11S601GN3R11000	\$106,258	A-357
EDP11S720GN12	\$88,556	A-350
EDP11S720GN1201000	\$89,414	A-352
EDP11S720GN1210000	\$119,944	A-351
EDP11S720GN1211000	\$120,802	A-353
EDP11S720GN3R	\$94,509	A-354
EDP11S720GN3R01000	\$95,367	A-356
EDP11S720GN3R10000	\$125,897	A-355
EDP11S720GN3R11000	\$126,755	A-357
ENCCBLMS-10	\$232	A-426
ENCCBLMS-20	\$413	A-426
ENCCBLMS-30	\$454	A-426
ENCCBLMS-50	\$672	A-426
ESW-105V18A-R44	\$1,028	A-372
ESW-105V18A-R45	\$1,028	A-372
ESW-105V18E-R44	\$975	A-372
ESW-105V18E-R45	\$975	A-372
ESW-105V24A-R44	\$1,028	A-372
ESW-105V24A-R45	\$1,028	A-372
ESW-105V24E-R44	\$975	A-372
ESW-105V24E-R45	\$975	A-372
ESW-105V47A-R44	\$1,028	A-372
ESW-105V47A-R45	\$1,028	A-372
ESW-105V47E-R44	\$975	A-372
ESW-105V47E-R45	\$975	A-372
ESW-40V18A-R35	\$345	A-372
ESW-40V18E-R35	\$292	A-372
ESW-40V24A-R35	\$345	A-372
ESW-40V24E-R35	\$292	A-372
ESW-40V47A-R35	\$345	A-372
ESW-40V47E-R35	\$292	A-372
ESW-50V18A-R38	\$403	A-372
ESW-50V18E-R38	\$350	A-372
ESW-50V24A-R38	\$403	A-372
ESW-50V24E-R38	\$350	A-372
ESW-50V47A-R38	\$403	A-372
ESW-50V47E-R38	\$350	A-372
ESW-65V18A-R39	\$428	A-372
ESW-65V18E-R39	\$375	A-372
ESW-65V24A-R39	\$428	A-372
ESW-65V24E-R39	\$375	A-372

Part Number	List Price	Pages
ESW-65V47A-R39	\$428	A-372
ESW-65V47E-R39	\$375	A-372
ESW-80V18A-R41	\$474	A-372
ESW-80V18E-R41	\$421	A-372
ESW-80V24A-R41	\$474	A-372
ESW-80V24E-R41	\$421	A-372
ESW-80V47A-R41	\$474	A-372
ESW-80V47E-R41	\$421	A-372
ESW-95V18A-R43	\$929	A-372
ESW-95V18E-R43	\$876	A-372
ESW-95V24A-R43	\$929	A-372
ESW-95V24E-R43	\$876	A-372
ESW-95V47A-R43	\$929	A-372
ESW-95V47E-R43	\$876	A-372
ESW-B12D15A-R30	\$227	A-372
ESW-B12D15E-R30	\$174	A-372
ESW-B12D39A-R30	\$227	A-372
ESW-B12D39E-R30	\$174	A-372
ESW-B12V24A-R30	\$227	A-372
ESW-B12V24E-R30	\$174	A-372
ESW-B18D15A-R32	\$241	A-372
ESW-B18D15E-R32	\$188	A-372
ESW-B18D39A-R32	\$241	A-372
ESW-B18D39E-R32	\$188	A-372
ESW-B18V24A-R32	\$241	A-372
ESW-B18V24E-R32	\$188	A-372
ESW-B25D15A-R33	\$276	A-372
ESW-B25D15E-R33	\$223	A-372
ESW-B25D39A-R33	\$276	A-372
ESW-B25D39E-R33	\$223	A-372
ESW-B25V24A-R33	\$276	A-372
ESW-B25V24E-R33	\$223	A-372
ESW-B32D15A-R34	\$298	A-372
ESW-B32D15E-R34	\$245	A-372
ESW-B32D39A-R34	\$298	A-372
ESW-B32D39E-R34	\$245	A-372
ESW-B32V24A-R34	\$298	A-372
ESW-B32V24E-R34	\$245	A-372
ESW-B38D15A-R35	\$345	A-372
ESW-B38D15E-R35	\$292	A-372
ESW-B38D39A-R35	\$345	A-372
ESW-B38D39E-R35	\$292	A-372
ESW-B38V24A-R35	\$345	A-372
ESW-B38V24E-R35	\$292	A-372
ESW-B9D15A-R23	\$210	A-372
ESW-B9D15A-R24	\$210	A-372
ESW-B9D15A-R25	\$210	A-372
ESW-B9D15A-R26	\$210	A-372
ESW-B9D15A-R27	\$210	A-372
ESW-B9D15A-R28	\$210	A-372
ESW-B9D15A-R29	\$210	A-372

Part Number	List Price	Pages
ESW-B9D15E-R23	\$157	A-372
ESW-B9D15E-R24	\$157	A-372
ESW-B9D15E-R25	\$157	A-372
ESW-B9D15E-R26	\$157	A-372
ESW-B9D15E-R27	\$157	A-372
ESW-B9D15E-R28	\$157	A-372
ESW-B9D15E-R29	\$157	A-372
ESW-B9D39A-R23	\$210	A-372
ESW-B9D39A-R24	\$210	A-372
ESW-B9D39A-R25	\$210	A-372
ESW-B9D39A-R26	\$210	A-372
ESW-B9D39A-R27	\$210	A-372
ESW-B9D39A-R28	\$210	A-372
ESW-B9D39A-R29	\$210	A-372
ESW-B9D39E-R23	\$157	A-372
ESW-B9D39E-R24	\$157	A-372
ESW-B9D39E-R25	\$157	A-372
ESW-B9D39E-R26	\$157	A-372
ESW-B9D39E-R27	\$157	A-372
ESW-B9D39E-R28	\$157	A-372
ESW-B9D39E-R29	\$157	A-372
ESW-B9V24A-R23	\$210	A-372
ESW-B9V24A-R24	\$210	A-372
ESW-B9V24A-R25	\$210	A-372
ESW-B9V24A-R26	\$210	A-372
ESW-B9V24A-R27	\$210	A-372
ESW-B9V24A-R28	\$210	A-372
ESW-B9V24A-R29	\$210	A-372
ESW-B9V24E-R23	\$157	A-372
ESW-B9V24E-R24	\$157	A-372
ESW-B9V24E-R25	\$157	A-372
ESW-B9V24E-R26	\$157	A-372
ESW-B9V24E-R27	\$157	A-372
ESW-B9V24E-R28	\$157	A-372
ESW-B9V24E-R29	\$157	A-372
ESWC-105T5A9-RE6	\$3,355	A-382
ESWC105TM1A9-RE6	\$3,355	A-382
ESWC-12T5A9-RE3	\$2,020	A-382
ESWC-12TM1A9-RE3	\$2,020	A-382
ESWC-150T5A9-RE7	\$5,400	A-382
ESWC-150T5A9-RE8	\$7,500	A-382
ESWC-150TM1A9-RE7	\$5,400	A-382
ESWC-180T5A9-RE7	\$6,440	A-382
ESWC-180TM1A9-RE7	\$6,440	A-382
ESWC-18T5A9-RE3	\$2,070	A-382
ESWC-18TM1A9-RE3	\$2,070	A-382
ESWC-25T5A9-RE4	\$2,070	A-382
ESWC-25TM1A9-RE4	\$2,070	A-382
ESWC-300TM1A9-RE8	\$7,500	A-382
ESWC-38T5A9-RE4	\$2,255	A-382

Part Number	List Price	Pages
ESWC-38TM1A9-RE4	\$2,255	A-382
ESWC-65T5A9-RE6	\$2,552	A-382
ESWC-65TM1A9-RE6	\$2,552	A-382
ESWC-9T5A9-RE2	\$2,020	A-382
ESWC-9TM1A9-RE2	\$2,020	A-382
ESWE-18T02KX-D11	\$1,155	A-385
ESWE-18T04KX-D11	\$1,155	A-385
ESWE-18T05KX-D11	\$1,155	A-385
ESWE-18V18KX-D11	\$875	A-385
ESWE-18V24KX-D11	\$875	A-385
ESWE-18V47KX-D11	\$875	A-385
ESWE-25T02KX-D12	\$1,175	A-385
ESWE-25T04KX-D12	\$1,175	A-385
ESWE-25T05KX-D12	\$1,175	A-385
ESWE-25V18KX-D12	\$900	A-385
ESWE-25V24KX-D12	\$900	A-385
ESWE-25V47KX-D12	\$900	A-385
ESWE-40T02KX-D14	\$1,260	A-385
ESWE-40T04KX-D14	\$1,260	A-385
ESWE-40T05KX-D14	\$1,260	A-385
ESWE-40V18KX-D14	\$990	A-385
ESWE-40V24KX-D14	\$990	A-385
ESWE-40V47KX-D14	\$990	A-385
ESWE-9T02KX-D06	\$1,140	A-385
ESWE-9T02KX-D07	\$1,140	A-385
ESWE-9T02KX-D08	\$1,140	A-385
ESWE-9T02KX-D09	\$1,140	A-385
ESWE-9T02KX-D10	\$1,140	A-385
ESWE-9T04KX-D05	\$1,140	A-385
ESWE-9T04KX-D06	\$1,140	A-385
ESWE-9T04KX-D07	\$1,140	A-385
ESWE-9T04KX-D08	\$1,140	A-385
ESWE-9T04KX-D09	\$1,140	A-385
ESWE-9T04KX-D10	\$1,140	A-385
ESWE-9T05KX-D05	\$1,140	A-385
ESWE-9T05KX-D06	\$1,140	A-385
ESWE-9T05KX-D07	\$1,140	A-385
ESWE-9T05KX-D08	\$1,140	A-385
ESWE-9T05KX-D09	\$1,140	A-385
ESWE-9T05KX-D10	\$1,140	A-385
ESWE-9V18KX-D05	\$855	A-385
ESWE-9V18KX-D06	\$855	A-385
ESWE-9V18KX-D07	\$855	A-385
ESWE-9V18KX-D08	\$855	A-385
ESWE-9V18KX-D09	\$855	A-385
ESWE-9V18KX-D10	\$865	A-385
ESWE-9V24KX-D06	\$855	A-385
ESWE-9V24KX-D07	\$855	A-385
ESWE-9V24KX-D08	\$855	A-385
ESWE-9V24KX-D09	\$855	A-385

Part Number	List Price	Pages
ESWE-9V24KX-D10	\$865	A-385
ESWE-9V47KX-D05	\$855	A-385
ESWE-9V47KX-D06	\$855	A-385
ESWE-9V47KX-D07	\$855	A-385
ESWE-9V47KX-D08	\$855	A-385
ESWE-9V47KX-D09	\$855	A-385
ESWE-9V47KX-D10	\$865	A-385
ESWF-105T02N4-D24	\$2,465	A-389
ESWF-105T04N4-D24	\$2,635	A-389
ESWF-105T05N4-D24	\$2,635	A-389
ESWF-105V18N4-D24	\$2,265	A-388
ESWF-105V24N4-D24	\$2,435	A-388
ESWF-105V47N4-D24	\$2,435	A-388
ESWF-18T02N4-D11	\$1,325	A-389
ESWF-18T04N4-D11	\$1,400	A-389
ESWF-18T05N4-D11	\$1,400	A-389
ESWF-18V18N4-D11	\$1,225	A-388
ESWF-18V24N4-D11	\$1,300	A-388
ESWF-18V47N4-D11	\$1,300	A-388
ESWF-25T02N4-D12	\$1,400	A-389
ESWF-25T04N4-D12	\$1,490	A-389
ESWF-25T05N4-D12	\$1,490	A-389
ESWF-25V18N4-D12	\$1,300	A-388
ESWF-25V24N4-D12	\$1,390	A-388
ESWF-25V47N4-D12	\$1,390	A-388
ESWF-40T02N4-D14	\$1,490	A-389
ESWF-40T04N4-D14	\$1,620	A-389
ESWF-40T05N4-D14	\$1,620	A-389
ESWF-40V18N4-D14	\$1,390	A-388
ESWF-40V24N4-D14	\$1,470	A-388
ESWF-40V47N4-D14	\$1,470	A-388
ESWF-50T02N4-D14	\$1,620	A-389
ESWF-50T04N4-D19	\$1,990	A-389
ESWF-50T05N4-D19	\$1,990	A-389
ESWF-50V18N4-D19	\$1,470	A-388
ESWF-50V24N4-D19	\$1,840	A-388
ESWF-50V47N4-D19	\$1,840	A-388
ESWF-65T02N4-D20	\$1,990	A-389
ESWF-65T04N4-D20	\$2,120	A-389
ESWF-65T05N4-D20	\$2,120	A-389
ESWF-65V18N4-D20	\$1,840	A-388
ESWF-65V24N4-D20	\$1,920	A-388
ESWF-65V47N4-D20	\$1,920	A-388
ESWF-80T02N4-D21	\$2,120	A-389
ESWF-80T04N4-D21	\$2,210	A-389
ESWF-80T05N4-D21	\$2,210	A-389
ESWF-80V18N4-D21	\$1,920	A-388
ESWF-80V24N4-D21	\$2,010	A-388
ESWF-80V47N4-D21	\$2,010	A-388
ESWF-95T02N4-D22	\$2,210	A-389
ESWF-95T02N4-D23	\$2,350	A-389

Part Number	List Price	Pages
ESWF-95T04N4-D22	\$2,350	A-389
ESWF-95T04N4-D23	\$2,465	A-389
ESWF-95T05N4-D22	\$2,350	A-389
ESWF-95T05N4-D23	\$2,465	A-389
ESWF-95V18N4-D22	\$2,010	A-388
ESWF-95V18N4-D23	\$2,150	A-388
ESWF-95V24N4-D22	\$2,150	A-388
ESWF-95V24N4-D23	\$2,265	A-388
ESWF-95V47N4-D22	\$2,150	A-388
ESWF-95V47N4-D23	\$2,265	A-388
ESWF-9T02N4-D06	\$1,325	A-389
ESWF-9T02N4-D07	\$1,325	A-389
ESWF-9T02N4-D08	\$1,325	A-389
ESWF-9T02N4-D09	\$1,325	A-389
ESWF-9T02N4-D10	\$1,325	A-389
ESWF-9T04N4-D06	\$1,325	A-389
ESWF-9T04N4-D07	\$1,325	A-389
ESWF-9T04N4-D08	\$1,325	A-389
ESWF-9T04N4-D09	\$1,325	A-389
ESWF-9T04N4-D10	\$1,325	A-389
ESWF-9T05N4-D05	\$1,325	A-389
ESWF-9T05N4-D06	\$1,325	A-389
ESWF-9T05N4-D07	\$1,325	A-389
ESWF-9T05N4-D08	\$1,325	A-389
ESWF-9T05N4-D09	\$1,325	A-389
ESWF-9T05N4-D10	\$1,325	A-389
ESWF-9V18N4-D06	\$1,225	A-388
ESWF-9V18N4-D07	\$1,225	A-388
ESWF-9V18N4-D08	\$1,225	A-388
ESWF-9V18N4-D09	\$1,225	A-388
ESWF-9V18N4-D10	\$1,225	A-388
ESWF-9V24N4-D06	\$1,225	A-388
ESWF-9V24N4-D07	\$1,225	A-388
ESWF-9V24N4-D08	\$1,225	A-388
ESWF-9V24N4-D09	\$1,225	A-388
ESWF-9V24N4-D10	\$1,225	A-388
ESWF-9V47N4-D05	\$1,225	A-388
ESWF-9V47N4-D06	\$1,225	A-388
ESWF-9V47N4-D07	\$1,225	A-388
ESWF-9V47N4-D08	\$1,225	A-388
ESWF-9V47N4-D09	\$1,225	A-388
ESWF-9V47N4-D10	\$1,225	A-388
ESWS-40V18A-RM35	\$351	A-373
ESWS-40V18E-RM35	\$274	A-373
ESWS-40V24A-RM35	\$351	A-373
ESWS-40V24E-RM35	\$274	A-373
ESWS-50V18A-RM38	\$423	A-373
ESWS-50V18E-RM38	\$330	A-373
ESWS-50V24A-RM38	\$423	A-373
ESWS-50V24E-RM38	\$330	A-373
ESWS-B12D15A-RM30	\$227	A-373

Part Number	List Price	Pages
ESWS-B12D15E-RM30	\$135	A-373
ESWS-B12V24A-RM30	\$227	A-373
ESWS-B12V24E-RM30	\$135	A-373
ESWS-B18D15A-RM31	\$241	A-373
ESWS-B18D15A-RM32	\$241	A-373
ESWS-B18D15E-RM31	\$161	A-373
ESWS-B18D15E-RM32	\$170	A-373
ESWS-B18V24A-RM31	\$241	A-373
ESWS-B18V24A-RM32	\$241	A-373
ESWS-B18V24E-RM31	\$161	A-373
ESWS-B18V24E-RM32	\$170	A-373
ESWS-B25D15A-RM33	\$276	A-373
ESWS-B25D15E-RM33	\$180	A-373
ESWS-B25V24A-RM33	\$276	A-373
ESWS-B25V24E-RM33	\$180	A-373
ESWS-B32D15A-RM34	\$276	A-373
ESWS-B32D15E-RM34	\$230	A-373
ESWS-B32V24A-RM34	\$276	A-373
ESWS-B32V24E-RM34	\$230	A-373
ESWS-B38D15A-RM35	\$327	A-373
ESWS-B38D15E-RM35	\$274	A-373
ESWS-B38V24A-RM35	\$327	A-373
ESWS-B38V24E-RM35	\$274	A-373
ESWS-B9D15A-RM23	\$188	A-373
ESWS-B9D15A-RM24	\$188	A-373
ESWS-B9D15A-RM25	\$188	A-373
ESWS-B9D15A-RM26	\$188	A-373
ESWS-B9D15A-RM27	\$188	A-373
ESWS-B9D15A-RM28	\$188	A-373
ESWS-B9D15A-RM29	\$188	A-373
ESWS-B9D15E-RM23	\$135	A-373
ESWS-B9D15E-RM24	\$135	A-373
ESWS-B9D15E-RM25	\$135	A-373
ESWS-B9D15E-RM26	\$135	A-373
ESWS-B9D15E-RM27	\$135	A-373
ESWS-B9D15E-RM28	\$135	A-373
ESWS-B9D15E-RM29	\$135	A-373
ESWS-B9V24A-RM23	\$188	A-373
ESWS-B9V24A-RM24	\$188	A-373
ESWS-B9V24A-RM25	\$188	A-373
ESWS-B9V24A-RM26	\$188	A-373
ESWS-B9V24A-RM27	\$188	A-373
ESWS-B9V24A-RM28	\$188	A-373
ESWS-B9V24A-RM29	\$188	A-373
ESWS-B9V24E-RM23	\$135	A-373
ESWS-B9V24E-RM24	\$135	A-373
ESWS-B9V24E-RM25	\$135	A-373
ESWS-B9V24E-RM26	\$135	A-373
ESWS-B9V24E-RM27	\$135	A-373
ESWS-B9V24E-RM28	\$135	A-373
ESWS-B9V24E-RM29	\$135	A-373

Part Number	List Price	Pages
ESWX-105V18A79-R43	\$4,600	A-395
ESWX-105V18A79-R44	\$4,600	A-395
ESWX-105V18A79-R45	\$4,600	A-395
ESWX-105V18E79-R43	\$3,870	A-395
ESWX-105V18E79-R44	\$3,870	A-395
ESWX-105V18E79-R45	\$3,870	A-395
ESWX-105V24A79-R43	\$4,600	A-395
ESWX-105V24A79-R45	\$4,600	A-395
ESWX-105V24E79-R43	\$3,870	A-395
ESWX-105V24E79-R45	\$3,870	A-395
ESWX-105V47A79-R43	\$4,600	A-395
ESWX-105V47A79-R44	\$4,600	A-395
ESWX-105V47E79-R43	\$3,870	A-395
ESWX-105V47E79-R44	\$3,870	A-395
ESWX-25V18A79-R23	\$3,850	A-395
ESWX-25V18A79-R24	\$3,850	A-395
ESWX-25V18A79-R25	\$3,850	A-395
ESWX-25V18A79-R26	\$3,850	A-395
ESWX-25V18A79-R27	\$3,850	A-395
ESWX-25V18A79-R28	\$3,850	A-395
ESWX-25V18A79-R29	\$3,850	A-395
ESWX-25V18A79-R30	\$3,850	A-395
ESWX-25V18A79-R32	\$3,850	A-395
ESWX-25V18A79-R33	\$3,850	A-395
ESWX-25V18E79-R23	\$3,250	A-395
ESWX-25V18E79-R24	\$3,250	A-395
ESWX-25V18E79-R25	\$3,250	A-395
ESWX-25V18E79-R26	\$3,250	A-395
ESWX-25V18E79-R27	\$3,250	A-395
ESWX-25V18E79-R28	\$3,250	A-395
ESWX-25V18E79-R29	\$3,250	A-395
ESWX-25V18E79-R30	\$3,250	A-395
ESWX-25V18E79-R32	\$3,250	A-395
ESWX-25V18E79-R33	\$3,250	A-395
ESWX-25V24A79-R23	\$3,850	A-395
ESWX-25V24A79-R25	\$3,850	A-395
ESWX-25V24A79-R26	\$3,850	A-395
ESWX-25V24A79-R27	\$3,850	A-395
ESWX-25V24A79-R28	\$3,850	A-395
ESWX-25V24A79-R29	\$3,850	A-395
ESWX-25V24A79-R32	\$3,850	A-395
ESWX-25V24A79-R33	\$3,850	A-395
ESWX-25V24E79-R23	\$3,250	A-395
ESWX-25V24E79-R25	\$3,250	A-395
ESWX-25V24E79-R26	\$3,250	A-395
ESWX-25V24E79-R27	\$3,250	A-395
ESWX-25V24E79-R28	\$3,250	A-395
ESWX-25V24E79-R29	\$3,250	A-395
ESWX-25V24E79-R32	\$3,250	A-395
ESWX-25V24E79-R33	\$3,250	A-395
ESWX-25V47A79-R23	\$3,850	A-395

Part Number	List Price	Pages
ESWX-25V47A79-R24	\$3,850	A-395
ESWX-25V47A79-R25	\$3,850	A-395
ESWX-25V47A79-R26	\$3,850	A-395
ESWX-25V47A79-R27	\$3,850	A-395
ESWX-25V47A79-R28	\$3,850	A-395
ESWX-25V47A79-R30	\$3,850	A-395
ESWX-25V47A79-R32	\$3,850	A-395
ESWX-25V47A79-R33	\$3,850	A-395
ESWX-25V47E79-R23	\$3,250	A-395
ESWX-25V47E79-R24	\$3,250	A-395
ESWX-25V47E79-R25	\$3,250	A-395
ESWX-25V47E79-R26	\$3,250	A-395
ESWX-25V47E79-R27	\$3,250	A-395
ESWX-25V47E79-R28	\$3,250	A-395
ESWX-25V47E79-R30	\$3,250	A-395
ESWX-25V47E79-R32	\$3,250	A-395
ESWX-25V47E79-R33	\$3,250	A-395
ESWX-40V18A79-R34	\$3,950	A-395
ESWX-40V18A79-R35	\$3,950	A-395
ESWX-40V18E79-R34	\$3,300	A-395
ESWX-40V18E79-R35	\$3,300	A-395
ESWX-40V24A79-R34	\$3,950	A-395
ESWX-40V24A79-R35	\$3,950	A-395
ESWX-40V24E79-R34	\$3,300	A-395
ESWX-40V24E79-R35	\$3,300	A-395
ESWX-40V47A79-R34	\$3,950	A-395
ESWX-40V47A79-R35	\$3,950	A-395
ESWX-40V47E79-R34	\$3,300	A-395
ESWX-40V47E79-R35	\$3,300	A-395
ESWX-80V18A79-R38	\$4,050	A-395
ESWX-80V18A79-R39	\$4,050	A-395
ESWX-80V18A79-R41	\$4,050	A-395
ESWX-80V18E79-R38	\$3,400	A-395
ESWX-80V18E79-R39	\$3,400	A-395
ESWX-80V18E79-R41	\$3,420	A-395
ESWX-80V24A79-R38	\$4,050	A-395
ESWX-80V24A79-R39	\$4,050	A-395
ESWX-80V24A79-R41	\$4,050	A-395
ESWX-80V24E79-R38	\$3,400	A-395
ESWX-80V24E79-R39	\$3,400	A-395
ESWX-80V24E79-R41	\$3,420	A-395
ESWX-80V47A79-R38	\$4,050	A-395
ESWX-80V47A79-R39	\$4,050	A-395
ESWX-80V47A79-R41	\$4,050	A-395
ESWX-80V47E79-R38	\$3,400	A-395
ESWX-80V47E79-R39	\$3,400	A-395
ESWX-80V47E79-R41	\$3,420	A-395
ESWX-M100R79-U075	\$3,350	A-393
ESWX-M100R79-U090	\$3,350	A-393
ESWX-M100R79-U100	\$3,350	A-393

Part Number	List Price	Pages
ESWX-M16A79-D016	\$1,595	A-392
ESWX-M16A79-D025	\$1,595	A-392
ESWX-M16A79-D063	\$1,595	A-392
ESWX-M16A79-U001	\$1,595	A-392
ESWX-M16A79-U004	\$1,595	A-392
ESWX-M16A79-U010	\$1,595	A-392
ESWX-M16A79-U016	\$1,595	A-392
ESWX-M25R79-D016	\$2,200	A-393
ESWX-M25R79-D025	\$2,200	A-393
ESWX-M25R79-D063	\$2,200	A-393
ESWX-M25R79-U001	\$2,200	A-393
ESWX-M25R79-U004	\$2,200	A-393
ESWX-M25R79-U010	\$2,200	A-393
ESWX-M25R79-U016	\$2,200	A-393
ESWX-M25R79-U020	\$2,200	A-393
ESWX-M25R79-U025	\$2,200	A-393
ESWX-M25R79-U032	\$2,200	A-393
ESWX-M65R79-U040	\$2,600	A-393
ESWX-M65R79-U050	\$2,600	A-393
ESWX-M65R79-U065	\$2,600	A-393
ETHERNET/IP-05	\$1,100	A-402
FAN -E1404P-AL	\$116	A-432
FAN-11101736-AL-W22	\$580	A-433;A-434
FAN-11101737-AL-W22	\$250	A-433;A-434
FAN-11101746-AL-W22	\$3,293	A-433;A-434
FAN-11272463-AL-W22	\$511	A-433;A-434
FAN-11482642-W22	\$74	A-430;A-431
FAN-11482679-W22	\$66	A-430;A-431
FAN-E100	\$18	A-429;A-430;A-435
FAN-E100-AL	\$161	A-432;A-433
FAN-E1404P-AL	\$116	A-432;A-433
FAN-E1804P-AL-B	\$223	A-432;A-433
FAN-E180W21024P-AL	\$112	A-432;A-433
FAN-E180W2102P	\$12	A-429;A-430;A-435
FAN-E180W2104P	\$19	A-429;A-430;A-435
FAN-E210-2/8P-AL	\$147	A-432
FAN-E2102P	\$17	A-429;A-435
FAN-E210-4/6P-AL	\$313	A-432;A-433
FAN-E2104P	\$24	A-429;A-430;A-435
FAN-E2502-4P-AL-W22	\$116	A-432;A-433
FAN-E2502P	\$12	A-429;A-430
FAN-E2504P	\$24	A-429;A-430
FAN-E2504P-AL-B	\$259	A-432;A-433
FAN-E2802P	\$12	A-429;A-430
FAN-E2802P-AL	\$112	A-432;A-433
FAN-E2804P	\$24	A-429;A-430
FAN-E2804P-AL-W22	\$161	A-432;A-433
FAN-E3202P	\$18	A-429;A-430
FAN-E3202P-AL-W22	\$157	A-432;A-433
FAN-E3204P	\$27	A-429;A-430
FAN-E3204P-AL	\$421	A-432;A-433

Part Number	List Price	Pages
FAN-E360/4002P-W22	\$59	A-430;A-431
FAN-E360-4002PAL-W22	\$205	A-433;A-434
FAN-E440/500468P-W22	\$89	A-430;A-431
FAN-E444-505/2P-W22	\$63	A-430;A-431
FAN-E63	\$6	A-429;A-430
FAN-E63-AL	\$55	A-432;A-433
FAN-E71	\$7	A-429;A-430
FAN-E71-AL	\$70	A-432;A-433
FAN-E80	\$8	A-429;A-430;A-435
FAN-E80-AL	\$88	A-432;A-433
FAN-FD56/140-15MM	\$12	A-435
FAN-FD56/140-17MM	\$12	A-429;A-430
FAN-W22-11101738-AL	\$902	A-433;A-434
FAN-W22-11101739-AL	\$280	A-433;A-434
FAN-W22-11101744-AL	\$2,042	A-433;A-434
FCO-BM140-W22	\$185	A-423
FCO-BM180-W22	\$222	A-423
FCO-BM210-W22	\$222	A-423
FCO-BM250-W22	\$406	A-423
FCO-BM280-W22	\$406	A-423
FCO-BM320-W22	\$611	A-423
FCO-E100	\$33	A-434
FCO-E140-W22	\$26	A-434
FCO-E180-S	\$46	A-435
FCO-E180-W22	\$38	A-434
FCO-E210-S	\$49	A-435
FCO-E210-W22	\$53	A-434
FCO-E250-S	\$89	A-435
FCO-E250-W22	\$121	A-434
FCO-E280-W22	\$149	A-434
FCO-E320-W22	\$256	A-434
FCO-E360-W22	\$672	A-434
FCO-E400-W22	\$672	A-434
FCO-E440-W22	\$1,032	A-434
FCO-E48/W56-S	\$20	A-435
FCO-E500-W22	\$1,032	A-434
FCO-E56/140-S	\$19	A-435
FCO-E580-W22	\$1,605	A-434
FCO-E63	\$23	A-434
FCO-E71	\$23	A-434
FCO-E80	\$23	A-434
FCO-EL440-W22	\$1,032	A-434
FLC-048/W56-S	\$67	A-417
FLC-E140-S	\$85	A-415;A-416
FLC-E140-UBC	\$85	A-415
FLC-E180-S	\$145	A-415
FLC-E180-UBC-W22	\$145	A-415
FLC-E210-S	\$150	A-415
FLC-E210-UBC	\$150	A-415
FLC-E250-S	\$195	A-415
FLC-E250-W22	\$195	A-415

Part Number	List Price	Pages
FLC-E280	\$290	A-415
FLC-E320	\$440	A-415
FLC-E360-314-W22	\$575	A-415;A-416
FLC-E400-314	\$620	A-415;A-416
FLC-E400-316	\$620	A-415
FLC-E440-314	\$830	A-415;A-416
FLC-E440-314-VENT *	\$1,660	A-415
FLC-E440-319	\$830	A-415
FLC-E440-322	\$830	A-415
FLC-E440-322-VENT *	\$1,743	A-415
FLC-E48/W56-S	\$80	A-416
FLC-E500-314-W22	\$1,200	A-415;A-416
FLC-E500-319-W22	\$1,200	A-415;A-416
FLC-E500-322-W22	\$1,200	A-415
FLC-E56-203-FC149-S	\$85	A-416
FLC-E56-204-S	\$85	A-416
FLC-E580-314	\$1,465	A-415
FLC-E580-314-VENT *	\$1,905	A-415
FLC-E580-316	\$1,650	A-416
FLC-E580-322	\$1,650	A-415;A-416
FLC-E580-322-VENT *	\$1,980	A-415
FLC-E580-324	\$1,650	A-415
FLC-EL440-314-VENT *	\$1,800	A-415
FLC-EL440-322-VENT *	\$1,861	A-415
FLC-IE140	\$250	A-415
FLC-IE180-W22	\$285	A-415
FLC-IE210	\$300	A-415
FLC-IE250-W22	\$325	A-415
FLC-IE280	\$365	A-415
FLC-IE320	\$550	A-415
FLC-IM100DIN-AL-UBC	\$128	A-416
FLC-IM112DIN-UBC-W22	\$145	A-416
FLC-IM132DIN-AL-UBC	\$150	A-416
FLC-IM160DIN-W22	\$195	A-416
FLC-IM160-W22	\$195	A-416
FLC-IM180	\$290	A-416
FLC-IM200	\$440	A-416
FLC-IM280-316	\$830	A-416
FLC-IM63DIN-AL	\$39	A-416
FLC-IM71DIN-BC-W22	\$43	A-416
FLC-IM80DIN-AL-BC	\$45	A-416
FLC-IM90DIN-AL-UBC	\$85	A-416
FLC-O140-S	\$85	A-417
FLC-O180-S	\$145	A-417
FLC-O210-S	\$150	A-417
FLC-O250 **	\$195	A-417
FLC-O250-S	\$195	A-417
FLC-O250-W40 **	\$195	A-417
FLC-O280	\$290	A-417
FLC-O280-W40	\$290	A-417
FLC-O320	\$440	A-417

Part Number	List Price	Pages
FLC-0320-W40	\$440	A-417
FLC-0360/400-314-W40	\$575	A-417
FLC-0360/400-316-W40	\$620	A-417
FLC-0360-314	\$575	A-417
FLC-0400-316	\$620	A-417
FLC-0440-314	\$830	A-417
FLC-0440-319	\$830	A-417
FLC-0444/5-314-W40	\$830	A-417
FLC-0444/5-319-W40	\$830	A-417
FLC-0447/9-314-W40	\$830	A-417
FLC-0447/9-319-W40	\$830	A-417
FLC-056-203-FC149-S	\$85	A-417
FLC-056-204-S	\$85	A-417
FLC-X140	\$120	A-416
FLC-X180	\$201	A-416
FLC-X210	\$214	A-416
FLC-X250-W21X	\$291	A-416
FLC-X280-W21X	\$517	A-416
FLC-X320-W21X	\$663	A-416
FLC-X360-314	\$992	A-416
FLC-X400-217	\$1,210	A-416
FLC-X440-219	\$1,508	A-416
FLC-X440-314	\$1,508	A-416
FLC-X440-319	\$1,508	A-416
FLD-E140-UBC	\$98	A-418
FLD-E180-W22	\$171	A-418
FLD-E210-UBC	\$184	A-418
FLD-E250-W22	\$244	A-418
FLD-E280	\$318	A-418
FLD-E320	\$465	A-418
FLD-E360-314-W22	\$620	A-418
FLD-E400-314	\$765	A-418
FLD-E400-316	\$765	A-418
FLD-E440-314	\$932	A-418
FLD-E440-314-VENT *	\$1,771	A-418
FLD-E440-319	\$932	A-418
FLD-E440-322	\$932	A-418
FLD-E440-322-VENT *	\$1,864	A-418
FLD-E500-314-W22	\$1,350	A-418
FLD-E500-319-W22	\$1,350	A-418
FLD-E500-322-W22	\$1,350	A-418
FLD-E580-314	\$2,130	A-418
FLD-E580-314-VENT *	\$2,343	A-418
FLD-E580-322	\$2,130	A-418
FLD-E580-322-VENT *	\$2,450	A-418
FLD-E580-324	\$2,130	A-418
FLD-EL440-314-VENT *	\$1,890	A-418
FLD-EL440-322-VENT *	\$1,987	A-418
FLD-IE210	\$350	A-418
FLD-IE250-W22	\$425	A-418
FLD-IE280	\$490	A-418

FLD-IE320	\$785	A-418
FLD-O280	\$318	A-419
FLD-O280-W40	\$318	A-419
FLD-O320	\$465	A-419
FLD-O320-W40	\$465	A-419
FLD-O360-314	\$620	A-419
FLD-O360-314-W40	\$620	A-419
FLD-O400-314	\$765	A-419
FLD-O400-314-W40	\$765	A-419
FLD-O400-316	\$765	A-419
FLD-O400-316-W40	\$765	A-419
FLD-O440-314	\$932	A-419
FLD-O440-319	\$932	A-419
FLD-O444/5-314-W40	\$932	A-419
FLD-O444/5-319-W40	\$932	A-419
FLD-O447/9-314-W40	\$932	A-419
FLD-O447/9-319-W40	\$932	A-419
FLD-X140	\$154	A-419
FLD-X180	\$210	A-419
FLD-X210	\$291	A-419
FLD-X250-W21X	\$534	A-419
FLD-X280-W21X	\$637	A-419
FLD-X320-W21X	\$795	A-419
FLD-X360-314	\$1,141	A-419
FLD-X400-217	\$1,338	A-419
FLD-X400-314	\$1,338	A-419
FLD-X440-219	\$1,878	A-419
FLD-X440-314	\$1,878	A-419
FLD-X440-319	\$1,878	A-419
FLF-IM100-AL-UBC	\$169	A-419
FLF-IM112-UBC-W22	\$171	A-419
FLF-IM132-AL-UBC	\$184	A-419
FLF-IM160-W22	\$245	A-419
FLF-IM180	\$318	A-419
FLF-IM200	\$465	A-419
FLF-IM225-W22	\$620	A-419
FLF-IM250	\$765	A-419
FLF-IM280-314	\$932	A-419
FLF-IM280-316	\$932	A-419
FLF-IM315-314-W22	\$1,350	A-419
FLF-IM315-319-W22	\$1,350	A-419
FLF-IM63-AL	\$63	A-419
FLF-IM71-BC-W22	\$72	A-419
FLF-IM80-AL-BC	\$96	A-419
FLF-IM90-AL-UBC	\$98	A-419
GH1001	\$470	A-308
GH1002	\$470	A-308
GH1003	\$470	A-308
GH1004	\$460	A-308
GH1005	\$460	A-308
GH1006	\$460	A-308

Part Number	List Price	Pages
GH2001	\$651	A-309
GH2002	\$651	A-309
GH2003	\$651	A-309
GH2004	\$656	A-309
GH2005	\$663	A-309
GH2006	\$663	A-309
GH2007	\$663	A-309
GH2008	\$653	A-309
GH2009	\$653	A-309
GH2010	\$653	A-309
GH2011	\$667	A-309
GL2001	\$656	A-309
GL2002	\$667	A-309
GL2003	\$658	A-309
GL2004	\$658	A-309
GPH2005PC2000	\$3,900	A-364
GPH2005PC2001	\$4,395	A-365
GPH2005QC2000	\$3,650	A-362
GPH2005QC2001	\$4,145	A-363
GPH2007PC2000	\$4,032	A-364
GPH2007PC2001	\$4,527	A-365
GPH2007QC2000	\$3,750	A-362
GPH2007QC2001	\$4,245	A-363
GPH2010PC2000	\$4,243	A-364
GPH2010PC2001	\$4,738	A-365
GPH2010PC4000	\$3,900	A-364
GPH2010PC4001	\$4,395	A-365
GPH2010QC2000	\$3,900	A-362
GPH2010QC2001	\$4,395	A-363
GPH2010QC4000	\$3,650	A-362
GPH2010QC4001	\$4,145	A-363
GPH2015PC2000	\$4,865	A-364
GPH2015PC2001	\$5,360	A-365
GPH2015PC4000	\$4,032	A-364
GPH2015PC4001	\$4,527	A-365
GPH2015QC2000	\$4,300	A-362
GPH2015QC2001	\$4,795	A-363
GPH2015QC4000	\$3,750	A-362
GPH2015QC4001	\$4,245	A-363
GPH2020PC4000	\$4,243	A-364
GPH2020PC4001	\$4,738	A-365
GPH2020QC4000	\$3,900	A-362
GPH2020QC4001	\$4,395	A-363
GPH2025PC2000	\$5,412	A-364
GPH2025PC2001	\$5,907	A-365
GPH2025QC2000	\$4,800	A-362
GPH2025QC2001	\$5,295	A-363
GPH2030PC2000	\$6,585	A-364
GPH2030PC2001	\$7,080	A-365
GPH2030PC4000	\$4,865	A-364
GPH2030PC4001	\$5,360	A-365

Part Number	List Price	Pages
GPH2030QC2000	\$5,800	A-362
GPH2030QC2001	\$6,295	A-363
GPH2030QC4000	\$4,300	A-362
GPH2030QC4001	\$4,795	A-363
GPH2050PC2000	\$8,260	A-364
GPH2050PC2001	\$8,755	A-365
GPH2050PC4000	\$5,412	A-364
GPH2050PC4001	\$5,907	A-365
GPH2050QC2000	\$6,990	A-362
GPH2050QC2001	\$7,485	A-363
GPH2050QC4000	\$4,800	A-362
GPH2050QC4001	\$5,295	A-363
GPH2060PC2000	\$9,013	A-364
GPH2060PC2001	\$9,508	A-365
GPH2060QC2000	\$7,500	A-362
GPH2060QC2001	\$7,995	A-363
GPH2075PC2000	\$10,350	A-364
GPH2075PC2001	\$10,845	A-365
GPH2075PC4000	\$6,585	A-364
GPH2075PC4001	\$7,080	A-365
GPH2075QC2000	\$8,450	A-362
GPH2075QC2001	\$8,945	A-363
GPH2075QC4000	\$5,800	A-362
GPH2075QC4001	\$6,295	A-363
GPH2100PC2000	\$12,965	A-364
GPH2100PC2001	\$13,460	A-365
GPH2100PC4000	\$8,260	A-364
GPH2100PC4001	\$8,755	A-365
GPH2100QC2000	\$10,700	A-362
GPH2100QC2001	\$11,195	A-363
GPH2100QC4000	\$6,990	A-362
GPH2100QC4001	\$7,485	A-363
GPH2125PC2000	\$14,847	A-364
GPH2125PC2001	\$15,342	A-365
GPH2125PC4000	\$9,013	A-364
GPH2125PC4001	\$9,508	A-365
GPH2125QC2000	\$11,880	A-362
GPH2125QC2001	\$12,375	A-363
GPH2125QC4000	\$7,500	A-362
GPH2125QC4001	\$7,995	A-363
GPH2150PC2000	\$15,706	A-364
GPH2150PC2001	\$16,201	A-365
GPH2150PC4000	\$10,350	A-364
GPH2150PC4001	\$10,845	A-365
GPH2150QC2000	\$12,700	A-362
GPH2150QC2001	\$13,195	A-363
GPH2150QC4000	\$8,450	A-362
GPH2150QC4001	\$8,945	A-363
GPH2175PC2000	\$21,075	A-364
GPH2175PC2001	\$21,570	A-365
GPH2175QC2000	\$14,500	A-362

Part Number	List Price	Pages
GPH2175QC2001	\$14,995	A-363
GPH2200PC4000	\$12,965	A-364
GPH2200PC4001	\$13,460	A-365
GPH2200QC4000	\$10,700	A-362
GPH2200QC4001	\$11,195	A-363
GPH2250PC4000	\$14,847	A-364
GPH2250PC4001	\$15,342	A-365
GPH2250QC4000	\$11,880	A-362
GPH2250QC4001	\$12,375	A-363
GPH2300PC4000	\$15,706	A-364
GPH2300PC4001	\$16,201	A-365
GPH2300QC4000	\$12,700	A-362
GPH2300QC4001	\$13,195	A-363
GPH2350PC4000	\$21,075	A-364
GPH2350PC4001	\$21,570	A-365
GPH2350QC4000	\$14,500	A-362
GPH2350QC4001	\$14,995	A-363
GTA161AIHI	\$3,787	A-300
GTA161AIHS	\$3,501	A-300
GTA162AIVD	\$4,453	A-300
GTA201AIHB	\$6,357	A-300
GTA201AIHE	\$6,507	A-300
GTA201AIHS	\$5,382	A-300
GTA201AIHV	\$5,674	A-300
GTA202AIVJ	\$8,058	A-300
GTA202AIVS	\$7,037	A-300
GTA251AIHD	\$9,165	A-300
GTA251AIHE	\$10,725	A-300
H311007110(1	\$4,953	A-137
H311007111(1	\$4,210	A-137
H311007112 (1	\$4,924	A-138
H311007113 (1	\$4,155	A-138
HMI-01	\$320	A-402
HMI-02	\$320	A-339
HMI-03	\$320	A-339
HMID-01	\$54	A-339
IHM-CAB-RS-10M	\$102	A-339
IHM-CAB-RS-1M	\$54	A-339
IHM-CAB-RS-2M	\$60	A-339
IHM-CAB-RS-3M	\$66	A-339
IHM-CAB-RS-5M	\$75	A-339
IHM-CAB-RS-7.5M	\$90	A-339
IOE-04	\$2,795	A-402
KESWFP	\$80	A-374
KESWHP	\$80	A-374
KESWPE	\$80	A-374
KESWPP	\$25	A-374
KESWPS	\$80	A-374
KIP21D-01	\$120	A-339
KN1A-02	\$125	A-339
KN1B-02	\$125	A-339

Part Number	List Price	Pages
KN1C-02	\$142	A-339
KN1E-01	\$78	A-339
KN1E-02	\$213	A-339
LRW002G3N1	\$387	A-341
LRW004G3N1	\$394	A-341
LRW008G3N1	\$415	A-341
LRW012D3N1	\$436	A-341
LRW012G3N1	\$452	A-341
LRW018D3N1	\$512	A-341
LRW018G3N1	\$519	A-341
LRW025D3N1	\$590	A-341
LRW025G3N1	\$601	A-341
LRW035D3N1	\$634	A-341
LRW035G3N1	\$715	A-341
LRW045D3N1	\$756	A-341
LRW045G3N1	\$841	A-341
LRW055D3N1	\$890	A-341
LRW055G3N1	\$987	A-341
LRW080D3N1	\$905	A-341
LRW080G3N1	\$1,179	A-341
LRW100G3N1	\$9,788	A-341
LRW100D3N1	\$1,086	A-341
LRW100G3N1	\$1,450	A-341
LRW130D3N1	\$1,175	A-341
LRW130G3N1	\$1,750	A-341
LRW160D3N1	\$1,424	A-341
LRW160G3N1	\$2,060	A-341
LRW200D3N1	\$1,488	A-341
LRW200G3N1	\$2,400	A-341
LRW250G3N1	\$2,990	A-341
LRW320G3N1	\$3,700	A-341
LRW400G3N1	\$4,962	A-341
LRW500G3N1	\$6,446	A-341
LRW600G3N1	\$7,950	A-341
MH1601	\$258	A-306
MH4301	\$337	A-307
MH4401	\$344	A-307
ML1601	\$228	A-306
ML4301	\$351	A-307
ML4401	\$372	A-307
MMF-01	\$71	A-402
MMF-02	\$71	A-339
MT-031	\$516	A-172;A-304
MT-032	\$644	A-172;A-304
MT-033	\$563	A-172;A-304
MT-034	\$930	A-172;A-304
MT-035	\$791	A-172;A-304
MT-037	\$930	A-172;A-304
MT-038	\$1,151	A-172;A-304
MT-039	\$2,093	A-172;A-304
MT-040	\$2,930	A-172;A-304



Part Number	List Price	Pages
MT-041	\$516	A-172;A-304
MT-042	\$563	A-172;A-304
MT-043	\$644	A-172;A-304
MT-044	\$791	A-172;A-304
MT-065	\$613	A-304
MT-066	\$613	A-304
MT-067	\$674	A-304
MT-068	\$645	A-304
MT-069	\$702	A-304
MT-070	\$669	A-304
MT-071	\$773	A-304
MT-072	\$701	A-304
MT-073	\$921	A-304
MT-074	\$849	A-304
MT-145BS	\$41	A-305
MT-56BS	\$34	A-305
MT-75BS	\$34	A-305
NDE-E360T-314-I-W22	\$2,150	A-427
NDE-E400T-314-I-W22	\$2,150	A-427
NDE-E440T-314-I-W22	\$2,592	A-427
NDE-E440T-316-I-W22	\$2,592	A-427
NDE-E440T-319-I-W22	\$2,592	A-427
NDE-E580-314-I-W22	\$3,371	A-427
NDE-E580-319-I-W22	\$3,371	A-427
NDE-EL440T-314-I-W22	\$3,220	A-427
NDE-EL440T-319-I-W22	\$3,220	A-427
PCJ105H	\$236	A-207
PCJ107	\$236	A-208
PCJ107H	\$263	A-207
PCJ110	\$263	A-208
PCJ110H	\$300	A-207
PCJ115	\$300	A-208
PCJ115H	\$400	A-207
PCJ120	\$400	A-208
PCJ120H	\$486	A-207
PCJ125	\$486	A-208
PCQ103H	\$231	A-207
PCQ105	\$231	A-208
PCQ105H	\$241	A-207
PCQ107	\$241	A-208
PCQ107H	\$275	A-207
PCQ110	\$275	A-208
PCQ110H	\$320	A-207
PCQ115	\$320	A-208
PCQ115H	\$411	A-207
PCQ120	\$411	A-208
PCQ120H	\$500	A-207
PCQ125	\$500	A-208
PCSA-01	\$48	A-339
PCSB-01	\$51	A-339
PCSC-01	\$54	A-339

Part Number	List Price	Pages
PCSD-01	\$56	A-339
PCSE-01	\$76	A-339
PESW-105V18AX-R44	\$1,199	A-378
PESW-105V18AX-R45	\$1,199	A-378
PESW-105V18EX-R44	\$1,184	A-378
PESW-105V18EX-R45	\$1,184	A-378
PESW-105V24AX-R44	\$1,199	A-378
PESW-105V24AX-R45	\$1,199	A-378
PESW-105V24EX-R44	\$1,184	A-378
PESW-105V24EX-R45	\$1,184	A-378
PESW-105V47AX-R44	\$1,199	A-378
PESW-105V47AX-R45	\$1,199	A-378
PESW-105V47EX-R44	\$1,184	A-378
PESW-105V47EX-R45	\$1,184	A-378
PESW-40V18AX-R35	\$345	A-378
PESW-40V18EX-R35	\$321	A-378
PESW-40V24AX-R35	\$345	A-378
PESW-40V24EX-R35	\$321	A-378
PESW-40V47AX-R35	\$345	A-378
PESW-40V47EX-R35	\$321	A-378
PESW-50V18AX-R38	\$579	A-378
PESW-50V18EX-R38	\$564	A-378
PESW-50V24AX-R38	\$579	A-378
PESW-50V24EX-R38	\$564	A-378
PESW-50V47AX-R38	\$579	A-378
PESW-50V47EX-R38	\$564	A-378
PESW-65V18AX-R39	\$604	A-378
PESW-65V18EX-R39	\$589	A-378
PESW-65V24AX-R39	\$604	A-378
PESW-65V24EX-R39	\$589	A-378
PESW-65V47AX-R39	\$604	A-378
PESW-65V47EX-R39	\$589	A-378
PESW-80V18AX-R41	\$650	A-378
PESW-80V18EX-R41	\$635	A-378
PESW-80V24AX-R41	\$650	A-378
PESW-80V24EX-R41	\$635	A-378
PESW-80V47AX-R41	\$650	A-378
PESW-80V47EX-R41	\$635	A-378
PESW-95V18AX-R43	\$1,100	A-378
PESW-95V18EX-R43	\$1,085	A-378
PESW-95V24AX-R43	\$1,100	A-378
PESW-95V24EX-R43	\$1,085	A-378
PESW-95V47AX-R43	\$1,100	A-378
PESW-95V47EX-R43	\$1,085	A-378
PESW-B12D15AX-R64	\$227	A-377
PESW-B12D15EX-R64	\$174	A-377
PESW-B12D39AX-R64	\$227	A-377
PESW-B12D39EX-R64	\$174	A-377
PESW-B12V24AX-R64	\$227	A-377
PESW-B12V24EX-R64	\$174	A-377
PESW-B18D15AX-R66	\$241	A-377

Part Number	List Price	Pages
PESW-B18D15EX-R66	\$188	A-377
PESW-B18D39AX-R66	\$241	A-377
PESW-B18D39EX-R66	\$188	A-377
PESW-B18V24AX-R66	\$241	A-377
PESW-B18V24EX-R66	\$188	A-377
PESW-B25D15AX-R67	\$276	A-377
PESW-B25D15EX-R67	\$223	A-377
PESW-B25D39AX-R67	\$276	A-377
PESW-B25D39EX-R67	\$223	A-377
PESW-B25V24AX-R67	\$276	A-377
PESW-B25V24EX-R67	\$223	A-377
PESW-B32D15AX-R68	\$298	A-377
PESW-B32D15EX-R68	\$262	A-377
PESW-B32D39AX-R68	\$298	A-377
PESW-B32D39EX-R68	\$262	A-377
PESW-B32V24AX-R68	\$298	A-377
PESW-B32V24EX-R68	\$262	A-377
PESW-B38D15AX-R69	\$345	A-377
PESW-B38D15EX-R69	\$321	A-377
PESW-B38D39AX-R69	\$345	A-377
PESW-B38D39EX-R69	\$321	A-377
PESW-B38V24AX-R69	\$345	A-377
PESW-B38V24EX-R69	\$321	A-377
PESW-B9D15AX-R57	\$210	A-377
PESW-B9D15AX-R58	\$210	A-377
PESW-B9D15AX-R59	\$210	A-377
PESW-B9D15AX-R60	\$210	A-377
PESW-B9D15AX-R61	\$210	A-377
PESW-B9D15AX-R62	\$210	A-377
PESW-B9D15AX-R63	\$210	A-377
PESW-B9D15EX-R57	\$157	A-377
PESW-B9D15EX-R58	\$157	A-377
PESW-B9D15EX-R59	\$157	A-377
PESW-B9D15EX-R60	\$157	A-377
PESW-B9D15EX-R61	\$157	A-377
PESW-B9D15EX-R62	\$157	A-377
PESW-B9D15EX-R63	\$157	A-377
PESW-B9D39AX-R57	\$210	A-377
PESW-B9D39AX-R58	\$210	A-377
PESW-B9D39AX-R59	\$210	A-377
PESW-B9D39AX-R60	\$210	A-377
PESW-B9D39AX-R61	\$210	A-377
PESW-B9D39AX-R62	\$210	A-377
PESW-B9D39AX-R63	\$210	A-377
PESW-B9D39EX-R57	\$157	A-377
PESW-B9D39EX-R58	\$157	A-377
PESW-B9D39EX-R59	\$157	A-377
PESW-B9D39EX-R60	\$157	A-377
PESW-B9D39EX-R61	\$157	A-377
PESW-B9D39EX-R62	\$157	A-377
PESW-B9D39EX-R63	\$157	A-377

Part Number	List Price	Pages
PESW-B9V24AX-R57	\$210	A-377
PESW-B9V24AX-R58	\$210	A-377
PESW-B9V24AX-R59	\$210	A-377
PESW-B9V24AX-R60	\$210	A-377
PESW-B9V24AX-R61	\$210	A-377
PESW-B9V24AX-R62	\$210	A-377
PESW-B9V24AX-R63	\$210	A-377
PESW-B9V24EX-R57	\$157	A-377
PESW-B9V24EX-R58	\$157	A-377
PESW-B9V24EX-R59	\$157	A-377
PESW-B9V24EX-R60	\$157	A-377
PESW-B9V24EX-R61	\$157	A-377
PESW-B9V24EX-R62	\$157	A-377
PESW-B9V24EX-R63	\$157	A-377
PESWS-40V18AX-RM35	\$300	A-379
PESWS-40V18EX-RM35	\$274	A-379
PESWS-40V24AX-RM35	\$300	A-379
PESWS-40V24EX-RM35	\$274	A-379
PESWS-50V18AX-RM38	\$440	A-379
PESWS-50V18EX-RM38	\$430	A-379
PESWS-50V24AX-RM38	\$440	A-379
PESWS-50V24EX-RM38	\$430	A-379
PESWS-B12D15AX-RM64	\$155	A-379
PESWS-B12D15EX-RM64	\$140	A-379
PESWS-B12V24AX-RM64	\$155	A-379
PESWS-B12V24EX-RM64	\$140	A-379
PESWS-B18D15AX-RM65	\$170	A-379
PESWS-B18D15AX-RM66	\$182	A-379
PESWS-B18D15EX-RM65	\$161	A-379
PESWS-B18D15EX-RM66	\$170	A-379
PESWS-B18V24AX-RM65	\$170	A-379
PESWS-B18V24AX-RM66	\$182	A-379
PESWS-B18V24EX-RM65	\$161	A-379
PESWS-B18V24EX-RM66	\$170	A-379
PESWS-B25D15AX-RM67	\$195	A-379
PESWS-B25D15EX-RM67	\$180	A-379
PESWS-B25V24AX-RM67	\$195	A-379
PESWS-B25V24EX-RM67	\$180	A-379
PESWS-B32D15AX-RM68	\$195	A-379
PESWS-B32D15EX-RM68	\$180	A-379
PESWS-B32V24AX-RM68	\$195	A-379
PESWS-B32V24EX-RM68	\$180	A-379
PESWS-B38D15AX-RM69	\$300	A-379
PESWS-B38D15EX-RM69	\$274	A-379
PESWS-B38V24AX-RM69	\$300	A-379
PESWS-B38V24EX-RM69	\$274	A-379
PESWS-B9D15AX-RM60	\$155	A-379
PESWS-B9D15AX-RM61	\$155	A-379
PESWS-B9D15AX-RM62	\$155	A-379
PESWS-B9D15AX-RM63	\$155	A-379
PESWS-B9D15EX-RM60	\$140	A-379



Part Number	List Price	Pages
PESWS-B9D15EX-RM61	\$140	A-379
PESWS-B9D15EX-RM62	\$140	A-379
PESWS-B9D15EX-RM63	\$140	A-379
PESWS-B9V24AX-RM60	\$155	A-379
PESWS-B9V24AX-RM61	\$155	A-379
PESWS-B9V24AX-RM62	\$155	A-379
PESWS-B9V24AX-RM63	\$155	A-379
PESWS-B9V24EX-RM60	\$140	A-379
PESWS-B9V24EX-RM61	\$140	A-379
PESWS-B9V24EX-RM62	\$140	A-379
PESWS-B9V24EX-RM63	\$140	A-379
PM-10	\$1,950	A-302
PM-20	\$2,025	A-302
PROFDP-05	\$1,100	A-402
PROFIBUS DP-01	\$520	A-339
REC-BM220V	\$148	A-424
REC-BM440V	\$148	A-424
REC-BM575V	\$148	A-424
RHMIF-01	\$69	A-402
RHMIF-02	\$69	A-339
RHMIF-03	\$69	A-339
RS232-01	\$180	A-402
RS232-02	\$180	A-402
RS232-05	\$290	A-402
RS485-01	\$240	A-402
RS485-05	\$360	A-402
SMB-143T	\$73	A-428
SMB-145T	\$73	A-428
SMB-182T	\$87	A-428
SMB-182TA2	\$120	A-428
SMB-184T	\$87	A-428
SMB-184TA2	\$120	A-428
SMB-213T	\$118	A-428
SMB-215T	\$118	A-428
SMB-254T	\$220	A-428
SMB-256T	\$220	A-428
SMB-284T	\$240	A-428
SMB-286T	\$240	A-428
SMB-324T	\$321	A-428
SMB-326T	\$321	A-428
SMB-364T	\$410	A-428
SMB-365T	\$410	A-428
SMB-404T	\$600	A-428
SMB-405T	\$600	A-428
SMB-444T	\$746	A-428
SMB-445T	\$746	A-428
SMB-447T	\$1,023	A-428
SMB-449T	\$1,023	A-428
SMB-504	\$1,422	A-428
SMB-505	\$1,422	A-428
SMB-580	\$3,504	A-428

Part Number	List Price	Pages
SRMP D51	\$56	A-394
SRMP D59	\$56	A-394
SRMP D65	\$56	A-394
SSW7000C125T211N2	\$55,750	A-298;A-401
SSW7000C125T211N3	\$60,820	A-298;A-401
SSW7000C125T411N2	\$63,950	A-298;A-401
SSW7000C125T411N3	\$69,015	A-298;A-401
SSW7000C180T211N2	\$58,665	A-298;A-401
SSW7000C180T211N3	\$63,725	A-298;A-401
SSW7000C180T411N2	\$67,195	A-298;A-401
SSW7000C180T411N3	\$72,250	A-298;A-401
SSW7000C250T211N2	\$65,195	A-298;A-401
SSW7000C250T211N3	\$70,255	A-298;A-401
SSW7000C250T411N2	\$75,235	A-298;A-401
SSW7000C250T411N3	\$80,295	A-298;A-401
SSW7000C360T211N2	\$67,430	A-298;A-401
SSW7000C360T211N3	\$73,020	A-298;A-401
SSW7000C360T411N2	\$77,980	A-298;A-401
SSW7000C360T411N3	\$83,550	A-298;A-401
STUBSHAFT-A-TEFC	\$220	A-426
STUBSHAFT-B-TEFC	\$240	A-426
STUBSHAFT-C-TEFC	\$240	A-426
STUBSHAFT-D-TEFC	\$270	A-426
TBX-ADPT-360/400- W22	\$660	A-422
TBX-ADPT-444/500- W22	\$921	A-422
TBX-ADPT-444/5-W22	\$777	A-422
TBX-ADPT-580-W22	\$1,273	A-422
TBX-ADPT-L440-W22	\$1,080	A-422
TBX-BM140-W22	\$135	A-424
TBX-BM180/210-W22	\$177	A-424
TBX-BM250/280-W22	\$191	A-424
TBX-BM320-W22	\$238	A-424
TBX-E140-S	\$62	A-422
TBX-E140-W22	\$71	A-421
TBX-E180/210-W22	\$99	A-421
TBX-E180-S	\$73	A-422
TBX-E210-S	\$108	A-422
TBX-E250/280-W22	\$144	A-421
TBX-E250-S	\$154	A-422
TBX-E320-W22	\$214	A-421
TBX-E360/400-3-W22	\$324	A-421
TBX-E440-3-W22	\$497	A-421
TBX-E447/505-3-W22	\$768	A-421
TBX-E56-S	\$40	A-422
TBX-EL447/9-586/7-W2	\$1,686	A-421
TERMBLCK-W22-112/132	\$52	A-428
TERMBLCK-W22-160/180	\$86	A-428
TERMBLCK-W22-200	\$151	A-428
TERMBLCK-W22-225/250	\$280	A-428
TERMBLCK-W22-280	\$533	A-428
TERMBLCK-W22-315S/M	\$533	A-428

Part Number	List Price	Pages
TERMBLCK-W22-355M/L	\$1,032	A-428
TERMBLCK-W22-63-100	\$35	A-428
TQ1310D56SP	\$515	A-312
TQ1310H56SP	\$538	A-312
TQ1310L56SP	\$509	A-312
TQ1310R56SP	\$509	A-312
TQ1315D56SP	\$515	A-313
TQ1315H56SP	\$538	A-313
TQ1315L56SP	\$509	A-313
TQ1315R56SP	\$509	A-313
TQ1320D56SP	\$515	A-313
TQ1320H56SP	\$538	A-313
TQ1320L56SP	\$509	A-313
TQ1320R56SP	\$509	A-313
TQ1330D56SP	\$515	A-314
TQ1330H56SP	\$538	A-314
TQ1330L56SP	\$509	A-314
TQ1330R56SP	\$509	A-314
TQ1340D56SP	\$515	A-314
TQ1340H56SP	\$538	A-314
TQ1340L56SP	\$509	A-314
TQ1340R56SP	\$509	A-314
TQ1350D56SP	\$515	A-315
TQ1350H56SP	\$538	A-315
TQ1350L56SP	\$509	A-315
TQ1350R56SP	\$509	A-315
TQ135D56SP	\$515	A-312
TQ135H56SP	\$538	A-312
TQ135L56SP	\$509	A-312
TQ135R56SP	\$509	A-312
TQ1360D56SP	\$470	A-315
TQ1360H56SP	\$507	A-315
TQ1360L56SP	\$457	A-315
TQ1360R56SP	\$457	A-315
TQ1510D140SP	\$569	A-312
TQ1510H140SP	\$593	A-312
TQ1510L140SP	\$558	A-312
TQ1510R140SP	\$558	A-312
TQ1515D56SP	\$569	A-313
TQ1515H56SP	\$593	A-313
TQ1515L56SP	\$558	A-313
TQ1515R56SP	\$558	A-313
TQ1520D56SP	\$569	A-313
TQ1520H56SP	\$593	A-313
TQ1520L56SP	\$558	A-313
TQ1520R56SP	\$558	A-313
TQ1530D56SP	\$569	A-314
TQ1530H56SP	\$593	A-314
TQ1530L56SP	\$558	A-314
TQ1530R56SP	\$558	A-314
TQ1540D56SP	\$569	A-314

Part Number	List Price	Pages
TQ1540H56SP	\$593	A-314
TQ1540L56SP	\$558	A-314
TQ1540R56SP	\$558	A-314
TQ1550D56SP	\$569	A-315
TQ1550H56SP	\$593	A-315
TQ1550L56SP	\$558	A-315
TQ1550R56SP	\$558	A-315
TQ155D140SP	\$569	A-312
TQ155H140SP	\$593	A-312
TQ155L140SP	\$558	A-312
TQ155R140SP	\$558	A-312
TQ1560D56SP	\$559	A-315
TQ1560H56SP	\$573	A-315
TQ1560L56SP	\$533	A-315
TQ1560R56SP	\$533	A-315
TQ1810D140SP	\$586	A-312
TQ1810H140SP	\$643	A-312
TQ1810L140SP	\$575	A-312
TQ1810R140SP	\$575	A-312
TQ1815D56SP	\$586	A-313
TQ1815H56SP	\$643	A-313
TQ1815L56SP	\$575	A-313
TQ1815R56SP	\$575	A-313
TQ1820D56SP	\$586	A-313
TQ1820H56SP	\$643	A-313
TQ1820L56SP	\$575	A-313
TQ1820R56SP	\$575	A-313
TQ1830D56SP	\$586	A-314
TQ1830H56SP	\$643	A-314
TQ1830L56SP	\$575	A-314
TQ1830R56SP	\$575	A-314
TQ1840D56SP	\$586	A-314
TQ1840H56SP	\$643	A-314
TQ1840L56SP	\$575	A-314
TQ1840R56SP	\$575	A-314
TQ1850D56SP	\$586	A-315
TQ1850H56SP	\$643	A-315
TQ1850L56SP	\$575	A-315
TQ1850R56SP	\$575	A-315
TQ185D140SP	\$586	A-312
TQ185H140SP	\$643	A-312
TQ185L140SP	\$575	A-312
TQ185R140SP	\$575	A-312
TQ1860D56SP	\$580	A-315
TQ1860H56SP	\$619	A-315
TQ1860L56SP	\$551	A-315
TQ1860R56SP	\$551	A-315
TQ2110D140SP	\$600	A-312
TQ2110H140SP	\$669	A-312
TQ2110L140SP	\$590	A-312
TQ2110R140SP	\$590	A-312



Part Number	List Price	Pages
TQ2115D56SP	\$600	A-313
TQ2115H56SP	\$669	A-313
TQ2115L56SP	\$590	A-313
TQ2115R56SP	\$590	A-313
TQ2120D56SP	\$600	A-313
TQ2120H56SP	\$669	A-313
TQ2120L56SP	\$590	A-313
TQ2120R56SP	\$590	A-313
TQ2130D56SP	\$600	A-314
TQ2130H56SP	\$669	A-314
TQ2130L56SP	\$590	A-314
TQ2130R56SP	\$590	A-314
TQ2140D56SP	\$600	A-314
TQ2140H56SP	\$669	A-314
TQ2140L56SP	\$590	A-314
TQ2140R56SP	\$590	A-314
TQ2150D56SP	\$600	A-315
TQ2150H56SP	\$669	A-315
TQ2150L56SP	\$590	A-315
TQ2150R56SP	\$590	A-315
TQ215D140SP	\$600	A-312
TQ215H140SP	\$669	A-312
TQ215L140SP	\$590	A-312
TQ215R140SP	\$590	A-312
TQ2160D56SP	\$632	A-315
TQ2160H56SP	\$672	A-315
TQ2160L56SP	\$585	A-315
TQ2160R56SP	\$585	A-315
TQ2410D140SP	\$723	A-312
TQ2410H140SP	\$805	A-312
TQ2410L140SP	\$712	A-312
TQ2410R140SP	\$712	A-312
TQ2415D56SP	\$723	A-313
TQ2415H56SP	\$805	A-313
TQ2415L56SP	\$712	A-313
TQ2415R56SP	\$712	A-313
TQ2420D56SP	\$723	A-313
TQ2420H56SP	\$805	A-313
TQ2420L56SP	\$712	A-313
TQ2420R56SP	\$712	A-313
TQ2430D56SP	\$723	A-314
TQ2430H56SP	\$805	A-314
TQ2430L56SP	\$712	A-314
TQ2430R56SP	\$712	A-314
TQ2440D56SP	\$723	A-314
TQ2440H56SP	\$805	A-314
TQ2440L56SP	\$712	A-314
TQ2440R56SP	\$712	A-314
TQ2450D56SP	\$723	A-315
TQ2450H56SP	\$805	A-315
TQ2450L56SP	\$712	A-315

Part Number	List Price	Pages
TQ2450R56SP	\$712	A-315
TQ245D140SP	\$723	A-312
TQ245H140SP	\$805	A-312
TQ245L140SP	\$712	A-312
TQ245R140SP	\$712	A-312
TQ2460D56SP	\$748	A-315
TQ2460H56SP	\$816	A-315
TQ2460L56SP	\$701	A-315
TQ2460R56SP	\$701	A-315
TQ2610D140SP	\$904	A-312
TQ2610H140SP	\$990	A-312
TQ2610L140SP	\$876	A-312
TQ2610R140SP	\$876	A-312
TQ2615D56SP	\$904	A-313
TQ2615H56SP	\$990	A-313
TQ2615L56SP	\$876	A-313
TQ2615R56SP	\$876	A-313
TQ2620D56SP	\$904	A-313
TQ2620H56SP	\$990	A-313
TQ2620L56SP	\$876	A-313
TQ2620R56SP	\$876	A-313
TQ2630D56SP	\$904	A-314
TQ2630H56SP	\$990	A-314
TQ2630L56SP	\$876	A-314
TQ2630R56SP	\$876	A-314
TQ2640D56SP	\$904	A-314
TQ2640H56SP	\$990	A-314
TQ2640L56SP	\$876	A-314
TQ2640R56SP	\$876	A-314
TQ2650D56SP	\$904	A-315
TQ2650H56SP	\$990	A-315
TQ2650L56SP	\$876	A-315
TQ2650R56SP	\$876	A-315
TQ265D140SP	\$904	A-312
TQ265H140SP	\$990	A-312
TQ265L140SP	\$876	A-312
TQ265R140SP	\$876	A-312
TQ2660D56SP	\$918	A-315
TQ2660H56SP	\$983	A-315
TQ2660L56SP	\$868	A-315
TQ2660R56SP	\$868	A-315
TS1310DSP	\$470	A-316
TS1310HSP	\$507	A-316
TS1310LSP	\$457	A-316
TS1310RSP	\$457	A-316
TS1315DSP	\$470	A-317
TS1315HSP	\$507	A-317
TS1315LSP	\$457	A-317
TS1315RSP	\$457	A-317
TS1320DSP	\$470	A-317
TS1320HSP	\$507	A-317

Part Number	List Price	Pages
TS1320LSP	\$457	A-317
TS1320RSP	\$457	A-317
TS1330DSP	\$470	A-318
TS1330HSP	\$507	A-318
TS1330LSP	\$457	A-318
TS1330RSP	\$457	A-318
TS1340DSP	\$470	A-318
TS1340HSP	\$507	A-318
TS1340LSP	\$457	A-318
TS1340RSP	\$457	A-318
TS1350DSP	\$470	A-319
TS1350HSP	\$507	A-319
TS1350LSP	\$457	A-319
TS1350RSP	\$457	A-319
TS135DSP	\$470	A-316
TS135HSP	\$507	A-316
TS135LSP	\$457	A-316
TS135RSP	\$457	A-316
TS1360DSP	\$470	A-319
TS1360HSP	\$507	A-319
TS1360LSP	\$457	A-319
TS1360RSP	\$457	A-319
TS1510DSP	\$559	A-316
TS1510HSP	\$573	A-316
TS1510LSP	\$533	A-316
TS1510RSP	\$533	A-316
TS1515DSP	\$559	A-317
TS1515HSP	\$573	A-317
TS1515LSP	\$533	A-317
TS1515RSP	\$533	A-317
TS1520DSP	\$559	A-317
TS1520HSP	\$573	A-317
TS1520LSP	\$533	A-317
TS1520RSP	\$533	A-317
TS1530DSP	\$559	A-318
TS1530HSP	\$573	A-318
TS1530LSP	\$533	A-318
TS1530RSP	\$533	A-318
TS1540DSP	\$559	A-318
TS1540HSP	\$573	A-318
TS1540LSP	\$533	A-318
TS1540RSP	\$533	A-318
TS1550DSP	\$559	A-319
TS1550HSP	\$573	A-319
TS1550LSP	\$533	A-319
TS1550RSP	\$533	A-319
TS155DSP	\$559	A-316
TS155HSP	\$573	A-316
TS155LSP	\$533	A-316
TS155RSP	\$533	A-316
TS1560DSP	\$559	A-319
TS1560HSP	\$573	A-319

Part Number	List Price	Pages
TS1560LSP	\$533	A-319
TS1560RSP	\$533	A-319
TS1810DSP	\$580	A-316
TS1810HSP	\$619	A-316
TS1810LSP	\$551	A-316
TS1810RSP	\$551	A-316
TS1815DSP	\$580	A-317
TS1815HSP	\$619	A-317
TS1815LSP	\$551	A-317
TS1815RSP	\$551	A-317
TS1820DSP	\$580	A-317
TS1820HSP	\$619	A-317
TS1820LSP	\$551	A-317
TS1820RSP	\$551	A-317
TS1830DSP	\$580	A-318
TS1830HSP	\$619	A-318
TS1830LSP	\$551	A-318
TS1830RSP	\$551	A-318
TS1840DSP	\$580	A-318
TS1840HSP	\$619	A-318
TS1840LSP	\$551	A-318
TS1840RSP	\$551	A-318
TS1850DSP	\$580	A-319
TS1850HSP	\$619	A-319
TS1850LSP	\$551	A-319
TS1850RSP	\$551	A-319
TS185DSP	\$580	A-316
TS185HSP	\$619	A-316
TS185LSP	\$551	A-316
TS185RSP	\$551	A-316
TS1860DSP	\$580	A-319
TS1860HSP	\$619	A-319
TS1860LSP	\$551	A-319
TS1860RSP	\$551	A-319
TS2110DSP	\$632	A-316
TS2110HSP	\$672	A-316
TS2110LSP	\$585	A-316
TS2110RSP	\$585	A-316
TS2115DSP	\$632	A-317
TS2115HSP	\$672	A-317
TS2115LSP	\$585	A-317
TS2115RSP	\$585	A-317
TS2120DSP	\$632	A-317
TS2120HSP	\$672	A-317
TS2120LSP	\$585	A-317
TS2120RSP	\$585	A-317
TS2130DSP	\$632	A-318
TS2130HSP	\$672	A-318
TS2130LSP	\$585	A-318
TS2130RSP	\$585	A-318
TS2140DSP	\$632	A-318
TS2140HSP	\$672	A-318

Part Number	List Price	Pages
TS2140LSP	\$585	A-318
TS2140RSP	\$585	A-318
TS2150DSP	\$632	A-319
TS2150HSP	\$672	A-319
TS2150LSP	\$585	A-319
TS2150RSP	\$585	A-319
TS215DSP	\$632	A-316
TS215HSP	\$672	A-316
TS215LSP	\$585	A-316
TS215RSP	\$585	A-316
TS2160DSP	\$632	A-319
TS2160HSP	\$672	A-319
TS2160LSP	\$585	A-319
TS2160RSP	\$585	A-319
TS2410DSP	\$748	A-316
TS2410HSP	\$816	A-316
TS2410LSP	\$701	A-316
TS2410RSP	\$701	A-316
TS2415DSP	\$748	A-317
TS2415HSP	\$816	A-317
TS2415LSP	\$701	A-317
TS2415RSP	\$701	A-317
TS2420DSP	\$748	A-317
TS2420HSP	\$816	A-317
TS2420LSP	\$701	A-317
TS2420RSP	\$701	A-317
TS2430DSP	\$748	A-318
TS2430HSP	\$816	A-318
TS2430LSP	\$701	A-318
TS2430RSP	\$701	A-318
TS2440DSP	\$748	A-318
TS2440HSP	\$816	A-318
TS2440LSP	\$701	A-318
TS2440RSP	\$701	A-318
TS2450DSP	\$748	A-319
TS2450HSP	\$816	A-319
TS2450LSP	\$701	A-319
TS2450RSP	\$701	A-319
TS245DSP	\$748	A-316
TS245HSP	\$816	A-316
TS245LSP	\$701	A-316
TS245RSP	\$701	A-316
TS2460DSP	\$748	A-319
TS2460HSP	\$816	A-319
TS2460LSP	\$701	A-319
TS2460RSP	\$701	A-319
TS2610DSP	\$918	A-316
TS2610HSP	\$983	A-316
TS2610LSP	\$868	A-316
TS2610RSP	\$868	A-316
TS2615DSP	\$918	A-317

Part Number	List Price	Pages
TS2615HSP	\$983	A-317
TS2615LSP	\$868	A-317
TS2615RSP	\$868	A-317
TS2620DSP	\$918	A-317
TS2620HSP	\$983	A-317
TS2620LSP	\$868	A-317
TS2620RSP	\$868	A-317
TS2630DSP	\$918	A-318
TS2630HSP	\$983	A-318
TS2630LSP	\$868	A-318
TS2630RSP	\$868	A-318
TS2640DSP	\$918	A-318
TS2640HSP	\$983	A-318
TS2640LSP	\$868	A-318
TS2640RSP	\$868	A-318
TS2650DSP	\$918	A-319
TS2650HSP	\$983	A-319
TS2650LSP	\$868	A-319
TS2650RSP	\$868	A-319
TS265DSP	\$918	A-316
TS265HSP	\$983	A-316
TS265LSP	\$868	A-316
TS265RSP	\$868	A-316
TS2660DSP	\$918	A-319
TS2660HSP	\$983	A-319
TS2660LSP	\$868	A-319
TS2660RSP	\$868	A-319
URMP D02	\$56	A-394
URMP V18	\$56	A-394
URMP V23	\$56	A-394
URMP V30	\$56	A-394
URMP V43 MPW100	\$56	A-394
URMP V47	\$56	A-394
WEG180-USEM	\$177	A-427
WEG250-280-REL	\$181	A-427
WEG250-280-USEM	\$181	A-427
WEG280-SIEM	\$181	A-427
WEG320-REL	\$202	A-427
WEG320-SIEM	\$202	A-427
WEG320-USEM	\$202	A-427
WEG360-400-REL	\$224	A-427
WEG360-400-SIEM	\$224	A-427
WEG360-400-USEM	\$224	A-427
WEG444/5-REL	\$228	A-427
WEG444/5-SIEM	\$228	A-427
WEG445/7-447/9-REL	\$263	A-427
WEG445/7-447/9-SIEM	\$263	A-427
WEG445/7-447/9-USEM	\$263	A-427

This image shows a single sheet of white paper with horizontal ruling lines. The lines are evenly spaced and run across the width of the page. There is no text or other markings on the paper.



B-133



Quote/Order Request Guidance



WEG's goal is to provide quick and accurate quotes to our customers and to insure orders can be processed accurately.

To assist customers in this process WEG has developed the form below to insure the minimum information required is included on the request, and to guide you where options may also be desired.

The form highlights in **red** the minimum information required to define a motor. Today, this includes destination (Country) to insure we comply with Energy Efficiency and certification regulations, and avoid rejection of the motor at the border.

This interactive form is available on our website (www.weg.net) or by scanning the QR code below. While we do not require use of this form, we encourage customers to be aware of the minimum information required and include it with their requests.

The minimum information required is:

1. Quantity
2. Destination (Country) important to insure compliance with Regulations
3. HP or kW
4. RPM
5. Efficiency level (NEMA Premium®, IE2, IE3...)
6. Enclosure
7. Frame Size (if need specific or IEC Vs NEMA)
8. Phase
9. Hz
10. Voltage
11. Mounting (Foot/Flange/both)
12. Type of flange (if flange, C, D, FF..)
13. Application – Helps understand load type



Scan the QR code above or visit www.weg.net/usmotorquote to download the form.

WEG Electric Corp.
Inquiry Form for AC Low Voltage Motors



WEG Division: WEG Motors		Date Entered: 5/4/2017	Date Required: 5/9/2017
Submitted By:		Customer:	
WEG ref.:		Customer ref.:	
Project:		Specification:	

MOTOR DESCRIPTION:

* IFC (R) (N) (S) * Application * Motor Destination

* Phase Three phase * Line V22 General Purpose * Efficiency NEMA Premium Efficiency * Enclosure T13C

Item	* Qty	* HP	* kW	* RPM	* Frame	* Voltage (V)	* Freq. (Hz)	* Mount	* Terminal Box Location (DE)	* Type of Flange
1										
2										
3										
4										

* If the motor is for replacement, please include the SN in the nameplate, nameplate pictures, drawings, all applicable documentation available.

ELECTRICAL FEATURES:

Insulation class: F Other: Design: B Other: Starts/hour: /

Temperature rise: (B3 (B Rise)) Other: Duty: S1 - Continuous B-directional

Service factor: 1.15 Other: Rotation (From DE): B-directional

Inverter Operation: ☐ No ☐ Yes Speed range: Torque: ☐ Insulated DE Enclosed + NDE Brush ☐ Insulated NDE Enclosed + NDE Brush

MECHANICAL FEATURES:

Protection: IP55 Drive Method: Direct Printing Plan: 20A - Enamel Alloy

Frame Material: Casted Steel Fan Material (TEFC): N/A Color: AL 9009 - Azure Blue

D.E. Bearings: (N) Special bearings (DE/NDE): / Other:

ENVIRONMENT FEATURES:

Ambient Temperature: 40°C Other: Altitude: 1000 m.a.s.l. Other:

Humidity: Other: Location: Other:

Hazardous Area: ☐ No ☐ Yes Zone / Class: Group: Temperature class: Other:

LOAD INFORMATION:

Load Torque: R/b Axial Load: 1F Application point (x): in

Load Inertia: R/b² Radial Load: 1F § Distance from shaft shoulder to ball pull center.

ACCESSORIES:

Space Heaters: Without Vibration sensor: Without

Thermal Protection: ALARM Without Thermal Protection - SWITCH OFF: Without

Bearing Protection: Without ☐ Stainless Steel Fasteners ☐ Additional Terminal Box ☐ Internal Anti-Corrosion Epoxy Coating

SPECIAL FEATURES REQUIRED:

TESTING REQUIRED:

☐ Routine Test (Un-witnessed) ☐ Type Test (Un-witnessed) ☐ Vibration Test (Un-witnessed) ☐ Other

☐ Routine Test (Witnessed) ☐ Type Test (Witnessed) ☐ Noise Level Test (Un-witnessed)

DOCUMENTATION REQUIRED:

☐ Data Sheet ☐ Drawing ☐ Performance Curves ☐ Other

