



# LACKTHERM® 1320 F

<b>PRODUCT DESCRIPTION:</b>	Protective varnish based on air-dried synthetic resin.	
<b>PROPERTIES:</b>	Protection of machined metal parts.	
<b>INDICATION OF USE:</b>	Shafts, rotors and stators.	
<b>APPLICATION SYSTEM:</b>	Pistol or Brush.	
<b>CHARACTERISTICS:</b>	<b>Code:</b>	10001662 (20L) 10001663 (0,9L) 10001664 (5L)
	<b>Appearance / Color:</b>	Blue
	<b>Viscosity CF4:</b> 25°C (ASTM D1200/94)	20 – 30"
	<b>Specific weight:</b> (ASTM D1475/98)	0,92 ± 0,02 g/cm³
	<b>Solids by Weight:</b> (ASTM D2697/03)	12± 2%
	<b>Thermal Class:</b> (DIN 46452/77)	F (155°C)
	<b>Viscosity Reducer:</b>	Diluent Alq. 1021. If necessary, the product is ready for use
	<b>Healing:</b>	Air drying
	<b>Diluent:</b>	Diluent Alq. 1021
	<b>Recommended Thickness:</b>	<b>Dry</b> 12 to 18µm
	<b>Emergency form:</b>	UN 1263
	<b>Expiration date:</b>	12 months
<b>RECOMMENDATIONS:</b>	Store in a cool place, away from ignition points; Keep the packaging closed after partial use; The application tank must be kept closed after use; Use in a place with good ventilation.	
<b>SAFETY PRECAUTIONS:</b>	<p>Handling must be carried out away from flames, sparks or excessive heat and in ventilated places as it is a flammable product. Make sure that the electrical installations are perfect and that they do not cause sparks.</p> <p>When using this product, always use PPE's: safety glasses, PVC gloves, apron and mask with filters against organic vapors. Storage must be in ventilated places, protected from weathering.</p> <p>Do not smoke in the work area.</p> <p>In case of fire, use CO2 or chemical powder extinguishers. Use water in the form of fog, except in energized equipment.</p> <p>Skin contact causes irritation. Do not use thinner to clean the skin, hands and body parts. To clean your hands, use alcohol, then wash with water and cleaning paste. Use protective skin replenishing cream.</p> <p>If ingested, induce vomiting only if the victim is conscious, in case of contact with eyes, rinse with plenty of water. If symptoms of poisoning occur when inhaling solvent vapors, immediately remove the person to a ventilated area. In the event of accidents, provide first aid and call a doctor immediately.</p> <p>Keep the packaging in a cool place, away from ignition points. Keep the package closed after partial use. The application tank must be kept closed after use. Use in a place with good ventilation.</p>	
<b>NOTE:</b>	All information mentioned in this technical bulletin is based on our experiences and knowledge, however, as we have no control over the use of our products, no warranty - expressed or implied, is given or suggested regarding this information. We therefore do not assume any responsibility for performance, performance or any material or personal damages resulting from the incorrect use of the information provided.	