

WEG Low Voltage AC Drives Introduces CFW11 Frame H Variable Frequency Drive


The CFW11 Variable Frequency Drive Product Line Extension

WEG is pleased to introduce the CFW11 Frame H stand-alone drive with ratings up to 1000HP at 480 Volts AC. This extension of the CFW11 drive family offers WEG customers a continuous line of variable frequency drives from 1.5 through 1000 horsepower at 480 VAC. Sharing common features and options such as I/O and communication option cards, integral Soft PLC and free programming and diagnostic software, the CFW11 family of drives provides WEG customers all the benefits of a flexible and easy to use product line that meets all of their needs for variable speed AC motor control.

Features

- Stand-alone AC Variable Frequency Drive with ratings up to 1000HP at 480 Volts AC
- Extends the CFW11 Product Line in a single stand-alone drive package, not modular!
- Compatible with all standard and optional features of the CFW11 Product Family
- Integral Soft PLC for local logic control saves the cost of adding an external controller

CFW11 Drives Lineup



CFW11 Ratings

- CFW11 Frame H is available in ratings up to 1141 Amps at 460 Vac and up to 804 Amps at 575 Vac
- Available with all options and accessories of the CFW11 product family beginning July 2016.



CFW11 Frame H Variable Frequency Drive

CFW11 Drives Frame H Pricing

480VAC


ND / VT		HD / CT		Catalog Number	Dimensions (in.) HxWxD	Approx. Weight (lbs.)	Includes Loose Line Reactor (UL Listed, IP00 Open Style) ¹				List Price (Multiplier V1)
Motor HP	Drive Amps	Motor HP	Drive Amps				WEG Line Reactor P/N	Dimensions (in.) HxWxD/EA	Weight (lbs)/EA	Qty Included	
700	795	550	637	CFW110795T40YZ-LR	55.7 x 27.1 x 16.6	470	WKDRULL8H	12.3 x 15.5 x 13.5	125	2	\$66,157
750	877	600	715	CFW110877T40YZ-LR	55.7 x 27.1 x 16.6	470	WKDRULL8H	12.3 x 15.5 x 13.5	125	2	\$74,135
950	1062	750	855	CFW111062T40YZ-LR	55.7 x 27.1 x 16.6	486	WKDRULS3H	12.61 x 15.25 x 16.5	190	2	\$92,842
1000	1141	800	943	CFW111141T40YZ-LR	55.7 x 27.1 x 16.6	486	WKDRULS3H	12.61 x 15.25 x 16.5	190	2	\$105,623

575VAC

ND / VT		HD / CT		Catalog Number	Dimensions (in.) HxWxD	Approx. Weight (lbs.)	Includes Loose Line Reactor (UL Listed, IP00 Open Style) ¹				List Price (Multiplier V1)
Motor HP	Drive Amps	Motor HP	Drive Amps				WEG Line Reactor P/N	Dimensions (in.) HxWxD/EA	Weight (lbs)/EA	Qty Included	
600	584	500	504	CFW110584T60YZ-LR	55.7 x 27.1 x 16.6	441	WKDRULS50H	12.5 x 17 x 15	195	1	\$78,880
650	625	600	540	CFW110625T60YZ-LR	55.7 x 27.1 x 16.6	441	WKDRULS50H	12.5 x 17 x 15	195	1	\$85,780
800	758	650	614	CFW110758T60YZ-LR	55.7 x 27.1 x 16.6	470	WKDRULS43L	12.5 x 15.5 x 14	175	2	\$102,734
900	804	750	682	CFW110804T60YZ-LR	55.7 x 27.1 x 16.6	470	WKDRULS43L	12.5 x 15.5 x 14	175	2	\$114,957

Note:

1) AC Line Reactors are supplied with the CFW11 Frame H Drive providing 3% total impedance to AC supply network. The reactors are open style (IP00) and are shipped loose per the quantities listed above.



CFW11 Frame H Drive Module



Transforming Energy into Solutions www.weg.net/us

For more information please contact WEG Electric Corp.
1-800-ASK-4WEG | www.weg.net/us