

POLITHERM 27 R TX GRAY W RAL 7032 BR

PRODUCT: 15370144

DESCRIPTION / USES: Metallic parts coating for outdoor use.

CHARACTERISTICS:

Resin: Polyester
Specific gravity: 1,69 ± 0,10 g/cm³
Stability: 06 month (max. 30°C)
Observations: Free of heavy metals and other substances provided for in Directive 2015/863 EU of 03/31/2015 (RoHS).

APPLICATION CHARACTERISTICS:

Surface: Ferrous and non-ferrous
Surface preparation: Ferrous : Phosphatization
 Non-ferrous: Chromatization or phosphatization*
Cure conditions: 10 minutes at 180 °C**
Thickness: 70 – 90 µm
Application system: Electrostatic gun

AFTER CURE CHARACTERISTICS:***

TEST	METHOD	SPECIFICATION
ADHESION	WPS-3905	: GR0
GLOSS @ 60°	WPS-3854	: Visual std
IMPACT (REVERSE)	WPS-4130	: Min 50 kg X cm
FLEXIBILITY (CONIC MANDREL)	WPS-4856	: Max 3 mm

CHEMICAL RESISTANCE ***

Salt spray: : Min. 500 h (ASTM B117 – 03)
Humidity: : Min. 1000 h (35°C)

* For non-ferrous metals phosphatizing, please contact our technical service.

** After stabilization on correct temperature (metal temperature).

*** The tests were conducted on degreased steel panels in accordance with the cure and thickness specifications. The results may vary, depending on the surface characteristics. For chemical resistance testing, panels were degreased and treated with tricationic phosphat.

IMPORTANT: This coating, when properly applied and cured is suitable for the use of adhesives and sealants. However, because of the different products on the market, it requires prior testing by the user in order to select the adhesive and / or sealant appropriate.

If is not possible the use of the product according to the directions given above we ask you to contact our technical service.

STORAGE: Fresh, dry and covered place.