

W-ACQUA 800 COLOR



Product Description:

Water-based base coat formulated on the basis of special aliphatic resins, ensuring good drying, adherence, low odor, low VOC (volatile organic compounds) and excellent color fidelity. Product suitable for partial and general retouching. Always apply the entire preparation system and properly degrease the surface before applying Base Coat W-ACQUA.



VOC:

The EU limit value for this product in ready-to-use form is max. 420 g/liter of VOC. The VOC rating for this product in ready-to-use form is max. 413 g/liter.



Homogenize:

With *MOVE* technology, just shake the package before use, eliminating the need for machine homogenization



Mixing Ratio:

One-component product (1K), does not require a catalyst (comp. B)



Dilution:

Application viscosity: 13 – 17 seconds CF04
20% dilution is recommended
- W-ACQUA Normal Thinner
- Fast W-ACQUA Thinner



Application:

-**Pistol Types:** Gravity; Conventional and HVLP.
-**Nozzle:** 1.3-1.4 mm
-**Application Pressure:** 1.2 -1.5 Bar (HVLP 0.7 Bar max)



Coats:

- **Solid colors (2 coats):** 2 single coats.
- **Metallic colors (2-3 coats):** Full coat, Intermediate coat and Powdered coat.



Flash Off & Drying:

Use air circulation and heat to accelerate drying.
DryJet / Venture assistance.



Recommendations:

-Apply the entire WEG system (pastes, wash primers, primers, degreasers and varnishes)
-Sand the primer well and degrease properly before painting;

For more information, consult the technical department of WEG Coatings:

PAUMAR S.A. - IND. E COM. - GRUPO WEG : Mauá - SP – Phone +55 (11) 4547-6100/ Guaramirim - SC – Phone+55 (47) 3276-4000 / Cabo de Santo Agostinho - PE - Phone +55 (81) 3512-3000 / PULVERLUX : Buenos Aires - Argentina - Phone: +54 (11) 4299-8000