

POLITHERM 24 R SM WHITE 64114 UM

PRODUCT: 15371191

DESCRIPTION / USES: Epoxy powder coating for indoor use on metallic parts.

ATTENTION: This product is sensitive to variations on the cure schedule. Color and/or gloss can change if the temperature in the parts differs from the specified in the technical bulletin.

CHARACTERISTICS:

Resin:	Epoxy
Specific gravity:	1,56 ± 0,10 g/cm ³
Stability:	6 months (máx. 30°C)
Observations:	Free of heavy metals and other substances provided for in Directive 2015/863 EU of 03/31/2015 (RoHS).

APPLICATION CHARACTERISTICS:

Surface:	Ferrous and non-ferrous
Surface preparation:	Ferrous: Phosphatization Non-ferrous: Chromatization or phosphatization*
Cure conditions:	10 minutes at 200 °C**
Thickness:	70 – 90 µm
Application system:	Electrostatic gun

AFTER CURE CHARACTERISTICS*:**

TEST	METHOD	SPECIFICATION
ADHESION	WPS-3905	: GR0
GLOSS at 60°	WPS-3854	: 5 ± 3 UB
IMPACT (REVERSE)	WPS-4130	: Minimum 50 kg X cm
FLEXIBILITY (CONIC MANDREL)	WPS-4856	: Maximum 3 mm

CHEMICAL RESISTANCE ***

Salt spray:	: Minimum 500 h (ASTM B117 – 03)
Humidity:	: Minimum 1000 h (35°C)

* For non-ferrous metals phosphatizing, please contact our technical service.

** After stabilization on correct temperature (metal temperature).

*** The tests were conducted on degreased steel panels in accordance with the cure and thickness specifications. The figures may be change, depending on the surface characteristics. For chemical resistance tests the panels were degreased and treated with tricationic phosphat.

IMPORTANT: If is not possible the use of the product according to the directions given above we ask you to contact our technical service.

STORAGE: Fresh, dry and covered place.