

Product name W-POXI CVA 31 1 R WHITE MBB 9004 Code 11910817
COMPONENT A
Last revision: 22.12.2016 Page: 1 of 14



1. PRODUCT AND COMPANY IDENTIFICATION

Product name : W-POXI CVA 31 1 R WHITE MBB 9004 COMPONENT A
Code : 11910817
Main recommended uses : Coating for industrial sector
Address : Rodovia BR 280 - km 50
CEP 89270-000, Guaramirim - SC

Telephone : +55 47 3276-4000
Emergency telephone : 0800 720 8000
number
E-mail / site : tintas@weg.net | www.weg.net

2. HAZARD IDENTIFICATION

Mixture classification

Flammable liquids : Category 3
Acute toxicity (Ingestion) : Category 5
Acute toxicity (Inhalation) : Category 5
Acute toxicity (Dermal) : Category 5
Skin Corrosion/irritation : Category 2
Skin sensitization : Category 1
Specific target organ toxicity - : Category 1
Repeated exposure

Classification according to NBR 14725-2/2009

Labelling Elements



Warning phrase : Danger

Hazard phrases : H226 Flammable liquid and vapour.
H303 May be harmful if swallowed.
H333 May be harmful if inhaled.
H313 May be harmful in contact with skin.
H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H372 Causes damage to organs through prolonged or repeated exposure.

Caution Phrases :

Prevention:

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P233 Keep container tightly closed.

P240 Ground/bond container and receiving equipment.

Reaction:

P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.

P304+P312 IF INHALED: Call a POISON CENTER or doctor/physician if you feel unwell.

P314 Get Medical advice/attention if you feel unwell.

P333+P313 If skin irritation or a rash occurs: Get medical advice/attention.

P362+P364 Take off contaminated clothing and wash it before reuse.

P370+P378 In case of fire: Use as chapter 5 of MSDS to extinguish.

Storage:

P403+P235 Store in a well ventilated place. Keep cool.

Treatment and disposal of waste:

P501 Dispose of contents/container as chapter 13 of the MSDS.

Other hazard :

Can cause allergic reactions on the skin.
When heated above its flash point, this material will release toxic vapors and flames, and can burn in open area if exposed to an ignition source.

3. COMPOSITION AND INFORMATION ABOUT THE INGREDIENTS

Product type: : Mixture

Ingredients that contribute to danger:

Product name	CAS No.	Risck classification	Concentration [%]
SOLVENT XYLENE	1330-20-7	Flammable liquids , Category 3 Acute toxicity Dermal, Category 4 Acute toxicity Inhalation, Category 4 Skin Corrosion/irritation , Category 2	>= 5 - < 10
ADDITIVE THINNER REACTIVE	68609-97-2	Skin Corrosion/irritation , Category 2 Skin sensitization , Category 1	>= 1 - < 5
SOLVENT BUTANOL	71-36-3	Acute toxicity Ingestion, Category 4 Skin Corrosion/irritation , Category 2 Serious eye damage/eye irritation , Category 2A Specific target organ toxicity - Single exposure , Category 3 Specific target organ toxicity - Repeated exposure , Category 1 Flammable liquids , Category 3	>= 1 - < 5

4. FIRST AID MEASURES

Inhalation : Take the victim to fresh air, keeping them rested and warm. If breathing is irregular or has stopped, apply artificial respiration. Do not give anything orally. Seek medical assistance immediately, bringing the product label whenever

possible.

- Contact with the skin** : Remove the product with vegetal oil (cooking oil) and then wash the skin thoroughly with plenty of water. Do not use solvents or thinners. Seek medical attention in case of any irritation or other symptoms.
- Contact with the eyes** : Remove contact lenses, if wearing any. Flush the eyes with running water for at least 15 minutes, holding the eyelids apart. Seek medical assistance immediately, bringing the product label with you.
- Ingestion** : Do not provoke vomiting. Consult with a doctor immediately.
- Most important symptoms and effects, both acute and delayed** : Headaches, dizziness, fatigue and in extreme cases, loss of consciousness.
- Notes for the doctor** : Treat symptomatically. Do not induce vomiting because of risk of aspiration of gastric contents into the lungs. Gastric lavage is recommended when the patient ingests large quantities, more than 5ml of the substance in its pure form. The toxic potential of the quantity consumed must be evaluated in relation to the risk of aspiration during gastric lavage. Activated coal in solution could be useful. However, in some cases the coal induces vomiting.

5. FIRE-FIGHTING MEASURES

- Suitable extinguishing methods** : Water in mist form
Carbon dioxide (CO₂)
Foam alcohol resistant
Dry chemical powder
- Extinguishing methods not recommended** : Direct water jet.
- Specific dangers** : Flammable liquid and vapour. Dangerous when exposed to heat or ignition source. Exposed packaging to the fire may rupture due to the increased pressure with risk of a subsequent explosion. The vapours are heavier than the air and spread close to the ground and it can move to the ignition source and provoke fire or backdraft of the flames. Avoid the accumulation of vapours in depressions on the ground, manholes, basement etc. The vapours and/or the particles finely divided (spray) may form explosive mixtures with the air. In case of burning of the product, it forms carbon and nitrogen compounds. The inhalation of these subproducts may cause damage to health.
- Protective measures of the fire fighting team.** : Use recommended personal protective equipment: face mask with OV filter and protective goggles.
- Specific methods** : Evacuate and isolate the area. Approach from fire with wind at

WEG TINTAS LTDA CNPJ 12.006.058/0001-21

Matriz: Rodovia BR 280, km 50 – fone (+55) (47) 3276-4000 – fax: (+55) (47) 3276-5500- CEP 89270-000 – Guaramirim – SC.
 PAUMAR S.A INDÚSTRIA E COMÉRCIO – CNPJ 60.621.141/0001-53

Rua Dr. Ulysses Guimarães, 918 - Fone: +55 (11) 4547-6100 – CEP 09372-050 - Mauá – SP
 EMERGÊNCIA: (+55) 0800 720 8000 - E-mail: tintas@weg.net - www.weg.net

your back. Fight the fire to a secure distance. Remove the packaging of the product from the fire area if this can be made with safety. Chill sideways with water in form of fog all the closed packaging near the fire. Avoid that the resulting water from fire fighting reaches drains or waterways. Use dikes to contain this water and eliminate it according to environmental regulations.

6. SPILL / LEAK CONTROL PROCEDURES

Personal precautions, protective equipment and emergency procedures

For the emergency service staff : If specialized clothing is needed to combat the leak/spillage, Section 8 should be consulted. All precautions described in the previous section must be followed.

For staff who are not part of the emergency services : No action should be taken that may generate danger to people without adequate training and qualifications. Understand the dangers of leaked/spilled products. Use appropriate personal protective equipment - see section 8. Evacuate surrounding areas. Isolate area and keep onlookers away. Do not touch or walk through spilled material. Eliminate all sources of ignition. Avoid breathing vapor or mist. Provide adequate ventilation if possible. Wear appropriate respiratory mask when ventilation is inadequate. In accordance with characteristics of the location and/or area and in relation to the amount of spilled/leaked product, additional emergency measures may be taken under the supervision of a trained professional.

Environmental precautions : Prevent the product or the water used in the service reaches waterways, channels, drains, or galleries. In case of significant spill, retain spilled liquid with inert material such as sand or earth. In appropriate, use absorbent materials such as sawdust, rags, vermiculites, etc.

Methods and materials for containment and cleaning

Large spills / leaks : Understand the dangers of leaked/spilled products. Approaching the site with the wind from behind. Stop leak if this can be done safely. Prevent from entering holes / depressions in the floor. If this happens to provide ventilation. Confine the spill in a dike away from the leak point for later disposal. Remove local packaging from the spills site. Use anti-sparking tools and explosion-proof equipment to collect the product. All equipment used when handling the product must be electrically grounded. Soak up with an inert dry material (sand, vermiculite) placing the same in a suitable container for later disposal - see chapter 13.

Small spills / leaks : Stop the leak if this can be done safely. Prevent from entering holes / depressions in the floor. Cover up spillage in a tarp to prevent the spread by wind or rain. Use antifaiscantes tools and explosion-proof equipment properly grounded to collect the product. Place the material collected in dry, clean and properly identified containers. Cap the container loosened so removing them from the spill site. Avoid formation of dust. Remove the packaging from the spill site. If there is product disposal need refer to chapter 13

Contain and collect the material of the leak with absorbent materials and non-combustible, such as sand, earth, vermiculite, calcined diatomite, etc. in a waste container in accordance with local regulations.

7. HANDLING AND STORAGE

Precautions for safe handling

Instructions for safe treatment : Use individual protective equipment. Emergency showers and eye wash basins must be installed in locations of use and storage.

Precautions for safe handling : Avoid contact with eyes, skin and clothes. Do not re-use packaging. Do not eat, drink or smoke during use. Do not handle the product before reading and understanding all safety precautions.

Fire protection : Only use in well-ventilated locations, to prevent accumulation of vapors in explosive concentrations. All conductive elements of the system, in contact with the product, must be electrically grounded. Keep away from heat and sources of ignition. Tools that do not produce sparks should be used. Do not smoke.

Storage conditions

Substances to be avoid : Keep away from oxidising agents, strong acid solutions and strong alkaline solutions.

Storage conditions : The electrical installation must comply with NEC (National Electrical Code) or IEC (International Electrical Commission) standards and/or those of the ABNT (Brazilian Association of Technical Standards). The floor of the storage area must be impermeable, non-combustible and must have ditches that allow run off into the containment reservoir. Storage tanks must be surrounded by embankments and have drains in case of leakage.

Appropriate storage conditions : Store the material in covered, dry, well ventilated and identified areas. Keep out of direct sunlight. Store in a closed container.

Product name W-POXI CVA 31 1 R WHITE MBB 9004 Code 11910817
 COMPONENT A
 Last revision: 22.12.2016 Page: 7 of 14



Inappropriate storage conditions : Exposed to elevated temperatures, sun and rain. Close to oxidizing agents. Close to food. Close to sources of heat and ignition.

Materials to avoid : Do not store with explosive materials, flammable and/or toxic gases, oxidizing, corrosive substances, or materials that may generate spontaneous combustion.

Secure packaging materials

Recommended packaging materials : Amber type glass.
Metal packaging

Packaging materials to be avoided : Certain plastic materials

8. EXPOSURE CONTROL – PERSONAL PROTECTION

The information in this chapter contains general guidelines. Chapter 1 should be consulted for any information on the recommended use of this product in different scenarios of exposure.

Engineering control measures : Preferably use the product in adequate application cabin. In case it is not possible, provide exhaustion/ventilation enough to keep the concentration of the agents indicated in this section under the limits of tolerance (L.T.), otherwise, use adequate respiratory protection equipment. The engineering controls should keep the concentrations of gas/vapour under the limit of LEL - Lower Explosive Limit (see section 9). Use equipment explosion proof.

Control parameters

Occupational Exposure Limits

Name	CAS No.	TLV/TWA	TLV/STEL	TLV/TETO	Source
SOLVENT XYLENE	1330-20-7	78 ppm 340 mg/m ³ 100 ppm 434 mg/m ³	150 ppm 651 mg/m ³		NR15 ACGIH
ADDITIVE THINNER REACTIVE	68609-97-2				ACGIH
SOLVENT BUTANOL	71-36-3	20 ppm 40 ppm			ACGIH NR15

*PPM - parts of vapour or gas per million of parts of contaminated air

**MG/m³ - milligrams per cubic meter of air.

Personal protective equipment required

Product name W-POXI CVA 31 1 R WHITE MBB 9004 Code 11910817
 COMPONENT A
 Last revision: 22.12.2016 Page: 8 of 14



- Respiratory protection** : In case of the concentrations are above the indicated tolerance limits, the use of appropriated mask is necessary for this goal (half-face mask or full face mask with filter to organic vapors and acid gases).
- Hand protection** : Use nitrilic gloves associated with the use of the adequate protection cream
- Eye protection** : Use hermetic goggles to protect against liquid splashes.
- Body and skin protection** : It is recommended the use of apron barber type to protecting upper limbs, trunk and lower limbs in case of splash. In case of risk of static electricity generation the cloth should be antistatic, includin the apron.

9. PHYSICAL AND CHEMICAL PROPERTIES

- Form** : Liquid
- State of matter** : Liquid
- Color** : White
- Odour** : Distinctive
- Odour limit** : Not applicable
- pH** : Not applicable
- Melting point** : Data not available.
- Boiling point** : Data not available.
- Flash Point (Open cup)** : 28 °C
- Evaporation rate** : Data not available.
- Inflammation point** : Method: Data not available.
- Upper explosive limit** :
Data not available.
- Lower explosive limit** :
Data not available.
- Vapor pressure** : Data not available.
- Density** : 1,15 - 1,35 g/cm³
- Solubility(ies)** : Water-insoluble
- N-octano /water partition coefficient** : Data not available.
- Auto flammability** : Data not available.

Product name W-POXI CVA 31 1 R WHITE MBB 9004 Code 11910817
 COMPONENT A
 Last revision: 22.12.2016 Page: 9 of 14



Cinematic viscosity (25°C) : 85 - 95 UK
Vapor density : Data not available.

10. STABILITY AND REACTIVITY

Reactivity : Presents no reactivity at room temperature and under normal conditions of use.

Chemical stability : Stable at room temperature and under normal conditions of use. Unstable at temperatures above the flash point.

Possibility of dangerous reactions : Presents no reactivity at room temperature and under normal conditions of use.
None when the product is stored, applied and processed correctly.

Need to add additives and inhibitors : Not necessary.

Conditions to avoid : Extreme heat and open flame.

Incompatible materials : Do not store with explosive materials, flammable and/or toxic gases, oxidizing, corrosive substances, or materials that may generate spontaneous combustion.
Plastic materials soluble in Xylene.

Dangerous products of decomposition : Produces noxious gases such as carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x).

11. TOXICOLOGICAL INFORMATION

Components SOLVENT XYLENE

Acute toxicity by oral use	: Test species DL50 Observations	Rat 4.300 mg/kg
Acute toxicity by inhalation	: Test species DL50 Observations	Rat 21,7 mg/l
Acute toxicity by cutaneous use	: Test species DL50 Observations	Rabbit > 1.700 mg/kg Data not available.
Acute toxicity (other methods of	: Test species DL50	Data not available.

MATERIAL SAFETY DATA SHEET - MSDS

Product name W-POXI CVA 31 1 R WHITE MBB 9004 Code 11910817
 COMPONENT A
 Last revision: 22.12.2016 Page: 10 of 14



administration) LC50
 Non-standard unit value

Corrosion/irritation of skin : Category 2

Serious eye damage/eye irritation : Data not available.

Respiratory or dermal sensitivity : Category 1

Mutageneses : Data not available.

Carcinogenicity : Data not available.

Toxic effects for reproduction : Category 1C

Specific target organ toxicity (STOT) - single exposure : Data not available.

Specific target organ toxicity (STOT) - repeat exposure : Data not available.

ADDITIVE THINNER REACTIVE

Acute toxicity by oral use : Test species Rat
 DL50 17,100 mg/kg
 Observations

Acute toxicity by inhalation : Test species Rat
 DL50
 Observations Data not available.

Acute toxicity by cutaneous use : Test species Rabbit
 DL50
 Observations Data not available.

Acute toxicity (other methods of administration) : Test species Data not available.
 DL50
 LC50
 Non-standard unit value

Corrosion/irritation of skin : Category 2

Serious eye damage/eye irritation : Data not available.

Respiratory or dermal sensitivity : Category 1

Mutageneses : Data not available.

Carcinogenicity : Data not available.

Toxic effects for : Data not available.

WEG TINTAS LTDA CNPJ 12.006.058/0001-21

Matriz: Rodovia BR 280, km 50 – fone (+55) (47) 3276-4000 – fax: (+55) (47) 3276-5500- CEP 89270-000 – Guaramirim – SC.
 PAUMAR S.A INDÚSTRIA E COMÉRCIO – CNPJ 60.621.141/0001-53

Rua Dr. Ulysses Guimarães, 918 - Fone: +55 (11) 4547-6100 – CEP 09372-050 - Mauá – SP
 EMERGÊNCIA: (+55) 0800 720 8000 - E-mail: tintas@weg.net - www.weg.net

Product name W-POXI CVA 31 1 R WHITE MBB 9004 Code 11910817
 COMPONENT A
 Last revision: 22.12.2016 Page: 11 of 14

**reproduction**

Specific target organ toxicity (STOT) - single exposure : Data not available.

Specific target organ toxicity (STOT) - repeat exposure : Data not available.

SOLVENT BUTANOL

Acute toxicity by oral use : Test species Rat
DL50 790 mg/kg
Observations

Acute toxicity by inhalation : Test species Rat
DL50
Observations Data not available.

Acute toxicity by cutaneous use : Test species Rabbit
DL50 3.400 mg/kg
Observations

Acute toxicity (other methods of administration) : Test species Data not available.
DL50
LC50
Non-standard unit value

Corrosion/irritation of skin : Category 2

Serious eye damage/eye irritation : Category 2A

Respiratory or dermal sensitivity : Data not available.

Mutageneses : Data not available.

Carcinogenicity : Data not available.

Toxic effects for reproduction : Data not available.

Specific target organ toxicity (STOT) - single exposure : Passengers effects on organ target . These are effects that alter human function for a short period of exposure

Specific target organ toxicity (STOT) - repeat exposure : Substance which produces significant toxicity in humans, or on the basis of evidence from studies on experimental animals can probably provide a potential to produce significant toxicity in humans by repeated exposure

Not classified in terms of toxicity based on the data available.

12. ECOLOGICAL INFORMATION

- Stability in soil** : The product easily infiltrates into the soil
- Other toxicological observations** : Data not available.
- Ecotoxicity** : Contaminates the ground water.
 Detrimental to the fauna
 Detrimental to the flora.

13. DIOSPOSAL AND TREATMENT CONSIDERATIONS

Recommended methods for final disposal

- Product** : Class I Waste - Dispose of in industrial landfill or a facility authorized for recycling in accordance with federal, state or local regulations
- Waste** : Class I Waste - Dispose of in industrial landfill or a facility authorized for recycling in accordance with federal, state or local regulations
- Used packaging** : Clean packaging should be sent for recycling. Packaging with class I waste should be disposed of in industrial landfill or a facility authorized for recycling in accordance with federal, state or local regulations.

14. TRANSPORTATION INFORMATION

- Land**
- ONU** : 1263
- Class of risk** : 3
- Risk number** : 30
- Packaging group** : III
- Name** Tinta
- Shipping**
- ONU** : 1263
- Class of risk** : 3
- Packaging group** : III
- EmS** F-E
- MFAG** 310

Appropriate name for dispatch Tinta

Air transport ONU : 1263
Class of risk : 3
Packaging group : III
Appropriate name for dispatch Tinta

15. REGULATORY INFORMATION

This MSDS (Material Safety Data Sheet) was generated according to the criteria of NBR 14725 (Brazilian standard that defines the GHS).

Specific Regulations for the Chemical Product.	<p>Federal Decree No. 2657, July 3rd , 1998.</p> <p>Law No. 12305, August 2nd 2010 (Solid Waste National Policy).</p> <p>Decree No. 7404, December 23rd , 2010.</p> <p>Ordinance No. 229, May 24th, 2011 - Changes to Regulatory Standard No. 26.</p> <p>ABNT NBR 14725: 2012.</p>
--	--

16. ADDITIONAL INFORMATION

Acronyms Used:

Legenda:

CAS	Chemical Abstract Service
VO	Organic Vapors
NEC	National Eletrical code/Código Nacional de Eletricidade
IEC:	International Eletrical Commision
ABNT	Brazilian Association of Technical Standards
ACGIH	American Conference of Governmental Industrial Hygienists
TLV	Threshold Limit Values
TLV/TWA	Time Weighted Average

MATERIAL SAFETY DATA SHEET - MSDS

Product name W-POXI CVA 31 1 R WHITE MBB 9004 Code 11910817
 COMPONENT A
 Last revision: 22.12.2016 Page: 14 of 14



TLV/STEL	Short Term Exposure Limit
TLC/C:	Tolerance Limit - Ceiling Value
EPI:	Individual Protective Equipment
CA	Approval Certificate
PPRA	Environmental Risk Prevention Program
NR	Regulatory Standard
NFPA	National Fire Protection Agency
mmHg	Millimeters of mercury - pressure unit
DL50	Lethal Dose average
CL50	Lethal Concentration average
ppm	Parts per million
N.d	Not available
A+B	Viscosity of the mixture of component A + component B

Important information, but not specifically described in the previous sections:
 This MSDS was prepared based on current knowledge about the handling of the product under normal conditions of use, according to the application specified on the packaging and recommended usage in Section 1 of this MSDS. Any other use of the product involving its combination with other materials, as well as forms of use different from those indicated, are the user's responsibility. The company advises that the handling of any chemical substance requires prior knowledge of its hazards by the user. In the workplace it is responsibility of the company user of the product to provide training of its employees and contractors about the possible risks arising from exposure to the chemical.
 We reserve the right to change the information contained in this document without prior notice, due to the improvement and continuous evolution of the product and technical knowledge.

Vertical lines in the left hand margin indicate changes from the current version