

Data Sheet



PRIMER UHT W-79

	Product Description	2K HS polyurethane primer. Features very fast drying and easy sanding. The product is easy to apply and has excellent leveling, filling power, and adhesion to metallic substrates. Suitable for general painting, partial painting, and repainting of motor vehicles in a short period of time.	
		Shelf life: 3 years	
	VOC / Yield	258 g/L	9 – 10,5 m ² /L 60 - 90 μm
	Mixing ratio	4 Parts of A 1 Part of B	
		Pot life 30 minutes	
	Hardener	Ambiente temperatura 25°C - Hardener UHT 5578 intermediary	
	Thinner	Temperature below de 15°C - Thinner 5860 below temperature Ambient temperature 25°C - Thinner 5870 intermediary Temperature above de 30°C - Thinner 5880 above temperature	
		Dilution 10 - 20%	
	Application viscosity	18 – 22s Cup FORD 4 25° C 77°F 21 – 25s Cup DIN 4 25° C 77°F	
	Application gun	1,8mm a 2,0mm	2 - 3 BAR 35 - 45 PSI
	Evaporation at 25°C 77°F	5 - 10 minutes	
	Number of passes	2 a 3 pass	1 pass = 20 a 30 micra
	Drying at 10°C 50°F	Touch 15 minutes Handling 40 minutes Sanding 50 minutes	
	Drying at 25°C 77°F	Touch 10 minutes Handling 30 minutes Sanding 40 minutes	
	Drying at 60°C 140°F	10 minutes	
	Short-wave infrared	10 minutes at 1 m	

- Perform a thorough degreasing to clean the part before repainting;
- Avoid excessive thickness;
- Cleaning application equipment with acrylic/polyurethane thinners;
- Wash-primer application is necessary for better product adhesion;
- Use hardener and thinner as recommended;
- Always use the complete range of WEG products and accessories.