



LACKTHERM® 1351 H

Code: 13937860

PRODUCT DESCRIPTION

Single-component impregnation varnish based on modified polyester, thermal class H, air-dried.

RECOMMENDED USE

Windings, stators and transformers.

PROPERTIES

Excellent flexibility.
Excellent dielectric properties.
Excellent mechanical properties.

APPLICATION SYSTEMS

Immersion
Brush
Spray Gun

CERTIFICATIONS AND APPROVALS

UL certified product.
Product in compliance with RoHS directive.

PACKAGING

Pail 20 L

CHARACTERISTICS

Color	LIGHT AMBER
Viscosity	30 - 45" CF4 (ASTM D1200/94)
Specific Gravity	0.88 +/- 0.02 g/cm ³ (ASTM D1475/98)
Solids by Weight	36+/-4 % (ASTM D2697/03)
Thermal Class	180 °C (DIN 46452/77)
Dielectric Strength	60 - 90 kV/mm (IEC 60464-2)
VOC content	230.48 g/l
Shelf Life	9 months

APPLICATION DATA

Component B	MONOCOMPONENT
Curing Time	30 - 60 min
Curing Temperature	50 - 80 °C
Touch Dry	6 min
Handle Dry	6 h
Thinner	DILUENT SL 12

RECOMMENDATIONS

Keep the package closed after partial use.
Use in a well-ventilated location.
Keep in a cool place, away from ignition points.
Keep the application tank closed after use.



SAFETY PRECAUTIONS

This product has been developed for industrial use and is intended to be handled by qualified professionals. Carefully read all the information contained in the Safety Data Sheet (SDS) available at: www.weg.net.

When handling this product, use the Personal Protective Equipment (PPE) as indicated in the product's SDS.

Empty packaging and materials with product residues must be disposed of in accordance with current legislation. Preserve the environment.

NOTE

The information contained in this technical bulletin is based on the experience and field knowledge acquired by the WEG technical team. If the product is used without prior consultation with WEG regarding its suitability for the intended application, the customer acknowledges that such use is at their sole responsibility. WEG does not assume any liability for the behavior, safety, suitability, or durability of the product.

Some of the information provided in this bulletin is based on estimates and may vary due to factors beyond the manufacturer's control. Therefore, WEG makes no guarantees and assumes no responsibility for yield, performance, or for any material or personal damages resulting from the improper use of the products or the information contained in this Technical Data Sheet.

The information contained in this document is subject to periodic changes without prior notice, in line with our policy of continuous improvement and development of products and services, aiming to deliver quality solutions that meet our customers' needs.
