



## W-POXI GNP 41

### PRODUCT DESCRIPTION

Two-component polyamine epoxy primer based on epoxy resin. Isocyanate-free product.

### RECOMMENDED USE

Recommended as an adhesion promoter for galvanized substrates, aluminum, degreased carbon steel, fiberglass, and stainless steel. This product replaces the use of LACKPOXI N2198.

### CERTIFICATIONS AND APPROVALS

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

### PACKAGING

|                    |                                                                                          |
|--------------------|------------------------------------------------------------------------------------------|
| <b>Component A</b> | 0.95 US gal Package containing 0.95 US gal<br>5.28 US gal Package containing 5.28 US gal |
| <b>Component B</b> | 0.95 US gal Package containing 0.95 US gal<br>0.95 US gal Package containing 5.28 US gal |

### CHARACTERISTICS

|                             |                                                                                                                                                                                |
|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Color</b>                | Green.<br>Red.                                                                                                                                                                 |
| <b>Gloss</b>                | Ultra-matte (0 - 15 UB) W-POXI GNP 415                                                                                                                                         |
| <b>Volume Solids</b>        | 25 ± 3% (ISO 3233)                                                                                                                                                             |
| <b>Shelf Life</b>           | 12 months                                                                                                                                                                      |
| <b>Dry Film Thickness</b>   | 0.8 mils - 1.2 mils                                                                                                                                                            |
| <b>Dry Heat Resistance</b>  | Maximum temperature 194 °F.<br>The product maintains its chemical properties up to a temperature of 194 °F, but from 140°F, color and gloss variations in the paint may occur. |
| <b>Theoretical Coverage</b> | 407.5 ft <sup>2</sup> /gal without dilution at a dry film thickness of 1.0 mils. Loss factors during application are not considered.                                           |

### DRYING

#### Drying

|                     | 50 °F     | 77 °F     | 95 °F     |
|---------------------|-----------|-----------|-----------|
| <b>Touch</b>        | 25 min    | 10 min    | 5 min     |
| <b>Manipulation</b> | 2 hours   | 1 hour    | 30 min    |
| <b>Final</b>        | 168 hours | 168 hours | 168 hours |

#### Recoat Drying

|                | 50 °F     | 77 °F     | 95 °F     |
|----------------|-----------|-----------|-----------|
| <b>Minimum</b> | 1 hour    | 30 min    | 20 min    |
| <b>Maximum</b> | 168 hours | 168 hours | 168 hours |

### SURFACE PREPARATION

#### Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The surface must be clean, dry, and free of contaminants. Completely remove oils, greases, and fats according to SSPC-SP1.

Remove accumulated dirt using a dry brush, clean dry cloth, compressed air blow, vacuum, or a combination of these. Remove soluble salts by washing with plenty of fresh water, preferably under low pressure (up to 5,000 psi), according to SSPC-SP12/NACE No. 5 standard.

#### Degreasing

Completely remove oils and greases by applying a degreasing product or according to the solvent

cleaning method. Whenever cleaning surfaces with cloths, replace them to avoid saturation. Do not use cotton waste or colored cloths.

#### Carbon Steel Surfaces

Hard surface layers (e.g., layers resulting from flame cutting) must be removed by grinding before starting abrasive blasting.

All welds must be inspected and, if necessary, repaired before completing abrasive blasting. Porosities, cavities, weld splatter, etc., must be repaired with proper mechanical treatment or welding repair. In other areas, round edges and sharp corners (r e 0.0787 in, ISO 8501-3).

#### Hot-Dip Galvanized Surfaces

Wash the substrate with running water to remove soluble salts resulting from the galvanizing process prior to abrasive blasting. Use a non-woven abrasive pad made of synthetic fibers bonded with resin impregnated with abrasive mineral.

It is recommended to apply the coating over surfaces blasted to Sa 1 (brush-off) according to ISO 8501-1 or SSPC-SP7 standards, using 20-40 mesh steel grit, ensuring the operation only produces a surface roughness between 0.4 and 1.0 mils and a uniform matte appearance (visual standard ISO 8501-1).

For light abrasive blasting (brush-off), hot-dip galvanized carbon steel plates should have a minimum thickness of 1/8 inch and a zinc coating of at least 2.4 mils.

For small areas, it is acceptable to first remove surface oil and grease with clean cloths soaked in Cleaning Thinner in accordance with SSPC-SP1.

Perform a "light sanding" using 100-grit sandpaper, preferably creating cross-hatch (horizontal and vertical) scratches. Clean the surface again with thinner-soaked cloths, changing them frequently. When cleaning with cloths, avoid using rags or colored fabrics.

Note: Hot-dip galvanized carbon steel intended for painting should not undergo passivation to avoid coating defects or failures.

#### Fiber Surfaces

Remove all dirt and grease from the surface using clean cloths soaked in Cleaning Solvent according to SSPC SP1. Avoid using rags or colored cloths. Proceed with a "light sanding" using 180-grit sandpaper to promote roughness. Whenever possible, make cross-hatch scratches (horizontal and vertical). Clean the surface again with cloths soaked in solvent, changing them frequently.

#### Over Primer

Respect the product recoat interval. If exceeded, perform light manual/mechanical sanding to break gloss and clean dust/residues for better adhesion between coats.

### APPLICATION PREPARATION

|                       |                                                                                                                                                                                                                                                                                                                                                                                                                           |
|-----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Mixing</b>         | Homogenize the content of each component using mechanical or pneumatic stirring (A and B). Ensure no sediment remains at the bottom of the container. Add component B to component A in the indicated mixing ratio under stirring until completely homogenized, respecting the mixing ratio.                                                                                                                              |
| <b>Mixing Ratio</b>   | By volume: 1 A x 1 B.                                                                                                                                                                                                                                                                                                                                                                                                     |
| <b>Thinner</b>        | Not applicable.                                                                                                                                                                                                                                                                                                                                                                                                           |
| <b>Dilution</b>       | Ready to use.                                                                                                                                                                                                                                                                                                                                                                                                             |
| <b>Notes</b>          | No dilution is required. Product ready to use. If necessary, consult the WEG Technical Department.                                                                                                                                                                                                                                                                                                                        |
| <b>Pot Life</b>       | 4 h<br><br>The shelf life of the mixture is reduced as the ambient temperature increases.<br><br>The pot-life test of the mixture is carried out according to ABNT NBR 15742; however, different volumes of paint prepared at once, combined with varying ambient and paint temperatures, will affect the mixture's shelf life, potentially resulting in outcomes different from those stated in this technical bulletin. |
| <b>Induction Time</b> | No induction time required.                                                                                                                                                                                                                                                                                                                                                                                               |



In very hot locations, we recommend consulting WEG's Technical Department.

## APPLICATION METHODS

|                                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
|------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Roller</b>                      | <p>Not recommended.</p> <p>For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <b>Brush</b>                       | <p>Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups).</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| <b>Cleaning of the equipments:</b> | <p>Not applicable.</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <b>Notes</b>                       | <p>The data presented serves as a guide and similar equipment may be used.</p> <p>Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination.</p> <p>Do not allow catalyzed product to remain in contact with application equipment, as at temperatures above the indicated "pot life", the paint will show variation in flow and will harden, making cleaning difficult.</p> <p>Before application, ensure that the equipment and respective components are clean and in optimal condition.</p> <p>After mixing two-component products, if there are application stops and the pot life has been exceeded (paint shows variation in flow), it can no longer be re-thinned for later application.</p> <p>In spray application, overlap each gun pass by 50%, finishing with a cross pass. This technique avoids uncovered or unprotected areas and ensures proper aesthetic finish.</p> <p>Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.</p> <p>Clean all equipment immediately after use.</p> <p>It is considered good practice to periodically wash the spraying equipment during the day. The cleaning frequency depends on the amount sprayed, temperature, and elapsed time, including all delays.</p> <p>For cleaning, use Epoxy Thinner 3005.</p> |

## APPLICATION PERFORMANCE

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Do not apply the product after the pot life has been exceeded.

As this is a primer, color variation between batches of this material may occur.

For optimal application properties, the paint temperature must be between 69.8°F - 80.6°F before mixing and application.

Before application, observe weather conditions: there must be no threat of rain or drizzle. Surface temperature must be at least 37.4°F above the dew point, and relative humidity should not exceed 85%. Adverse conditions may cause color variations and other characteristics. Consult WEG Technical Department.

We recommend painting only if the measured surface temperature is at least 5.4°F above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

Under adverse weather conditions in indoor and/or outdoor environments with high relative humidity, rain or drizzle, low or very low temperatures, and excessively high temperatures,



variations in color and other product characteristics may occur. Please consult WEG's Technical Department for more information.

## SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: [www.weg.net](http://www.weg.net).  
Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.  
Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.  
Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.  
Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

## NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.  
In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.  
Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.  
The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.