

## W-POXI ENG 069

<b>PRODUCT DESCRIPTION:</b>	Two-component conventional epoxy primer, zinc phosphate-based with corrosion-inhibiting pigmentation. Fast drying, excellent anti-corrosion protection, flexibility and hardness.
<b>RECOMMENDED USES:</b>	Used as primer and finishing with excellent adhesion and anti-corrosion protection on phosphatized or degreased carbon steel surfaces. Recommended for painting machinery, equipment, agricultural implements and metallic structures.
<b>CERTIFICATIONS AND APPROVAL:</b>	This product, when supplied to comply with the RoHs Directive (Restriction of Certain Hazardous Substances) has the letter R in its description.

PACKAGING:	Component	Content	Package	Unit of measurement
	Component A	20	20	L
	Component B	4	4	L

<b>CHARACTERISTICS:</b>	<b>Color:</b>	Gray		
	<b>Gloss:</b>	Ultra matte		
	<b>Volume solid:</b>	37 ± 3% (ISO 3233).		
	<b>Shelf-Life:</b>	12 months at 25°C - Component A		
	<b>Thickness per coat (dry):</b>	50 µm –60 µm		
	<b>Theoretical coverage:</b>	6,72 m <sup>2</sup> /l without dilution in the thickness of 55 µm dry. Without considering loss factors in application.		
	<b>Resistance to dry heat:</b>	Maximum temperature 120 °C . The product retains its physical and chemical properties up to the temperature of 120 °C however, variations in the coating color and gloss may occur from 60 °C (140°F).		
	<b>Drying:</b>			
		<b>10°C (50°F)</b>	<b>25°C (77°F)</b>	<b>35°C (95°F)</b>
	<b>Touch:</b>	1 hour	20 minutes	15 minutes
	<b>Handling:</b>	6 hours	3 hours	2 horas
	<b>Final:</b>	168 hours	168 hours	120 hours
	<b>Overcoating Drying:</b>			
		<b>10°C (50°F)</b>	<b>25°C (77°F)</b>	<b>35°C (95°F)</b>
	Min	30 minutes	20 minutes	10 minutes
	Max	24 hours	24 hours	24 hours

<b>SURFACE PREPARATION</b>	<p>The performance of this product is associated with the degree of surface preparation.</p> <p>The surface must be clean, dry and free of any contaminants. Completely remove oils, greases and fats, as described in the SSPC-SP 1 standard.</p> <p>Accumulated dirt must be removed using a dry brush and soluble salts must be removed by washing with high pressure fresh water.</p> <p><b>Surface treatment through Abrasive Blasting process</b></p> <p>We recommend painting on surfaces blasted to Sa 2½ or Sa 3 or according to SSPC SP10 or SSPC SP5. ISO 8501-1 visual standard.</p> <p>Evaluate the surface after blasting, observing the presence of surface defects revealed after treatment, adopting appropriate practices to minimize defects through grinding or filling.</p>
----------------------------	--

It is recommended a roughness profile between 20 and 40 µm.

### Treatment of Steel Carbon Surfaces

The surface must be clean, dry and free from contaminants. Completely remove oils, greases and grease using a degreasing product or according to the solvent cleaning method SSPC SP1. Wash with fresh water at high pressure.

### Maintenance and repair

**NOTE:** Observe the product overcoating interval to apply the next coat. In case the maximum overcoating interval has been exceeded, it is necessary to manually/mechanically sand the surface to break the gloss of the previous coat and clean the sanding residues so as to provide better adhesion between the coats.

For further information, consult WEG Technical Department.

### PREPARATION FOR APPLICATION

#### Mixture

Homogenize the contents of each component with mechanical or pneumatic stirring (A and B). Check there are no sediment settled at the bottom of the package. Add component B to component A, at the recommended proportion (volume), under stirring, until complete homogenization, observing the mixing ratio.

#### Mixing ratio (Volume)

5 A X 1 B.

#### Diluent

Not applicable

#### Dilution

No dilution required. Product ready for use.

#### Pot life of the mixture (25°C) (77°F)

4 h

#### Induction time (25°C)

Wait 5 minutes before application.

In hot areas, we recommend consulting WEG Technical Department.

### APPLICATION FORMS

The data below is a guide, and similar equipment may be used.

Changes in nozzle sizes and pressures may be necessary to improve spraying characteristics. Before application, check if the equipment and its components are clean and in best condition. Purge the compressed air line to prevent contamination of the coating.

After mixing two-component products, if there are stops in the application, and pot life is exceeded (the coating shows variation in fluidity) it can no longer be diluted for further application.

Recoat all sharp edges, cracks and weld beads with a brush to prevent premature failures in these areas.

#### Conventional gun:

Gun:	JGA 502/3 Devilbiss or equivalent
Fluid nozzle:	EX
Air cap:	704
Atomization pressure:	50 - 70 psi
Pressure in the tank:	5 - 15 psi

#### Airless Gun:

Use Airless:	Use at least pump 60: 1
Fluid pressure:	2000 – 3000 psi
Hose:	¼" internal diameter
Nozzle:	0,015" - 0,021"
Filter:	Mesh 60

Dilution:	Max. 5%
-----------	---------



**Brush:**

Only recommended for touch up small areas or stripe coat (screws, nuts, weld and sharp edges). Use a brush 75 to 100 mm wide for larger surfaces and 25 to 38 mm for touch up.

**Cleaning the equipment:**

Not applicable

**NOTE:**

For application with brush and/or roller, two or more passes may be necessary to obtain a uniform layer according to the recommended film thickness per coat.  
Do not leave catalyzed product in contact with the equipment used in the application, because the coating will vary in fluidity at temperatures above specified in the pot life and will cure faster, making the cleaning difficult.

Clean all equipment immediately after use.

**PERFORMANCE IN THE APPLICATION**

For a good performance of the product, we recommend following the directions below:

For application with brush and/or roller, two or more passes may be necessary to obtain a uniform layer according to the recommended film thickness per coat.  
In paintings carried out in front of the sea, if exposed to sea air, we recommend to wash with fresh water between coats eliminating settled impurities.

Do not apply the product after the pot life has expired.

We recommend coating only if the surface temperature is at least 3 °C (37,4°F) above the dew point temperature.

Variations in color, aspect and gloss (more noticeable in dark colors) may occur, as well as delay in curing and low coating performance, when applied during periods of high air relative humidity, rainy days, low temperatures or drying the coating outdoor.

The temperature of the substrate, the weather and environmental conditions during the application and during the curing of the product, and the thickness of the coat may interfere in the product drying time.

It should not be applied under adverse conditions, such as air relative humidity (RH) above 85%, as changes in color and appearance may occur.

Epoxy-based products are known by having excellent anti-corrosion properties and low resistance to sunlight exposure. In situations of exposure of the film to the weather, over time it will present a loss of gloss known as chalking and its shade will change as a consequence. Remember that even undergoing such chalking, the film anti-corrosion protection is not impaired.

On newly painted surfaces in direct contact with water during the curing process, localized stains may occur with changes in their color (more visible in dark colors), delay in curing and compromised product performance.

In coatings with variation in application method in the same job, the final aspect and gloss of the painted surfaces may show differences.

For further information, consult WEG Technical Department.

**COMPATIBILITY OF SYSTEMS AND MAINTENANCE REFINISHING**

To apply topcoat over the product, the overcoating interval should be observed. The surface must be dry and free of any contaminants.

For further information, consult WEG Technical Department.

**SAFETY PRECAUTIONS**

Product developed for industrial use intended for handling by qualified professionals.

Please read carefully all the information contained in the MSDS of this product, available at: [www.weg.net](http://www.weg.net).

Store in a covered, well-ventilated area. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists / vapors / aerosols generated during handling and / or application.

Wear protective gloves / protective clothing / eye protection / face protection.

Avoid release this product and its packaging, as well as materials used during handling and application in the environment.

**NOTE:**

The information contained in this technical datasheet is based upon the experience and knowledge acquired in the field by the technical team of WEG.

If using the product without previous inquiry to WEG Coating concerning its suitability for the customer's



intended purpose, the customer is aware that the use shall be its exclusive responsibility, WEG not being responsible for behavior, safety, suitability or durability of the product.

Some information contained in this datasheet are estimated, and can undergo variances arising from factors outside the manufacturer's control. Thus, WEG does not guarantee and does not assume any responsibility regarding the yield, performance or any other material or personal damage resulting from the incorrect use of the products concerned or the information contained in this Technical datasheet.

The information contained in this technical datasheet is subject to periodic modification, without prior notice, due to the policy of evolution and continuous improvement of our products and services, providing solutions with quality to satisfy our customers' requirements.

