



W-LACK CVP 12

PRODUCT DESCRIPTION

High-performance phenolated alkyd resin primer, normal drying. Contains zinc chromate corrosion-inhibiting pigments.

RECOMMENDED USE

Used as a primer for protection of carbon steel on machinery, equipment, and metal structures exposed to normal environments.

CERTIFICATIONS AND APPROVALS

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

PACKAGING

Single Component

5.28 US gal Package containing 5.28 US gal

CHARACTERISTICS

Color

Beige.
Gray.
Black.
Green.
Red Oxide.

Gloss

Semi-matte (30 - 60 UB) W-LACK CVP 123
Ultra-matte (0 - 15 UB) W-LACK CVP 125

Volume Solids

47 ± 5% (ISO 3233)

Shelf Life

12 months

Dry Film Thickness

1.2 mils - 1.6 mils

Dry Heat Resistance

Maximum temperature 140 °F.
Organic coatings can undergo changes in color, gloss, and adhesion when exposed to temperatures above 140 °F.

Theoretical Coverage

547.3 ft²/gal without dilution at a dry film thickness of 1.4 mils. Loss factors during application are not considered.

DRYING

Drying

77 °F

Touch

2 hours

Manipulation

24 hours

Final

72 hours

Recoat Drying

77 °F

Minimum

5 hours

Maximum

24 hours

SURFACE PREPARATION

Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The surface to be painted must be clean, dry, and free of impurities such as rust, dust, soluble salts, grease, oils, or other contaminants that may compromise product performance.

Abrasive Blasting

Abrasive treatment or phosphating as required by the substrate.



APPLICATION PREPARATION

Mixing	Homogenize the content manually, ensuring no pigment remains at the bottom of the container.
Thinner	DILUENT 1001
Dilution	Depending on the application method, dilute to a maximum of 25%.
Notes	The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.
Pot Life	Not relevant.

APPLICATION METHODS

Conventional Spray Gun	Spray gun: JGA 502 Devilbiss or equivalent Fluid nozzle: FX Air cap: 704.
Airless Spray Gun	Fluid pressure: 1200 - 2200 psi Hose: 1/4" inner diameter Nozzle: 0.013" - 0.017".
Roller	Use a short-haired, seamless wool or synthetic roller for epoxy paints.
Brush	Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups). Use a brush 3.0 to 3.94 inches wide for larger surfaces and 0.98 to 1.5 inches for touch-ups.
Cleaning of the equipments:	DILUENT 1001
Notes	The data presented serves as a guide and similar equipment may be used. Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination. Before application, ensure that the equipment and respective components are clean and in optimal condition. After mixing two-component products, if there are application stops and the pot life has been exceeded (paint shows variation in flow), it can no longer be re-thinned for later application. Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.

APPLICATION PERFORMANCE

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Light colors may require more than one coat to achieve uniform coverage.

Do not apply the product after the pot life has been exceeded.

For optimal application properties, the paint temperature must be between 69.8°F - 80.6°F before mixing and application.

We recommend painting only if the measured surface temperature is at least 5.4°F above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Must not be applied under adverse conditions, such as relative humidity (RH) above 85%, as color and appearance changes may occur.



Polyurethane systems (components A and B) are sensitive to relative humidity, which may cause defects in the dry film and reduction in pot life. After use, keep containers closed and protected.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

On freshly painted surfaces in direct contact with water during the curing process, localized staining with color change (more visible in darker colors), curing delay, and compromised product performance may occur.

Product not recommended for internal tank painting.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.