



W-POXI ENG 069

PRODUCT DESCRIPTION

Conventional two-component epoxy primer with zinc phosphate corrosion-inhibiting pigmentation. Fast-drying, excellent anticorrosive protection, flexibility, and hardness.

RECOMMENDED USE

Used as a primer and finish with excellent adhesion and anticorrosive protection on phosphated or degreased carbon steel surfaces. Recommended for painting machinery, equipment, agricultural implements, and metal structures.

CERTIFICATIONS AND APPROVALS

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

PACKAGING

Component A	5.28 US gal Package containing 5.28 US gal
Component B	1.06 US gal Package containing 1.06 US gal

CHARACTERISTICS

Color	Gray.
Gloss	Ultra-Matte
Volume Solids	37 ± 3% (ISO 3233)
Shelf Life	12 months
Dry Film Thickness	2.0 mils - 2.4 mils
Dry Heat Resistance	Maximum temperature 248 °F. The product maintains its chemical properties up to a temperature of 248 °F, but from 140°F, color and gloss variations in the paint may occur.
Theoretical Coverage	274.2 ft ² /gal without dilution at a dry film thickness of 2.2 mils. Loss factors during application are not considered.

DRYING

Drying

	50 °F	77 °F	95 °F
Touch	1 hour	20 min	15 min
Manipulation	6 hours	3 hours	2 hours
Final	168 hours	168 hours	168 hours

Recoat Drying

	50 °F	77 °F	95 °F
Minimum	30 min	20 min	10 min
Maximum	24 hours	24 hours	24 hours

SURFACE PREPARATION

Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The surface must be clean, dry, and free of contaminants. Completely remove oils, greases, and fats according to SSPC-SP1.

Accumulated dirt must be removed using a dry brush, and soluble salts must be removed by washing with fresh water under high pressure.

Recommended Surface Profile

It is recommended a roughness profile between 0.79 and 1.57 mils.

Abrasive Blasting



For other applications, it is recommended to paint on surfaces blasted to Sa 2½ or Sa 3 grade, according to SSPC-SP10 or SSPC-SP5, respectively. Visual standard ISO 8501-1.

Evaluate the surface after blasting, observing revealed defects and adopt practices to minimize them, such as grinding or filling.

Maintenance and Repair

NOTE: Respect the recoating interval for subsequent coat application. If exceeded, perform light manual/mechanical sanding to break the previous coat gloss, followed by dust and residue cleaning to ensure better adhesion between paint layers.

Carbon Steel Surfaces

Completely remove oils, greases, soluble salts, and other contaminants according to SSPC SP1 solvent cleaning method. Rinse with high-pressure fresh water.

The surface must be clean, dry, and free of contaminants.

APPLICATION PREPARATION

Mixing	Homogenize the content of each component using mechanical or pneumatic stirring (A and B). Ensure no sediment remains at the bottom of the container. Add component B to component A in the indicated mixing ratio under stirring until completely homogenized, respecting the mixing ratio.
Mixing Ratio	By volume: 5 A x 1 B.
Thinner	Not applicable.
Dilution	Ready to use.
Notes	No dilution is required. Product ready to use. If necessary, consult the WEG Technical Department.
Pot Life	4 h The shelf life of the mixture is reduced as the ambient temperature increases. The pot-life test of the mixture is carried out according to ABNT NBR 15742; however, different volumes of paint prepared at once, combined with varying ambient and paint temperatures, will affect the mixture's shelf life, potentially resulting in outcomes different from those stated in this technical bulletin.
Induction Time	Wait 5 minutes before application. In very hot locations, we recommend consulting WEG's Technical Department.

APPLICATION METHODS

Conventional Spray Gun	Spray gun: JGA 502/3 Devilbiss or equivalent Fluid nozzle: EX Air cap: 704 Atomization pressure: 50 - 70 psi Tank pressure: 5 - 15 psi.
Airless Spray Gun	Airless: Use minimum pump 60:1 Fluid pressure: 2000 - 3000 psi Hose: 1/4" inner diameter Nozzle: 0.015" - 0.021".
Brush	Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups). For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.
Cleaning of the equipments:	Not applicable.
Notes	The data presented serves as a guide and similar



equipment may be used.

Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination.

Do not allow catalyzed product to remain in contact with application equipment, as at temperatures above the indicated "pot life", the paint will show variation in flow and will harden, making cleaning difficult.

Before application, ensure that the equipment and respective components are clean and in optimal condition.

After mixing two-component products, if there are application stops and the pot life has been exceeded (paint shows variation in flow), it can no longer be re-thinned for later application.

Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.

Clean all equipment immediately after use.

Do not leave material in hoses, guns, or equipment used for spraying. Thoroughly wash all used equipment.

APPLICATION PERFORMANCE

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Do not apply the product after the pot life has been exceeded.

We recommend painting only if the measured surface temperature is at least 5.4°F above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Do not apply under adverse conditions, such as RH above 70% or on condensed surfaces. Small variations in color, appearance, and gloss may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

When applying by brush or roller, two or more coats may be necessary to achieve a uniform layer and recommended film thickness.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

On freshly painted surfaces in direct contact with water during the curing process, localized staining with color change (more visible in darker colors), curing delay, and compromised product performance may occur.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

Epoxy-based products are known for their excellent anticorrosive properties and low resistance to sun exposure. When the applied film is exposed to weathering, over time it will lose gloss, a phenomenon known as chalking, which consequently alters its color. It is important to note that, despite this chalking, the film's anticorrosive protection is not compromised.

SYSTEM COMPATIBILITY AND MAINTENANCE REPAINTING

The primer repainting interval must be respected for the application of the topcoat. If the maximum interval indicated is exceeded, manual/mechanical sanding with sandpaper to remove gloss is necessary. The primer surface must be dry and free of contaminants.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE



The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.
