

**1. PRODUCT AND COMPANY IDENTIFICATION**

Product name : POLITHERM 25 R SM WHITE 60295 MA

Code : 15899104

Main recommended uses : Electrostatic powder paint for surface coating.

Address : Rodovia BR 280 - km 50
CEP 89270-000, Guaramirim - SC

Telephone : +55 47 3276-4000

Emergency telephone number : Austria - Vienna 43-13649237
France - 33-975181407
Germany - Frankfurt 49-69643508409/ 0800-181-7059
Italy - Milan 39-0245557031 / 800-789-767
Netherlands - 31-858880596
United Kingdom - London 44-870-8200418
United Kingdom - 44-2038073798
China - 4001-204937
India - 000-800-100-7141 / 000-800-100-7141
Russia 8-800-100-6346
Italy 800-789-767
South Africa - 0-800-983-611 / 0-800-983-611

E-mail / site : tintas@weg.net | www.weg.net

2. HAZARD IDENTIFICATION**Mixture classification**

Skin sensitization : Category 1

Classification according to NBR 14725-2/2019

Labelling Elements**PAUMAR S.A. INDÚSTRIA E COMÉRCIO - GRUPO WEG**

Rua Dr. Ulisses Guimarães, 918 - 09372-050 - Mauá - SP - Fone: + 55 (11) 4547-6100
Rodovia Br 280 - Km 50, 6.918 - Bloco A - 89270-000 - Guaramirim - SC - Fone: + 55 (47) 3276-4000
Rua Via VII, 314 - 54590-000 - Cabo de Santo Agostinho - PE - Fone: + 55 (81) 3512-3000
EMERGÊNCIA: +55 0800 117 2020 - E-mail: tintas@weg.net - www.weg.net



Warning phrase : Warning

Hazard phrases : H317 May cause an allergic skin reaction.

Caution Phrases :

Prevention:

P261 Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.

P272 Contaminated work clothing should not be allowed out of the workplace.

Reaction:

P302+P352 IF ON SKIN: Wash with plenty of water.

P333+P313 If skin irritation or a rash occurs: Get medical advice/attention.

P362+P364 Take off contaminated clothing and wash it before reuse.

Treatment and disposal of waste:

P501 Dispose of contents/container as chapter 13 of the MSDS.

Other hazard : The finely dispersed particles form explosive mixtures in air, in the presence of sparks. Burning forms a thick black smoke. Inhalation of dangerous products of decomposition may cause serious damage to health.

3. COMPOSITION AND INFORMATION ABOUT THE INGREDIENTS

Product type: : Mixture

Ingredients that contribute to danger:

Product name	CAS No. EC No. REACH Registration No.	Risk classification	Concentration [%]
1-O-TOLYLBIGUANIDE	93-69-6	Skin sensitization , Category 1	>= 1 - < 5

PAUMAR S.A. INDÚSTRIA E COMÉRCIO - GRUPO WEG

Rua Dr. Ulisses Guimarães, 918 - 09372-050 - Mauá - SP - Fone: + 55 (11) 4547-6100
Rodovia Br 280 - Km 50, 6.918 - Bloco A - 89270-000 - Guaramirim - SC - Fone: + 55 (47) 3276-4000
Rua Via VII, 314 - 54590-000 - Cabo de Santo Agostinho - PE - Fone: + 55 (81) 3512-3000
EMERGÊNCIA: +55 0800 117 2020 - E-mail: tintas@weg.net - www.weg.net



4. FIRST AID MEASURES

- Inhalation** : Take the victim to fresh air, keeping them rested and warm. If breathing is irregular or has stopped, apply artificial respiration. Do not give anything orally. Seek medical assistance immediately, bringing the product label whenever possible.
- Contact with the skin** : Remove all contaminated clothing immediately. Wash affected area with plenty of soap and water.
- Contact with the eyes** : Remove contact lenses, if wearing any. Flush the eyes with running water for at least 15 minutes, holding the eyelids apart. Seek medical assistance immediately, bringing the product label with you.
- Ingestion** : Do not provoke vomiting. Consult with a doctor immediately.
- Notes for the doctor** : Treat symptomatically. Do not induce vomiting because of risk of aspiration of gastric contents into the lungs. Gastric lavage is recommended when the patient ingests large quantities of the substance.

5. FIRE-FIGHTING MEASURES

- Suitable extinguishing methods** : Water in mist form
Carbon dioxide (CO₂)
Foam alcohol resistant
Dry chemical powder
- Extinguishing methods not recommended** : Direct water jet.
- Specific dangers** : The finely dispersed particles form explosive mixtures in air, in the presence of sparks. Burning forms a thick black smoke. Inhalation of dangerous products of decomposition may cause serious damage to health.
- Protective measures of the fire fighting team.** : The personnel involved in firefighting should wear self contained breathing apparatus with positive pressure and full protection clothes.
- Specific methods** : Evacuate and isolate the area. Approach from fire with wind at your back. Fight the fire to a secure distance. Remove the packaging of the product from the fire area if this can be made with safety. Chill sideways with water in form of fog all the closed packaging near the fire. Avoid that the resulting water from fire fighting reaches drains or waterways. Use dikes to contain this water and eliminate it according to environmental regulations.



6. SPILL / LEAK CONTROL PROCEDURES

Personal precautions, protective equipment and emergency procedures

For the emergency service staff : If specialized clothing is needed to combat the leak/spillage, Section 8 should be consulted. All precautions described in the following section must be followed.

For staff who are not part of the emergency services : No action should be taken that may generate danger to people without adequate training and qualifications. Use appropriate personal protective equipment - see section 8. Evacuate surrounding areas. Isolate area and keep onlookers away. Do not touch or walk through spilled material. Eliminate all sources of ignition. Avoid breathing vapor or mist. Provide adequate ventilation if possible. Wear appropriate respiratory mask when ventilation is inadequate. In accordance with characteristics of the location and/or area and in relation to the amount of spilled/leaked product, additional emergency measures may be taken under the supervision of a trained professional.

Environmental precautions : Prevent spilled/leaked product from contact with soil, waterways, drains and sewers. Inform the relevant authorities in accordance with current legislation if the product causes environmental damage.

Methods and materials for containment and cleaning

Large spills / leaks : Stop the leak if this can be done safely. Cover up spillage in a tarp to prevent the spread by wind or rain. Use antifascantes tools and explosion-proof equipment properly grounded to collect the product. Place the material collected in dry, clean and properly identified containers. Cap the container loosened so removing them from the spill site. Avoid formation of dust. Remove the packaging from the spill site. If there is product disposal need refer to chapter 13

Small spills / leaks : The collected material can return to the process if you are in favorable conditions. Otherwise should be referred for appropriate disposal.

Dust control : Consult section 13.

7. HANDLING AND STORAGE

Precautions for safe handling

Instructions for safe treatment : Avoid contact with eyes, skin and clothes. Do not handle the product before reading and understanding all safety precautions. Do not re-use packaging. Refer to special instructions before use. Avoid inhalation of the powder. Do not eat, drink or smoke during use.

Precautions for safe : Use individual protective equipment. Environments and areas

PAUMAR S.A. INDÚSTRIA E COMÉRCIO - GRUPO WEG

Rua Dr. Ulisses Guimarães, 918 - 09372-050 - Mauá - SP - Fone: + 55 (11) 4547-6100
 Rodovia Br 280 - Km 50, 6.918 - Bloco A - 89270-000 - Guaramirim - SC - Fone: + 55 (47) 3276-4000
 Rua Via VII, 314 - 54590-000 - Cabo de Santo Agostinho - PE - Fone: + 55 (81) 3512-3000
 EMERGÊNCIA: +55 0800 117 2020 - E-mail: tintas@weg.net - www.weg.net

MATERIAL SAFETY DATA SHEET - MSDS

Product name

POLITHERM 25 R SM WHITE 60295

Code

15899104



MA

Last revision:

05.03.2021

Page: 5 of 11

handling

that will be used for electrostatic spraying of powder paints must provide controlled ventilation. Through controlled ventilation it must be ensured that the air in the inhalation scope is healthy from a health point of view (see limits in Section 8). Avoid sources of ignition and dust deposition in the environment. Antistatic clothes and shoes are recommended. Emergency showers and eye wash basins must be installed in locations of use and storage.

Fire protection

: Tools that do not produce sparks should be used. Keep away from heat and sources of ignition. Do not smoke. Avoid accumulation of electrostatic charges. All conductive elements of the system, in contact with the product, must be electrically grounded. Only use in well-ventilated locations, to prevent accumulation of powder in explosive concentrations.

Storage conditions

Substances to be avoid

: Keep away from oxidising agents, strong acid solutions and strong alkaline solutions.

Storage conditions

: The electrical installation must comply with NEC (National Electrical Code) or IEC (International Electrical Commission) standards and/or those of the ABNT (Brazilian Association of Technical Standards). The floor of the storage area must be impermeable, non-combustible.

Appropriate storage conditions

: Store the material in covered, dry, well ventilated and identified areas. Store at a temperature below 30°C. Store in a closed container. Keep out of direct sunlight.

Inappropriate storage conditions

: Exposed to elevated temperatures, sun and rain. Close to oxidizing agents. Close to food. Close to sources of heat and ignition.

Materials to avoid

: Do not store with explosive materials, flammable and/or toxic gases, oxidizing, corrosive substances, or materials that may generate spontaneous combustion.

Secure packaging materials

Recommended packaging materials

: Must be stored in plastic bags packed in cardboard boxes.

Packaging materials to be avoided

: Glass containers.

8. EXPOSURE CONTROL – PERSONAL PROTECTION

The information in this chapter contains general guidelines. Chapter 1 should be consulted for any information on the recommended use of this product in different scenarios of exposure.

Engineering control measures

: Preferably use the product in adequate application cabin. In case it is not possible, provide exhaustion/ventilation enough to keep the concentration of the agents indicated

PAUMAR S.A. INDÚSTRIA E COMÉRCIO - GRUPO WEG

Rua Dr. Ulisses Guimarães, 918 - 09372-050 - Mauá - SP - Fone: + 55 (11) 4547-6100
Rodovia Br 280 - Km 50, 6.918 - Bloco A - 89270-000 - Guaramirim - SC - Fone: + 55 (47) 3276-4000
Rua Via VII, 314 - 54590-000 - Cabo de Santo Agostinho - PE - Fone: + 55 (81) 3512-3000
EMERGÊNCIA: +55 0800 117 2020 - E-mail: tintas@weg.net - www.weg.net

MATERIAL SAFETY DATA SHEET - MSDS

Product name

POLITHERM 25 R SM WHITE 60295

Code

15899104



MA

Last revision:

05.03.2021

Page: 6 of 11

in this section under the limits of tolerance (L.T.), otherwise, use adequate respiratory protection equipment. The engineering controls should keep the concentrations of gas/vapour under the limit of LEL - Lower Explosive Limit (see section 9). Use equipment explosion proof.

Control parameters

Occupational Exposure Limits

Name	CAS No.	TLV/TWA	TLV/STEL	TLV/TETO	Source
1-O-TOLYLBIGUANIDE	93-69-6				

*PPM - parts of vapour or gas per million of parts of contaminated air

**MG/m³ - miligrams per cubic meter of air.

Personal protective equipment required

Respiratory protection : If the powder is above the tolerance limits (see engineering control measures, above) a dust mask must be used, suitable for this purpose (P2 particle filter). Occasionally other respiratory protective equipment may be used.

Hand protection : Protective creams can be used to protect exposed skin areas together with latex or nitrile gloves (never used after the exposure has occurred).

Eye protection : Use hermetic goggles to protect against powder spray.

Body and skin protection : Antistatic clothes and shoes are recommended.

9. PHYSICAL AND CHEMICAL PROPERTIES

Form	: Dust
State of matter	: Solid
Color	: White
Odour	: Weak and distinctive
Odour limit	: Not applicable
pH	: Not applicable
Melting point	: Not applicable
Boiling point	: Not applicable
Evaporation rate	: Not applicable
Inflammation point	: Method: Not applicable
Upper explosive limit	: 70 g/m ³

PAUMAR S.A. INDÚSTRIA E COMÉRCIO - GRUPO WEG

Rua Dr. Ulisses Guimarães, 918 - 09372-050 - Mauá - SP - Fone: + 55 (11) 4547-6100
 Rodovia Br 280 - Km 50, 6.918 - Bloco A - 89270-000 - Guaramirim - SC - Fone: + 55 (47) 3276-4000
 Rua Via VII, 314 - 54590-000 - Cabo de Santo Agostinho - PE - Fone: + 55 (81) 3512-3000
 EMERGÊNCIA: +55 0800 117 2020 - E-mail: tintas@weg.net - www.weg.net



Lower explosive limit	: 40 g/m ³
Vapor pressure	: Not applicable
Density	: 1,60 g/cm ³
Solubility(ies)	: Insoluble in water, partially soluble in some solvents and thinners oxygen as acetone , ethyl acetate , methyl ethyl ketone, among others.
N-octano /water partition coefficient	: Not applicable
Auto flammability	: 400 °C
Cinematic viscosity (25°C)	: Not applicable
Vapor density	: Not applicable
Decomposition temperature	:

10. STABILITY AND REACTIVITY

Reactivity	: Presents no reactivity at room temperature and under normal conditions of use.
Chemical stability	: Stable at room temperature and under normal conditions of use.
Possibility of dangerous reactions	: Presents no reactivity at room temperature and under normal conditions of use. None when the product is stored, applied and processed correctly. Otherwise, the mixture powder air mixture could ignite.
Need to add additives and inhibitors	: Not necessary.
Conditions to avoid	: Extreme heat and open flame.
Incompatible materials	: Do not store with explosive materials, flammable and/or toxic gases, oxidizing, corrosive substances, or materials that may generate spontaneous combustion.
Dangerous products of decomposition	: High temperatures (above 300°C) could result in dangerous products of decomposition, such as carbon dioxide and smoke.

PAUMAR S.A. INDÚSTRIA E COMÉRCIO - GRUPO WEG

Rua Dr. Ulisses Guimarães, 918 - 09372-050 - Mauá - SP - Fone: + 55 (11) 4547-6100
 Rodovia Br 280 - Km 50, 6.918 - Bloco A - 89270-000 - Guaramirim - SC - Fone: + 55 (47) 3276-4000
 Rua Via VII, 314 - 54590-000 - Cabo de Santo Agostinho - PE - Fone: + 55 (81) 3512-3000
 EMERGÊNCIA: +55 0800 117 2020 - E-mail: tintas@weg.net - www.weg.net



11. TOXICOLOGICAL INFORMATION

Components**1-O-TOLYLBIGUANIDE**

Acute toxicity by oral use : Test species Data not available.
DL50
Observations

Acute toxicity by inhalation : Test species
DL50
Observations Data not available.

Acute toxicity by cutaneous use : Test species Data not available.
DL50
Observations

Acute toxicity (other methods of administration) : Test species Data not available.
DL50
LC50
Non-standard unit value

Corrosion/irritation of skin : Data not available.

Serious eye damage/eye irritation : Data not available.

Respiratory or dermal sensitivity : Data not available.

Mutageneses : Data not available.

Carcinogenicity : Data not available.

Toxic effects for reproduction : Data not available.

Specific target organ toxicity (STOT) - single exposure : Data not available.

Specific target organ toxicity (STOT) - repeat exposure : Data not available.

Aspiration hazard : Data not available.

Acute toxicity

Powder coatings are generally inert dusts . No data are available on acute toxicity for the product. Powder coatings can cause irritation located in the skin , especially in skin folds or use of tight clothes . People allergic or respiratory problems should not work in the powder application. Repeated or prolonged contact with the product may cause removal of natural fat from the skin , resulting in non allergic contact dermatitis and skin absorption . The product that comes into contact with the eyes can cause irritation.

Chronic toxicity

On the skin , prolonged contact leads to degreasing , may cause fissures , dryness , dermatitis and eczema. The respiratory system may be affected by chronic bronchitis and decreased respiratory volume. Exposure of pregnant women to concentrations above the

MATERIAL SAFETY DATA SHEET - MSDS

Product name POLITHERM 25 R SM WHITE 60295 Code 15899104
 MA
 Last revision: 05.03.2021 Page: 9 of 11



limit can present threat of abortion. In contact with eyes, do not rub , wash with running water for at the least 15 minutes.

12. ECOLOGICAL INFORMATION

Stability in soil : Data not available.

Elimination of chemical physical ability : Not considered potentially bioaccumulative.

Other toxicological observations : Data not available.

Ecotoxicity : Detrimental to the flora.
 Detrimental to the fauna
 Contaminates the ground water.

13. DIOSPOSAL AND TREATMENT CONSIDERATIONS

Recommended methods for final disposal

Product : Class II Waste - Dispose of in industrial landfill or a facility authorized for recycling in accordance with federal, state or local regulations.

Waste : Class II Waste - Dispose of in industrial landfill or a facility authorized for recycling in accordance with federal, state or local regulations.

Used packaging : Clean packaging should be sent for recycling. Packaging with class II waste should be disposed of in industrial landfill or a facility authorized for recycling in accordance with federal, state or local regulations

14. TRANSPORTATION INFORMATION

National and international regulations

Land : Not classified as a dangerous good under transport regulations.

Shipping : Not classified as a dangerous good under transport regulations.

Air transport : Not classified as a dangerous good under transport regulations.

15. REGULATORY INFORMATION

This MSDS (Material Safety Data Sheet) was generated according to the criteria of NBR 14725/2014. (Brazilian standard that defines the GHS).

PAUMAR S.A. INDÚSTRIA E COMÉRCIO - GRUPO WEG

Rua Dr. Ulisses Guimarães, 918 - 09372-050 - Mauá - SP - Fone: + 55 (11) 4547-6100
 Rodovia Br 280 - Km 50, 6.918 - Bloco A - 89270-000 - Guaramirim - SC - Fone: + 55 (47) 3276-4000
 Rua Via VII, 314 - 54590-000 - Cabo de Santo Agostinho - PE - Fone: + 55 (81) 3512-3000
 EMERGÊNCIA: +55 0800 117 2020 - E-mail: tintas@weg.net - www.weg.net

MATERIAL SAFETY DATA SHEET - MSDS

Product name

POLITHERM 25 R SM WHITE 60295

Code

15899104

MA

Last revision:

05.03.2021

Page: 10 of 11



Specific Regulations for the Chemical Product.	Federal Decree No. 2657, July 3rd , 1998. Ordinance No. 229, May 24th, 2011 - Changes to Regulatory Standard No. 26. ABNT NBR 14725: 2014 - valid from 19/12/2014 - Amendment 1 (19/11/2014). Law No. 12305, August 2nd 2010 (Solid Waste National Policy). Decree No. 7404, December 23rd , 2010. Resolution ANTT N° 5.232, December 14th 2016.
--	---

16. ADDITIONAL INFORMATION

Acronyms Used:

Legenda:

CAS	Chemical Abstract Service
VO	Organic Vapors
NEC	National Eletrical code/Código Nacional de Eletricidade
IEC:	International Eletrical Commision
ABNT	Brazilian Association of Technical Standards
ACGIH	American Conference of Governmental Industrial Hygienists
TLV	Threshold Limit Values
TLV/TWA	Time Weighted Average
TLV/STEL	Short Term Exposure Limit
TLC/C:	Tolerance Limit - Ceiling Value
EPI:	Individual Protective Equipment
CA	Approval Certificate
PPRA	Environmental Risk Prevention Program
NR	Regulatory Standard
NFPA	National Fire Protection Agency
mmHg	Millimeters of mercury - pressure unit
DL50	Lethal Dose average
CL50	Lethal Concentration average
ppm	Parts per million
N.d	Not available
A+B	Viscosity of the mixture of component A + component B

Important information, but not specifically described in the previous sections:
This MSDS was prepared based on current knowledge about the handling of the

PAUMAR S.A. INDÚSTRIA E COMÉRCIO - GRUPO WEG

Rua Dr. Ulisses Guimarães, 918 - 09372-050 - Mauá - SP - Fone: + 55 (11) 4547-6100
Rodovia Br 280 - Km 50, 6.918 - Bloco A - 89270-000 - Guaramirim - SC - Fone: + 55 (47) 3276-4000
Rua Via VII, 314 - 54590-000 - Cabo de Santo Agostinho - PE - Fone: + 55 (81) 3512-3000
EMERGÊNCIA: +55 0800 117 2020 - E-mail: tintas@weg.net - www.weg.net

MATERIAL SAFETY DATA SHEET - MSDS

Product name

POLITHERM 25 R SM WHITE 60295

Code

15899104



MA

Last revision:

05.03.2021

Page: 11 of 11

product under normal conditions of use, according to the application specified on the packaging and recommended usage in Section 1 of this MSDS. Any other use of the product involving its combination with other materials, as well as forms of use different from those indicated, are the user's responsibility. The company advises that the handling of any chemical substance requires prior knowledge of its hazards by the user. In the workplace it is responsibility of the company user of the product to provide training of its employees and contractors about the possible risks arising from exposure to the chemical.

We reserve the right to change the information contained in this document without prior notice, due to the improvement and continuous evolution of the product and technical knowledge.

References

: Data not available.

Vertical lines in the left hand margin indicate changes from the current version

PAUMAR S.A. INDÚSTRIA E COMÉRCIO - GRUPO WEG

Rua Dr. Ulisses Guimarães, 918 - 09372-050 - Mauá - SP - Fone: + 55 (11) 4547-6100
Rodovia Br 280 - Km 50, 6.918 - Bloco A - 89270-000 - Guaramirim - SC - Fone: + 55 (47) 3276-4000
Rua Via VII, 314 - 54590-000 - Cabo de Santo Agostinho - PE - Fone: + 55 (81) 3512-3000
EMERGÊNCIA: +55 0800 117 2020 - E-mail: tintas@weg.net - www.weg.net