

## W-POXI ENG 034

**PRODUCT DESCRIPTION:** High-build, 2-pack polyamine epoxy direct to metal with anti-corrosion pigments for steel surface. Product developed for application on dry, wet and hydroblasted surfaces and on a specific primer.

**RECOMMENDED USES:** Ships, offshore and marine structures: ballast and fuel tanks, decks, oil exploration platforms and on-board machinery.  
 Industrial applications: Pulp and paper, chemical and petrochemical, bridges, metal structures and machinery, among others.  
 Piping: It can be applied inside and outside pipes.  
 Maintenance coating: This product may be used for maintenance coating of the exterior of tanks at an operating temperature up to 70 °C. For this situation, use 150 microns of dry thickness.

**CERTIFICATIONS AND APPROVAL:** This product, when supplied to comply with the RoHs Directive (Restriction of Certain Hazardous Substances) has the letter R in its description.

PACKAGING:	Component	Content	Package	Unit of measurement
	Component A	16 2,88	20 3,6	L
	Component B	4 0,72	4 0,9	L

**CHARACTERISTICS:** **Color:** Ral, Munsell or as per customer standard.  
**Gloss:** Gloss >80 UB  
**VOC content:** 190 g/l  
**Volume solid:** 85 ± 2% (ISO 3233).  
**Expiry Date:** 12 months at 25°C.  
**Thickness per coat (dry):** 100 µm –200 µm  
**Theoretical coverage:** 5,66 m<sup>2</sup>/l without dilution in the thickness of 150 µm dry. Without considering the loss factors in the application.  
**Resistance to dry heat:** Maximum temperature 120 °C . The product retains its physical and chemical properties up to the temperature of 120 °C however, variations in the coating color and gloss may occur from 60 °C.

Drying:	5°C	15°C	25°C	40°C	70°C
<b>Touch:</b>	8 hours	6 hours	3 hours	2 hours	30 minutes
<b>Handling:</b>	30 hours	16 hours	8 hours	5 hours	3 hours
<b>Final:</b>	-	-	168 hours	-	-
<b>Pot Life</b>	3 hours	2 hours	90 minutes	45 minutes	30 minutes
<b>Repainting Drying:</b>					
Min	24 hours	18 hours	8 hours	3 hours	3 hours
Max	14 days	10 days	7 days	5 days	24 hours

**SURFACE PREPARATION** The performance of this product is related to the degree of surface preparation.

The surface must be clean, dry and free of any contaminants. Completely remove oils, greases and fats, as described in the SSPC-SP 1 standard.

The accumulated dirt must be removed using a dry brush, clean and dry cloth, compressed air blow, vacuum cleaner and/or with the combination of such items, and the soluble salts must be removed through wash with a great quantity of fresh water, preferably with low pressure (up to 5,000 psi) according to SSPC-SP 12/NACE No. 5.

## Surface treatment through Abrasive Blasting process

Execute the abrasive blasting to near white metal, Sa 2 ½ grade of the ISO 8501-1 visual standard (A Sa 2 ½, B Sa 2 ½, C Sa 2 ½ and D Sa 2 ½) or according to SSPC-SP 10/NACE No. 2, SSPC-VIS 1 visual standard (A SP 10, B SP 10, C SP 10, D SP 10, G1 SP 10, G2 SP 10, G3 SP 10).

It is recommended a roughness profile between 50 and 75 µm.

Inspect the newly blasted surface observing the presence of surface flaws that could become apparent after this stage, adopting appropriate actions to mitigate such defects through grinding, weld filling and/or epoxy putty.

In case of oxidation on the substrate from the end of the abrasive blasting to the beginning of the coating application, the surface must be blasted again until reaching the specified visual standard.

For areas close to sea air, it is necessary to wash the surface with fresh water at low pressure (minimum 3,000 psi) before the abrasive blasting. And in some cases it is necessary to repeat the washing procedure after the abrasive blasting to remove possible soluble contaminants settled on the surface proceeding with a new abrasive blasting.

## Surface treatment through the manual mechanical cleaning process

Execute manual mechanical cleaning for carbon steel surfaces that present the oxidation grades C or D, according to the SSPC-VIS 3 visual standard. For surfaces previously painted that present grades E, F or G according to standard SSPC-VIS 3.

**NOTE:** If it is not possible to execute the manual mechanical cleaning process, as an alternative the surface can be prepared with commercial abrasive blasting, grade Sa 2 of the ISO 8501-1 visual standard (C Sa 2 and D Sa 2) or according to SSPC-SP 6/NACE No. 3, SSPC-VIS 1 visual standard (C SP 6, D SP 6).

## Treatment of Steel Carbon Surfaces

Hard superficial layers (for example, layers resulting from flame cut) must be removed by grinding it before beginning the abrasive blasting.

All the welds must be inspected e, if necessary, be repaired before the ending of the abrasive blasting. Porosity, cavities, weld splashes, etc. must be repaired by means of proper mechanical treatment or weld repair; in the other areas, round the sharp edges ( $r \geq 2$  mm, ISO 8501-3).

**For further information, consult WEG Technical Department.**

PREPARATION FOR APPLICATION

### Mixture

Homogenize the contents of each component by means of mechanical or pneumatic stirring (A and B). Ensure that no sediment is settled at the bottom of the package. Add component B to component A, at the recommended proportion (volume), under stirring, until complete homogenization, observing the mixing ratio.

### Mixing ratio (Volume)

4 A X 1 B.

### Diluent

**Epoxy diluent 3005**

### Dilution

Depending on the application method, dilute at most 10%

Do not dilute with solvents that are not allowed by local legislation and do not exceed the recommended dilution percentage.

Only add the diluent after the complete mixing of components A + B.

The quantity of diluent may vary depending on the type of equipment used and the ambient conditions during the application.

Excessive dilution of the coating may affect the formation of the film and appearance and hinder the attainment of the specified thickness.

### Pot life of the mixture (25°C)

1 h 30 min

The pot life is reduced with a higher room temperature.

The pot-life test is performed according to the Brazilian standard ABNT NBR 15742; however, different volumes of coating prepared at once combined with different ambient and coating temperatures will

influence the pot life, and different results than those mentioned in this data sheet may be found.

**Induction time (25°C)**

Wait 15 to 20 minutes before application.

In hot areas, we recommend consulting WEG Technical Department.

**APPLICATION FORMS**

**The data below is a guide, and similar equipment may be used.**

In the spray application, make a 50% overlap in each gun pass, concluding with a cross pass. This technique is used to avoid uncovered and unprotected areas and to obtain a suitable aesthetic finish.

Reinforce all sharp edges, cracks and weld beads with a brush to prevent premature failures in these areas.

Changes in nozzle sizes and pressures may be necessary to improve the spraying characteristics.

Before the application, make sure the equipment and its components are clean and in the best condition.

Purge the compressed air line to prevent contamination of the coating.

After mixing the 2-pack products, if there are stops in the application, and the pot life is exceeded (the coating presents variation in its fluidity), it can no longer be diluted for further application.

**Conventional gun:**

Gun:	JGA 502/3 Devilbiss or equivalent
Fluid nozzle:	EX
Air cap:	704
Atomization pressure:	50 - 70 psi
Pressure in the tank:	10 - 20 psi
Dilution:	10%

**Airless Gun:**

Use Airless:	Use at least pump 60: 1
Fluid pressure:	2000 – 3000 psi
Hose:	¼" internal diameter
Nozzle:	0,015" - 0,021"
Filter:	Mesh 60

**Brush:**

Only recommended for retouching small areas or stripe coat (screws, nuts, weld beads, sharp edges and retouching). Use a brush 75 to 100 mm wide for larger surfaces and 25 to 38 mm for retouching.

**Roller:**

Use a thin nap, seamless sheepskin or microfiber roller for epoxy coatings.

For application with brush and/or roller, application in two or more passes may be necessary to obtain a uniform layer according to the recommended film thickness per coat.

**Cleaning the equipment:**

Epoxy diluent 3005  
Clean all equipment immediately after use.

**NOTE:**

Do not leave the catalyzed product in contact with the equipment used in the application, because the coating will present variations in fluidity at temperatures above the specification in the pot life and will harden, making the cleaning difficult.

Furthermore, it is a good working practice to periodically wash the spray equipment along the day. The cleaning frequency will depend on the amount sprayed, temperature and elapsed time, including all delays.

**PERFORMANCE IN THE APPLICATION**

For a good performance of the product, we recommend following the directions below:

Minor variations in color, appearance and gloss (more noticeable in dark colors) may occur, as well as delay in curing and impairment of surface performance, when applied during periods of high air relative humidity, rainy days, low temperatures or in case the coated parts are put to dry outdoors.

Epoxy-based products are known to have excellent anti-corrosion properties and low resistance to sunlight exposure. In situations of exposure of the film to the weather, over time it will present a loss of gloss known as chalking and its shade will change as a consequence. Remember that even undergoing such chalking, the film anti-corrosion protection is not impaired.

In paintings executed on the seafront, if exposed to the action of sea air, we recommend to wash with fresh water between coats eliminating the settled impurities.

It should not be applied in adverse conditions, such as air relative humidity above 85% or on condensed surfaces. Small variations in color, appearance and gloss of the coated parts may occur in periods of high air relative humidity, rainy days, at low temperatures or in situations where the coated parts are placed to dry outdoors.

Product not recommended for painting the interior of tanks

We recommend coating only if the measured surface temperature is at least 3 °C above the dew point temperature.

Do not apply the product after the pot life has expired.

For better application properties, the coating temperature should be between 21 - 27 °C prior to the mixing and application.

In coatings with variation in the application method in the same job, the final appearance and gloss of the painted surfaces may present differences.

The temperature of the substrate, the weather and environmental conditions during the application and during the curing of the product, and the thickness of the applied film may interfere with the product drying time.

For a good performance of the product, we recommend following the directions below:

For further information, consult WEG Technical Department.

## COMPATIBILITY OF SYSTEMS AND MAINTENANCE REFINISHING

The product can be directly applied to aged coatings or other coating systems. It is, however, advisable to test the contact of the product with the previous coating in a small test area. We recommend sanding to break the gloss for a better performance of the product. Make sure the original material is well bonded. All loose coating must be removed. Points with corrosion or application over aged coatings should be treated according to technical guidance.

To apply topcoat over the product, the overcoating interval should be observed. The surface must be dry and free of any contaminants.

For further information, consult WEG Technical Department.

## SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals.

Please read carefully all the information contained in the MSDS of this product, available at: [www.weg.net](http://www.weg.net).

Store in a covered, well-ventilated area. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists / vapors / aerosols generated during handling and / or application.

Wear protective gloves / protective clothing / eye protection / face protection.

Avoid release of the product and its packaging, as well as materials used during handling and application in the environment.

## NOTE:

The information contained in this technical datasheet is based upon the experience and knowledge acquired in the field by the technical team of WEG.

If using the product without prior inquiry to WEG Coating concerning its suitability for the customer's intended purpose, the customer is aware that the use shall be its exclusive responsibility, WEG not being responsible for the behavior, safety, suitability or durability of the product.

Certain information contained in this datasheet is merely an estimate, and can undergo variances arising from factors outside the manufacturer's control. Thus, WEG does not guarantee and does not assume any responsibility regarding the yield, performance or any other material or personal damage resulting from the incorrect use of the products concerned or the information contained in this Technical datasheet.

The information contained in this technical datasheet is subject to periodic modification, without prior notice, due to the policy of evolution and continuous improvement of our products and services, providing solutions with quality to satisfy our customers' requirements.

