

LACKPOXI N 2629

PRODUCT DESCRIPTION

Two-component, solvent-free polyamine epoxy topcoat. Provides high chemical resistance to solvents and petroleum derivatives.

RECOMMENDED USE

Recommended for interior painting of tanks for petroleum, lubricating oil, naphtha, automotive and aviation gasoline, kerosene, gas, hexane, mineral spirits, rubber solvent, diesel oil, and fuel.

CERTIFICATIONS AND APPROVALS

Complies with Petrobras Standard N 2629.

Meets the requirements of ANVISA Resolution No. 105 for contact with non-acidic aqueous foods (drinking water).

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

PACKAGING

Component A	3.6L Package containing 2.7L 20L Package containing 15L
Component B	0.9L Package containing 0.9L 5L Package containing 5L

CHARACTERISTICS

Color	White. Green.
Gloss	Gloss
VOC content	182.91 g/l
Volume Solids	90 ± 2% (ISO 3233)
Shelf Life	24 months
Dry Film Thickness	150 µm - 220 µm
Dry Heat Resistance	Maximum temperature 120 °C. The product maintains its chemical properties up to a temperature of 120 °C, but from 60°C, color and gloss variations in the paint may occur.
Theoretical Coverage	4,86 m ² /l without dilution at a dry film thickness of 185 µm. Loss factors during application are not considered.

DRYING

Drying

	10 °C	25 °C	35 °C
Pegajosidade	24 hours	16 hours	12 hours
Pressão	72 hours	48 hours	24 hours
Final	288 hours	240 hours	168 hours

Recoat Drying

	10 °C	25 °C	35 °C
Minima	24 hours	12 hours	10 hours
Maxima	48 hours	24 hours	18 hours

SURFACE PREPARATION

Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The surface must be clean, dry, and free of contaminants. Completely remove oils, greases, and



fats according to SSPC-SP1.

Over Primer

Respect the product recoat interval. If exceeded, perform light manual/mechanical sanding to break gloss and clean dust/residues for better adhesion between coats.

APPLICATION PREPARATION

Mixing

Homogenize the content of each component using mechanical or pneumatic stirring (A and B). Ensure no sediment remains at the bottom of the container. Add component B to component A in the indicated mixing ratio under stirring until completely homogenized, respecting the mixing ratio.

Mixing Ratio

By volume: 3 A x 1 B.

Thinner

Not applicable.

Dilution

Ready to use.

Notes

No dilution is required. Product ready to use. If necessary, consult the WEG Technical Department.

Pot Life

1 h 30 min

The shelf life of the mixture is reduced as the ambient temperature increases.

The pot-life test of the mixture is carried out according to ABNT NBR 15742; however, different volumes of paint prepared at once, combined with varying ambient and paint temperatures, will affect the mixture's shelf life, potentially resulting in outcomes different from those stated in this technical bulletin.

Induction Time

No induction time required.

In very hot locations, we recommend consulting WEG's Technical Department.

APPLICATION METHODS

Airless Spray Gun

Airless: Use minimum pump 60:1

Fluid pressure: 4000 - 4500 psi

Hose: 1/4" inner diameter

Nozzle: 0.023" - 0.027"

Note: When it is necessary to use a hose longer than 15 meters, the first 15 meters must be 1/4" and the remaining meters 3/8".

Roller

Use a short-haired, seamless wool or synthetic roller for epoxy paints.

For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.

Brush

Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups).

Cleaning of the equipments:

Not applicable.

Notes

The data presented serves as a guide and similar equipment may be used.

Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination.

Do not allow catalyzed product to remain in contact with application equipment, as at temperatures above the indicated "pot life", the paint will show variation in flow and will harden, making cleaning difficult.

Before application, ensure that the equipment and respective components are clean and in optimal condition.

After mixing two-component products, if there are



application stops and the pot life has been exceeded (paint shows variation in flow), it can no longer be re-thinned for later application.

In spray application, overlap each gun pass by 50%, finishing with a cross pass. This technique avoids uncovered or unprotected areas and ensures proper aesthetic finish.

Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.

Clean all equipment immediately after use.

It is considered good practice to periodically wash the spraying equipment during the day. The cleaning frequency depends on the amount sprayed, temperature, and elapsed time, including all delays.

APPLICATION PERFORMANCE

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Do not apply the product after the pot life has been exceeded.

As this is a primer, color variation between batches of this material may occur.

For optimal application properties, the paint temperature should be between 21°C and 27°C before mixing and application.

Before application, observe weather conditions: there must be no threat of rain or drizzle. Surface temperature must be at least 3°C above the dew point, and relative humidity should not exceed 85%. Adverse conditions may cause color variations and other characteristics. Consult WEG Technical Department.

Painting is recommended only if surface temperature is at least 3°C above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Epoxy systems may have longer curing times when exposed to low temperatures. For curing at temperatures below 10°C, consult the WEG Technical Department.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

Epoxy-based products are known for their excellent anticorrosive properties and low resistance to sun exposure. When the applied film is exposed to weathering, over time it will lose gloss, a phenomenon known as chalking, which consequently alters its color. It is important to note that, despite this chalking, the film's anticorrosive protection is not compromised.

SYSTEM COMPATIBILITY AND MAINTENANCE REPAINTING

The primer repainting interval must be respected for the application of the topcoat. If the maximum interval indicated is exceeded, manual/mechanical sanding with sandpaper to remove gloss is necessary. The primer surface must be dry and free of contaminants.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or



durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.
