



## WEGTHANE HPA 501 ALUMÍNIO

**PRODUCT DESCRIPTION:** Gloss three-component aliphatic acrylic polyurethane topcoat pigmented with aluminum. It provides excellent durability and extended refinish.

**RECOMMENDED USES:** Used as topcoat in areas above the waterline on metal structures, industrial equipment and different kinds of machinery.

**CERTIFICATIONS AND APPROVAL:** This product, when supplied to comply with the RoHs Directive (Restriction of Certain Hazardous Substances) has the letter R in its description.

PACKAGING:	Component	Content	Package	Unit of measurement
	Component A	2,78	3,6	L
		15,48	20	
	Component B	0,52	0,5	L
		2,85	4	
	Component C	0,441 kg	0,9	L
		2,45 kg	3,6	

**CHARACTERISTICS:** **Color:** Aluminum  
**Gloss:** Metallic  
 Semigloss  
**Shelf-Life:** 24 months at 25°C.  
**Theoretical coverage:** 10,1 m<sup>2</sup>/l without dilution in the thickness of 55 µm dry. Without considering loss factors in application.

**Drying:**

	10°C	25°C	35°C
<b>Touch:</b>	4 hours	2 hours	1 hour
<b>Handling:</b>	24 hours	6 hours	4 hours
<b>Final:</b>	240 hours	168 hours	168 hours

**Overcoating Drying:**

	10°C	25°C	35°C
Min	24 hours	6 hours	5 hours
Max	48 hours	48 hours	48 hours

**SURFACE PREPARATION** The performance of this product depends on the degree of surface preparation.

The surface must be clean, dry and free of any contaminants. Completely remove oils, greases and fats, as described in the SSPC-SP 1 standard.

**Application over primer**

The product can be directly applied to a specific primer in order to form a suitable coating system.

**NOTE:** Observe the product overcoating interval to apply the next coat. In case the maximum overcoating interval has been exceeded, it is necessary to manually/mechanically sand the surface to break the gloss of the previous coat and clean the sanding residues so as to provide better adhesion between the coats.

**Refinishing of surfaces with aged coating in good conservation conditions**

We recommend the user of this coating to seek ways to make sure the original aged painting is still well bond to the substrate before executing this refinish. Loose aged coatings or not well bonded must be completely removed. We emphasize that the refinishing must only be made on surfaces in good conservation conditions.

Remove all the existing contaminants on the coating. In case the film has spots not well bonded, remove it with brush off grade 1 or according to SSPC-SP7 standard. ISO 8501-1 visual standard.

Corrosion spots, worn or damaged areas and the like shall be prepared by commercial abrasive blasting to Sa 2 of ISO 8501-1 visual standard or according to SSPC-SP 6 / NACE No. 3, SSPC-VIS 1 visual standard. If it is not possible to execute the abrasive blasting, as an alternative the surface can be prepared with rotary power tools according to SSPC-SP 11.

**For further information, consult WEG Technical Department.**

## PREPARATION FOR APPLICATION

### Mixture

Homogenize the contents of component A by means of mechanical or pneumatic stirring. Ensure that no sediment is settled at the bottom of the package. Slowly add component A to component C. Slowly homogenize by manual or pneumatic stirring until a homogeneous, lump-free mixture is obtained. Only then add component B. Repeat the homogenization process. The mixing ratio recommended for the preparation of the paint should be observed. If necessary, filter using a 60 mesh screen.

### Mixing ratio (Volume)

A X B. X C

### Diluent

Only add the diluent after the complete mixing of components A + B + C.

### Dilution

Depending on the application method, dilute at most.

Do not dilute with solvents that are not allowed by local legislation and do not exceed the recommended dilution percentage.

Only add the diluent after the complete mixing of components A + B + C.

The quantity of diluent may vary depending on the type of equipment used and the ambient conditions during the application.

Excessive dilution of the coating may affect the formation and aspect of the film and not allow to reach the specified thickness.

### Induction time (25°C)

Wait 15 to 20 minutes before application.

In hot areas, we recommend consulting WEG Technical Department.

## APPLICATION FORMS

**The data below is a guide, and similar equipment may be used.**

In the spray application, make a 50% overlap in each gun pass, concluding with a cross pass. This technique is used to avoid uncovered and unprotected areas and to obtain a suitable aesthetic finish.

Recoat all sharp edges, cracks and weld beads with a brush to prevent premature failures in these areas.

Changes in nozzle sizes and pressures may be necessary to improve spraying characteristics. Before application, check if the equipment and its components are clean and in best condition. Purge the compressed air line to prevent contamination of the coating.

After mixing two-component products, if there are stops in the application, and pot life is exceeded (the coating shows variation in fluidity) it can no longer be diluted for further application.

The data below is a guide, and similar equipment may be used.

### Airless Gun:

Use Airless:	Use at least pump 60: 1
Fluid pressure:	1500 - 2500 psi
Hose:	¼" internal diameter
Nozzle:	0,015" - 0,021"

### Brush:

Only recommended for touch up small areas or stripe coat (screws, nuts, weld and sharp edges). Use a brush 75 to 100 mm wide for larger surfaces and 25 to 38 mm for touch up.

### Roller:

Use a thin nap, seamless sheepskin or microfiber roller for epoxy coatings.



For application with brush and/or roller, two or more passes may be necessary to obtain a uniform layer according to the recommended film thickness per coat.

**Cleaning the equipment:**

**NOTE:**

Clean all equipment immediately after use.

Do not leave catalyzed product in contact with the equipment used in the application, because the coating will vary in fluidity at temperatures above specified in the pot life and will cure faster, making the cleaning difficult.

Furthermore, it is a good working practice to periodically wash the spray equipment along the day. The cleaning frequency will depend on the amount sprayed, temperature and elapsed time, including all delays.

**PERFORMANCE IN THE APPLICATION**

For a good performance of the product, we recommend following the directions below:

Variations in color, aspect and gloss (more noticeable in dark colors) may occur, as well as delay in curing and low coating performance, when applied during periods of high air relative humidity, rainy days, low temperatures or drying the coating outdoor.

In paintings carried out in front of the sea, if exposed to sea air, we recommend to wash with fresh water between coats eliminating settled impurities.

It should not be applied in adverse conditions, such as air relative humidity above 85% or on condensed surfaces. Small variations in color, appearance and gloss of the coated parts may occur in periods of high air relative humidity, rainy days, at low temperatures or in situations where the coated parts are placed to dry outdoors.

Polyurethane systems (component A, B and C) present sensitivity when exposed to air relative humidity, which can cause flaws in the dry film and reduction of pot life. Therefore, we recommend that the packages of each component be properly closed after use and kept in dry places protected from bad weather.

We recommend coating only if the surface temperature is at least 3 °C above the dew point temperature.

Do not apply the product after the pot life has expired.

For better application properties, the coating temperature should be between 21 - 27 °C prior to the mixing and application.

In coatings with variation in application method in the same job, the final aspect and gloss of the painted surfaces may show differences.

The temperature of the substrate, the weather and environmental conditions during the application and during the curing of the product, and the thickness of the coat may interfere in the product drying time.

It should not be applied under adverse conditions, such as air relative humidity (RH) above 85%, as changes in color and appearance may occur.

For further information, consult WEG Technical Department.

**COMPATIBILITY OF SYSTEMS AND MAINTENANCE REFINISHING**

The primer overcoating interval should be respected before applying the topcoat. If the maximum recommended overcoating interval is exceeded, manual/mechanical sanding is necessary to break the gloss. The primer surface must be dry and free of any contaminants.

In situations where the nature of the primer is unknown, it is recommended to test the compatibility of the product in a small area. Check the original material is well adhered. All loose coating must be removed. Points with corrosion or application over aged coatings should be treated according to technical guidance.

The direct application of this product on zinc-rich ethyl silicate-based primers, alkyd primers, coal tar-based coatings and other single-component primers is not recommended. When necessary to apply the topcoat over one of the primers mentioned above, we recommend the application of an appropriate intermediate coating.

For further information, consult WEG Technical Department.

**SAFETY PRECAUTIONS**

Product developed for industrial use intended for handling by qualified professionals.

Please read carefully all the information contained in the MSDS of this product, available at: [www.weg.net](http://www.weg.net).

Store in a covered, well-ventilated area. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists / vapors / aerosols generated during handling and / or application.

Wear protective gloves / protective clothing / eye protection / face protection.

Avoid release this product and its packaging, as well as materials used during handling and application in the environment.

**NOTE:**

The information contained in this technical datasheet is based upon the experience and knowledge acquired in the field by the technical team of WEG.

If using the product without previous inquiry to WEG Coating concerning its suitability for the customer's intended purpose, the customer is aware that the use shall be its exclusive responsibility, WEG not being responsible for behavior, safety, suitability or durability of the product.

Some information contained in this datasheet are estimated, and can undergo variances arising from factors outside the manufacturer's control. Thus, WEG does not guarantee and does not assume any responsibility regarding the yield, performance or any other material or personal damage resulting from the incorrect use of the products concerned or the information contained in this Technical datasheet.

The information contained in this technical datasheet is subject to periodic modification, without prior notice, due to the policy of evolution and continuous improvement of our products and services, providing solutions with quality to satisfy our customers' requirements.

