



WEGPOXI WET SURFACE 89 PW UL

PRODUCT DESCRIPTION

Two-component polyamine epoxy primer/finish, high solids, high-build, with aluminum-based anticorrosive pigmentation, providing superior barrier corrosion protection. Tolerant to surfaces: applicable on dry/wet blasted, hydroblasted, or manually/mechanically treated steel substrates. Can be used as a system converter. Offers excellent anticorrosive protection in aggressive environments.

RECOMMENDED USE

Ships, maritime structures, and offshore: internal and external painting of potable water and ballast tanks, decks, oil exploration platforms, onboard machinery. Industrial applications: pulp and paper, chemical and petrochemical, bridges, metal structures, and various machinery, mining, among others. Pipes: can be applied inside and outside of pipelines.

CERTIFICATIONS AND APPROVALS

Pre-qualified according to NORSOK M-501, Edition 6, System 1.

Pre-qualified according to NORSOK M-501, Edition 5, System 1.

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

Product approved as part of a painting plan for UL 1332 - Organic Coatings for Steel Enclosures for Outdoor Use electrical equipment.

PACKAGING

Component A	3.6L Package containing 3.08L 20L Package containing 17.15L
Component B	0.9L Package containing 0.52L 4L Package containing 2.85L

CHARACTERISTICS

Color	Bronze.
Gloss	Semi-Matte
VOC content	490.68 g/l
Volume Solids	83 ± 2% (ISO 3233)
Shelf Life	24 months
Dry Film Thickness	150 µm - 300 µm
Dry Heat Resistance	Maximum temperature 120 °C. The product maintains its chemical properties up to a temperature of 120 °C, but from 60°C, color and gloss variations in the paint may occur.
Theoretical Coverage	3,69 m ² /l without dilution at a dry film thickness of 225 µm. Loss factors during application are not considered.

DRYING

Drying

	5 °C	10 °C	25 °C	35 °C
Touch	12 hours	8 hours	3 hours	2 hours
Manipulation	36 hours	24 hours	8 hours	6 hours
Final	336 hours	240 hours	168 hours	144 hours

Recoat Drying

	5 °C	10 °C	25 °C	35 °C
Minimum	36 hours	24 hours	8 hours	6 hours
Maximum	30 days	21 days	15 days	7 days

SURFACE PREPARATION



Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The surface must be clean, dry, and free of contaminants. Completely remove oils, greases, and fats according to SSPC-SP1.

Remove accumulated dirt using a dry brush, clean dry cloth, compressed air blow, vacuum, or a combination of these. Remove soluble salts by washing with plenty of fresh water, preferably under low pressure (up to 5,000 psi), according to SSPC-SP12/NACE No. 5 standard.

Recommended Surface Profile

It is recommended a roughness profile between 50 and 75 micrometers.

Abrasive Blasting

Perform abrasive blasting to near-white metal, Sa 2½ grade, according to ISO 8501-1 visual standard (A Sa 2½, B Sa 2½, C Sa 2½, D Sa 2½), or according to SSPC-SP10/NACE No. 2, visual standard SSPC-VIS 1 (A SP10, B SP10, C SP10, D SP10, G1 SP10, G2 SP10, G3 SP10).

Inspect the freshly blasted surface, observing defects that may appear after treatment. Correct them by grinding, filling with welds and/or epoxy putty.

For areas near marine environments, wash with fresh water at low pressure (minimum 3,000 psi) before abrasive blasting. In some cases, repeat washing after blasting to remove soluble contaminants and perform a new abrasive blasting.

If oxidation occurs between the end of abrasive blasting and coating application, the surface must be blasted again until the specified visual standard is achieved.

Water Jetting

Perform hydroblasting (pressure e 10,000 psi) according to SSPC-SP 12/NACE No. 5, reaching WJ-2 grade (C WJ-2, D WJ-2, E WJ-2, F WJ-2, G WJ-2, and H WJ-2) of SSPC-VIS 4/NACE VIS 7 visual standard.

It is recommended to paint on hydroblasted surfaces to CWJ-2 grade according to SSPC-VIS 4. The product can be applied on surfaces with light flash rust, grade CWJ-2L.

Hand and Power Tool Cleaning

Perform manual mechanical cleaning for carbon steel surfaces with oxidation grades C or D, according to SSPC-VIS 3 visual standards. For previously painted surfaces with grades E, F, or G, follow SSPC-VIS 3.

If manual mechanical cleaning is not possible, alternatively perform commercial abrasive blasting, Sa 2 grade according to ISO 8501-1 visual standard (C Sa 2 and D Sa 2) or SSPC-SP 6/NACE No. 3, visual standard SSPC-VIS 1 (C SP 6, D SP 6).

Maintenance and Repair

When the aged coating shows good adhesion, perform light sanding to break gloss, followed by dust and residue cleaning to ensure better adhesion between coats.

Carbon Steel Surfaces

Hard surface layers (e.g., layers resulting from flame cutting) must be removed by grinding before starting abrasive blasting.

All welds must be inspected and, if necessary, repaired before completing abrasive blasting. Porosities, cavities, weld splatter, etc., must be repaired with proper mechanical treatment or welding repair. In other areas, round edges and sharp corners (r e 2 mm, ISO 8501-3).

Over Primer

Respect the product recoat interval. If exceeded, perform light manual/mechanical sanding to break gloss and clean dust/residues for better adhesion between coats.

Over Aged Coating

For aged paint with good adhesion, perform light sanding to break gloss and clean dust/residues, ensuring better adhesion between coats.

It is recommended to test the paint on a small area to check compatibility and ensure aged paint is well adhered. Loose or poorly adhered paints must be removed. Repainting should be done only on well-preserved surfaces.

It is acceptable to adopt less stringent preparation standards as long as contaminant absence is ensured via high-pressure fresh water cleaning (5,000-10,000 psi) according to SSPC-SP12/NACE



No.5. In case of doubt, consult the technical area.

Remove all contaminants from the existing paint. Areas where the film is not adhered must be removed with light blasting grade Sa 1 (brush off) or according to SSPC-SP7, ISO 8501-1 visual standard. Corrosion points, worn, or damaged areas must be prepared by commercial abrasive blasting grade Sa 2, ISO 8501-1 standard or SSPC-SP6/NACE No.3, SSPC-VIS 1 standard. If not possible, use rotary-mechanical tools according to SSPC-SP 11.

For intact and well-preserved Inorganic Zinc Silicate Shop Primers, prepare only with a nylon brush or low-pressure fresh water washing (up to 5,000 psi), according to SSPC-SP12/NACE No.5.

For Epoxy Iron Oxide Shop Primers, ensure primer is intact, clean, and dry. If the maximum recoat interval is exceeded, perform manual/mechanical sanding to break gloss and ensure adhesion between layers.

APPLICATION PREPARATION

Mixing	Homogenize the content of each component using mechanical or pneumatic stirring (A and B). Ensure no sediment remains at the bottom of the container. Add component B to component A in the indicated mixing ratio under stirring until completely homogenized, respecting the mixing ratio.
Mixing Ratio	By volume: 6 A x 1 B.
Thinner	EPOXY DILUENT 3005
Alternative Thinners	PU 5003 Diluent - Recommended for temperatures below 25 °C. PU 5007 Diluent - Recommended for temperatures above 35 °C and baking cure. PU 5004 Diluent - Recommended for temperatures between 25°C and 35°C.
Dilution	Depending on the application method, dilute to a maximum of 10%.
Notes	The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.
Pot Life	4 h The shelf life of the mixture is reduced as the ambient temperature increases. The pot-life test of the mixture is carried out according to ABNT NBR 15742; however, different volumes of paint prepared at once, combined with varying ambient and paint temperatures, will affect the mixture's shelf life, potentially resulting in outcomes different from those stated in this technical bulletin.
Induction Time	No induction time required. In very hot locations, we recommend consulting WEG's Technical Department.

APPLICATION METHODS

Conventional Spray Gun	Spray gun: JGA 502/3 Devilbiss or equivalent Fluid nozzle: EX Air cap: 704 Atomization pressure: 50 - 70 psi Tank pressure: 10 - 20 psi.
Airless Spray Gun	Airless: Use minimum pump 60:1 Fluid pressure: 2000 - 3000 psi Hose: 1/4" inner diameter Nozzle: 0.017" - 0.025".



Roller	<p>Use a short-haired, seamless wool or synthetic roller for epoxy paints.</p> <p>Recommended only for small areas or touch-ups. Use a low-pile seamless wool roller or synthetic roller for epoxy paints.</p> <p>For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.</p>
Brush	<p>Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups).</p>
Cleaning of the equipments:	EPOXY DILUENT 3005
Notes	<p>The data presented serves as a guide and similar equipment may be used.</p> <p>Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination.</p> <p>Do not allow catalyzed product to remain in contact with application equipment, as at temperatures above the indicated "pot life", the paint will show variation in flow and will harden, making cleaning difficult.</p> <p>Before application, ensure that the equipment and respective components are clean and in optimal condition.</p> <p>After mixing two-component products, if there are application stops and the pot life has been exceeded (paint shows variation in flow), it can no longer be re-thinned for later application.</p> <p>In spray application, overlap each gun pass by 50%, finishing with a cross pass. This technique avoids uncovered or unprotected areas and ensures proper aesthetic finish.</p> <p>Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.</p> <p>Clean all equipment immediately after use.</p> <p>It is considered good practice to periodically wash the spraying equipment during the day. The cleaning frequency depends on the amount sprayed, temperature, and elapsed time, including all delays.</p>

APPLICATION PERFORMANCE

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Do not apply the product after the pot life has been exceeded.

Not recommended for highly alkaline and/or acidic corrosive environments. Consult WEG Technical Department.

For optimal application properties, the paint temperature should be between 21°C and 27°C before mixing and application.

Before application, observe weather conditions: there must be no threat of rain or drizzle. Surface temperature must be at least 3°C above the dew point, and relative humidity should not exceed 85%. Adverse conditions may cause color variations and other characteristics. Consult WEG Technical Department.

Painting is recommended only if surface temperature is at least 3°C above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

Epoxy-based products are known for their excellent anticorrosive properties and low resistance to sun exposure. When the applied film is exposed to weathering, over time it will lose gloss, a phenomenon known as chalking, which consequently alters its color. It is important to note that,



despite this chalking, the film's anticorrosive protection is not compromised.

Under adverse weather conditions in indoor and/or outdoor environments with high relative humidity, rain or drizzle, low or very low temperatures, and excessively high temperatures, variations in color and other product characteristics may occur. Please consult WEG's Technical Department for more information.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.
