

W-POXI ENG 127

PRODUCT DESCRIPTION

Single-component epoxy primer/finish, extra-fast drying, with good applicability. Excellent adhesion to carbon steel prepared by abrasive blasting. Applicable in a single high-build coat, simplifying the painting process.

RECOMMENDED USE

Recommended for painting metal structures, exterior of tanks, pipelines, silos, and various equipment, whether new or maintenance, in pulp and paper, sugar ethanol, chemical and petrochemical industries, among others. Recommended for low to medium aggressiveness environments.

CERTIFICATIONS AND APPROVALS

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

PACKAGING

Component A 200L Package containing 200L

CHARACTERISTICS

Color	RAL, Munsell, or according to the customer's standard.
Gloss	Satin
Volume Solids	37 ± 3% (ISO 3233)
Dry Film Thickness	75 µm - 150 µm
Dry Heat Resistance	Maximum temperature 100 °C. The product maintains its chemical properties up to a temperature of 100 °C, but from 60°C, color and gloss variations in the paint may occur.
Theoretical Coverage	3,29 m ² /l without dilution at a dry film thickness of 113 µm. Loss factors during application are not considered.

DRYING

Drying

	10 °C	25 °C	35 °C
Touch	15 min	7 min	5 min
Manipulation	40 min	20 min	15 min
Final	168 hours	168 hours	120 hours

Recoat Drying

	10 °C	25 °C	35 °C
Minimum	40 min	20 min	15 min
Maximum	6 meses	6 meses	6 meses

SURFACE PREPARATION

Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The surface must be clean, dry, and free of contaminants. Completely remove oils, greases, and fats according to SSPC-SP1.

Remove accumulated dirt using a dry brush, clean dry cloth, compressed air blow, vacuum, or a combination of these. Remove soluble salts by washing with plenty of fresh water, preferably under low pressure (up to 5,000 psi), according to SSPC-SP12/NACE No. 5 standard.

Abrasive Blasting

Perform abrasive blasting to near-white metal, Sa 2½ grade, according to ISO 8501-1 visual standard (A Sa 2½, B Sa 2½, C Sa 2½, D Sa 2½), or according to SSPC-SP10/NACE No. 2, visual standard SSPC-VIS 1 (A SP10, B SP10, C SP10, D SP10, G1 SP10, G2 SP10, G3 SP10).

Evaluate the surface after blasting, observing revealed defects and adopt practices to minimize

them, such as grinding or filling.

APPLICATION PREPARATION

Mixing	Homogenize the contents of each component by mechanical or pneumatic agitation (A and B). Add component B to component A according to the indicated mixing ratio, under agitation, until fully homogenized.
Dilution	Dilute if necessary.
Notes	The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.
Induction Time	No induction time required. In very hot locations, we recommend consulting WEG's Technical Department.

APPLICATION METHODS

Conventional Spray Gun	Spray gun: JGA 502/3 Devilbiss or equivalent Fluid nozzle: EX Air cap: 704 Atomization pressure: 50 - 65 psi Tank pressure: 10 - 30 psi.
Airless Spray Gun	Use minimum pump 60:1 Fluid pressure: 2100 - 2400 psi Hose: 1/4" inner diameter Nozzle: 0.015" - 0.019".
Roller	Use a short-haired, seamless wool or synthetic roller for epoxy paints. For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.
Brush	Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups). For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.
Notes	The data presented serves as a guide and similar equipment may be used. Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination. Before application, ensure that the equipment and respective components are clean and in optimal condition. Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas. Clean all equipment immediately after use. Do not leave material in hoses, guns, or equipment used for spraying. Thoroughly wash all used equipment. It is considered good practice to periodically wash the spraying equipment during the day. The cleaning frequency depends on the amount sprayed, temperature, and elapsed time, including all delays.

APPLICATION PERFORMANCE

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Proper washing and degreasing of the surface are essential, as well as sanding of old paints whenever necessary to promote adhesion.



In situations where the product is intended for internal tank painting, dilution for application is not recommended.

For optimal application properties, the paint temperature should be between 21°C and 27°C before mixing and application.

Surface preparation is recommended to Sa 2½ or SSPC SP10 (ISO 8501-1 visual standard). Less stringent standards are acceptable as long as there are no contaminants, supplemented with high-pressure water cleaning.

Painting is recommended only if surface temperature is at least 3°C above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Must not be applied under adverse conditions, such as relative humidity (RH) above 85%, as color and appearance changes may occur.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

On freshly painted surfaces in direct contact with water during the curing process, localized staining with color change (more visible in darker colors), curing delay, and compromised product performance may occur.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

SYSTEM COMPATIBILITY AND MAINTENANCE REPAINTING

It must be ensured that the original material is well adhered. All non-adherent paint must be removed.

W-ESTER ERD 955 R can be applied over aged coatings or other paint systems. However, it is recommended to test the compatibility of W-ESTER ERD 955 R with the previous coating on a small test area.

When applying topcoats over W-ESTER ERD 955 R, the specified overcoating interval must be observed.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.