

Technical Data Sheet



LIGHT PLASTIC ADHESIVE ST

	Product Description	Product based on polyester resin developed to correct surface defects, replacing quick putty and putty plastic in a single product. It is a product with high concentration of titanium dioxide providing softer sanding and white color. It is a product with a high solids content, easy to apply and excellent sandability.	
Recommended for correcting imperfections on metal surfaces automotive, and also to correct defects in wood, marble and granite.		Useful life 9 months	
			Mixing Ratio
	Hardener	MEK peroxide (liquid).	
	Application Viscosity	N/A	
	Application	Apply the product with the help of celluloid, in thin layers until the defect is corrected.	
	Catalyzed product useful life 25°C 77°F	5 - 8 minutes	
	Number of Coats	1 – 3 pass	1 pass: 80 a 120 µm
	Drying 10°C 50°F Drying 25°C 77°F	Touch 20 minutes Handling 40 minutes Sanding 80 minutes Touch 15 minutes Handling 30 minutes Sanding 60 minutes	
Sanding		Use dry sandpaper 80 - 150 - 220.	

- Carry out a degreased good of the pieza to be repainted
- Avoid excessive thicknesses
- Cleaning of application tools with acrylic / polyurethane thinners;
- Necessary application of Wash-primer for better product adhesion and anti-corrosion protection;
- Use hardener and thinner as recommended;
- Always use the set of WEG products and complements.

The technical information is the result of our experience. We guarantee the quality of the product, however, if the conditions of use are not under our control, we cannot assume any responsibility for the results obtained.