

W-LACK PRIMER OCEAN 395

PRODUCT DESCRIPTION

Single-component alkyd resin primer, fast-drying and high-build.

RECOMMENDED USE

Indicated for painting new constructions, maintenance, and repairs above the waterline.

PACKAGING

Single Component

0.95 US gal Package containing 0.95 US gal

5.28 US gal Package containing 5.28 US gal

CHARACTERISTICS

Color

Gray.
Red Oxide.

Gloss

Gloss

VOC content

1.78 lb/gal

Volume Solids

57 ± 3% (ISO 3233)

Shelf Life

12 months

Dry Film Thickness

2.6 mils - 3.0 mils

Dry Heat Resistance

Maximum temperature 140 °F.
The product maintains its chemical properties up to a temperature of 140 °F, but from 140°F, color and gloss variations in the paint may occur.

Theoretical Coverage

331.7 ft²/gal without dilution at a dry film thickness of 2.8 mils. Loss factors during application are not considered.

DRYING

Drying

50 °F	77 °F	95 °F
2 hours	1 hour	30 min
4 hours	3 hours	2 days
96 hours	72 hours	60 hours

Recoat Drying

	50 °F	77 °F	95 °F
Minimum	24 hours	12 hours	8 hours
Maximum	5 days	5 days	5 days

SURFACE PREPARATION

Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

Remove accumulated dirt using a dry brush, clean dry cloth, compressed air blow, vacuum, or a combination of these. Remove soluble salts by washing with plenty of fresh water, preferably under low pressure (up to 5,000 psi), according to SSPC-SP12/NACE No. 5 standard.

The surface must be clean, dry, and free of any contaminants. Remove oils, greases, and fats according to SSPC-SP1 standard.

Recommended Surface Profile

It is recommended a roughness profile between 1.57 and 2.36 mils.

Maintenance and Repair

The surface must be clean, dry, and free of contaminants. Completely remove oils using clean cloths soaked in cleaning Diluent according to SSPC SP1. Replace cloths to avoid saturation during cleaning. Do not use rags or colored cloths.



Corrosion spots, worn, or damaged areas must be prepared by commercial abrasive blasting, Sa 2 grade of ISO 8501-1 visual standard or according to SSPC-SP 6/NACE No. 3, visual standard SSPC-VIS 1. If not possible, use manual or mechanical cleaning to St 2 grade according to SSPC-SP2, ISO 8501-1 visual standard.

Carbon Steel Surfaces

Hard surface layers (e.g., layers resulting from flame cutting) must be removed by grinding before starting abrasive blasting.

All welds must be inspected and, if necessary, repaired before completing abrasive blasting. Porosities, cavities, weld splatter, etc., must be repaired with proper mechanical treatment or welding repair. In other areas, round edges and sharp corners (r e 0.0787 in, ISO 8501-3).

APPLICATION PREPARATION

Mixing	Homogenize the content of the container using mechanical or pneumatic stirring. Ensure no sediment remains at the bottom of the container.
Thinner	RAZ SOLVENT
Dilution	Depending on the application method, dilute to a maximum of 5%.
Notes	The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.
Pot Life	Not relevant.

APPLICATION METHODS

Conventional Spray Gun	Spray gun: JGA 502/3 Devilbiss or equivalent Fluid nozzle: EX Air cap: 704 Atomization pressure: 50 - 70 psi Tank pressure: 10 - 20 psi.
Roller	Use a short-haired, seamless wool or synthetic roller for epoxy paints. For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.
Brush	Use a brush 3.0 to 3.94 inches wide for larger surfaces and 0.98 to 1.5 inches for touch-ups.
Cleaning of the equipments:	RAZ SOLVENT
Notes	Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination. Before application, ensure that the equipment and respective components are clean and in optimal condition. In spray application, overlap each gun pass by 50%, finishing with a cross pass. This technique avoids uncovered or unprotected areas and ensures proper aesthetic finish. Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas. Clean all equipment immediately after use. Do not leave material in hoses, guns, or equipment used for spraying. Thoroughly wash all used equipment. It is considered good practice to periodically wash the spraying equipment during the day. The cleaning frequency depends on the amount sprayed, temperature, and elapsed time, including all delays.

APPLICATION PERFORMANCE



For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

For optimal application properties, the paint temperature must be between 69.8°F - 80.6°F before mixing and application.

Before application, observe weather conditions: there must be no threat of rain or drizzle. Surface temperature must be at least 37.4°F above the dew point, and relative humidity should not exceed 85%. Adverse conditions may cause color variations and other characteristics. Consult WEG Technical Department.

We recommend painting only if the measured surface temperature is at least 5.4°F above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Product not recommended for internal tank painting.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

Under adverse weather conditions in indoor and/or outdoor environments with high relative humidity, rain or drizzle, low or very low temperatures, and excessively high temperatures, variations in color and other product characteristics may occur. Please consult WEG's Technical Department for more information.

SYSTEM COMPATIBILITY AND MAINTENANCE REPAINTING

The primer repainting interval must be respected for the application of the topcoat. If the maximum interval indicated is exceeded, manual/mechanical sanding with sandpaper to remove gloss is necessary. The primer surface must be dry and free of contaminants.

It is recommended to apply the W-LACK OCEANO 395 topcoat over the W-LACK PRIMER OCEANO 395; respect the primer repainting interval before applying the topcoat.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.