



**POLITHERM 96 WFQ R SM MARROM AMBAR 73466 MA**

**Code:** 17524871

**PRODUCT DESCRIPTION**

QUALICOAT-approved polyester powder coating, offering excellent adhesion and flexibility, as well as good chemical and yellowing resistance. It has high physical resistance and excellent weathering resistance.

**RECOMMENDED USE**

QUALICOAT-approved coating for metal parts intended for industrial and architectural applications in outdoor environments.

**PROPERTIES**

This coating, when properly applied and cured is suitable for the use of adhesives and sealants. However, because of the different products on the market, it requires prior testing by the user in order to select the adhesive and / or sealant appropriate.

**CERTIFICATIONS AND APPROVALS**

Free from heavy metals and other substances provided for in RoHs Directive 2015/863 EU of 31/03/2015.

The Politherm 96 WFQ line is QUALICOAT APPROVAL N° P-1717 Class 1, Category 1 certified and complies with AAMA 2603 standard.

**PACKAGING**

Cardboard box with 55 lb in high-density polyethylene bag.

**CHARACTERISTICS OF MANUFACTURED PRODUCT**

<b>Resin</b>	Polyester
<b>Gloss</b>	Matte
<b>Finish</b>	Smooth
<b>Specific gravity (± 0,10)</b>	1,49 g/cm³
<b>Theoretical Coverage</b>	131.0 ft²/lb at 1.0 mil
<b>Mass loss during cure</b>	Maximum 2%
<b>Moisture content</b>	Maximum 0.6%
<b>Shelf life</b>	12 months
<b>Storage condition</b>	It must be stored in closed containers, in cool, dry and covered places, at an ambient temperature not exceeding 86°F.

**APPLICATION CHARACTERISTICS**

<b>Substrate</b>	Aluminum Galvanized steel
<b>Surface preparation</b>	Aluminum: Chromatization. Aluminum: Nanoceramic Galvanized steel: Phosphatization.
<b>Surface cleaning</b>	The performance of this product is related to the degree of surface preparation. The surface must be clean, dry and free of any contaminants. Completely remove oils, grease and fats.
<b>Thickness</b>	2.4 mils - 3.1 mils
<b>Cure conditions</b>	10 min à 392 °F (metal temperature).
<b>Cure windows</b>	12 min - 20 min at 374 °F 10 min - 15 min at 392 °F
<b>Application system</b>	Electrostatic spray gun corona

**CHARACTERISTICS OF APPLIED PRODUCT**



<b>Test</b>	<b>Specification/Standard</b>
<b>Adhesion</b>	5B (ASTM D 3359)
<b>Gloss 60°</b>	20 - 30 (ASTM D523)
<b>Impact</b>	Minimum 43 lb.in (ASTM D2794)
<b>Flexibility (conic mandrel)</b>	Maximum 1/8 in (ASTM D790)
<b>Cupping test</b>	Minimum 1/5 in (EN ISO 1520)
<b>Indentation</b>	Minimum 80 (EN ISO 2815)
<b>Bend test (5mm diameter cilinder)</b>	No cracking or detachment (EN ISO 1519)

**CHEMICAL RESISTANCE CHARACTERISTICS**

<b>Test</b>	<b>Specification/Standard</b>
<b>Humidity</b>	Minimum 2000h (ASTM D2247)
<b>Acetic salt spray</b>	Minimum 1000h (ISO 9227)
<b>Salt spray</b>	Minimum 1000h (ASTM B117)

**NOTE:**

Chemical resistance and mechanical strength tests were performed on aluminum sheets pretreated with zirconium nanoceramic under curing conditions and coatings specific to the product. Values may vary depending on the substrate and pretreatment used.

**SAFETY PRECAUTIONS**

Guidance is available in the product's Safety Data Sheet (SDS).

**NOTE**

The information provided herein is based on our testing and experience and is intended to inform you about the product and its possible applications. The information provided in this bulletin is not intended to be complete, and the user assumes the risk of using the product for a purpose other than the specifications recommended in this bulletin without first obtaining our written confirmation of its suitability for the intended purpose. While we strive to ensure the accuracy of the information provided herein, we cannot control the quality or condition of the substrate, nor any other factors that affect the use and application of this paint. Therefore, unless we agree in writing to any condition that deviates from our recommendations, we accept no liability that may arise regarding the performance of this product. The information contained in this bulletin is subject to change without notice, based on our experience and policy of continuous development.