



## POLITHERM 20 R SM WHITE MOEZ 60728 UM

**PRODUCT:** 18774323

**DESCRIPTION / USES:** Metallic parts coating for indoor use.

### CHARACTERISTICS:

|                          |                                                                                                       |
|--------------------------|-------------------------------------------------------------------------------------------------------|
| <b>Resin:</b>            | Epoxy / Polyester                                                                                     |
| <b>Specific gravity:</b> | 1,69 g/cm <sup>3</sup>                                                                                |
| <b>Shelf life:</b>       | 6 months (max. 86 °F)                                                                                 |
| <b>Observations:</b>     | Free of heavy metals and other substances provided for in Directive 2015/863 EU of 03/31/2015 (RoHS). |

### APPLICATION CHARACTERISTICS:

|                             |                                                                              |
|-----------------------------|------------------------------------------------------------------------------|
| <b>Surface:</b>             | Ferrous and non-ferrous                                                      |
| <b>Surface preparation:</b> | Ferrous : Phosphatization<br>Non-ferrous: Chromatization or phosphatization* |
| <b>Cure conditions:</b>     | 10 minutes at 392 °F                                                         |
| <b>Thickness:</b>           | 2.4 - 3.1 mils                                                               |
| <b>Application system:</b>  | Electrostatic gun                                                            |

### AFTER CURE CHARACTERISTICS:\*\*\*

| TEST                        | METHOD               | SPECIFICATION    |
|-----------------------------|----------------------|------------------|
| ADHESION                    | ASTM D 3359          | 5B               |
| GLOSS @ 60°                 | ASTM D 523           | 1 - 5 UB         |
| IMPACT (REVERSE)            | ASTM 2794            | Minimum 43 Lb/in |
| FLEXIBILITY (CONIC MANDREL) | ASTM D 790 / ISO 178 | Minimum 3 mm     |

### CHEMICAL RESISTANCE \*\*\*

|                    |                                |
|--------------------|--------------------------------|
| <b>Salt spray:</b> | Minimum 500 h (ASTM B117 - 03) |
| <b>Humidity:</b>   | Minimum 1000 h (89,6 °F)       |

\* For non-ferrous metals phosphatizing, please contact our technical service.

\*\* After stabilization on correct temperature (metal temperature).

\*\*\* The tests were conducted on degreased steel panels in accordance with the cure and thickness specifications. The results may vary, depending on the surface characteristics. For chemical resistance testing, panels were degreased and treated with tricationic phosphat.

**IMPORTANT:** If is not possible the use of the product according to the directions given above we ask you to contact our technical service.

**STORAGE:** Fresh, dry and covered place.

COPY FOR INFORMATION

Review: 0

Date: 09/07/2025