

POLITHERM 20 TX GREEN RAL 6024 BR

PRODUCT: 12502706

DESCRIPTION / USES: Metallic parts coating for indoor use.

CHARACTERISTICS:

Resin:	Epoxy / polyester
Specific gravity:	1,70 ± 0,10 g/cm ³
Stability:	12 months (máx. 30°C)

APPLICATION CHARACTERISTICS:

Surface:	Ferrous and non-ferrous
Surface preparation:	Ferrous: Phosphatization Non-ferrous: Chromatization or phosphatization*
Cure conditions:	10 minutes at 200 °C**
Thickness:	70 – 90 µm
Application system:	Electrostatic gun

AFTER CURE CHARACTERISTICS***:

TEST	METHOD	SPECIFICATION
ADHESION	WPS-3905	GR0
GLOSS	WPS-3854	Visual Std
IMPACT (REVERSE)	WPS-4130	Min. 40 kg X cm
FLEXIBILITY (CONIC MANDREL)	WPS-4856	Max. 5 mm

CHEMICAL RESISTANCE ***

Salt spray:	Min. 500 h (ASTM B117 – 73)
Humidity:	Min. 1000 h (35°C)

* For non-ferrous metals phosphatizing, please contact our technical service.

** After stabilization on correct temperature (metal temperature).

*** The tests were conducted on degreased steel panels in accordance with the cure and thickness specifications. The figures may be change, depending on the surface characteristics. For chemical resistance tests the panels were degreased and treated with tricationic phosphat.

IMPORTANT: If is not possible the use of the product according to the directions given above we ask you to contact our technical service.

STORAGE: Fresh, dry and covered place.