



W-LACK FINISH



PRODUCT DESCRIPTION	Fast-drying modified alkyd resin topcoat.
----------------------------	---

RECOMMENDED USE	Indicated for painting metal structures, agricultural and road implements, machinery, and equipment.
------------------------	--

CERTIFICATIONS AND APPROVALS	When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.
-------------------------------------	--

PACKAGING	Single Component	20L Package containing 20L
------------------	-------------------------	----------------------------

CHARACTERISTICS	Color	Aluminum.
	Gloss	Gloss
	Volume Solids	35 ± 5% (ISO 3233)
	Shelf Life	12 months
	Dry Film Thickness	30 µm - 40 µm
	Dry Heat Resistance	Maximum temperature 60 °C. Organic coatings can undergo changes in color, gloss, and adhesion when exposed to temperatures above 60 °C.
	Theoretical Coverage	10,00 m ² /l without dilution at a dry film thickness of 35 µm. Loss factors during application are not considered.

DRYING	Drying	25 °C
	Touch	20 min
	Manipulation	5 hours
	Final	168 hours
	Recoat Drying	25 °C
	Minimum	12 hours
	Maximum	16 hours

SURFACE PREPARATION

Standard Surface Preparation
The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The surface must be clean, dry, and free of contaminants. Completely remove oils, greases, and fats according to SSPC-SP1.

Maintenance and Repair
NOTE: Respect the recoating interval for subsequent coat application. If exceeded, perform light manual/mechanical sanding to break the previous coat gloss, followed by dust and residue cleaning to ensure better adhesion between paint layers.

Over Primer
The product must be applied over a specific primer. The primer must be clean, dry, and free of contaminants. The topcoat must be applied within the primer recoat interval. Consult the primer technical bulletin for correct application.

Respect the product recoat interval. If exceeded, perform light manual/mechanical sanding to break



gloss and clean dust/residues for better adhesion between coats.

APPLICATION PREPARATION

Mixing	Homogenize the content of the container using mechanical or pneumatic stirring. Ensure no sediment remains at the bottom of the container.
Thinner	DILUENT 1001
Alternative Thinners	Dilution is not recommended.
Dilution	Depending on the application method, dilute to a maximum of 15%.
Notes	The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.
Pot Life	Not relevant.

APPLICATION METHODS

Conventional Spray Gun	Spray gun: JGA 502/3 Devilbiss or equivalent Fluid nozzle: EX Air cap: 704 Atomization pressure: 60 - 65 psi Tank pressure: 10 - 20 psi.
Roller	Not recommended. For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.
Brush	Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups).
Cleaning of the equipments:	DILUENT 1001
Notes	The data presented serves as a guide and similar equipment may be used. Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination. Before application, ensure that the equipment and respective components are clean and in optimal condition. In spray application, overlap each gun pass by 50%, finishing with a cross pass. This technique avoids uncovered or unprotected areas and ensures proper aesthetic finish. Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas. Clean all equipment immediately after use. Do not leave material in hoses, guns, or equipment used for spraying. Thoroughly wash all used equipment. It is considered good practice to periodically wash the spraying equipment during the day. The cleaning frequency depends on the amount sprayed, temperature, and elapsed time, including all delays.

APPLICATION PERFORMANCE

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Light colors may require more than one coat to achieve uniform coverage.

For optimal application properties, the paint temperature should be between 21°C and 27°C before mixing and application.



Painting is recommended only if surface temperature is at least 3°C above the dew point.

Must not be applied under adverse conditions, such as relative humidity (RH) above 85%, as color and appearance changes may occur.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.
