

POLITHERM 29 TF R SM PAC BLACK UL W RAL 9005 MA

Code: 17640646

PRODUCT DESCRIPTION

TGIC-free polyester powder coating with good adhesion, flexibility and chemical resistance. It has high physical resistance and good weathering resistance.

RECOMMENDED USE

Coating of metal parts for industrial purposes in outdoor environments.

PROPERTIES

Enhanced with additives to reduce baking time and/or temperature.

CERTIFICATIONS AND APPROVALS

Free from heavy metals and other substances provided for in RoHs Directive 2015/863 EU of 31/03/2015.

Powder coating certified according to UL license MH63984.

PACKAGING

Cardboard box with 25 kg in high-density polyethylene bag.

CHARACTERISTICS OF MANUFACTURED PRODUCT

Resin	Polyester
Gloss	Matte
Finish	Smooth
Specific gravity ($\pm 0,10$)	1,51 g/cm ³
Theoretical Coverage	9,46 m ² /kg in medium thickness 70 μ m
Mass loss during cure	Maximum 2%
Moisture content	Maximum 0,6%
Shelf life	12 months
Storage condition	It must be stored in closed containers, in cool, dry and covered places, at an ambient temperature not exceeding 30°C.

APPLICATION CHARACTERISTICS

Substrate	Ferrous metals Non-ferrous metals
Surface preparation	Ferrous : Phosphatization or nanoceramic Non-ferrous: Chromatization or nanoceramic
Surface cleaning	The performance of this product is related to the degree of surface preparation. The surface must be clean, dry and free of any contaminants. Completely remove oils, grease and fats.
Thickness	60 μ m - 80 μ m
Cure conditions	10 min à 180 °C (metal temperature).
Cure windows	15 min - 25 min at 170 °C 10 min - 20 min at 180 °C 7 min - 15 min at 190 °C 5 min - 12 min at 200 °C
Application system	Electrostatic spray gun corona

NOTE:

For non-ferrous metals phosphatizing, please contact our technical service.



CHARACTERISTICS OF APPLIED PRODUCT

Test	Specification/Standard
Adhesion	Maximum GR0 (ASTM D3359)
Gloss 60°	20 - 25 (ASTM D523)
Impact	Minimum 50 kg.cm (ASTM D2794)
Flexibility (conic mandrel)	Maximum 3,00 mm (ASTM D790)

CHEMICAL RESISTANCE CHARACTERISTICS

Test	Specification/Standard
Humidity	Minimum 1500h (ASTM D2247)
Salt spray	Minimum 700h (ASTM B117)

NOTE:

In the chemical resistance tests, the substrate used was cold-rolled steel sheet with tricationic phosphate. The mechanical resistance tests were performed on degreased common. The tests for UL certification were carried out on sheets of cold-rolled steel and hot-rolled steel substrate, with iron phosphate treatments and nanoceramics. Both single-layer and two-layer paint systems were evaluated using the products Politherm 22 R UL and Politherm 29 R UL. In the two-layer system, Politherm 22 R UL was used as a coating, followed by a finishing layer with Politherm 29 R UL. The test conditions included tests of moisture resistance in controlled atmosphere containing carbon dioxide (CO2), sulfur dioxide (SO2) and air as per UL specification with a minimum requirement of 1200 hours. Salt fog tests were performed according to ASTM B117 standard, with a minimum requirement of 600 hours.

SAFETY PRECAUTIONS

Guidance is available in the product's Safety Data Sheet (SDS).

NOTE

The information provided herein is based on our testing and experience and is intended to inform you about the product and its possible applications. The information provided in this bulletin is not intended to be complete, and the user assumes the risk of using the product for a purpose other than the specifications recommended in this bulletin without first obtaining our written confirmation of its suitability for the intended purpose. While we strive to ensure the accuracy of the information provided herein, we cannot control the quality or condition of the substrate, nor any other factors that affect the use and application of this paint. Therefore, unless we agree in writing to any condition that deviates from our recommendations, we accept no liability that may arise regarding the performance of this product. The information contained in this bulletin is subject to change without notice, based on our experience and policy of continuous development.