

W-NÍLICA PRIMER CINZA

PRODUCT DESCRIPTION: Primer based on modified vinyl resin. One-component primer, excellent anti-corrosion protection.

RECOMMENDED USES: Recommended as primer for internal and external structure of equipment that requires excellent adhesion. This product is versatile because it is single-component, ready for use and easy to apply. It has excellent coverage. It has fast drying, so it can be used in the painting of other equipment requiring the application of the topcoat soon after the previous coat.

CERTIFICATIONS AND APPROVAL: This product, when supplied to comply with the RoHs Directive (Restriction of Certain Hazardous Substances) has the letter R in its description.

PACKAGING:	Component	Content	Package	Unit of measurement
	Monocomponent	3,6	3,6	L

CHARACTERISTICS: Color: Gray

Gloss:	Matte	15 – 30 UB
Volume solid:	21 ± 2% (ISO 3233).	
Shelf-Life:	6 months.	
Thickness per coat (dry):	30 µm –40 µm	
Theoretical coverage:	6 m ² /l without dilution in the thickness of 35 µm dry. Without considering loss factors in application.	
Resistance to dry heat:	Maximum temperature 60 °C Organic coatings can undergo alterations of color, gloss and adherence when exposed to temperatures exceeding 60 °C	
Drying:	25°C	
Touch:	20 minutes	
Handling:	1 hour	
Final:	168 hours	
Overcoating Drying:	25°C	
	Min	5 hours
	Max	24 hours
Obs	If the maximum interval indicated for applying the subsequent coat is exceeded, it is necessary to proceed with superficial sanding. This procedure is necessary to obtain adhesion between the coats.	

SURFACE PREPARATION

Treatment of Steel Carbon Surfaces

The product must be applied on carbon steel surfaces properly treated by cleaning with solvents or degreasers. Abrasive treatment or phosphating as needed.

For further information, consult WEG Technical Department.

PREPARATION FOR APPLICATION

Mixture

Homogenize the contents of the package by means of mechanical or pneumatic stirring. Ensure that no sediment is settled at the bottom of the package.

Diluent
Diluent 1001

Dilution

Depending on the application method, dilute at most 5%

The quantity of diluent may vary depending on the type of equipment used and the ambient conditions during the application.

Pot life of the mixture (25°C)

Not relevant

Conventional gun:

Gun: JGA 502 DevilBiss or equivalent

Fluid nozzle: FX

Air cap: 704

Dilution: 5%

Brush:

Only recommended for touch up small areas or stripe coat (screws, nuts, weld and sharp edges). Use a brush 75 to 100 mm wide for larger surfaces and 25 to 38 mm for touch up.

Roller:

Use a thin nap, seamless sheepskin or microfiber roller for epoxy coatings.

Cleaning the equipment:

Diluent 1001

Do not leave material in the hoses, spray guns and equipment used in the spraying. Thoroughly wash all equipment used.

NOTE:

PERFORMANCE IN THE APPLICATION

For a good performance of the product, we recommend following the directions below:

In paintings carried out in front of the sea, if exposed to sea air, we recommend to wash with fresh water between coats eliminating settled impurities.

We recommend coating only if the surface temperature is at least 3 °C above the dew point temperature.

Variations in color, aspect and gloss (more noticeable in dark colors) may occur, as well as delay in curing and low coating performance, when applied during periods of high air relative humidity, rainy days, low temperatures or drying the coating outdoor.

The temperature of the substrate, the weather and environmental conditions during the application and during the curing of the product, and the thickness of the coat may interfere in the product drying time.

For better application properties, the coating temperature should be between 21 - 27 °C prior to the mixing and application.

It should not be applied under adverse conditions, such as air relative humidity (RH) above 85%, as changes in color and appearance may occur.

In coatings with variation in application method in the same job, the final aspect and gloss of the painted surfaces may show differences.

Due to the technical characteristics of the product, we inform you that it does not always follow a reference pattern and, therefore, may present scratches, variations in color tone, drying, presence of bubbles during repainting of the finishing paint and difference in appearance between sequential batches.

Technical Quality Claims involving the characteristics described above will be considered unfounded and without indemnity coverage.

For further information, consult WEG Technical Department.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals.

Please read carefully all the information contained in the MSDS of this product, available at: www.weg.net.

Store in a covered, well-ventilated area. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas avoiding the accumulation of flammable vapors. Keep the product away



from heat and sources of ignition.

Do not inhale mists / vapors / aerosols generated during handling and / or application.

Wear protective gloves / protective clothing / eye protection / face protection.

Avoid release this product and its packaging, as well as materials used during handling and application in the environment.

NOTE:

The information contained in this technical datasheet is based upon the experience and knowledge acquired in the field by the technical team of WEG.

If using the product without previous inquiry to WEG Coating concerning its suitability for the customer's intended purpose, the customer is aware that the use shall be its exclusive responsibility, WEG not being responsible for behavior, safety, suitability or durability of the product.

Some information contained in this datasheet are estimated, and can undergo variances arising from factors outside the manufacturer's control. Thus, WEG does not guarantee and does not assume any responsibility regarding the yield, performance or any other material or personal damage resulting from the incorrect use of the products concerned or the information contained in this Technical datasheet.

The information contained in this technical datasheet is subject to periodic modification, without prior notice, due to the policy of evolution and continuous improvement of our products and services, providing solutions with quality to satisfy our customers' requirements.

