

W-MIX UHT POLIÉSTER

PRODUCT DESCRIPTION: Base Coat, single component, high coverage, polyester resin base. Available in plain, metallic and pearl colors. It composes a double layer system, applying PU Varnish over the polyester base.

RECOMMENDATIONS FOR USE: Indicated for general and partial painting and touch-ups in automotive vehicles.

PACKAGING: 0,9 L e 3,6 L

TECHINICAL FEATURES:

Expirete Data	36 months
Thickness per coat	15 - 25 micrómetros dry
Viscos. de Aplicacion	16 - 21 s CF2 77°F

Drying

25°C

Touch	05 - 10 Minutes
Handling	15 - 20 Minutes
Final	20 Minutes

SURFACE PREPARATION

For further information contact the Technical Department of WEG (tintas@weg.net).

PREPARACIÓN PARA APLICACIÓN

Mix
Homogenize the content of each of the components by means of mechanical or pneumatic agitation (A and B). Ensure that no sediment remains on the bottom of the package. Add component B to component A, in the proportions (volume) indicated, under agitation, until complete homogenization, respecting the mixing ratio.

Mix Ratio

Hardener
Part A

Thinning
100%

Thinner
DILUENTE 5870 PARA PU | POLIESTER

Pot Life (77°C)
Ready to use

Induction Period (77°C)
No induction required.

Note: In places of great heat, we recommend contacting the Technical Department of WEG.



APPLICATION

The data below is a guide, similar equipment being able to be used.

METHODS

Changes in the pressures and sizes of the nozzles may be required to improve the spraying features.

Before application, ensure that the equipment and respective components are clean and in the best condition.

Empty the compressed air line to avoid contamination of the coating.

After mixing the bicomponent products, if stoppages occur in application, and they exceed the useful life of the mixture (where the coating has variance in its fluidity), it can no longer be diluted again for later application.

Reinforce all the sharp edges, cracks and weld beads with the wide paintbrush, to avoid premature flaws in these areas. When applying by spraying, make an overlap of 50% of each spray gun application, to avoid having uncovered and unprotected areas, ending with a cross transfer.

DESEMPEÑO EN LA APLICACIÓN

For a good performance of the product, we recommend following the guidelines below:

For application by wide paintbrush or roller, it may be necessary to apply in two or more coats to obtain a uniform layer in accordance with the thickness of the film recommended per coat.

Light colors may require more than one coat to obtain uniform coverage. Product not recommended for the painting of internal parts of tanks.

If application occurs in maritime areas, it is recommended to wash the coated surfaces with freshwater between each coating, to remove all loose powdery deposits and soluble salts.

Do not apply the product after the mixture pot life, if this time is exceeded.

Surface temperature must always be a minimum of 3°C above dew point. Do not apply if temperature is below 0°C.

The temperature of the substrate, climatic and environmental conditions may interfere in the drying time of the product.

For better application properties, the paint temperature shall be between 21-27°C, before mixing and application.

It shall not be applied in adverse conditions, as relative air humidity (RH) above 85% or condensed surfaces. Color, aspect and gloss changes can be noticed in the film when application occurs in high relative humidity periods, rainy or low temperature days or when the film is exterior exposed before curing.

Polyurethane systems (component A and B) have sensitivity when exposed to relative air humidity, able to cause defects in the dry film and reduce the pot-life. Therefore, we recommend that the packaging of each one of the components, after use, is duly closed and maintained in dry places protected from weathering.

In recently painted surfaces in direct contact with water, during the cure process localized staining may occur with alteration in color (most visible in dark colors), delay in the cure and impairment in product performance.

In painting varying the application method of coatings in the same work, it may occur differences in gloss and final aspect of the coated surfaces.

For further information contact the Technical Department of WEG (tintas@weg.net).

SYSTEM COMPATIBILITY AND MAINTENANCE RECOATING

The overcoating interval of the primer shall be respected for applying the top coat. If the maximum interval indicated is exceeded, it is necessary to proceed with manual / mechanical sanding to promote surface profile. The surface of the primer shall be dry and free of contaminants.

For further information contact the Technical Department of WEG (tintas@weg.net).

SAFETY PRECAUTIONS

Before handling this product it is essential to read carefully all the information contained in the chemical product safety information sheet (MSDS), available at our site, (www.weg.net).

The preparation of the surface, handling and use of paints during the painting and drying, as it concerns inflammable products, must be performed in ventilated places, far from flames, sparks or excessive heat, using appropriate personal protection equipment (PPE) for the stage to be executed.

Contact with the skin can cause irritation.

If swallowed, do not induce vomiting. In the case of contact with the eyes, wash them abundantly with water. In either case, seek medical aid immediately.

Do not smoke in the work area.

Ensure that the electrical installations are perfect and do not cause sparks.

Do not use diluent to clean the skin, hands and other parts of the body. To clean the hands use alcohol, and then wash with water and appropriate cleaning pastes.

If there is a fire, use CO₂ or chemical powder extinguishers. It is not recommended to use water to extinguish the fire produced by burning paint.

Coatings and diluents must be stored in ventilated places protected from bad weather. The temperature can oscillate between 10 and 40°C.

If symptoms of intoxication by inhaling chemical vapors occur, the intoxicated person must be removed immediately from the work place to ventilated places.

If fainting, call a doctor immediately.

Product intended for use and handling of professionals linked to the painting area.

This product shall be applied and used, in compliance with all the National Health, Safety and Environment standards and regulations.

If it is necessary to remove the coating already applied and hardened from the substratum, the operator and the people who are in the same environment shall use appropriate personal protection equipment (PPE), as indicated in the safety information sheet (MSDS).

In situations where it is necessary to execute processes of welding metallic parts painted with this product, powder and gases will be released (smoke) which will require the use of appropriate personal protection equipment (masks with activated charcoal filters and even remote air supply equipment) in accordance with each environment.

The applications in confined areas require suitable ventilation, besides specific methods and procedures. For these situations contact the safety area of your company.

For further information contact the Technical Department of WEG (tintas@weg.net).

NOTE

The information contained in this technical datasheet is based upon the experience and knowledge acquired in the field by the technical team of WEG.

If using the product without prior inquiry to WEG concerning its suitability for the customer's intended purpose, the customer is aware that the use shall be its exclusive responsibility, WEG not being responsible for the behavior, safety, suitability or durability of the product.

Certain information contained in this datasheet is merely an estimate, and can undergo variances arising from factors outside the manufacturer's control. Thus, WEG does not guarantee and does not assume any responsibility regarding the yield, performance or any other material or personal damage resulting from the incorrect use of the products concerned or the information contained in this Technical datasheet.

The information contained in this technical datasheet is subject to periodic modification, without prior notice, due to the policy of evolution and continuous improvement of our products and services, providing solutions with quality to satisfy our customers' requirements.