

Farm Duty Motors

WEG RELIABLE & TOUGH
For ALL Seasons

Motors

Automation

Energy

Transmission and
Distribution

Coatings



Driving efficiency and sustainability



Table of Contents

Farm Duty Motors

	Farm Duty, Single-Phase, TEFC	3
	Farm Duty, Three-Phase, TEFC	4
	Poultry Fan, Single-Phase, TEAO	5
	Poultry Fan, Single-Phase, TEAO, Resilient Base	5
	PSC Direct Drive Fan Motors - Single Phase, TEAO	6
	Auger Drive, Single-Phase, TEFC, Flange Mount	6
	Grain Dryer/Vane Axial, Single and Three-Phase, TEAO.....	7
	Grain Dryer for Centrifugal Fans.....	8
	Aeration Fan, Single-Phase, TEAO	9
	Aeration Fan, Three-Phase, TEAO.....	9
	Irrigation Duty	10
	Irrigation Drive	11
	End Jet Booster Pump	11


Farm Duty Motors

WEG RELIABLE & TOUGH
For ALL Seasons



Farm Duty, Single-Phase, TEFC

- Double shielded ball bearings
- Insulation class F with class B temperature rise
- Start and run capacitor on 1.5 HP and up
- High and Extra High Starting Torque
- Manual Reset Thermal Overload Protector



TEFC – Single-Phase – General Purpose – Foot Mount



HP	kW	RPM	Frame	Catalog Number	List Price	Mult. Symbol	Approx. Shipping Weight (lbs)	Service Factor	FL Amps @ High	FL Eff (%)	"C" Dimension (in)	Voltage (V)	Notes
0.33	0.25	1800	W56	.3318ES1RFDW56-S	\$284	R1	22	1.15	3.00	61.0	11.500	115/230	4,9
0.5	0.37	1800	W56	.5018ES1RFDW56-S	\$308	R1	25	1.15	4.00	64.0	11.894	115/230	4,9
0.75	0.55	1800	56	.7518ES1RFD56-S	\$357	R1	34	1.15	5.30	68.5	13.114	115/230	4,9
1	0.75	1800	56	00118ES1RFD56-S	\$394	R1	40	1.15	6.80	71.0	13.902	115/230	4,9
		1800	143/5T	00118ES1RFD143T-S	\$400	R1	40	1.15	6.80	71.0	13.969	115/230	4,9
1.5	1.1	1800	56H	00158ES1RFD56H-S	\$502	R1	51	1.15	7.48	77.0	15.083	115/230	4,9
		1800	143/5T	00158ES1RFD145T-S	\$504	R1	50	1.15	7.48	77.0	15.152	115/230	4,9
2	1.5	1800	56H	00218ES1RFD56H-S	\$529	R1	56	1.15	10.0	78.5	15.870	115/230	4,9
		1800	143/5T	00218ES1RFD145T-S	\$578	R1	57	1.15	10.0	78.5	15.938	115/230	4,9
		1800	182/4T	00218ES1RFD184T-S	\$790	R1	90	1.15	9.96	77.0	19.094	230	4, 9; 52
		1800	182/4T	00218ES1RFD182T-W22	\$790	R1	97	1.15	8.40	80.0	17.012	115/230	4,39
3	2.2	1800	182/4T	00318ES1DFD182T-S	\$915	R1	100	1.15	11.9	78.5	19.094	230	4, 9; 52
		1800	182/4T	00318ES1DFD184T-W22	\$915	R1	104	1.15	13.8	77.0	17.012	230	4,39
5	3.7	1800	182/4T	00518ES1DFD184T-S	\$1,074	R1	112	1.15	19.9	84.0	19.882	230	4, 9; 52
		1800	213/5T	00518ES1DFD215T-S	\$1,205	R1	156	1.15	20.2	84.0	22.441	230	4, 9; 52
		1800	182/4T	00518ES1DFD184T-W22	\$1,074	R1	117	1.15	21.4	80.0	17.012	230	4,39
		1800	213/5T	00518ES1DFD215T-W22	\$1,205	R1	157	1.15	21.3	80.5	19.462	230	4,39
		1800	213/5TZ	00518ES1DFD215Z-W22	\$1,205	R1	146	1.15	21.3	80.5	19.462	230	4,39
7.5	5.5	1800	213/5T	00718ES1DFD213T-S	\$1,463	R1	172	1.15	28.8	85.5	22.441	230	4, 9; 52
		1800	213/5T	00718ES1DFD215T-W22	\$1,463	R1	176	1.15	31.7	83.0	19.462	230	4,39
		1800	213/5TZ	00718ES1DFD215Z-W22	\$1,463	R1	176	1.15	31.7	83.0	19.462	230	4,39
10	7.5	1800	213/5T	01018ES1DFD215T-S	\$1,692	R1	179	1.15	39.1	85.0	22.441	230	4, 9; 52
		1800	213/5T	01018ES1DFD215T-W22	\$1,692	R1	194	1.15	40.9	84.0	19.462	230	4,39
12.5	9.2	1800	213/5T	01218ES1DFD215T-W22	\$1,889	R1	205	1.15	27.2	82.5	19.462	208-230/460	4,39

4) Manual Reset Thermal Overload Protector

9) Rolled Still Frame - Cannot be modified with T-box on opposite side

39) Cannot be modified with T-box on opposite side

52) Extra-High starting torque





Farm Duty, Three-Phase, TEFC

WEG Rolled Steel motors offer a robust and light weight solution for a variety of general farm/Ag applications.

- TEFC enclosure
- Bearing seals as standard
- IP55 ingress protection rating
- Robust mounting feet
- Inverter rated
- Option for internal AEGIS® SGR



WEG W22 Cast Iron motors are severe duty as standard and the perfect solution for heavy duty Farm/Ag applications, with demanding loads and tough environments

- TEFC enclosure
- Bearing seals as standard
- IP55 ingress protection rating
- FC-200 grade cast iron
- Inverter rated
- Option for internal AEGIS® SGR

HP	KW	RPM	NEMA Frame	Catalog Number	List Price	Mult. Symbol	Approx. Shipping Weight (lbs)	Service Factor	FL Amps @ High	FL. Eff (%)	"C" Dimension (in)	Voltage (V)	Notes
1	0.75	1800	143/5T	00118ET3E143T-S	\$459	RSP	43	1.15	1.47	85.5	13.583	208-230/460	9
1	0.75	1800	143/5T	00118ET3E143T-W22	\$527	N1	46	1.25	1.41	85.5	13.346	208-230/460	
1.5	1.1	1800	143/5T	00158ET3E145T-S	\$480	RSP	43	1.15	2.02	86.5	13.583	208-230/460	9
1.5	1.1	1800	143/5T	00158ET3E145T-W22	\$551	N1	54	1.25	2.02	86.5	13.346	208-230/460	
2	1.5	1800	143/5T	00218ET3E145T-S	\$533	RSP	47	1.15	2.72	86.5	13.976	208-230/460	9
2	1.5	1800	143/5T	00218ET3E145T-W22	\$612	N1	56	1.25	2.61	86.5	13.346	208-230/460	
3	2.2	1800	182/4T	00318ET3E182T-S	\$577	RSP	87	1.15	3.81	89.5	17.894	208-230/460	9
3	2.2	1800	182/4T	00318ET3E182T-W22	\$663	N1	96	1.25	3.88	89.5	15.860	208-230/460	
5	3.7	1800	182/4T	00518ET3E184T-S	\$672	RSP	79	1.15	6.49	89.5	17.894	208-230/460	9
5	3.7	1800	182/4T	00518ET3E184T-W22	\$772	N1	105	1.25	6.45	89.5	15.860	208-230/460	
7.5	5.5	1800	213/5T	00718ET3E213T-S	\$948	RSP	131	1.15	9.07	91.7	18.898	208-230/460	9
7.5	5.5	1800	213/5T	00718ET3E213T-W22	\$1,089	N1	169	1.25	9.00	91.7	19.517	208-230/460	
10	7.5	1800	213/5T	01018ET3E215T-S	\$1,110	RSP	142	1.15	12.2	91.7	19.291	208-230/460	9
10	7.5	1800	213/5T	01018ET3E215T-W22	\$1,273	N1	192	1.25	12.4	91.7	19.517	208-230/460	
15	11	1800	254/6T	01518ET3E254T-S	\$1,610	RSP	242	1.15	18.2	92.4	22.559	208-230/460	9
15	11	1800	254/6T	01518ET3E254T-W22	\$1,848	N1	333	1.25	18.0	92.4	24.945	208-230/460	
20	15	1800	254/6T	02018ET3E256T-S	\$1,918	RSP	271	1.15	24.5	92.4	23.346	208-230/460	9
20	15	1800	254/6T	02018ET3E256T-W22	\$2,201	N1	363	1.25	24.1	93.0	24.945	208-230/460	
25	18.5	1800	284/6T	02518ET3E284T-W22	\$2,743	N1	433	1.25	29.5	93.6	27.929	208-230/460	
30	22	1800	284/6T	03018ET3E286T-W22	\$3,223	N1	482	1.25	35.1	93.6	27.929	208-230/460	
40	30	1800	324/6T	04018ET3E324T-W22	\$4,178	N1	595	1.25	48.2	94.1	31.116	208-230/460	
50	37	1800	324/6T	05018ET3E326T-W22	\$5,100	N1	634	1.25	59.2	94.5	31.116	208-230/460	
60	45	1800	364/5T	06018ET3E364T-W22	\$7,389	N1	1027	1.25	68.3	95.0	34.251	208-230/460	
60	45	1800	364/5T	06018ET3G364T-W22	\$7,389	N1	1013	1.25	68.3	95.0	34.251	460	
75	55	1800	364/5T	07518ET3E365T-W22	\$8,705	N1	1044	1.25	84.1	95.4	34.251	208-230/460	
75	55	1800	364/5T	07518ET3G365T-W22	\$8,705	N1	1045	1.25	84.1	95.4	34.251	460	
100	75	1800	404/5T	10018ET3E405T-W22	\$11,689	N1	1292	1.25	111	95.4	39.730	208-230/460	
100	75	1800	404/5T	10018ET3G405T-W22	\$11,689	N1	1278	1.25	111	95.4	39.730	460	

Notes:

9) Rolled Steel Frame

Poultry Fan, Single-Phase, TEAO

- Double shielded ball bearings
- Insulation class B
- Automatic Reset Thermal Overload Protector



TEAO – Single-Phase – Poultry Fan – Foot Mount

HP	kW	RPM	Frame	Catalog Number	List Price	Mult. Symbol	Approx. Shipping Weight (lbs)	Service Factor	FL Amps @ High	FL Eff (%)	"C" Dimension (in)	Voltage (V)	Notes
0.33	0.25	1800	48	.3318AS1BPF48-S	\$311	G1	22	1.25	2.76	61.5	10.157	115/208-230	3;9;16
0.5	0.37	1800	W56	.5018AS1BPFW56-S	\$336	G1	27	1.25	4.20	65.0	11.102	115/208-230	3;9;16
0.75	0.55	1800	56	.7518AS1BPF56-S	\$385	G1	26	1.25	5.30	68.5	11.496	115/208-230	3;9
1	0.75	1800	56	00118AS1BPF56-S	\$410	G1	35	1.15	7.00	72.0	12.992	115/208-230	3;9
	0.75	1800	56	00118AS1BPFH56-S	\$445	G1	32	1.40	6.20	73.0	13.464	115/208-230	3;9
1.5	1.10	1800	56	00158AS1BPF56-S	\$458	G1	33	1.15	7.48	77.0	13.464	115/208-230	3;9
	1.10	1800	56	00158AS1BPFH56-S	\$484	G1	34	1.30	8.74	76.0	13.858	115/208-230	3;9
2	1.5	1800	143/5T	00218AS1BPF145T-S	\$548	G1	54	1.15	10.0	78.5%	14.516	115/208-230	3;9



Poultry Fan, Single-Phase, TEAO, Resilient Base

TEAO – Single-Phase – Poultry Fan – Resilient Base

HP	kW	RPM	Frame	Catalog Number	List Price	Mult. Symbol	Approx. Shipping Weight (lbs)	Service Factor	FL Amps @ High	FL Eff (%)	"C" Dimension (in)	Voltage (V)	Notes
0.33	0.25	1800	48	.3318AS1BRBPF48-S	\$325	G1	20	1.25	2.76	61.5	10.157	115/208-230	3;9;16
0.5	0.37	1800	W56	.5018AS1BRBPFW56-S	\$350	G1	21	1.25	3.48	66.0	11.318	115/208-230	3;9;16
0.75	0.55	1800	56	.7518AS1BRBPF56-S	\$400	G1	26	1.25	5.63	68.5	12.008	115/208-230	3;9
1	0.75	1800	56	00118AS1BRBPF56-S	\$435	G1	35	1.15	7.00	72.0	12.992	115/208-230	3;9
1.5	1.10	1800	56	00158AS1BRBPF56-S	\$477	G1	35	1.15	7.48	77	13.976	115/208-230	3;9

Notes:

3) Automatic Reset Thermal Overload Protector

9) Rolled Steel Frame

16) Split-Phase Motor

* Available until inventory is depleted



PSC Direct Drive Fan Motors - Single Phase, TEAO

- Extended Through-Bolts
- Automatic Reset Thermal Overload Protector
- Permanent Split Capacitor



Extended Through-Bolts

HP	kW	RPM	Frame	New Catalog Number	List Price	Mult. Symbol	Approx. Shipping Weight (lbs)	Service Factor	FL Amps @ High	FL. Eff (%)	"C" Dimension (in)	Voltage (V)	Notes
0.33	0.25	1800	48Z	.3318AS1BPFPC48Z-S	\$287	G1	20	1.25	1.83	62	10.554	115/208-230	3;9
	0.25	1200	48Z	.3312AS1BPFPC48Z-S	\$322	G1	22	1.25	1.88	61	11.735	115/208-230	3;9

Notes:

3) Automatic Reset Thermal Overload Protector

9) Rolled Steel Frame

13) Resilient Base

Auger Drive, Single-Phase, TEFC, Flange Mount

- IP55 ingress protection
- 56NZ Frame (Shaft with flat), 56 Frame with keyed shaft
- 207N Painting Plan
- Centrifugal switch with overspeed protection
- Extended shaft on NDE for hand crank (with cover)
- V'ring on DE and NDE
- New aluminum NEMA N flange
- Manual thermal protector
- Shielded bearings
- Steel fan cover



HP	Kw	RPM	Frame	Catalog Number	List price	Mult. Symbol	Approx. Shipping Weight (Lbs)	Service Factor	FL Amps @ high	FL EFF (%)	"C" Dimension (in)	Voltage (V)	Notes
0.33	0.25	1800	56YZ	.3318ES1RAD56NZ-S	\$363	A1	22	1.15	3.00	60%	12.785	115/230	4
0.5	0.37	1800	56YZ	.5018ES1RAD56NZ-S	\$409	A1	31	1.15	3.50	68%	13.572	115/230	4, 52
0.75	0.55	1800	56YZ	.7518ES1RAD56NZ-S	\$447	A1	34	1.15	3.50	74%	13.572	115/230	4, 52
0.75	0.55	1800	56Y	.7518ES1RAD56N-S	\$464	A1	34	1.15	3.50	74%	16.660	115/230	4, 52
0.75	0.55	3600	56YZ	.7536ES1RAD56NZ-S	\$470	A1	33	1.15	3.63	68%	12.593	230	4, 52
1	0.75	1800	56Y	.00118ES1RAD56N-S	\$481	A1	35	1.15	4.64	76%	14.640	115/230	4, 52
1.5	1.1	1800	56Y	.00158ES1RAD56N-S	\$597	A1	43	1.15	6.50	77%	15.427	115/230	4

4) Manual Reset Thermal Overload Protector

52) Suitable to work at 60/50hz

Grain Dryer/Vane Axial Fan, Single and Three-Phase, TEAO

- Designed for air over direct coupling crop dryer vane axial fans
- Capable of continuous duty operation
- Normally-closed thermostats (one per phase)
- 30 inch extended leads
- Longer than NEMA shaft end
- Low profile lifting lugs
- Drive End with locked bearing and threaded center hole
- Spare nameplate and IP55 ingress protection



TEAO - Three-Phase - Grain Dryer

HP	RPM	NEMA Frame	Catalog Number	List Price	Mult. Symbol	FL Amps @ High	FL. Eff. (%)	"C"Dim. (in)	Voltage (V)	Notes
1.5-3	3600	143/5TZ	00336AP3EGD145TZ-S	\$750	GD3	2.41	79.70	12.401	208-230/460	9;38
3-4.5	3600	143/5TZ	00456AP3EGD145TZ-S	\$795	GD3	4.01	83.80	13.582	208-230/460	9;38
3-4.5	3600	182/4TZ	00456AP3EGD182TZ-S	\$827	GD3	4.27	86.20	14.601	208-230/460	9;38
5-7.5	3600	182/4TZ	00736AP3EGD184TZ-S	\$933	GD3	6.45	87.80	16.282	208-230/460	9;38
7.5-10	3600	182/4TZ	01036AP3EGD184TZ-S	\$1,123	GD3	9.04	89.80	17.070	208-230/460	9;38
10-15	3600	213/5TZ	01536AP3EGD215TZ-S	\$1,408	GD3	12.20	92.50	17.756	208-230/460	9;38

Notes:

9) Rolled Steel Frame

38) TEAO - Totally Enclosed Air Over

TEAO - Single-Phase - Grain Dryer


HP	RPM	NEMA Frame	Catalog Number	List Price	Mult. Symbol	FL Amps @ High	FL. Eff. (%)	"C"Dim. (in)	Voltage (V)	Notes
1.5-3	3600	145TZ	00336AP1DGD145TZ-S	\$900	GD1	7.51	73.20	13.555	230	1,9;38
3-4.5	3600	145TZ	00456AP1DGD145TZ-S	\$1,025	GD1	11.80	82.40	15.130	230	1,9;38
5-7.5	3600	182TZ	00736AP1DGD182TZ-S	\$1,296	GD1	19.80	82.90	17.070	230	1,9;38
7.5-10	3600	182TZ	01036AP1DGD182TZ-S	\$1,338	GD1	27.20	87.80	17.858	230	1,9;38
10-15	3600	215TZ	01536AP1DGD215TZ-S	\$2,024	GD1	37.80	88.00	19.720	230	1,9;38

Notes:

1) 1.0 Service Factor

9) Rolled Steel Frame

38) TEAO - Totally Enclosed Air Over



Grain Dryer for Centrifugal Fan

- Shaft length 1" longer than NEMA standard
- Lubed for life double sealed ball bearings
- Lip seal and slinger
- Roedent screen for ODP
- IP55 for TEFC, IP21 of ODP
- Single phase units include NC Thermostat



TEFC - Three Phase - Grain Dryer for Centrifugal Fans

HP	RPM	NEMA Frame	Catalog Number	List Price	Mult. Symbol	Approx. Shipping Weight (lbs)	Service Factor	FL Amps @ High	FL. Eff. (%)	"C"Dim. (in)	Voltage (V)	Notes
5	1800	182/4T	00518ET3EGD184TZ-S	\$925	GD3	76.1	1.15	6.49	89.50	16.913	208-230/460	9
7.5	1800	182/4T	00718ET3EGD184TZ-S	\$1,105	GD3	121	1.15	9.18	91.70	19.897	208-230/460	9
10	1800	213/5T	01018ET3EGD215TZ-S	\$1,255	GD3	127	1.15	12.2	91.70	20.291	208-230/460	9
15	1800	254/6T	01518ET3EGD254TZ-S	\$1,600	GD3	211	1.15	18.2	92.40	23.559	208-230/460	9

TEFC - Single Phase - Grain Dryer for Centrifugal Fans

HP	RPM	NEMA Frame	Catalog Number	List Price	Mult. Symbol	Approx. Shipping Weight (lbs)	Service Factor	FL Amps @ High	FL. Eff. (%)	"C"Dim. (in)	Voltage (V)	Notes
10	1800	213/5T	01018ES1DGD215TZ-S	\$2,040	GD1	205	1.25	39.5	86	23.441	230	4, 9
10	1800	213/5T	01018ES1DGD215TZ-W22	\$2,040	GD1	230	1.15	40.9	84	20.488	230	4



ODP - Three Phase - Grain Dryer for Centrifugal Fans

HP	RPM	NEMA Frame	Catalog Number	List Price	Mult. Symbol	Approx. Shipping Weight (lbs)	Service Factor	FL Amps @ High	FL. Eff. (%)	"C"Dim. (in)	Voltage (V)	Notes
5	1800	182/4T	00518OT3EGD184TZ-S	\$840	GD3	81.8	1.15	6.33	89.5	17.339	208-230/460	9
7.5	1800	182/4T	00718OT3EGD184TZ-S	\$1,090	GD3	116	1.15	9.25	91.0	17.181	208-230/460	9
10	1800	213/5T	01018OT3EGD215TZ-S	\$1,220	GD3	121	1.15	12.4	91.7	17.181	208-230/460	9
15	1800	254/6T	01518OT3EGD254TZ-S	\$1,550	GD3	189	1.15	18.6	93.0	20.482	208-230/460	9



ODP - Single Phase - Grain Dryer for Centrifugal Fans

HP	RPM	NEMA Frame	Catalog Number	List Price	Mult. Symbol	FL Amps @ High	Approx. Shipping Weight (lbs)	Service Factor	FL. Eff. (%)	"C"Dim. (in)	Voltage (V)	Notes
5	1800	182/4T	00518OS1DGD184TZ-S	\$1,205	GD1	88	1.00	9.87	84.0%	18.520	230	9
7.5	1800	182/4T	00718OS1DGD184TZ-S	\$1,595	GD1	120	1.00	14.3	85.5%	19.976	230	9
10	1800	213/5T	01018OS1DGD215TZ-S	\$1,980	GD1	216	1.00	19.2	86.5%	20.370	230	9

Notes:

4) Manual Reset Thermal Overload Protector

9) Rolled Steel Frame

Aeration Fan Motors, Single-Phase, TEAO

- Suitable for air-over applications such as aeration fans, exhaust fans and other air handling units
- Automatic reset thermal overload protector
- IP55



HP	RPM	NEMA Frame	Catalog Number	List Price	Mult. Symbol	FL Amps @ High	FL. Eff. (%)	"C"Dim. (in)	Voltage (V)	Notes
0.75	3600	56Z	.7536AS1RAF56Z-S	\$395	R1	4.00	66.0	11.201	115/230	3,9;38
1	3600	56Z	00136AS1RAF56Z-S	\$459	R1	5.10	70.0	11.594	115/230	3,9;38
1.5	3600	56Z	00156AS1RAF56Z-S	\$601	R1	6.60	75.0	12.382	115/230	3,9;38
2	3600	143/5TZ	00236AS1RAF143TZ-S	\$643	R1	6.60	75.0	12.413	115/230	3,9;38
3	3600	143/5TZ	00336AS1RAF145TZ-S	\$783	R1	8.70	77.0	12.807	115/230	3,9;38

Notes:

3) Automatic Reset Thermal Overload Protector

9) Rolled Steel Frame

38) TEAO - Totally Enclosed Air Over

Aeration Fan Motors, Three-Phase, TEAO

- Suitable for air-over applications such as aeration fans, exhaust fans and other air handling units
- Normally-closed thermostats (one per phase)
- IP55



HP	RPM	NEMA Frame	Catalog Number	List Price	Mult. Symbol	FL Amps @ High	FL. Eff. (%)	"C"Dim. (in)	Voltage (V)	Notes
0.75	3600	56Z	.7536AS3EAF56Z-S	\$402	R1	1.13	72.0	10.380	208-230/460	9;38
1	3600	56Z	00136AS3EAF56Z-S	\$435	R1	1.51	74.0	10.380	208-230/460	9;38
1.5	3600	143/5TZ	00156AP3EAF143TZ-S	\$498	R1	1.90	82.5	11.624	208-230/460	9;38
2	3600	143/5TZ	00236AP3EAF143TZ-S	\$578	R1	2.55	84.0	12.018	208-230/460	9;38
3	3600	143/5TZ	00336AP3EAF145TZ-S	\$659	R1	3.55	85.5	12.805	208-230/460	9;38

Notes:

9) Rolled Steel Frame

38) TEAO - Totally Enclosed Air Over




IRRIGATION DUTY MOTORS

TEFC

High Starting Torque makes these motors ideal for a wide range of applications.

Feature that makes a difference:

- Constructed with Metal Fan



Standard Features:

- Shielded Ball bearings
- Class F insulation (impregnation resin and magnet wire are class H)
- Gasketed Conduit Box

TEFC – Single-Phase – C-Face – Foot Mount

HP	kW	RPM	Frame	Catalog Number	List Price	Mult. Symbol	Approx. Shipping Weight (lbs)	Service Factor	FL Amps @ High	FL. Eff (%)	"C" Dimension (in)	Voltage (V)	Notes
5	3.7	1800	182/4TC	00518ES1EID184TC-W22	\$1,153	W1	121	1.15	10.7	80.0	17.012	208-230/460	11
7.5	5.5	1800	213/5TC	00718ES1EID215TC-W22	\$1,471	W1	179	1.15	15.0	83.0	19.462	208-230/460	11
10	7.5	1800	213/5TC	01018ES1EID215TC-W22	\$1,694	W1	196	1.15	20.4	84.0	19.462	208-230/460	11
12.5	9.2	1800	213/5TC	01218ES1EID215TC-W22	\$1,888	W1	209	1.15	27.2	82.5	19.462	208-230/460	11

W22 - Cast Iron

Standard Features:

- 50/60 Hz rated (380V on nameplate - 400/415V available)
- Rated 50Hz at same horsepower 1.0 Service Factor
- Class F insulation (impregnation resin and magnet wire are class H)
- F1 mount (field convertible to F2)
- Regreasable ball bearings (frames 254T and up)
- Gasketed conduit box

Feature that makes a difference:

- Constructed with Metal Fan

TEFC – Three-Phase – C-Face – Foot Mount

HP	kW	RPM	Frame	Catalog Number	List Price	Mult. Symbol	Approx. Shipping Weight (lbs)	Service Factor	FL Amps @ High	FL. Eff (%)	"C" Dimension (in)	Voltage (V)	Notes
5	3.7	1800	182/4TC	00518ET3EID184TC-W22	\$860	N1	110	1.25	6.45	89.5	15.860	230/460	11
7.5	5.5	1800	213/5TC	00718ET3EID213TC-W22	\$1,202	N1	180	1.25	9.18	91.7	19.517	230/460	11
10	7.5	1800	213/5TC	01018ET3EID215TC-W22	\$1,386	N1	194	1.25	12.4	91.7	19.517	230/460	11
15	11	1800	254/6TC	01518ET3EID254TC-W22	\$1,996	N1	353	1.25	18.0	92.4	24.945	230/460	11
20	15	1800	254/6TC	02018ET3EID256TC-W22	\$2,349	N1	403	1.25	24.1	93.0	24.945	230/460	11
25	18.5	1800	284/6TC	02518ET3EID284TC-W22	\$2,947	N1	451	1.25	29.5	93.6	27.929	230/460	11;51



Irrigation Drive Motors

These drive motors for center pivot and linear travel irrigation towers have been used on OEM equipment for decades. Its unique design offers a stainless steel rain shield for extra protection against water and other elements typically present in an agricultural environment. These motors are rated for 50°C ambient, making it the best for this application. Also featuring double sealed ball bearings, an automatic reset thermal overload protector, corrosion resistant phosphate shaft coating and a gasketed conduit box.

HP	kW	RPM	Frame	Catalog Number	List Price	Mult. Symbol	Approx. Shipping Weight (lbs)	Service Factor	FL Amps @ High	FL. Eff (%)	"C" Dimension (in)	Voltage (V)	Notes
1	.75	1800	56C	00118ET3QID56C	\$680	A1	35	1	1.57	85.5	14.11	460//380-415	3, 42, 45
1.5	1.1	1800	56C	00158ET3QID56C	\$695	A1	38	1	2.13	85.5	14.11	460//380-415	3, 42, 45

Notes:

3) Automatic Reset Thermal Overload Protector

42) Rated 50°C ambient

45) Also rated 380V 50Hz

Jet End Booster Pump

The Jet Booster Pump is perfect for irrigation systems. The solution includes a stainless steel rain shield and canopy for vertical application, a fully gasketed conduit box, an automatic reset thermal overload protection, and stainless steel shaft end.

HP	kW	RPM	Frame	Catalog Number	List Price	Mult. Symbol	Approx. Shipping Weight (lbs)	Service Factor	FL Amps @ High	FL. Eff (%)	"C" Dimension (in)	Voltage (V)	Notes
2	1.5	3600	56J	00236ET3QID56J	\$725	A1	43	1.5	2.8	85.5	14.65	460//380-415	3, 15
2	1.5	3600	56CZ	00236ET3QID56Z	\$730	A1	43	1.5	2.9	85.5	14.93	460//380-415	3, 15, 46

Notes:

3) Automatic Reset Thermal Overload Protector

15) Round Body - Drip Cover Included

46) 56J shaft end with dual opposed threads (7/16-20 UNF-2A R.H and 3/8-16 UNF-2A L.H)



WEG's scope of solutions is not limited to the products and solutions presented in this brochure.

Contact WEG for information on additional products and solutions.

**For WEG's worldwide
operations visit our website**



www.weg.net



 **1-800-ASK-4WEG**

 **info-us@weg.net**

 **Duluth, GA**

US.FARM.DUTY.2.2025

Information contained herein is subject to change without notice.