



# LACKTHERM® 1351

<b>PRODUCT DESCRIPTION:</b>	Air-dried modified polyester varnish.	
<b>PROPERTIES:</b>	Excellent dielectric properties, chemical resistance and moisture.	
<b>INDICATION OF USE:</b>	Coiled, stators and transformers.	
<b>APPLICATION SYSTEM:</b>	Immersion, Brush and Pistol.	
<b>CHARACTERISTICS:</b>	<b>Code:</b>	13937858 (5L) 13937860 (20 L) 13937861 (200L)
	<b>Appearance / Color:</b>	Ambar
	<b>Viscosity CF4:</b> 25°C (ASTM D1200/94)	20 – 30"
	<b>Specific weight:</b> (ASTM D1475/98)	0,90 ± 0,02 g/cm <sup>3</sup>
	<b>Solids by Weight:</b> (ASTM D2697/03)	36 ± 2%
	<b>Thermal Class:</b> (DIN 46452/77)	F (155°C)
	<b>Air drying:</b>	Ringin - Max. 6min. / Handling - Max. 6h
	<b>Greenhouse Healing:</b>	50°C – 80°C / 30min. – 60 min.
	<b>Diluent:</b>	Diluent SL-12
	<b>Emergency form:</b>	UN 1263
	<b>Expiration date:</b>	6 months
	<b>Additional information:</b>	Free of heavy metals according to the Rohs Directive 2002/95/CE to 27/01/2003

<b>RECOMMENDATIONS:</b>	<p>Store in a cool place, away from ignition points;                  Keep the packaging closed after partial use;                  The application tank must be kept closed after use;                  Use in a place with good ventilation.</p>
-------------------------	--



**SAFETY PRECAUTIONS:** Before handling this product, it is essential to carefully read all the information contained in its chemical safety information sheet (MSDS), available on our website, at the electronic address indicated at the end of this technical bulletin.

Contact with the skin can cause irritation.  
 If swallowed, do not induce vomiting. In case of contact with eyes, wash them with plenty of water. In any case, seek medical attention immediately.  
 Do not smoke in the work area.  
 Make sure that the electrical installations are perfect and that they do not cause sparks.  
 In case of fire, use CO2 or chemical powder extinguishers. It is not recommended to use water to extinguish the fire produced by burning.  
 Varnishes, resins and thinners should be stored in ventilated places and protected from weathering. The temperature can range from 10 to 40°C.  
 In the event of symptoms of intoxication by inhaling chemical vapors, the intoxicated person must be removed immediately from the workplace to ventilated areas.  
 In case of fainting, call a doctor immediately.  
 Product intended for use and handling by professionals related to the area of use (application).  
 The application and use of this product must be carried out, in compliance with all the National Health, Safety and Environment rules and regulations.  
 Applications in confined areas require adequate ventilation, in addition to specific methods and procedures. For these situations contact the security area of your company.

**For more information, consult the Technical Department of WEG Tintas through the phone specified at the end of this bulletin.**

**NOTE:** The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by the technical team of WEG Tintas.

If the product is used without prior consultation with WEG Tintas about its suitability for the purpose for which the customer intends to use it, the customer is aware that the use will be at its sole responsibility, and WEG Tintas is not responsible for the behavior, safety, suitability or durability of the product.  
 Some information contained in this bulletin is only an estimate, and may vary due to factors beyond the manufacturer's control. Thus, WEG Tintas does not guarantee and does not assume any responsibility for performance, performance or any material or personal damages resulting from the incorrect use of the products in question or the information contained in this Technical Bulletin.

**The information contained in this technical bulletin is subject to periodic changes, without prior notice, due to the policy of evolution and continuous improvement of our products and services, providing quality solutions to satisfy the needs of our customers.**