



## W-THANE WTA 501

<b>PRODUCT DESCRIPTION:</b>	High gloss, high aliphatic acrylic polyurethane finish paint solids by volume. Product developed to compose a system of anti-corrosion protection, offering high waterproofing power, chemical resistance and excellent resistance to natural weathering, providing high color and gloss retention.
<b>RECOMMENDED USES:</b>	Widely used in the painting of wind energy towers, where requires resistance to weathering and aesthetics. Combining the product wit
<b>CERTIFICATIONS AND APPROVAL:</b>	This product, when supplied to comply with the RoHs Directive (Restriction of Certain Hazardous Substances) has the letter R in its description.

PACKAGING:	Component	Content	Package	Unit of measurement
	Component A	2,88	3,6	L
	Component B	0,72	0,9	L

<b>CHARACTERISTICS:</b>	<b>Color:</b>	Ral, Munsell or as per customer standard.		
	<b>Gloss:</b>	Gloss >80 UB		
	<b>Volume solid:</b>	62 ± 2% (ISO 3233).		
	<b>Expiry Date:</b>	12 months at 25°C.		
	<b>Thickness per coat (dry):</b>	50 µm –60 µm		
	<b>Theoretical coverage:</b>	11,27 m2/l without dilution in the thickness of 55 µm dry. Without considering the loss factors in the application.		
	<b>Resistance to dry heat:</b>	Maximum temperature 90 °C . The product retains its physical and chemical properties up to the temperature of 90 °C however, variations in the coating color and gloss may occur from 60 °C.		
	<b>Drying:</b>			
		<b>10°C</b>	<b>25°C</b>	<b>35°C</b>
	<b>Touch:</b>	7 hours	6 hours	3 hours
		12 hours	10 hours	5 hours
		240 hours	240 hours	168 hours
	<b>Repainting Drying:</b>	<b>10°C</b>	<b>25°C</b>	<b>35°C</b>
	Min	12 hours	6 hours	5 hours
	Max	48 hours	16 hours	48 hours

<b>SURFACE PREPARATION</b>	The performance of this product is related to the degree of surface preparation.  The accumulated dirt must be removed using a dry brush, clean and dry cloth, compressed air blow, vacuum cleaner and/or with the combination of such items, and the soluble salts must be removed through wash with a great quantity of fresh water, preferably with low pressure (up to 5,000 psi) according to SSPC-SP 12/NACE No. 5.  <b>Application over primer</b> The product can be directly applied to a specific primer in order to form a suitable coating system.  <b>Maintenance and repair</b> <b>NOTE:</b> Observe the product overcoating interval to apply the next coat. In case the maximum overcoating interval has been exceeded, it is necessary to manually/mechanically sand the surface to break the gloss of the previous coat and clean the sanding residues so as to provide better adhesion between the coats.
----------------------------	--

For further information, consult WEG Technical Department.

## PREPARATION FOR APPLICATION

### Mixture

Homogenize the contents of each component by means of mechanical or pneumatic stirring (A and B). Ensure that no sediment is settled at the bottom of the package. Add component B to component A, at the recommended proportion (volume), under stirring, until complete homogenization, observing the mixing ratio.

### Mixing ratio (Volume)

4 A X 1 B.

### Diluent

**Pu diluent 5003**  
**PU Diluent 5004**

Para temperaturas por debajo de 30°C.  
For temperatures above 30°C.

### Dilution

Depending on the application method, dilute at most 15%

Only add the diluent after the complete mixing of components A + B.

Do not dilute with solvents that are not allowed by local legislation and do not exceed the recommended dilution percentage.

Excessive dilution of the coating may affect the formation of the film and appearance and hinder the attainment of the specified thickness.

### Pot life of the mixture (25°C)

2 h

### Induction time (25°C)

No induction time required.

In hot areas, we recommend consulting WEG Technical Department.

## APPLICATION FORMS

**The data below is a guide, and similar equipment may be used.**

The data below is a guide, and similar equipment may be used. Changes in nozzle sizes and pressures may be necessary to improve the spraying characteristics.

Purge the compressed air line to prevent contamination of the coating.

After mixing the 2-pack products, if there are stops in the application, and the pot life is exceeded (the coating presents variation in its fluidity), it can no longer be diluted for further application.

Reinforce all sharp edges, cracks and weld beads with a brush to prevent premature failures in these areas.

Before the application, make sure the equipment and its components are clean and in the best condition.

### Conventional gun:

Gun:	JGA 502/3 Devilbiss or equivalent
Fluid nozzle:	EX
Air cap:	704
Atomization pressure:	60 - 65 psi
Pressure in the tank:	10 - 20 psi
Dilution:	15%

### Airless Gun:

Use Airless:	Use at least pump 60: 1
Fluid pressure:	1200 – 2200 psi
Hose:	¼" internal diameter
Nozzle:	0,015" - 0,021"
Dilution:	Max. 5%

### Brush:

Only recommended for retouching small areas or stripe coat (screws, nuts, weld beads, sharp edges and retouching). Use a brush 75 to 100 mm wide for larger surfaces and 25 to 38 mm for retouching.

### Roller:

Use a thin nap, seamless sheepskin or microfiber roller for epoxy coatings.

For application with brush and/or roller, application in two or more passes may be necessary to obtain a uniform layer according to the recommended film thickness per coat.

### Cleaning the equipment:

Pu diluent 5003

### NOTE:

Do not leave the catalyzed product in contact with the equipment used in the application, because the coating will present variations in fluidity at temperatures above the specification in the pot life and will harden, making the cleaning difficult.

Clean all equipment immediately after use.

### PERFORMANCE IN THE APPLICATION

For a good performance of the product, we recommend following the directions below:

For a good performance of the product, we recommend following the directions below:

In paintings executed on the seafloor, if exposed to the action of sea air, we recommend to wash with fresh water between coats eliminating the settled impurities.

Do not apply the product after the pot life has expired.

We recommend coating only if the measured surface temperature is at least 3 °C above the dew point temperature.

For better application properties, the coating temperature should be between 21 - 27 °C prior to the mixing and application.

It should not be applied under adverse conditions, such as air relative humidity (RH) above 85%, as changes in color and appearance may occur.

Polyurethane systems (component A and B) present sensitivity when exposed to air relative humidity, which can cause flaws in the dry film and reduction of pot life. Therefore, we recommend that the packages of each component be properly closed after use and kept in dry places protected from bad weather.

In coatings with variation in the application method in the same job, the final appearance and gloss of the painted surfaces may present differences.

For further information, consult WEG Technical Department.

### SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals.

Please read carefully all the information contained in the MSDS of this product, available at: [www.weg.net](http://www.weg.net).

Store in a covered, well-ventilated area. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists / vapors / aerosols generated during handling and / or application.

Wear protective gloves / protective clothing / eye protection / face protection.

Avoid release of the product and its packaging, as well as materials used during handling and application in the environment.

### NOTE:

The information contained in this technical datasheet is based upon the experience and knowledge acquired in the field by the technical team of WEG.

If using the product without prior inquiry to WEG Coating concerning its suitability for the customer's intended purpose, the customer is aware that the use shall be its exclusive responsibility, WEG not being responsible for the behavior, safety, suitability or durability of the product.

Certain information contained in this datasheet is merely an estimate, and can undergo variances arising from factors outside the manufacturer's control. Thus, WEG does not guarantee and does not assume any responsibility regarding the yield, performance or any other material or personal damage resulting from the incorrect use of the products concerned or the information contained in this Technical datasheet.

The information contained in this technical datasheet is subject to periodic modification, without prior notice, due to the policy of evolution and continuous improvement of our products and services, providing solutions with quality to satisfy our customers' requirements.

