



W-THANE CVP 52

PRODUCT DESCRIPTION

Two-component aromatic polyurethane primer. Provides good anticorrosive protection, fast drying, and adhesion on ferrous metals.

RECOMMENDED USE

Recommended for painting equipment, metal structures, and machinery exposed to medium aggressiveness environments, such as pulp and paper plants, platforms, steel mills, and chemical industries.

CERTIFICATIONS AND APPROVALS

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

PACKAGING

Component A	0.95 US gal Package containing 0.71 US gal 5.28 US gal Package containing 3.96 US gal
Component B	0.24 US gal Package containing 0.24 US gal 1.32 US gal Package containing 1.32 US gal

CHARACTERISTICS

Color	According to customer standard. RAL and Munsell chart.
Gloss	Ultra-Matte
VOC content	5.28 lb/gal
Volume Solids	35 ± 5% (ISO 3233)
Shelf Life	12 months
Dry Film Thickness	1.2 mils - 1.6 mils
Dry Heat Resistance	Maximum temperature 194 °F. The product maintains its chemical properties up to a temperature of 194 °F, but from 140°F, color and gloss variations in the paint may occur.
Theoretical Coverage	407.5 ft ² /gal without dilution at a dry film thickness of 1.4 mils. Loss factors during application are not considered.

DRYING

	77 °F
Touch Dry:	50 min
Handle Dry:	8 h
Full Cure:	7 days
Minimum recoat drying time:	5 h
Maximum recoat drying time:	24 h

SURFACE PREPARATION

Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The surface must be clean, dry, and free of contaminants. Completely remove oils, greases, and fats according to SSPC-SP1.

Remove accumulated dirt using a dry brush, clean dry cloth, compressed air blow, vacuum, or a combination of these. Remove soluble salts by washing with plenty of fresh water, preferably under low pressure (up to 5,000 psi), according to SSPC-SP12/NACE No. 5 standard.



Degreasing

Completely remove oils and greases by applying a degreasing product or according to the solvent cleaning method. Whenever cleaning surfaces with cloths, replace them to avoid saturation. Do not use cotton waste or colored cloths.

Maintenance and Repair

NOTE: Respect the recoating interval for subsequent coat application. If exceeded, perform light manual/mechanical sanding to break the previous coat gloss, followed by dust and residue cleaning to ensure better adhesion between paint layers.

Phosphated Surfaces

Carry out the coating conversion process by phosphating, using either zinc or tricationic phosphate, with a mass between 0.041 oz/ft² and 0.082 oz/ft². Follow the sequential steps: degreasing; washing; pickling; washing; conditioner; phosphating; washing; passivation; deionized water rinse; drying.

NOTE: Surface preparation must be performed according to all sequential steps relevant to the phosphating process, following the recommendations of the pretreatment manufacturer.

APPLICATION PREPARATION

Mixing	Homogenize the content of each component using mechanical or pneumatic stirring (A and B). Ensure no sediment remains at the bottom of the container. Add component B to component A in the indicated mixing ratio under stirring until completely homogenized, respecting the mixing ratio.
Mixing Ratio	By volume: 3 A x 1 B.
Thinner	PU DILUENT 5001
Dilution	Depending on the application method, dilute to a maximum of 15%.
Notes	The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.
Pot Life	4 h The shelf life of the mixture is reduced as the ambient temperature increases. The pot-life test of the mixture is carried out according to ABNT NBR 15742; however, different volumes of paint prepared at once, combined with varying ambient and paint temperatures, will affect the mixture's shelf life, potentially resulting in outcomes different from those stated in this technical bulletin.
Induction Time	No induction time required. In very hot locations, we recommend consulting WEG's Technical Department.

APPLICATION METHODS

Conventional Spray Gun	Spray gun: JGA 502/3 Devilbiss or equivalent Fluid nozzle: EX Air cap: 704 Atomization pressure: 50 - 70 psi Tank pressure: 10 - 20 psi.
Airless Spray Gun	Airless: Use minimum pump 60:1 Fluid pressure: 1500 - 2500 psi Hose: 1/4" inner diameter Nozzle: 0.015" - 0.021".
Roller	For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.



Brush	Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups).
Cleaning of the equipments:	PU DILUENT 5001
Notes	<p>The data presented serves as a guide and similar equipment may be used.</p> <p>Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination.</p> <p>Do not allow catalyzed product to remain in contact with application equipment, as at temperatures above the indicated "pot life", the paint will show variation in flow and will harden, making cleaning difficult.</p> <p>Before application, ensure that the equipment and respective components are clean and in optimal condition.</p> <p>After mixing two-component products, if there are application stops and the pot life has been exceeded (paint shows variation in flow), it can no longer be re-thinned for later application.</p> <p>In spray application, overlap each gun pass by 50%, finishing with a cross pass. This technique avoids uncovered or unprotected areas and ensures proper aesthetic finish.</p> <p>Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.</p> <p>Clean all equipment immediately after use.</p> <p>It is considered good practice to periodically wash the spraying equipment during the day. The cleaning frequency depends on the amount sprayed, temperature, and elapsed time, including all delays.</p>

APPLICATION PERFORMANCE

Some colors may require an additional coat to achieve uniform coverage.

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Do not apply the product after the pot life has been exceeded.

For optimal application properties, the paint temperature must be between 69.8°F - 80.6°F before mixing and application.

Before application, observe weather conditions: there must be no threat of rain or drizzle. Surface temperature must be at least 37,4°F above the dew point, and relative humidity should not exceed 85%. Adverse conditions may cause color variations and other characteristics. Consult WEG Technical Department.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Polyurethane systems (components A and B) are sensitive to relative humidity, which may cause defects in the dry film and reduction in pot life. After use, keep containers closed and protected.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

Under adverse weather conditions in indoor and/or outdoor environments with high relative humidity, rain or drizzle, low or very low temperatures, and excessively high temperatures, variations in color and other product characteristics may occur. Please consult WEG's Technical Department for more information.

COMPATIBILITY

For topcoat application over the product, the repainting interval must be respected; the surface must be dry and free of contaminants.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read



all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.
