

POLITHERM 52 R TX GREY RAL 7042 SB

PRODUCT: 16527958

DESCRIPTION / USES: Metallic parts coating for indoor use.

ATTENTION: For the formation of the original texture of the product, it required the curing oven is preheated in curing temperature shown in this bulletin.

CHARACTERISTICS:

Resin:	Epoxy / polyester
Specific gravity:	1,52 ± 0,10 g/cm ³
Stability:	06 month (máx. 30°C)
Observations:	Free of heavy metals and other substances provided for in Directive 2015/863 EU of 03/31/2015 (RoHS).

APPLICATION CHARACTERISTICS:

Surface:	Ferrous and non-ferrous
Surface preparation:	Ferrous: Phosphatization Non-ferrous: Chromatization or phosphatization*
Cure conditions:	10 minutes at 180 °C**
Thickness:	120 – 140 µm
Application system:	Electrostatic gun

AFTER CURE CHARACTERISTICS*:**

TEST	METHOD	SPECIFICATION
ADHESION	ASTM D 3359	GR0
GLOSS @ 60°	ASTM D 523	Visual std.
IMPACT (REVERSE)	ASTM 2794	Min. 40 kg X cm
FLEXIBILITY (CONIC MANDREL)	ASTM D 790 / ISO 178	Max. 5 mm

CHEMICAL RESISTANCE ***

Salt spray:	Min. 500 h (ASTM B117 – 03)
Humidity:	Min. 1000 h (35°C)

* For non-ferrous metals phosphatizing, please contact our technical service.

** After stabilization on correct temperature (metal temperature).

*** The tests were conducted on degreased steel panels in accordance with the cure and thickness specifications. The figures may be change, depending on the surface characteristics. For chemical resistance tests the panels were degreased and treated with tricationic phosphat.

IMPORTANT: If is not possible the use of the product according to the directions given above we ask you to contact our technical service.

STORAGE: Fresh, dry and covered place.