



**PAINT ROTOR STAMPING**



<b>PRODUCT DESCRIPTION</b>		
	Epoxy-based topcoat paint.	
<b>RECOMMENDED USE</b>		
	Indicated for marking metal equipment using spray or stamping application.	
<b>CERTIFICATIONS AND APPROVALS</b>		
	When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.	
<b>PACKAGING</b>		
	<b>Single Component</b>	0.24 US gal Package containing 0.24 US gal
<b>CHARACTERISTICS</b>		
	<b>Color</b>	White.
	<b>Volume Solids</b>	45 ± 5% (ISO 3233)
	<b>Shelf Life</b>	12 months
	<b>Dry Film Thickness</b>	0.6 mils - 1.8 mils
	<b>Dry Heat Resistance</b>	Maximum temperature 140 °F. The product maintains its chemical properties up to a temperature of 140 °F, but from 140°F, color and gloss variations in the paint may occur.
	<b>Theoretical Coverage</b>	1 without dilution at a dry film thickness of 1.2 mils. Loss factors during application are not considered.
<b>DRYING</b>		
	<b>Drying</b>	<u>77 °F</u>
	<b>Touch</b>	1 hour
	<b>Manipulation</b>	24 hours
	<b>Final</b>	72 hours
<b>SURFACE PREPARATION</b>		
	<b>Standard Surface Preparation</b>	
	The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.	
	Completely remove oils and greases by applying a degreasing product or according to the solvent cleaning method. Whenever cleaning surfaces with cloths, replace them to avoid saturation. Do not use cotton waste or colored cloths.	
	Accumulated dirt must be removed using a dry brush, and soluble salts must be removed by washing with fresh water under high pressure.	
<b>APPLICATION PREPARATION</b>		
	<b>Mixing</b>	Homogenize the content of the container using mechanical or pneumatic stirring. Ensure no sediment remains at the bottom of the container.
	<b>Thinner</b>	Not applicable.
	<b>Dilution</b>	Ready to use.
	<b>Notes</b>	No dilution is required. Product ready to use. If necessary, consult the WEG Technical Department.
<b>APPLICATION METHODS</b>		
	<b>Conventional Spray Gun</b>	Spray gun: JGA 502/3 Devilbiss or equivalent Fluid nozzle: EX Air cap: 704 Atomization pressure: 60 - 65 psi



	Tank pressure: 10 - 20 psi.
<b>Airless Spray Gun</b>	Airless: not recommended.
<b>Other application methods</b>	For application with a stamp, consult WEG Technical Department.
<b>Cleaning of the equipments:</b>	Not applicable.
<b>Notes</b>	<p>The data presented serves as a guide and similar equipment may be used.</p> <p>Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination.</p> <p>Before application, ensure that the equipment and respective components are clean and in optimal condition.</p> <p>Do not leave material in hoses, guns, or equipment used for spraying. Thoroughly wash all used equipment.</p>

**APPLICATION PERFORMANCE**

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

For optimal application properties, the paint temperature must be between 69.8°F - 80.6°F before mixing and application.

We recommend painting only if the measured surface temperature is at least 5.4°F above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

Must not be applied under adverse conditions, such as relative humidity (RH) above 85%, as color and appearance changes may occur.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

**SAFETY PRECAUTIONS**

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: [www.weg.net](http://www.weg.net).

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

**NOTE**

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.