

POLITHERM 22 R ME- GRAY ONIX 30723 UM**Code:** 18876057**PRODUCT DESCRIPTION**

Hybrid powder coating with good adhesion and flexibility, high physical resistance and good chemical resistance.

RECOMMENDED USE

Coating of metal parts for use in indoor or sheltered environments.

PROPERTIES

Enhanced with additives to reduce baking time and/or temperature.

Metallic coatings are sensitive to scratches and exhibit variable wear, depending on the usage of the parts. The metallic appearance may change in situations such as heavy handling, contact with chemicals (including some cleaning products), friction between parts or with abrasive objects. To protect the film from wear, we recommend the application of a uniform layer of glossy polyester powder varnish. Note that this procedure diminishes the metallic effect to a varying degree, depending on the level of metallization of the paint. For non-glossy finishes, it is recommended to previously test the use of varnishes with lower gloss. It is recommended to test the use of varnishes beforehand, and the varnish should be applied after the metallic paint has partially cured.

CERTIFICATIONS AND APPROVALS

Free from heavy metals and other substances provided for in RoHs Directive 2015/863 EU of 31/03/2015.

PACKAGING

Cardboard box with 25 kg in high-density polyethylene bag.

CHARACTERISTICS OF MANUFACTURED PRODUCT

Resin	Epoxy/Polyester
Gloss	Ultra matte
Finish	Metallic
Specific gravity ($\pm 0,10$)	1,53 g/cm ³
Theoretical Coverage	13,07 m ² /kg in medium thickness 50 μ m
Mass loss during cure	Maximum 2%
Moisture content	Maximum 0,6%
Shelf life	12 months
Storage condition	It must be stored in closed containers, in cool, dry and covered places, at an ambient temperature not exceeding 30°C.

APPLICATION CHARACTERISTICS

Substrate	Ferrous metals Non-ferrous metals
Surface preparation	Ferrous : Phosphatization Non-ferrous: Chromatization or phosphatization
Surface cleaning	The performance of this product is related to the degree of surface preparation. The surface must be clean, dry and free of any contaminants. Completely remove oils, grease and fats.
Thickness	40 μ m - 60 μ m
Cure conditions	10 min à 180 °C (metal temperature).
Cure windows	15 min - 25 min at 170 °C 10 min - 20 min at 180 °C 7 min - 15 min at 190 °C



		5 min - 12 min at 200 °C
	Application system	Electrostatic spray gun corona
NOTE:	For non-ferrous metals phosphatizing, please contact our technical service.	
CHARACTERISTICS OF APPLIED PRODUCT		
	Test	Specification/Standard
	Adhesion	Maximum GR0 (ASTM D3359)
	Gloss	Visual standard
	Impact	Minimum 50 kg.cm (ASTM D2794)
	Flexibility (conic mandrel)	Maximum 3,00 mm (ASTM D790)
CHEMICAL RESISTANCE CHARACTERISTICS		
	Test	Specification/Standard
	Humidity	Minimum 1000h (ASTM D2247)
	Salt spray	Minimum 750h (ASTM B117)
NOTE:	In the chemical resistance tests, the substrate used was steel sheet treated with tricationic phosphate. Mechanical resistance tests were performed on degreased plain steel sheet under the curing conditions and coating specific to the product. Values may vary depending on the substrate used.	
SAFETY PRECAUTIONS		
	Guidance is available in the product's Safety Data Sheet (SDS).	
NOTE	The information provided herein is based on our testing and experience and is intended to inform you about the product and its possible applications. The information provided in this bulletin is not intended to be complete, and the user assumes the risk of using the product for a purpose other than the specifications recommended in this bulletin without first obtaining our written confirmation of its suitability for the intended purpose. While we strive to ensure the accuracy of the information provided herein, we cannot control the quality or condition of the substrate, nor any other factors that affect the use and application of this paint. Therefore, unless we agree in writing to any condition that deviates from our recommendations, we accept no liability that may arise regarding the performance of this product. The information contained in this bulletin is subject to change without notice, based on our experience and policy of continuous development.	