



NEW TECH 508 SPRAY



PRODUCT DESCRIPTION

Primer-finish developed with special resins. Fast drying, with anticorrosive pigmentation and nanotechnology particles.

CHARACTERISTICS

Color	Gray.
Gloss	Matte
Volume Solids	NOT RELEVANT
Solids by Weight	21 ± 2 %
Shelf Life	12 months
Dry Film Thickness	0.4 mils - 0.8 mils
Theoretical Coverage	1 without dilution at a dry film thickness of 0.6 mils. Loss factors during application are not considered.
Specific Gravity	Min: 1.14 Max: 1.24 g/cm ³
Viscosity	READY FOR USE

DRYING

77 °F

Touch Dry:	5 - 10 min
Handle Dry:	30 min
Full Cure:	24 h
Minimum recoat drying time:	NAO RELEVANTE
Maximum recoat drying time:	NAO RELEVANTE

SURFACE PREPARATION

Degreasing

Remove dust and dirt from the vehicle surfaces that need to be protected, using compressed air or a clean cloth. Make sure the vehicle is dry before applying the masking fluid. Do not apply to surfaces contaminated with oil or silicone.

APPLICATION PREPARATION

Mixing

Application must only be carried out with equipment that provides mechanical agitation during the entire application.
 Homogenize the content manually, ensuring no pigment remains at the bottom of the container.
 Shake the can well with circular movements before and during application. Perform a small test of the applicator by pressing the valve a few times on any surface, checking the jet. Spray at 3.9-7.9 in from the surface using uniform, crossed movements. For better coverage, apply several coats, respecting 5-10 minute intervals. Clean the valve by turning the can downwards and pressing until only gas comes out.

Mixing Ratio MONOCOMPONENT

Dilution Ready to use.

Notes No dilution is required. Product ready to use. If necessary, consult the WEG Technical Department.

Pot Life Not relevant.

APPLICATION METHODS

Spray Recommended.



Notes

The data presented serves as a guide and similar equipment may be used.
It is considered good practice to periodically wash the spraying equipment during the day. The cleaning frequency depends on the amount sprayed, temperature, and elapsed time, including all delays.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.
Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.
Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.
Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.
Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.
In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.
Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.
The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.
