



CREETY RP

PRODUCT DESCRIPTION

Three-component urethane-based coating designed to provide high performance in various environments with high durability. Applied on coves, walls, stairs and other vertical surfaces, it is waterproof and has antibacterial properties. Provides excellent resistance to abrasion, heavy mechanical impacts, chemicals and thermal variations.

RECOMMENDED USE

Developed to meet the needs of different sectors, the coating is ideal for: Industries: food, beverage, pharmaceutical, chemical, textile, among others; Baseboards; Protection of containment dikes, tanks, drains, walls and vertical surfaces.

Application on concrete aged 10 to 12 days, provided the moisture tolerance is met.

CERTIFICATIONS AND APPROVALS

Complies with ASTM G-21 standard: antimicrobial function.

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

PACKAGING

Component A	0.24 US gal Package containing 0.20 US gal
Component B	0.24 US gal Package containing 0.12 US gal
Component C	18.96#lbm package containing 16.53#lbm.

CHARACTERISTICS

Color	Blue. Beige. Gray. Green. Red.
Gloss	Matte
Volume Solids	95 ± 1% (ISO 3233)
Shelf Life	24 months
Dry Film Thickness	118.1 mils - 236.2 mils
Theoretical Coverage	Coating 0.12 in = 6.00; Coating 0.16 in = 8.00; Coating 0.20 in = 10.00; Coating 0.24 in = 12.00; Coating 0.28 in = 14.00; Coating 0.31 in = 16.00; Coating 0.35 in = 18.00.

DRYING

Drying	77 °F
Light traffic	8 - 12 hours
Heavy traffic	18 - 24 hours

PHYSICOCHEMICAL CHARACTERISTICS

Adhesion (ASTM D 4541)	100 % FAILURE CONCRETE
Thermal Expansion Coefficient (ASTM C 531)	2.0 X 10 ⁻⁵ / °C
Compressive Strength (ASTM C 109/109M)	Greater than or equal to 5,802 psi (28 days)

Flexural Strength (ASTM C 580)	Greater than or equal to 2,176 psi (28 days)
Tensile Strength (ASTM C 307)	2,50 MPa
Taber Abrasion Resistance CS-17 (ASTM D 4060)	~ 0.07 g
Modulus of Elasticity (ASTM C 469)	Greater than or equal to 168,244 psi
Permeability (CP.BM2/67/2)	ABSORPTION 0
Operating Temperature	-40 °C TO 140 °C

PRODUCT	CONCENTRATION (%)	TEMPERATURE	GRADUATION	PRODUCT	CONCENTRATION (%)	TEMPERATURE	GRADUATION
ACETALDEHYDE	100%	71.6 °F	R	CHLOROFORM	100%	71.6 °F	L
ETHYL ACETATE	100%	71.6 °F	L	AVIATION FUEL	-	71.6 °F	R
ACETONE	100%	71.6 °F	R	STYRENE	100%	71.6 °F	R
ACETIC ACID	10%	68/185 °F	R	ETHANOL	100%	71.6 °F	R
BENZOIC ACID	100%	71.6 °F	R	ETHYLENE GLYCOL	100%	71.6 °F	R
CITRIC ACID	60%	71.6 °F	R	BRAKE FLUID	-	71.6 °F	R
HYDROCHLORIC ACID	20/35 %	68/140 °F	R	GASOLINE	-	71.6 °F	R
HYDROFLUORIC ACID	4%	71.6 °F	R	FATS	-	167 °F	R
HYDROFLUORIC ACID	20%	71.6 °F	L	AMMONIUM HYDROXIDE	28%	71.6 °F	R
FORMIC ACID	40/70 %	71.6 °F	R	POTASSIUM HYDROXIDE	50%	71.6 °F	R
FORMIC ACID	90%	71.6 °F	L	SODIUM HYDROXIDE	50%	140 °F	R
PHOSPHORIC ACID	50%	71.6 °F	R	SODIUM HYDROXIDE	50%	194 °F	L
LACTIC ACID	85%	140 °F	R	MILK	-	71.6 °F	R
NITRIC ACID	65%	71.6 °F	L	METHANOL	100%	71.6 °F	R
SULFURIC ACID	98%	71.6 °F	L	METHYL ETHYL KETONE	100%	71.6 °F	L
HYDROGEN PEROXIDE	30%	71.6 °F	R	ENGINE OIL	-	71.6 °F	R
BLEACH	SATURATED	71.6 °F	R	PARAFFIN	-	71.6 °F	R
TURPENTINE	-	71.6 °F	R	PETROLEUM	-	71.6 °F	R
ISOPROPYL ALCOHOL	100%	71.6 °F	R	PROPYLENE GLYCOL	100%	71.6 °F	R
BENZENE	100%	71.6 °F	L	KEROSENE	-	71.6 °F	R
BUTANOL	100%	71.6 °F	R	TOLUENE	100%	71.6 °F	R
BEER	-	71.6 °F	R	XYLENE	100%	71.6 °F	R
CALCIUM CHLORIDE	50%	71.6 °F	R				
				Graduation: R - Resistant L - Limited resistance			
For more details regarding chemical resistance, consult WEG's technical department.							

SURFACE PREPARATION

Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

Concrete Surfaces

Mold release agents, cement laitance, grease, oil, wax, or any other contaminants that have penetrated or deposited on the surface must be removed, along with all accumulated dust.

Concrete must have a minimum age of 7 days, FCK # 30 MPa, and minimum tensile strength of 1.5 MPa. The substrate must be properly cured and intact. Before application, verify upward water vapor pressure according to ASTM D 4263.

The surface must be mechanically treated until achieving a surface profile of CSP 6 to 9, according

to the International Concrete Repair Institute recommendation.

Anchor cuts must be made across the entire application area, with a maximum distance of approximately 26.25 feet between cuts.

They must have double the width and depth of the coating thickness (Example: CREETY RP 0.24 inches = Cuts of 0.47 inches Width and 0.47 inches Depth).

Floor washing after preparation and cuts is not recommended; if done, pay attention to moisture issues and start application only after complete substrate drying.

APPLICATION PREPARATION

Mixing

Primer application - follow Step 1 for surfaces up to 11.8 inches in height or Step 2 for surfaces above 11.8 inches in height:

Step 1:

For priming the substrate of baseboards and/or vertical areas up to 11.8 inches in height: thoroughly homogenize component A. With component A in the mixing container, add component B and start mixing using a low-speed mechanical mixer (300 to 450 rpm) for 40 seconds. Immediately after mixing, use a brush, streaking brush, or roller to apply the primer to the surface to be coated. Between 15 and 30 minutes after application, the primer will reach tackiness (sticky but not leaving residue on touch), remaining in this condition for approximately 60 minutes. The Creety RP should be applied during this tack period of the primer.

Step 2:

For priming the substrate of baseboards and/or vertical areas above 11.8 inches in height: thoroughly homogenize component A. With component A in the mixing container, add component B and start mixing using a low-speed mechanical mixer (300 to 450 rpm) for 40 seconds. Then, add half of component C and mix until fully homogeneous. Immediately after mixing, use a brush, streaking brush, or roller to apply the primer to the surface to be coated. Between 15 and 30 minutes after application, the primer will reach tackiness (sticky but not leaving residue on touch), remaining in this condition for approximately 60 minutes. The Creety RP should be applied during this tack period of the primer.

For temperatures between 50.0°F and 58.8°F, the mixing time will be 3 minutes after adding part C.

Note: the primer will fully dry if the tack period is exceeded. If this occurs, do not apply the Creety RP. In this case, the surface must be sanded and the primer applied again, following the application steps.

Thinner

Not applicable.

Dilution

Ready to use.

Pot Life

10 min

The shelf life of the mixture is reduced as the ambient temperature increases.

The pot-life test of the mixture is carried out according to ABNT NBR 15742; however, different volumes of paint prepared at once, combined with varying ambient and paint temperatures, will affect the mixture's shelf life, potentially resulting in outcomes different from those stated in this technical bulletin.

APPLICATION METHODS

Cleaning of the equipments:

Not applicable.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product



away from heat and sources of ignition.
Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.
Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.
In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.
Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.
The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.