

POLITHERM 25 R SM GREEN 50251 BR

PRODUCT: 14447887

DESCRIPTION / USES: Epoxy powder coating for indoor use on metallic parts.

CHARACTERISTICS:

| | |
|--------------------------|---|
| Resin: | Epoxy |
| Specific gravity: | 1,46 ± 0,10 g/cm ³ |
| Stability: | 6 month (máx. 30°C) |
| Observations: | Free of heavy metals according to the RoHS Directive 2011/65/UE of 08/06/2011 |

APPLICATION CHARACTERISTICS:

| | |
|-----------------------------|--|
| Surface: | Ferrous and non-ferrous |
| Surface preparation: | Ferrous : Phosphatization Non-ferrous: Chromatization or phosphatization* |
| Cure conditions: | 10 minutes at 180 °C** |
| Thickness: | 60 – 80 µm |
| Application system: | Electrostatic gun |

AFTER CURE CHARACTERISTICS*:**

| TEST | METHOD | SPECIFICATION |
|-----------------------------|----------|----------------------|
| ADHESION | WPS-3905 | : GR0 |
| GLOSS at 60° | WPS-3854 | : Minimum 90 UB |
| IMPACT (REVERSE) | WPS-4130 | : Minimum 50 kg X cm |
| FLEXIBILITY (CONIC MANDREL) | WPS-4856 | : Maximum 3 mm |

CHEMICAL RESISTANCE ***

| | |
|--------------------|----------------------------------|
| Salt spray: | : Minimum 500 h (ASTM B117 – 03) |
| Humidity: | : Minimum 1000 h (35°C) |

* For non-ferrous metals phosphatizing, please contact our technical service.

** After stabilization on correct temperature (metal temperature).

*** The tests were conducted on degreased steel panels in accordance with the cure and thickness specifications. The figures may be change, depending on the surface characteristics. For chemical resistance tests the panels were degreased and treated with tricationic phosphat.

IMPORTANT: If is not possible the use of the product according to the directions given above we ask you to contact our technical service.

This product is not suitable for parts intended to be glued using silicon glue.

STORAGE: Fresh, dry and covered place.