



POLITHERM 49 WF TF R SM BLACK NIGHT SKY 70347 SM

Code: 18953058

PRODUCT DESCRIPTION

TGIC-free polyester powder coating with excellent adhesion and flexibility, in addition to good chemical resistance. It has high physical resistance and excellent weathering resistance.

RECOMMENDED USE

Coating of metal parts for industrial and architectural purposes in outdoor environments. Recommended for thicker parts or reduced baking cycles.

PROPERTIES

Enhanced with additives to reduce baking time and/or temperature.

CERTIFICATIONS AND APPROVALS

Free from heavy metals and other substances provided for in RoHs Directive 2015/863 EU of 31/03/2015.

Complies with performance requirements for AAMA 2603.

PACKAGING

Cardboard box with 55 lb in high-density polyethylene bag.

CHARACTERISTICS OF MANUFACTURED PRODUCT

Resin	Polyester
Gloss	Semi matte
Finish	Smooth
Specific gravity ($\pm 0,10$)	1,49 g/cm ³
Theoretical Coverage	131.0 ft ² /lb at 1.0 mil
Mass loss during cure	Maximum 2%
Moisture content	Maximum 0.6%
Shelf life	12 months
Storage condition	It must be stored in closed containers, in cool, dry and covered places, at an ambient temperature not exceeding 86°F.

APPLICATION CHARACTERISTICS

Substrate	Ferrous metals Non-ferrous metals
Surface preparation	Ferrous : Phosphatization Non-ferrous: Chromatization or phosphatization
Surface cleaning	The performance of this product is related to the degree of surface preparation. The surface must be clean, dry and free of any contaminants. Completely remove oils, grease and fats.
Thickness	2.0 mils - 2.8 mils
Cure conditions	5 min à 392 °F (metal temperature).
Cure windows	20 min - 25 min at 338 °F 15 min - 20 min at 356 °F 10 min - 15 min at 374 °F 5 min - 10 min at 392 °F
Application system	Electrostatic spray gun corona

NOTE:

For non-ferrous metals phosphatizing, please contact our technical service.

CHARACTERISTICS OF APPLIED PRODUCT

Test	Specification/Standard
------	------------------------



Adhesion	Maximum GR0 (ASTM D3359)
Gloss	50 UB - 60 UB (ASTM D523)
Impact	Minimum 43 lb.in (ASTM D2794)
Flexibility (conic mandrel)	Maximum 1/8 in (ASTM D790)

CHEMICAL RESISTANCE CHARACTERISTICS	
Test	Specification/Standard
Humidity	Minimum 1000h (ASTM D2247)
Salt spray	Minimum 500h (ASTM B117)
NOTE:	In the chemical resistance tests, the substrate used was steel sheet treated with tricationic phosphate. Mechanical resistance tests were performed on degreased plain steel sheet under the curing conditions and coating specific to the product. Values may vary depending on the substrate used.

SAFETY PRECAUTIONS	Non-hazardous coating, no special transport required. Guidelines are available in the product's Safety Data Sheet (SDS)
---------------------------	--

NOTE	The information provided herein is based on our testing and experience and is intended to inform you about the product and its possible applications. The information provided in this bulletin is not intended to be complete, and the user assumes the risk of using the product for a purpose other than the specifications recommended in this bulletin without first obtaining our written confirmation of its suitability for the intended purpose. While we strive to ensure the accuracy of the information provided herein, we cannot control the quality or condition of the substrate, nor any other factors that affect the use and application of this paint. Therefore, unless we agree in writing to any condition that deviates from our recommendations, we accept no liability that may arise regarding the performance of this product. The information contained in this bulletin is subject to change without notice, based on our experience and policy of continuous development.
-------------	--