

W-MARINE SUPER 2400

PRODUCT DESCRIPTION

Self-polishing antifouling paint based on special polymers, TBT-free, with excellent antifouling properties. Keeps surfaces smoother, maximizing speed. W-MARINE SUPER 2400 offers superior performance compared to conventional antifoulings, increasing intervals between dockings.

RECOMMENDED USE

Product developed for maintenance, repair, and new constructions, with excellent antifouling performance. Indicated for flat and vertical bottom painting of small, medium, and large vessels. W-MARINE SUPER 2400 ensures durability and provides fuel savings.

CERTIFICATIONS AND APPROVALS

This product contains no organotin active components acting as biocides, therefore complies with the International Convention on the Control of Harmful Antifouling Systems on Ships, as adopted by the IMO in October 2001 (Document IMO AFS/CONF/26).

PACKAGING

Single Component	0.9L Package containing 0.9L 3.6L Package containing 3.6L
-------------------------	--

CHARACTERISTICS

Color	Blue. Black.
Gloss	Not applicable.
VOC content	622.48 g/l
Volume Solids	58 ± 2% (ISO 3233)
Shelf Life	12 months
Dry Film Thickness	120 µm - 130 µm
Dry Heat Resistance	Maximum temperature 60 °C. The product maintains its chemical properties up to a temperature of 60 °C, but from 60°C, color and gloss variations in the paint may occur.
Theoretical Coverage	4,64 m ² /l without dilution at a dry film thickness of 125 µm. Loss factors during application are not considered.

DRYING

Drying

	10 °C	25 °C	35 °C
Touch	5 hours	2 hours	90 min
Before the flooding	24 hours	12 hours	12 hours

Recoat Drying

	10 °C	25 °C	35 °C
Minimum	12 hours	6 hours	4 hours
Maximum	15 days	15 days	10 days

SURFACE PREPARATION

Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The surface must be clean, dry, and free of contaminants. Completely remove oils, greases, and fats according to SSPC-SP1.

Maintenance and Repair

When exposed to long service periods, the product may present a leached layer. This must be removed before application by washing with fresh water under high pressure (above 3,000 psi). This procedure also removes slime, salinity, and encrustations.

Initially remove all dirt and oil from the surface with clean cloths soaked in cleaning Diluent according to SSPC SP1. Avoid using rags or colored cloths. Repair damaged areas and redo the anticorrosive scheme.

The product should not be directly applied to other TBT-free antifoulings, whether from WEG or other manufacturers, without prior consultation with WEG. Any application without consultation is not authorized.

NOTE: Respect the recoating interval for subsequent coat application. If exceeded, perform light manual/mechanical sanding to break the previous coat gloss, followed by dust and residue cleaning to ensure better adhesion between paint layers.

New Constructions

The antifouling paint must be applied over specific primer and sealer, forming an appropriate coating system. The sealer surface must be clean, dry, and free of contaminants, respecting the recoating interval between sealer coats. Consult the sealer technical bulletin for correct application.

Recommended primers: W-poxi Primer 717 late. Recommended sealers: Weg Tie Coat and W-nilica Tar Free CVI 810.

APPLICATION PREPARATION

Mixing	Homogenize the content of the container using mechanical or pneumatic stirring. Ensure no sediment remains at the bottom of the container.
Thinner	ANTIFOULING DILUENT
Dilution	Depending on the application method, dilute to a maximum of 10%.
Notes	The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.
Pot Life	Not relevant.

APPLICATION METHODS

Airless Spray Gun	Airless: Use minimum pump 60:1 Fluid pressure: 2000 - 3000 psi Hose: 3/8" inner diameter Nozzle: 0.019" - 0.023".
Roller	Recommended only for small areas or touch-ups. Use a low-pile seamless wool roller or synthetic roller for epoxy paints. For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.
Brush	Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups).
Cleaning of the equipments:	ANTIFOULING DILUENT
Notes	Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination. Before application, ensure that the equipment and respective components are clean and in optimal condition. In spray application, overlap each gun pass by 50%, finishing with a cross pass. This technique avoids uncovered or unprotected areas and ensures proper aesthetic finish. Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas. Clean all equipment immediately after use.



Do not leave material in hoses, guns, or equipment used for spraying. Thoroughly wash all used equipment. It is considered good practice to periodically wash the spraying equipment during the day. The cleaning frequency depends on the amount sprayed, temperature, and elapsed time, including all delays.

APPLICATION PERFORMANCE

The product must be applied within the recoat interval specified in the technical data sheet.

An increase in viscosity of this material may occur during storage, being a normal characteristic of the product.

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

For optimal application properties, the paint temperature should be between 21°C and 27°C before mixing and application.

Before application, observe weather conditions: there must be no threat of rain or drizzle. Surface temperature must be at least 3°C above the dew point, and relative humidity should not exceed 85%. Adverse conditions may cause color variations and other characteristics. Consult WEG Technical Department.

Painting is recommended only if surface temperature is at least 3°C above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

PERIODS WITHOUT APPLICATION:

Thoroughly wash all material and equipment with the recommended Diluent. Keep all unused paint stored in well-sealed containers. Material stored in partially filled containers may show skinning or viscosity increase after long periods. In such cases, it is recommended to filter the product before application.

WELDING:

In case of welding or cutting operations on coated metal, fumes and gases will be released, requiring the use of appropriate PPE and adequate ventilation and exhaust systems.

Consult WEG regarding repainting procedures over other antifoulings before starting any painting work.

LIMITATIONS:

Product performance depends on the specified dry film thickness, which may vary according to the type of water and the vessel's daily service time. Wear rate depends on water temperature, vessel speed, operating regions, among other factors. The interval before immersion is related to environmental conditions, ventilation, dry film thickness, and the number of coats applied.

Maximum recommended exposure time before immersion: 30 days.

Performance test results were obtained in a laboratory under controlled conditions. WEG does not guarantee that the results exactly represent all field environments, such as highly polluted waters, rivers, etc. Environmental factors may vary significantly; attention is required in paint selection, performance verification, and use.

The surface must always be coated with an appropriate primer and/or sealer. Consult WEG for the best primer or sealer to use.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

After 30 days of product application without water immersion, performance may be affected. Recoating information is provided mainly as guidance and is subject to regional climatic variations.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

Under adverse weather conditions in indoor and/or outdoor environments with high relative humidity, rain or drizzle, low or very low temperatures, and excessively high temperatures, variations in color and other product characteristics may occur. Please consult WEG's Technical Department for more information.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.



Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.