

## POLITHERM 20 R CR BLUE 43910 BR

**PRODUCT:** 10848541

**DESCRIPTION/ USES:** Metallic parts coating for indoor use.

### CHARACTERISTICS:

<b>Resin:</b>	Epoxy / polyester
<b>Specific gravity:</b>	1,43 ± 0,10 g/cm <sup>3</sup>
<b>Stability:</b>	12 months (máx. 30°C)
<b>Observations:</b>	Free of heavy metals and other substances provided for in Directive 2015/863 EU of 03/31/2015 (RoHS).

### APPLICATION CHARACTERISTICS:

<b>Surface:</b>	Ferrous and non-ferrous
<b>Surface preparation:</b>	Ferrous: Phosphatization Non-ferrous: Chromatization or phosphatization*
<b>Cure conditions:</b>	10 minutes at 200 °C**
<b>Thickness:</b>	80 – 100 µm
<b>Application system:</b>	Electrostatic gun

### AFTER CURE CHARACTERISTICS\*\*\*:

TEST	METHOD	SPECIFICATION
ADHESION	WPS-3905	GR0
GLOSS	WPS-3854	Visual std.
IMPACT (REVERSE)	WPS-4130	Min. 40 kg X cm
FLEXIBILITY (CONIC MANDREL)	WPS-4856	Max. 5 mm

### CHEMICAL RESISTANCE \*\*\*

<b>Salt spray:</b>	Min. 500 h (ASTMB117 – 03)
<b>Humidity:</b>	Min. 1000 h (35°C)

\* For non-ferrous metals phosphatizing, please contact our technical service.

\*\* After stabilization on correct temperature (metal temperature).

\*\*\* The tests were conducted on degreased steel panels in accordance with the cure and thickness specifications. The figures may change, depending on the surface characteristics. For chemical resistance tests the panels were degreased and treated with tricationic phosphat.

**IMPORTANT:** If it is not possible to use the product according to the directions given above we ask you to contact our technical service.

**STORAGE:** Fresh, dry and covered place.

COPY FOR INFORMATION