

# CPTW Series

## Control Power Transformers

### Compact and Economical Solutions



www.weg.net | 1-800-ASK-4WEG


## VOLTAGE TABLE

| VA             | Primary Voltage                           | Secondary Voltage   | Part Number    |
|----------------|---|---------------------|----------------|
| 5000           | 200/220/440,<br>208/230/460,<br>240 x 480 | 110, 115, 120       | CPTW5K0-GSC    |
| Max Depth      | Max Width                                 | Max Height          | Mounting Depth |
| 9.00"          | 9.00                                      | 7.62"               | 7.25"          |
| Mounting Width | Mounting Hole Depth                       | Mounting Hole Width | Phase          |
| 7.50"          | 0.44"                                     | 1.00"               | 1              |
| Frequency      | Shipping Weight                           | Voltage Group       |                |
| 50/60 Hz       | 89.0 lbs.                                 | G                   |                |

### Notes:

- Jumper Link and Fuse Clip height not included
- Add 5/16" to the Depth (A) when fuse clips are included (50 thru 350VA)
- Add 1 3/8" to the Height (D) when fuse block is included (1, 2, and 3 poles) (50 thru 350VA)
- Add 1/2" to the Height (D) when fuse block is included (1, 2, and 3 poles) (500 thru 5000VA)

## DIAGRAM



## SPECIFICATIONS

- Class 180°C (356°F) insulation system with 115°C (239°F) temperature rise.
- All transformers up to 750VA come with pre-installed secondary fuse kits, ready to accept 13/32" x 1 1/2" midget or Class CC fuses.
- Two parallel jumper links come standard with transformers with dual primary voltages.
- All transformers up to 3kVA include a built-in mounting adapter for fuse blocks.