

POLITHERM 20 R CR BLACK 70813 BR

Code: 13034035

PRODUCT DESCRIPTION

Hybrid powder coating with good adhesion and flexibility, high physical resistance and good chemical resistance.

RECOMMENDED USE

Coating of metal parts for use in indoor or sheltered environments.

PROPERTIES

Crackled coatings are sensitive to scratches and exhibit variable wear depending on the usage condition of the parts. The metallic appearance may change under conditions such as heavy handling, contact with chemicals (including some cleaning products), friction between parts or abrasive objects, and prolonged exposure to excessively humid environments. To protect the film from wear, we recommend the application of a uniform layer of glossy polyester powder varnish. Please, note that this procedure diminishes the visual effect of the finish to a varying degree, depending on the level of metallization of the paint. For non-glossy finishes, it is recommended to previously test the use of varnishes with lower gloss.

CERTIFICATIONS AND APPROVALS

Free from heavy metals and other substances provided for in RoHs Directive 2015/863 EU of 31/03/2015.

PACKAGING

Cardboard box with 25 kg in high-density polyethylene bag.

CHARACTERISTICS OF MANUFACTURED PRODUCT

| | |
|----------------------------------|--|
| Resin | Epoxy/Polyester |
| Gloss | Bright |
| Finish | VEIN |
| Specific gravity (± 0,10) | 1,48 g/cm ³ |
| Theoretical Coverage | 7,51 m ² /kg in medium thickness 90 µm |
| Mass loss during cure | Maximum 2% |
| Moisture content | Maximum 0.6% |
| Shelf life | 12 months |
| Storage condition | It must be stored in closed containers, in cool, dry and covered places, at an ambient temperature not exceeding 30°C. |

APPLICATION CHARACTERISTICS

| | |
|----------------------------|--|
| Substrate | Ferrous metals |
| Surface preparation | Ferrous : Phosphatization Non-ferrous: Chromatization or phosphatization |
| Surface cleaning | The performance of this product is related to the degree of surface preparation. The surface must be clean, dry and free of any contaminants. Completely remove oils, grease and fats. |
| Thickness | 80 µm - 100 µm |
| Cure conditions | 10 min à 200 °C (metal temperature). |
| Cure windows | 20 min - 30 min at 180 °C 15 min - 25 min at 190 °C 10 min - 18 min at 200 °C 8 min - 12 min at 210 °C |
| Application system | Electrostatic spray gun corona |

NOTE:

For non-ferrous metals phosphatizing, please contact our technical service.



CHARACTERISTICS OF APPLIED PRODUCT

| Test | Specification/Standard |
|-----------------------------|-------------------------------|
| Adhesion | Maximum GR0 (ASTM D3359) |
| Gloss | Visual standard |
| Impact | Minimum 40 kg.cm (ASTM D2794) |
| Flexibility (conic mandrel) | Maximum 5,00 mm (ASTM D790) |

CHEMICAL RESISTANCE CHARACTERISTICS

| Test | Specification/Standard |
|------------|----------------------------|
| Humidity | Minimum 2000h (ASTM D2247) |
| Salt spray | MINIMUM 1500 h |

NOTE:

In the chemical resistance tests, the substrate used was cold-rolled steel sheet with tricationic phosphate. The mechanical resistance tests were performed on degreased common steel sheet under specific curing and coating conditions for the product. The values ## may vary depending on the substrate used.

SAFETY PRECAUTIONS

Guidance is available in the product's Safety Data Sheet (SDS).

NOTE

The information provided herein is based on our testing and experience and is intended to inform you about the product and its possible applications. The information provided in this bulletin is not intended to be complete, and the user assumes the risk of using the product for a purpose other than the specifications recommended in this bulletin without first obtaining our written confirmation of its suitability for the intended purpose. While we strive to ensure the accuracy of the information provided herein, we cannot control the quality or condition of the substrate, nor any other factors that affect the use and application of this paint. Therefore, unless we agree in writing to any condition that deviates from our recommendations, we accept no liability that may arise regarding the performance of this product. The information contained in this bulletin is subject to change without notice, based on our experience and policy of continuous development.