



W-POXI RRP 32 INTER

PRODUCT DESCRIPTION

Two-component polyamine epoxy primer, high anticorrosive protection, flexibility, hardness, and excellent applicability.

RECOMMENDED USE

Recommended for protection painting of carbon steel and cast iron in machinery, equipment, and metal structures exposed to normal and mildly aggressive environments.

CERTIFICATIONS AND APPROVALS

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

PACKAGING

<b>Component A</b>	0.95 US gal Package containing 0.86 US gal 5.28 US gal Package containing 4.81 US gal
<b>Component B</b>	0.26 US gal package containing 0.09 US gal. 1.06 US gal Package containing 0.48 US gal

CHARACTERISTICS

<b>Color</b>	Gray. Black. Red.
<b>Gloss</b>	Ultra-Matte
<b>VOC content</b>	5.25 lb/gal
<b>Volume Solids</b>	48 ± 3% (ISO 3233)
<b>Shelf Life</b>	24 months
<b>Dry Film Thickness</b>	2.0 mils - 2.8 mils
<b>Theoretical Coverage</b>	326.0 ft <sup>2</sup> /gal without dilution at a dry film thickness of 2.4 mils. Loss factors during application are not considered.
<b>Specific Gravity</b>	Min: 1.236 Max: 1.137 g/cm <sup>3</sup>

DRYING

<b>Drying</b>			
	<b>50 °F</b>	<b>77 °F</b>	<b>95 °F</b>
<b>Touch</b>	3 hours	40 min	15 min
<b>Manipulation</b>	6 hours	3 hours	2 hours
<b>Final</b>	240 hours	168 hours	120 hours
<b>Recoat Drying</b>			
	<b>50 °F</b>	<b>77 °F</b>	<b>95 °F</b>
<b>Minimum</b>	6 hours	3 hours	2 hours
<b>Maximum</b>	96 hours	72 hours	48 hours
<b>Oven Drying</b>			
	<b>77 °F</b>	<b>176 °F</b>	<b>212 °F</b>
<b>Flash off</b>	5 min	-	-
<b>Time</b>	-	30 min	20 min

SURFACE PREPARATION

**Standard Surface Preparation**

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

The surface must be clean, dry, and free of contaminants. Completely remove oils, greases, and fats according to SSPC-SP1.



Remove accumulated dirt using a dry brush, clean dry cloth, compressed air blow, vacuum, or a combination of these. Remove soluble salts by washing with plenty of fresh water, preferably under low pressure (up to 5,000 psi), according to SSPC-SP12/NACE No. 5 standard.

**Recommended Surface Profile**

It is recommended a roughness profile between 1.57 and 2.36 mils.

**Abrasive Blasting**

Inspect the freshly blasted surface, observing defects that may appear after treatment. Correct them by grinding, filling with welds and/or epoxy putty.

For areas near marine environments, wash with fresh water at low pressure (minimum 3,000 psi) before abrasive blasting. In some cases, repeat washing after blasting to remove soluble contaminants and perform a new abrasive blasting.

If oxidation occurs between the end of abrasive blasting and coating application, the surface must be blasted again until the specified visual standard is achieved.

**Carbon Steel Surfaces**

Completely remove oils, greases, soluble salts, and other contaminants according to SSPC SP1 solvent cleaning method. Rinse with high-pressure fresh water.

The surface must be clean, dry, and free of contaminants.

**APPLICATION PREPARATION**

<b>Mixing</b>	Homogenize the content of each component using mechanical or pneumatic stirring (A and B). Ensure no sediment remains at the bottom of the container. Add component B to component A in the indicated mixing ratio under stirring until completely homogenized, respecting the mixing ratio.
<b>Mixing Ratio</b>	By volume: 10 A x 1 B.
<b>Thinner</b>	EPOXY DILUENT 3005
<b>Dilution</b>	Depending on the application method, dilute to a maximum of 15%.
<b>Notes</b>	<p>Dilute according to recommendation.</p> <p>Only add the thinner after the A + B components are completely mixed.</p> <p>Excessive thinning of the paint may affect film formation, appearance, and make it difficult to achieve the specified thickness.</p> <p>The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.</p>
<b>Pot Life</b>	<p>6 h</p> <p>The shelf life of the mixture is reduced as the ambient temperature increases.</p> <p>The pot-life test of the mixture is carried out according to ABNT NBR 15742; however, different volumes of paint prepared at once, combined with varying ambient and paint temperatures, will affect the mixture's shelf life, potentially resulting in outcomes different from those stated in this technical bulletin.</p>
<b>Induction Time</b>	<p>Wait 15 to 20 minutes before application.</p> <p>In very hot locations, we recommend consulting WEG's</p>

Technical Department.

**APPLICATION METHODS**

<b>Conventional Spray Gun</b>	<p>Spray gun: JGA 502/3 Devilbiss or equivalent                  Fluid nozzle: EX                  Air cap: 704                  Atomization pressure: 50 - 70 psi                  Tank pressure: 10 - 20 psi.</p>
<b>Airless Spray Gun</b>	<p>Airless: Use minimum pump 60:1                  Fluid pressure: 1500 - 2500 psi                  Hose: 1/4" inner diameter                  Nozzle: 0.015" - 0.021".</p>
<b>Roller</b>	<p>Use a short-haired, seamless wool or synthetic roller for epoxy paints.                  For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.</p>
<b>Brush</b>	<p>Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups).</p>
<b>Cleaning of the equipments:</b>	<p>EPOXY DILUENT 3005</p>
<b>Notes</b>	<p>The data presented serves as a guide and similar equipment may be used.                  Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination.                  Do not allow catalyzed product to remain in contact with application equipment, as at temperatures above the indicated "pot life", the paint will show variation in flow and will harden, making cleaning difficult.                  Before application, ensure that the equipment and respective components are clean and in optimal condition.                  After mixing two-component products, if there are application stops and the pot life has been exceeded (paint shows variation in flow), it can no longer be re-thinned for later application.                  In spray application, overlap each gun pass by 50%, finishing with a cross pass. This technique avoids uncovered or unprotected areas and ensures proper aesthetic finish.                  Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.                  Clean all equipment immediately after use.                  It is considered good practice to periodically wash the spraying equipment during the day. The cleaning frequency depends on the amount sprayed, temperature, and elapsed time, including all delays.</p>

**APPLICATION PERFORMANCE**

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Do not apply the product after the pot life has been exceeded.

As this is a primer, color variation between batches of this material may occur.

For optimal application properties, the paint temperature must be between 69.8°F - 80.6°F before mixing and application.

Before application, observe weather conditions: there must be no threat of rain or drizzle. Surface temperature must be at least 37,4°F above the dew point, and relative humidity should not exceed 85%. Adverse conditions may cause color variations and other characteristics. Consult WEG Technical Department.

We recommend painting only if the measured surface temperature is at least 5.4°F above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well



as applied film thickness, may affect drying time.

Epoxy systems may have longer curing times when exposed to low temperatures. For curing below 50°F, consult WEG Technical Department.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

Epoxy-based products are known for their excellent anticorrosive properties and low resistance to sun exposure. When the applied film is exposed to weathering, over time it will lose gloss, a phenomenon known as chalking, which consequently alters its color. It is important to note that, despite this chalking, the film's anticorrosive protection is not compromised.

Under adverse weather conditions in indoor and/or outdoor environments with high relative humidity, rain or drizzle, low or very low temperatures, and excessively high temperatures, variations in color and other product characteristics may occur. Please consult WEG's Technical Department for more information.

**SAFETY PRECAUTIONS**

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: [www.weg.net](http://www.weg.net).

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

**NOTE**

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.