



W-LACK TXA 11



PRODUCT DESCRIPTION		Fast-drying textured alkyd resin topcoat.
RECOMMENDED USE		Indicated for painting machinery and equipment subject to low physical and chemical aggressiveness.
CERTIFICATIONS AND APPROVALS		When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.
PACKAGING	Single Component	0.95 US gal Package containing 0.95 US gal
CHARACTERISTICS	Color	According to customer standard. RAL and Munsell chart.
	Gloss	Gloss (>80 UB) W-LACK TXA 111 Semi-gloss (60 - 80 UB) W-LACK TXA 112 Semi-matte (30 - 60 UB) W-LACK TXA 113 Matte (15 - 30 UB) W-LACK TXA 114 Ultra-matte (0 - 15 UB) W-LACK TXA 115
	Volume Solids	40 ± 5% (ISO 3233)
	Shelf Life	12 months
	Dry Film Thickness	1.0 mils - 1.2 mils
	Dry Heat Resistance	Maximum temperature 140 °F. The product maintains its chemical properties up to a temperature of 140 °F, but from 140°F, color and gloss variations in the paint may occur.
	Theoretical Coverage	592.9 ft ² /gal without dilution at a dry film thickness of 1.1 mils. Loss factors during application are not considered.
DRYING		77 °F
	Touch Dry:	30 min
	Handle Dry:	24 h
	Full Cure:	3 days
	Minimum recoat drying time:	5 h
	Maximum recoat drying time:	24 h
SURFACE PREPARATION		
	Standard Surface Preparation	The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department. The surface must be clean, dry, and free of contaminants. Completely remove oils, greases, and fats according to SSPC-SP1.
	Over Primer	The product must be applied over a specific primer. The primer must be clean, dry, and free of contaminants. The topcoat must be applied within the primer recoat interval. Consult the primer technical bulletin for correct application. Respect the product recoat interval. If exceeded, perform light manual/mechanical sanding to break gloss and clean dust/residues for better adhesion between coats.
APPLICATION PREPARATION		



Mixing	Homogenize the content of the container using mechanical or pneumatic stirring. Ensure no sediment remains at the bottom of the container.
Thinner	ALKYDIC DILUENT 1024
Dilution	Depending on the application method, dilute to a maximum of 30%.
Notes	<p>Smooth coat: dilute according to recommendation. Apply one coat at dry thickness 1-1.2 mils. Textured coat: adjust viscosity and pressure according to desired texture.</p> <p>Product dilution will affect the texture. The more diluted the paint, the lower the texture.</p> <p>The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.</p>
Pot Life	Not relevant.

APPLICATION METHODS

Conventional Spray Gun	<p>Spray gun: JGA 502 Devilbiss or equivalent Fluid nozzle: FX Air cap: 704 Atomization pressure: 50 - 70 psi Tank pressure: 10 - 20 psi.</p>
Roller	<p>Use a short-haired, seamless wool or synthetic roller for epoxy paints.</p> <p>Recommended only for small areas or touch-ups. Use a low-pile seamless wool roller or synthetic roller for epoxy paints.</p> <p>For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.</p>
Cleaning of the equipments:	ALKYDIC DILUENT 1024
Notes	<p>The data presented serves as a guide and similar equipment may be used.</p> <p>Changes in pressures and nozzle sizes may be necessary to improve spraying characteristics. Purge the compressed air line to avoid paint contamination.</p> <p>Before application, ensure that the equipment and respective components are clean and in optimal condition.</p> <p>In spray application, overlap each gun pass by 50%, finishing with a cross pass. This technique avoids uncovered or unprotected areas and ensures proper aesthetic finish.</p> <p>Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.</p> <p>Clean all equipment immediately after use.</p> <p>Do not leave material in hoses, guns, or equipment used for spraying. Thoroughly wash all used equipment.</p> <p>It is considered good practice to periodically wash the spraying equipment during the day. The cleaning frequency depends on the amount sprayed, temperature, and elapsed time, including all delays.</p>

APPLICATION PERFORMANCE

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Light colors may require more than one coat to achieve uniform coverage.



For optimal application properties, the paint temperature must be between 69.8°F - 80.6°F before mixing and application.

Before application, observe weather conditions: there must be no threat of rain or drizzle. Surface temperature must be at least 37.4°F above the dew point, and relative humidity should not exceed 85%. Adverse conditions may cause color variations and other characteristics. Consult WEG Technical Department.

We recommend painting only if the measured surface temperature is at least 5.4°F above the dew point.

Substrate temperature, climatic and environmental conditions during application and curing, as well as applied film thickness, may affect drying time.

To achieve a proper film appearance, first apply a smooth coat of 0.98 to 1.18 mils dry. After a 5-minute interval, apply the textured coat.

Paintings performed with varying application methods on the same project may result in differences in gloss and final appearance.

Small variations in color, appearance, and gloss (more noticeable in dark colors), as well as delayed curing and performance compromise, may occur during high humidity, rainy days, cold locations, or when parts dry outdoors.

Under adverse weather conditions in indoor and/or outdoor environments with high relative humidity, rain or drizzle, low or very low temperatures, and excessively high temperatures, variations in color and other product characteristics may occur. Please consult WEG's Technical Department for more information.

SYSTEM COMPATIBILITY AND MAINTENANCE REPAINTING

The primer repainting interval must be respected for the application of the topcoat. If the maximum interval indicated is exceeded, manual/mechanical sanding with sandpaper to remove gloss is necessary. The primer surface must be dry and free of contaminants.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.

Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.