



POLITHERM 12 SM ORANGE MUNSELL 2,5YR 5/14 SB

Code: 10004824

PRODUCT DESCRIPTION

Hybrid powder coating with good adhesion and flexibility, in addition to good physical and chemical resistance.

RECOMMENDED USE

Coating of metal parts for use in indoor or sheltered environments. Recommended for thicker parts or reduced baking cycles.

PROPERTIES

Enhanced with additives to reduce baking time and/or temperature.

There may be, among batches, some variations in the color shade around the pattern exhibited.

PACKAGING

Cardboard box with 25 kg in high-density polyethylene bag.

CHARACTERISTICS OF MANUFACTURED PRODUCT

Resin	Epoxy/Polyester
Gloss	Semi bright
Finish	Smooth
Specific gravity ($\pm 0,10$)	1,80 g/cm ³
Theoretical Coverage	6,94 m ² /kg in medium thickness 80 μ m
Mass loss during cure	Maximum 2%
Moisture content	Maximum 0,6%
Shelf life	6 months
Storage condition	It must be stored in closed containers, in cool, dry and covered places, at an ambient temperature not exceeding 30°C.

APPLICATION CHARACTERISTICS

Substrate	Ferrous metals Non-ferrous metals
Surface preparation	Ferrous : Phosphatization Non-ferrous: Chromatization or phosphatization
Surface cleaning	The performance of this product is related to the degree of surface preparation. The surface must be clean, dry and free of any contaminants. Completely remove oils, grease and fats.
Thickness	70 μ m - 90 μ m
Cure conditions	5 min à 200 °C (metal temperature).
Cure windows	12 min - at 180 °C 8 min - at 190 °C 5 min - at 200 °C
Application system	Electrostatic spray gun corona

NOTE:

For non-ferrous metals phosphatizing, please contact our technical service.

CHARACTERISTICS OF APPLIED PRODUCT

Test	Specification/Standard
Adhesion	Maximum GR0 (ASTM D3359)



	Gloss	65 UB - 75 UB (ASTM D523)
	Impact	Minimum 40 kg.cm (ASTM D2794)
	Flexibility (conic mandrel)	Maximum 5,00 mm (ASTM D790)
CHEMICAL RESISTANCE CHARACTERISTICS		
	Test	Specification/Standard
	Humidity	Minimum 500h (ASTM D2247)
	Salt spray	Minimum 300h (ASTM B117)
NOTE:	In the chemical resistance tests, the substrate used was steel sheet treated with tricationic phosphate. Mechanical resistance tests were performed on degreased plain steel sheet under the curing conditions and coating specific to the product. Values may vary depending on the substrate used.	
SAFETY PRECAUTIONS		
	Non-hazardous coating, no special transport required. Guidelines are available in the product's Safety Data Sheet (SDS)	
NOTE	The information provided herein is based on our testing and experience and is intended to inform you about the product and its possible applications. The information provided in this bulletin is not intended to be complete, and the user assumes the risk of using the product for a purpose other than the specifications recommended in this bulletin without first obtaining our written confirmation of its suitability for the intended purpose. While we strive to ensure the accuracy of the information provided herein, we cannot control the quality or condition of the substrate, nor any other factors that affect the use and application of this paint. Therefore, unless we agree in writing to any condition that deviates from our recommendations, we accept no liability that may arise regarding the performance of this product. The information contained in this bulletin is subject to change without notice, based on our experience and policy of continuous development.	