

LACKPOXI N 1195II

PRODUCT DESCRIPTION

High-build, two-component epoxy polyamine topcoat.

RECOMMENDED USE

Painting of new machines and equipment or maintenance in various industries. Also recommended for painting concrete floors and walls. Product intended for covered environments.

CERTIFICATIONS AND APPROVALS

When supplied to comply with the ROHS Directive (Restriction of Certain Hazardous Substances), this product includes the letter R in its nomenclature description.

Complies with Petrobras Standard N 1195, Type II.

PACKAGING

Component A	3.6L Package containing 2.4L 20L Package containing 13.3L
Component B	1.5L Package containing 1.2L 3.6L Package containing 3.35L

CHARACTERISTICS

Color	RAL, Munsell, or according to the customer's standard.
Gloss	Semi-Gloss
Volume Solids	62 ± 2% (N 1358)
Dry Film Thickness	120 µm - 130 µm
Dry Heat Resistance	Maximum temperature 120 °C. The product maintains its chemical properties up to a temperature of 120 °C, but from 60°C, color and gloss variations in the paint may occur.
Theoretical Coverage	5,17 m ² /l without dilution at a dry film thickness of 120 µm. Loss factors during application are not considered.

DRYING

Drying

	10 °C	25 °C	35 °C
Touch	10 hours	4 hours	2 hours
Pressure	24 hours	16 hours	12 hours
Final	240 hours	168 hours	144 hours

Recoat Drying

	10 °C	25 °C	35 °C
Minimum	24 hours	16 hours	8 hours
Maximum	48 hours	24 hours	16 hours

SURFACE PREPARATION

Standard Surface Preparation

The performance of this product is related to the degree of surface preparation. In case of doubts, for more information, consult WEG's Technical Department.

Remove accumulated dirt using a dry brush, clean dry cloth, compressed air blow, vacuum, or a combination of these. Remove soluble salts by washing with plenty of fresh water, preferably under low pressure (up to 5,000 psi), according to SSPC-SP12/NACE No. 5 standard.

Concrete Surfaces

Before painting, all masonry or concrete must be cured (28 days for cement mortar or concrete) and dry, without cracks, fissures, or voids, and perfectly adhered to the base or other mortar and coating layers.

Respect the recoat interval between product coats for applying the subsequent coat. If the maximum

recoat interval is exceeded, execute a light manual/mechanical sanding to break the gloss of the previous coat, followed by dust and residue cleaning, ensuring better adhesion between paint layers.

Over Primer

The product must be applied over a specific primer. The primer must be clean, dry, and free of contaminants. The topcoat must be applied within the primer recoat interval. Consult the primer technical bulletin for correct application.

APPLICATION PREPARATION

Mixing	Homogenize the content of each component using mechanical or pneumatic stirring (A and B). Ensure no sediment remains at the bottom of the container. Add component B to component A in the indicated mixing ratio under stirring until completely homogenized, respecting the mixing ratio.
Mixing Ratio	By volume: 2 A x 1 B.
Thinner	EPOXY DILUENT 3005
Dilution	Depending on the application method, dilute to a maximum of 15%.
Notes	The amount of Diluent may vary depending on the type of equipment used and environmental conditions during application. Only add Diluent after complete mixing of the other components. Do not dilute with solvents not allowed by local legislation, and do not exceed the indicated dilution percentage. Excessive dilution may affect film formation, appearance, and make it difficult to achieve the specified thickness.
Pot Life	2 h The shelf life of the mixture is reduced as the ambient temperature increases. The pot-life test of the mixture is carried out according to ABNT NBR 15742; however, different volumes of paint prepared at once, combined with varying ambient and paint temperatures, will affect the mixture's shelf life, potentially resulting in outcomes different from those stated in this technical bulletin.
Induction Time	Wait 15 to 20 minutes before application. In very hot locations, we recommend consulting WEG's Technical Department.

APPLICATION METHODS

Conventional Spray Gun	Spray gun: JGA 502/3 Devilbiss or equivalent Fluid nozzle: EX Air cap: 704 Atomization pressure: 60 - 65 psi Tank pressure: 10 - 20 psi.
Airless Spray Gun	Airless: Use minimum pump 60:1 Fluid pressure: 2500 - 3500 psi Hose: 1/4" inner diameter Nozzle: 0.019" - 0.023".
Roller	Use a short-haired, seamless wool or synthetic roller for epoxy paints.
Brush	Recommended only for small area touch-ups or "stripe coat" (screws, nuts, weld beads, sharp corners, and touch-ups). For application with brush and/or roller, it may be necessary to apply two or more coats to achieve a uniform layer and the recommended film thickness.
Cleaning of the equipments:	EPOXY DILUENT 3005

Notes

The data presented serves as a guide and similar equipment may be used.

Before application, ensure that the equipment and respective components are clean and in optimal condition.

After mixing two-component products, if there are application stops and the pot life has been exceeded (paint shows variation in flow), it can no longer be re-thinned for later application.

Reinforce all sharp corners, gaps, and weld beads with a brush to avoid premature failures in these areas.

Clean all equipment immediately after use.

Do not leave material in hoses, guns, or equipment used for spraying. Thoroughly wash all used equipment.

APPLICATION PERFORMANCE

For coatings applied in coastal areas exposed to sea spray, it is recommended to wash with fresh water between coats to remove deposited impurities.

Do not apply the product after the pot life has been exceeded.

For optimal application properties, the paint temperature should be between 21°C and 27°C before mixing and application.

Painting is recommended only if surface temperature is at least 3°C above the dew point.

Epoxy systems may have longer curing times when exposed to low temperatures. For curing at temperatures below 10°C, consult the WEG Technical Department.

Must not be applied under adverse conditions, such as relative humidity (RH) above 85%, as color and appearance changes may occur.

Epoxy-based products are known for their excellent anticorrosive properties and low resistance to sun exposure. When the applied film is exposed to weathering, over time it will lose gloss, a phenomenon known as chalking, which consequently alters its color. It is important to note that, despite this chalking, the film's anticorrosive protection is not compromised.

COMPATIBILITY

The primer repainting interval must be respected for the application of the topcoat. If the maximum interval indicated is exceeded, manual/mechanical sanding with sandpaper to remove gloss is necessary. The primer surface must be dry and free of contaminants.

In situations where the nature of the primer is unknown, it is recommended to test the product's compatibility on a small area; it must be ensured that the original material is well adhered. All non-adhered paint must be removed; areas with corrosion or applications over aged paints must be treated according to technical guidance.

Direct application of the product over zinc-rich primers based on ethyl silicate, alkyd primers, coal tar-based paints, and other single-component primers is not recommended. When topcoat application over any of the above primers is required, we recommend applying a suitable intermediate product.

The product accepts a wide range of topcoats, mainly epoxies and polyurethanes; in highly aggressive environments, we recommend using intermediate coatings before the specific topcoat.

SAFETY PRECAUTIONS

Product developed for industrial use intended for handling by qualified professionals. Carefully read all information contained in the SDS of this product, available at: www.weg.net.

Store in a covered and well-ventilated place. Keep the container tightly closed and away from sources of heat or ignition.

Use only in well-ventilated areas, avoiding the accumulation of flammable vapors. Keep the product away from heat and sources of ignition.

Do not inhale mists/vapors/aerosols generated during handling and/or application. Use protective gloves/protective clothing/eye protection/face protection.

Empty containers and materials with paint residues must be disposed of according to current legislation. Take care of the environment.

NOTE

The information contained in this technical bulletin is based on the experience and knowledge acquired in the field by WEG's technical team.

In the event of using the product without prior consultation with WEG regarding its suitability for the purpose for which the customer intends to use it, the customer acknowledges that the use will be at their own exclusive responsibility, and WEG is not liable for the behavior, safety, suitability, or durability of the product.



Some information mentioned in this bulletin is only an estimate and may vary due to factors beyond the manufacturer's control. Therefore, WEG does not guarantee and assumes no responsibility for performance, efficiency, or any material or personal damages resulting from the incorrect use of the products in question or from the information contained in this Technical Bulletin.

The information contained in this technical bulletin is subject to periodic modifications, without prior notice, due to our policy of continuous improvement and evolution of our products and services, providing quality solutions to meet the needs of our customers.
